

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P522056

Luminaire Tested: **SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P522056
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10706.2 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 106.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P522056

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P522056

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	89	86	88	84	81	79	69	67	65	55	54	53	43	42	41	35
2	88	82	76	72	80	75	70	66	62	58	56	50	48	46	39	37	36	31
3	81	73	66	61	74	67	61	56	55	51	48	45	42	40	35	33	32	27
4	75	65	58	52	68	60	53	49	50	45	42	41	37	35	32	30	28	24
5	69	58	51	45	63	54	47	42	45	40	37	37	34	31	29	27	25	22
6	64	53	45	40	58	49	42	37	41	36	32	34	30	28	27	25	23	20
7	59	48	40	35	54	44	38	33	37	32	29	31	27	25	25	23	21	18
8	55	44	36	32	50	40	34	30	34	29	26	29	25	22	23	21	19	16
9	52	40	33	28	47	37	31	27	32	27	24	26	23	20	22	19	17	15
10	48	37	30	26	44	34	28	24	29	25	21	25	21	19	20	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26864	26864	26864
5°	26528	26434	26588
10°	25065	25291	25878
15°	23138	23675	24737
20°	21011	21802	23244
25°	18846	19873	21656
30°	16851	17953	20008
35°	14736	15800	18059
40°	12403	13387	15634
45°	10236	11119	13053
50°	8546	9315	10874
55°	7255	7994	8980
60°	6200	6931	7167
65°	4936	5829	4630
70°	4378	4548	2827
75°	4053	3689	1729
80°	3735	3395	1493
85°	3377	3112	1217



TEST NUMBER: P522056

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.1	2.5
10°-20°	694.7	6.5
20°-30°	899.8	8.4
30°-40°	881.1	8.2
40°-50°	674.5	6.3
50°-60°	449.4	4.2
60°-70°	245.2	2.3
70°-80°	102.2	1.0
80°-90°	28.9	0.3
90°-100°	474.1	4.4
100°-110°	1349.1	12.6
110°-120°	1292.6	12.1
120°-130°	1023.0	9.6
130°-140°	821.1	7.7
140°-150°	642.8	6.0
150°-160°	470.4	4.4
160°-170°	291.4	2.7
170°-180°	98.9	0.9
0°-30°	1861.5	17.4
0°-40°	2742.7	25.6
0°-60°	3866.5	36.1
0°-90°	4242.9	39.6
90°-120°	3115.8	29.1
90°-150°	5602.8	52.3
90°-180°	6463.0	60.4
0°-180°	10706.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2912	2912	2912	2912	2912	
5°	2864	2836	2854	2861	2871	266
15°	2422	2414	2479	2546	2590	676
25°	1851	1856	1952	2037	2127	851
35°	1308	1314	1403	1497	1603	813
45°	784	800	852	917	1000	612
55°	451	470	497	516	558	409
65°	226	245	267	233	212	235
75°	114	114	104	71	48	121
85°	32	32	29	19	12	35
90°	0	0	0	0	0	4
95°	51	204	918	318	196	59
105°	210	318	1375	2428	2308	222
115°	390	471	1042	2208	2593	384
125°	550	610	995	1651	1974	492
135°	673	729	983	1395	1577	519
145°	793	834	991	1207	1316	496
155°	906	927	1015	1091	1136	419
165°	1001	1005	1027	1049	1064	281
175°	1048	1043	1038	1032	1025	99
180°	1040	1040	1040	1040	1040	

TEST NUMBER: P522056

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2911.7	2911.7	2911.7	2911.7	2911.7
2.5°	2918.9	2892.9	2899.4	2899.3	2891.3
5°	2864.4	2835.7	2854.2	2860.8	2870.8
7.5°	2758.1	2736.4	2770.2	2795.1	2815.4
10°	2675.4	2656.6	2699.6	2736.0	2762.2
12.5°	2579.3	2563.5	2616.8	2665.7	2699.9
15°	2422.4	2413.6	2478.6	2546.0	2589.8
17.5°	2254.5	2250.3	2324.8	2403.5	2459.4
20°	2140.0	2138.8	2220.5	2302.5	2367.4
22.5°	2024.5	2027.3	2113.2	2198.4	2272.4
25°	1851.3	1856.3	1952.2	2037.3	2127.3
27.5°	1691.1	1693.3	1792.5	1882.3	1978.3
30°	1581.7	1587.9	1685.2	1778.2	1878.1
32.5°	1472.3	1479.6	1574.8	1670.9	1772.8
35°	1308.3	1314.5	1402.8	1497.2	1603.4
37.5°	1139.1	1147.6	1226.0	1315.3	1419.7
40°	1029.8	1042.3	1111.5	1195.6	1298.1
42.5°	924.5	940.0	1004.2	1084.0	1176.4
45°	784.5	799.5	852.2	916.7	1000.4
47.5°	663.9	681.1	721.6	777.1	848.6
50°	595.4	611.6	649.0	690.2	757.6
52.5°	535.1	551.3	584.6	616.4	673.8
55°	451.0	469.7	497.0	515.8	558.3
57.5°	382.0	400.0	421.6	430.1	455.9
60°	336.0	356.0	375.6	374.7	388.4
62.5°	294.1	311.1	330.7	317.1	317.9
65°	226.1	244.9	267.0	233.3	212.1
67.5°	182.7	186.7	209.5	162.7	137.5
70°	162.3	162.3	168.6	126.0	104.8
72.5°	142.8	142.8	137.0	102.5	80.2
75°	113.7	113.7	103.5	71.0	48.5
77.5°	87.6	86.6	79.2	53.0	35.3
80°	70.3	70.3	63.9	41.8	28.1
82.5°	54.9	54.9	49.6	32.7	21.0
85°	31.9	31.9	29.4	19.0	11.5
87.5°	11.2	11.2	10.2	6.1	5.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.8	83.9	194.7	56.7	42.7
95°	51.4	204.2	917.9	317.7	195.8
97.5°	94.6	239.2	1413.6	1011.5	693.2
100°	124.6	260.0	1521.2	1540.9	1186.9
102.5°	157.9	282.4	1497.5	1972.3	1663.2
105°	209.7	318.0	1374.8	2428.4	2308.5
107.5°	262.3	359.4	1231.6	2557.0	2663.8
110°	298.7	389.6	1149.3	2507.8	2747.7

TEST NUMBER: P522056

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	333.5	419.8	1093.9	2391.5	2733.4
115°	389.7	470.9	1042.5	2208.5	2593.4
117.5°	439.2	515.4	1012.0	2008.4	2416.1
120°	478.7	542.5	1008.9	1894.1	2284.8
122.5°	510.4	574.2	1001.0	1793.7	2156.6
125°	549.9	609.9	995.0	1651.2	1974.2
127.5°	593.1	649.1	991.9	1566.0	1832.2
130°	615.2	671.3	987.1	1506.7	1738.8
132.5°	638.9	693.5	987.1	1460.4	1673.9
135°	672.6	728.7	983.2	1394.8	1576.6
137.5°	704.2	758.8	982.8	1339.2	1496.3
140°	728.0	784.1	981.2	1293.2	1444.1
142.5°	754.9	801.7	985.9	1256.4	1391.8
145°	793.2	833.9	991.1	1207.2	1315.5
147.5°	826.1	865.5	999.8	1157.4	1251.0
150°	854.6	881.6	1002.9	1140.9	1206.7
152.5°	876.7	905.4	1006.1	1118.7	1179.8
155°	906.0	927.3	1014.8	1091.0	1135.5
157.5°	942.4	955.2	1016.8	1078.4	1110.1
160°	961.4	971.1	1024.7	1068.8	1095.9
162.5°	972.5	983.7	1026.3	1060.8	1081.7
165°	1001.0	1004.8	1026.7	1048.8	1064.3
167.5°	1020.3	1016.9	1035.8	1045.8	1052.0
170°	1026.7	1024.7	1032.6	1034.8	1042.5
172.5°	1040.9	1034.3	1037.4	1031.6	1037.7
175°	1048.4	1042.6	1038.5	1032.4	1024.7
177.5°	1051.6	1042.3	1037.4	1031.1	1032.6
180°	1040.5	1040.5	1040.5	1040.5	1040.5

(END OF REPORT)