

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520906

Luminaire Tested: **SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520906
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1801.1 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 14.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520906
CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P520906

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520906

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	143.4	8.0
100°-110°	346.6	19.2
110°-120°	369.6	20.5
120°-130°	299.4	16.6
130°-140°	231.8	12.9
140°-150°	176.8	9.8
150°-160°	128.0	7.1
160°-170°	78.8	4.4
170°-180°	26.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	859.6	47.7
90°-150°	1567.6	87.0
90°-180°	1801.0	100.0
0°-180°	1801.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	14	72	246	160	112	16
105°	55	96	416	539	532	58
115°	101	130	335	634	708	100
125°	144	166	290	505	593	129
135°	177	198	279	398	458	137
145°	210	225	273	338	365	131
155°	240	251	277	300	310	111
165°	266	270	280	285	289	75
175°	281	280	281	279	278	27
180°	278	278	278	278	278	



TEST NUMBER: P520906

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	38.8	91.4	44.5	30.2
95°	14.1	71.7	245.7	159.8	111.9
97.5°	25.1	79.5	323.6	311.7	267.6
100°	33.6	84.3	366.5	386.8	350.6
102.5°	41.6	88.6	394.7	449.4	427.9
105°	55.4	95.7	416.5	538.9	532.0
107.5°	68.9	104.1	403.7	610.7	627.0
110°	78.4	111.2	383.0	641.7	672.2



TEST NUMBER: P520906

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	87.8	118.3	364.6	649.3	701.5
115°	101.3	129.6	334.6	634.4	707.6
117.5°	114.8	141.4	317.1	600.3	686.0
120°	123.7	148.5	305.8	573.5	663.4
122.5°	133.2	156.1	298.7	546.2	634.7
125°	144.3	166.2	290.5	504.6	592.7
127.5°	155.4	176.0	284.7	469.3	546.7
130°	162.0	182.2	282.8	444.8	520.8
132.5°	168.1	189.2	280.0	427.1	491.6
135°	177.3	198.1	278.7	397.9	457.8
137.5°	186.1	206.9	274.6	378.1	423.3
140°	192.7	211.7	274.6	363.9	405.3
142.5°	199.3	218.3	272.2	351.5	386.5
145°	209.7	225.3	273.4	338.2	364.7
147.5°	219.5	234.6	272.7	322.9	344.8
150°	225.7	238.9	274.6	316.2	333.5
152.5°	232.3	245.0	274.1	309.1	324.5
155°	240.4	250.8	276.9	299.5	310.5
157.5°	250.2	259.0	276.3	295.9	302.4
160°	253.9	261.4	278.7	291.2	295.8
162.5°	260.1	266.6	277.7	289.7	292.5
165°	265.7	269.7	280.4	284.7	288.7
167.5°	272.7	275.3	279.7	284.3	284.5
170°	274.6	276.3	281.6	281.1	284.0
172.5°	277.9	279.1	280.2	281.5	279.7
175°	281.0	279.9	281.0	278.7	278.1
177.5°	280.4	280.4	279.5	278.5	276.2
180°	278.1	278.1	278.1	278.1	278.1

(END OF REPORT)