

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P522060

Luminaire Tested: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P522060
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11469.3 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 106.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P522060

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P522060

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40																			
1	96	92	89	86	88	84	81	79	69	67	65	55	54	53	43	42	41	35																			
2	88	82	76	72	80	75	70	66	62	58	56	50	48	46	39	37	36	31																			
3	81	73	66	61	74	67	61	56	55	51	48	45	42	40	35	33	32	27																			
4	75	65	58	52	68	60	53	49	50	45	42	41	37	35	32	30	28	24																			
5	69	58	51	45	63	54	47	42	45	40	37	37	34	31	29	27	25	22																			
6	64	53	45	40	58	49	42	37	41	36	32	34	30	28	27	25	23	20																			
7	59	48	40	35	54	44	38	33	37	32	29	31	27	25	25	23	21	18																			
8	55	44	36	32	50	40	34	30	34	29	26	29	25	22	23	21	19	16																			
9	52	40	33	28	47	37	31	27	32	27	24	26	23	20	22	19	17	15																			
10	48	37	30	26	44	34	28	24	29	25	21	25	21	19	20	18	16	14																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28778	28778	28778
5°	28420	28318	28483
10°	26850	27094	27722
15°	24787	25363	26499
20°	22509	23356	24901
25°	20189	21290	23199
30°	18051	19233	21435
35°	15785	16926	19347
40°	13287	14342	16748
45°	10965	11911	13983
50°	9155	9980	11649
55°	7771	8564	9621
60°	6643	7425	7678
65°	5290	6246	4960
70°	4688	4874	3027
75°	4342	3953	1854
80°	4001	3634	1599
85°	3620	3335	1302

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13983 cd/sqm

TEST NUMBER: P522060

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.1	2.5
10°-20°	744.2	6.5
20°-30°	963.9	8.4
30°-40°	943.9	8.2
40°-50°	722.5	6.3
50°-60°	481.4	4.2
60°-70°	262.7	2.3
70°-80°	109.5	1.0
80°-90°	31.0	0.3
90°-100°	507.9	4.4
100°-110°	1445.2	12.6
110°-120°	1384.7	12.1
120°-130°	1095.9	9.6
130°-140°	879.7	7.7
140°-150°	688.7	6.0
150°-160°	503.9	4.4
160°-170°	312.1	2.7
170°-180°	105.9	0.9
0°-30°	1994.2	17.4
0°-40°	2938.1	25.6
0°-60°	4142.1	36.1
0°-90°	4545.3	39.6
90°-120°	3337.9	29.1
90°-150°	6002.1	52.3
90°-180°	6924.0	60.4
0°-180°	11469.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3119	3119	3119	3119	3119	
5°	3069	3038	3058	3065	3075	285
15°	2595	2586	2655	2728	2774	725
25°	1983	1989	2091	2182	2279	912
35°	1402	1408	1503	1604	1718	871
45°	840	856	913	982	1072	655
55°	483	503	532	553	598	438
65°	242	262	286	250	227	252
75°	122	122	111	76	52	130
85°	34	34	32	20	12	37
90°	0	0	0	0	0	4
95°	55	219	983	340	210	63
105°	225	341	1473	2602	2473	238
115°	418	504	1117	2366	2778	411
125°	589	653	1066	1769	2115	527
135°	720	781	1053	1494	1689	556
145°	850	893	1062	1293	1409	531
155°	971	993	1087	1169	1216	449
165°	1072	1076	1100	1124	1140	302
175°	1123	1117	1113	1106	1098	106
180°	1115	1115	1115	1115	1115	

TEST NUMBER: P522060

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3119.2	3119.2	3119.2	3119.2	3119.2
2.5°	3126.9	3099.1	3106.1	3105.9	3097.3
5°	3068.6	3037.8	3057.6	3064.7	3075.4
7.5°	2954.7	2931.4	2967.6	2994.4	3016.0
10°	2866.0	2846.0	2892.0	2931.0	2959.1
12.5°	2763.1	2746.2	2803.3	2855.6	2892.3
15°	2595.0	2585.7	2655.3	2727.5	2774.3
17.5°	2415.2	2410.6	2490.5	2574.8	2634.7
20°	2292.6	2291.2	2378.8	2466.6	2536.2
22.5°	2168.8	2171.8	2263.8	2355.1	2434.3
25°	1983.2	1988.6	2091.4	2182.5	2278.9
27.5°	1811.6	1814.0	1920.3	2016.5	2119.3
30°	1694.4	1701.1	1805.3	1904.9	2012.0
32.5°	1577.3	1585.0	1687.0	1790.0	1899.2
35°	1401.5	1408.2	1502.8	1604.0	1717.7
37.5°	1220.3	1229.4	1313.4	1409.0	1520.9
40°	1103.2	1116.5	1190.8	1280.8	1390.6
42.5°	990.4	1007.0	1075.8	1161.3	1260.3
45°	840.4	856.4	912.9	982.0	1071.7
47.5°	711.2	729.6	773.0	832.5	909.1
50°	637.8	655.2	695.3	739.4	811.6
52.5°	573.2	590.6	626.3	660.3	721.8
55°	483.1	503.2	532.4	552.6	598.1
57.5°	409.2	428.5	451.7	460.8	488.3
60°	360.0	381.4	402.4	401.4	416.1
62.5°	315.1	333.3	354.2	339.7	340.5
65°	242.3	262.3	286.1	250.0	227.2
67.5°	195.7	200.0	224.5	174.3	147.3
70°	173.8	173.8	180.7	135.0	112.2
72.5°	153.0	153.0	146.7	109.8	86.0
75°	121.8	121.8	110.9	76.1	52.0
77.5°	93.9	92.8	84.9	56.8	37.8
80°	75.3	75.3	68.4	44.8	30.1
82.5°	58.9	58.9	53.1	35.0	22.4
85°	34.2	34.2	31.5	20.3	12.3
87.5°	12.0	12.0	10.9	6.5	5.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.0	89.9	208.5	60.7	45.8
95°	55.1	218.8	983.3	340.3	209.8
97.5°	101.3	256.3	1514.4	1083.6	742.6
100°	133.5	278.6	1629.6	1650.7	1271.5
102.5°	169.1	302.6	1604.2	2112.9	1781.8
105°	224.6	340.7	1472.8	2601.5	2473.1
107.5°	281.0	385.0	1319.4	2739.3	2853.7
110°	320.0	417.4	1231.2	2686.6	2943.5

TEST NUMBER: P522060

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.3	449.7	1171.9	2561.9	2928.3
115°	417.5	504.5	1116.8	2365.9	2778.2
117.5°	470.5	552.1	1084.2	2151.6	2588.3
120°	512.8	581.2	1080.8	2029.1	2447.6
122.5°	546.7	615.1	1072.3	1921.6	2310.3
125°	589.1	653.4	1065.9	1768.9	2114.9
127.5°	635.3	695.4	1062.5	1677.6	1962.8
130°	659.1	719.1	1057.5	1614.1	1862.7
132.5°	684.5	742.9	1057.5	1564.5	1793.2
135°	720.5	780.6	1053.2	1494.2	1689.0
137.5°	754.4	812.9	1052.8	1434.7	1602.9
140°	779.9	839.9	1051.1	1385.4	1547.0
142.5°	808.7	858.8	1056.2	1346.0	1491.0
145°	849.8	893.3	1061.7	1293.2	1409.2
147.5°	885.0	927.2	1071.0	1239.9	1340.2
150°	915.5	944.5	1074.4	1222.2	1292.7
152.5°	939.2	969.9	1077.8	1198.4	1263.9
155°	970.6	993.4	1087.1	1168.7	1216.4
157.5°	1009.6	1023.2	1089.2	1155.3	1189.3
160°	1029.9	1040.3	1097.7	1145.0	1174.0
162.5°	1041.8	1053.8	1099.4	1136.4	1158.8
165°	1072.3	1076.4	1099.8	1123.5	1140.1
167.5°	1093.1	1089.3	1109.6	1120.3	1127.0
170°	1099.8	1097.8	1106.2	1108.5	1116.8
172.5°	1115.1	1108.1	1111.3	1105.1	1111.7
175°	1123.2	1116.9	1112.6	1106.0	1097.7
177.5°	1126.5	1116.6	1111.3	1104.5	1106.2
180°	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)