

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520958

Luminaire Tested: **SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520958
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5004.7 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 41.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520958
CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P520958

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520958

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	398.5	8.0
100°-110°	963.0	19.2
110°-120°	1027.1	20.5
120°-130°	831.9	16.6
130°-140°	644.1	12.9
140°-150°	491.3	9.8
150°-160°	355.7	7.1
160°-170°	219.1	4.4
170°-180°	74.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2388.6	47.7
90°-150°	4355.8	87.0
90°-180°	5005.0	100.0
0°-180°	5004.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	39	199	683	444	311	44
105°	154	266	1157	1498	1478	163
115°	282	360	930	1763	1966	278
125°	401	462	807	1402	1647	358
135°	493	550	774	1106	1272	380
145°	583	626	760	940	1013	364
155°	668	697	769	832	863	308
165°	738	750	779	791	802	208
175°	781	778	781	774	773	74
180°	773	773	773	773	773	



TEST NUMBER: P520958

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.1	107.9	254.1	123.5	83.8
95°	39.3	199.4	682.7	443.9	311.0
97.5°	69.7	220.8	899.1	866.2	743.6
100°	93.3	234.2	1018.3	1074.9	974.1
102.5°	115.6	246.2	1096.9	1248.7	1188.9
105°	153.9	265.9	1157.4	1497.5	1478.3
107.5°	191.5	289.2	1121.7	1697.1	1742.2
110°	217.7	309.0	1064.1	1783.1	1867.9



TEST NUMBER: P520958

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.9	328.8	1013.0	1804.1	1949.1
115°	281.6	360.0	929.9	1762.9	1966.2
117.5°	318.9	392.9	881.1	1668.1	1906.2
120°	343.8	412.6	849.7	1593.7	1843.4
122.5°	370.0	433.7	830.0	1517.6	1763.5
125°	401.1	461.9	807.1	1402.0	1646.9
127.5°	431.9	489.2	791.0	1304.1	1519.2
130°	450.2	506.2	785.8	1235.9	1447.2
132.5°	467.2	525.8	777.9	1186.7	1366.0
135°	492.8	550.4	774.3	1105.6	1272.0
137.5°	517.0	574.9	762.9	1050.6	1176.1
140°	535.3	588.2	762.9	1011.1	1126.3
142.5°	553.7	606.5	756.3	976.6	1073.9
145°	582.8	626.0	759.6	939.7	1013.4
147.5°	610.0	651.9	757.6	897.2	958.0
150°	627.0	663.8	762.9	878.6	926.6
152.5°	645.3	680.9	761.6	858.8	901.7
155°	667.9	696.7	769.4	832.3	862.8
157.5°	695.1	719.8	767.8	822.2	840.2
160°	705.6	726.4	774.3	809.0	821.8
162.5°	722.6	740.9	771.7	805.0	812.7
165°	738.3	749.5	779.3	791.0	802.2
167.5°	757.6	765.0	777.3	790.1	790.4
170°	762.9	767.7	782.5	781.1	789.1
172.5°	772.1	775.6	778.6	782.1	777.3
175°	780.9	777.7	780.9	774.3	772.7
177.5°	779.3	779.3	776.6	773.9	767.5
180°	772.7	772.7	772.7	772.7	772.7

(END OF REPORT)