

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520959

Luminaire Tested: **SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520959
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5100.5 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 41.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520959
CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P520959

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520959

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	406.1	8.0
100°-110°	981.4	19.2
110°-120°	1046.8	20.5
120°-130°	847.8	16.6
130°-140°	656.4	12.9
140°-150°	500.7	9.8
150°-160°	362.5	7.1
160°-170°	223.3	4.4
170°-180°	75.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2434.3	47.7
90°-150°	4439.2	87.0
90°-180°	5101.0	100.0
0°-180°	5100.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	40	203	696	452	317	45
105°	157	271	1180	1526	1507	166
115°	287	367	948	1797	2004	284
125°	409	471	822	1429	1678	365
135°	502	561	789	1127	1296	388
145°	594	638	774	958	1033	371
155°	681	710	784	848	879	314
165°	752	764	794	806	818	212
175°	796	793	796	789	788	75
180°	788	788	788	788	788	



TEST NUMBER: P520959

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.3	109.9	258.9	125.9	85.4
95°	40.0	203.2	695.7	452.4	317.0
97.5°	71.1	225.1	916.3	882.8	757.8
100°	95.1	238.7	1037.8	1095.5	992.7
102.5°	117.8	250.9	1117.9	1272.6	1211.6
105°	156.8	271.0	1179.6	1526.2	1506.6
107.5°	195.2	294.7	1143.2	1729.6	1775.6
110°	221.9	314.9	1084.5	1817.2	1903.7



TEST NUMBER: P520959

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	248.6	335.1	1032.4	1838.7	1986.5
115°	287.0	366.9	947.7	1796.6	2003.8
117.5°	325.0	400.4	898.0	1700.0	1942.7
120°	350.4	420.5	865.9	1624.2	1878.7
122.5°	377.1	442.0	845.9	1546.7	1797.3
125°	408.8	470.8	822.5	1428.9	1678.5
127.5°	440.1	498.5	806.2	1329.1	1548.3
130°	458.8	515.9	800.9	1259.6	1474.9
132.5°	476.2	535.9	792.8	1209.4	1392.2
135°	502.2	560.9	789.2	1126.7	1296.4
137.5°	526.9	586.0	777.5	1070.7	1198.6
140°	545.6	599.4	777.5	1030.4	1147.9
142.5°	564.3	618.1	770.8	995.3	1094.5
145°	594.0	638.0	774.2	957.7	1032.8
147.5°	621.7	664.4	772.2	914.4	976.4
150°	639.0	676.5	777.5	895.4	944.3
152.5°	657.7	693.9	776.2	875.3	919.0
155°	680.7	710.1	784.2	848.3	879.3
157.5°	708.4	733.5	782.5	838.0	856.2
160°	719.1	740.3	789.2	824.5	837.6
162.5°	736.5	755.0	786.5	820.4	828.2
165°	752.5	763.9	794.2	806.1	817.5
167.5°	772.2	779.7	792.2	805.2	805.5
170°	777.5	782.4	797.5	796.0	804.2
172.5°	786.8	790.4	793.5	797.1	792.2
175°	795.8	792.6	795.8	789.1	787.5
177.5°	794.2	794.2	791.5	788.7	782.2
180°	787.5	787.5	787.5	787.5	787.5

(END OF REPORT)