

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520910

Luminaire Tested: **SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520910
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1881.0 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 14.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520910
CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P520910

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520910

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	149.8	8.0
100°-110°	361.9	19.2
110°-120°	386.0	20.5
120°-130°	312.7	16.6
130°-140°	242.1	12.9
140°-150°	184.7	9.8
150°-160°	133.7	7.1
160°-170°	82.3	4.4
170°-180°	27.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	897.7	47.7
90°-150°	1637.1	87.0
90°-180°	1881.0	100.0
0°-180°	1881.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	15	75	257	167	117	17
105°	58	100	435	563	556	61
115°	106	135	350	663	739	105
125°	151	174	303	527	619	135
135°	185	207	291	416	478	143
145°	219	235	286	353	381	137
155°	251	262	289	313	324	116
165°	278	282	293	297	302	78
175°	294	292	294	291	290	28
180°	290	290	290	290	290	



TEST NUMBER: P520910

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.9	40.5	95.5	46.4	31.5
95°	14.8	74.9	256.6	166.8	116.9
97.5°	26.2	83.0	337.9	325.6	279.5
100°	35.1	88.0	382.7	404.0	366.1
102.5°	43.4	92.5	412.2	469.3	446.8
105°	57.8	100.0	435.0	562.8	555.6
107.5°	72.0	108.7	421.6	637.8	654.8
110°	81.8	116.1	399.9	670.2	702.1



TEST NUMBER: P520910

CATALOG NUMBER: SQ4-025U-0D-93050-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	91.7	123.6	380.7	678.1	732.6
115°	105.8	135.3	349.5	662.6	739.0
117.5°	119.9	147.7	331.2	626.9	716.4
120°	129.2	155.1	319.3	599.0	692.8
122.5°	139.1	163.0	312.0	570.4	662.8
125°	150.7	173.6	303.3	526.9	619.0
127.5°	162.3	183.9	297.3	490.1	571.0
130°	169.2	190.3	295.3	464.5	543.9
132.5°	175.6	197.6	292.4	446.0	513.4
135°	185.2	206.9	291.0	415.5	478.1
137.5°	194.3	216.1	286.7	394.9	442.0
140°	201.2	221.1	286.7	380.0	423.3
142.5°	208.1	227.9	284.3	367.1	403.6
145°	219.0	235.3	285.5	353.2	380.9
147.5°	229.3	245.0	284.8	337.2	360.1
150°	235.7	249.5	286.7	330.2	348.3
152.5°	242.5	255.9	286.2	322.8	338.9
155°	251.0	261.9	289.2	312.8	324.3
157.5°	261.3	270.5	288.6	309.0	315.8
160°	265.2	273.0	291.0	304.1	308.9
162.5°	271.6	278.4	290.0	302.5	305.4
165°	277.5	281.7	292.9	297.3	301.5
167.5°	284.8	287.5	292.1	296.9	297.1
170°	286.7	288.5	294.1	293.6	296.6
172.5°	290.2	291.5	292.6	293.9	292.1
175°	293.5	292.3	293.5	291.0	290.4
177.5°	292.9	292.9	291.9	290.9	288.5
180°	290.4	290.4	290.4	290.4	290.4

(END OF REPORT)