

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520961

Luminaire Tested: **SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520961
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5191.2 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 41.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520961
CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P520961

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520961

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	413.3	8.0
100°-110°	998.9	19.2
110°-120°	1065.4	20.5
120°-130°	862.9	16.6
130°-140°	668.1	12.9
140°-150°	509.6	9.8
150°-160°	368.9	7.1
160°-170°	227.2	4.4
170°-180°	76.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2477.6	47.7
90°-150°	4518.2	87.0
90°-180°	5191.0	100.0
0°-180°	5191.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	41	207	708	460	323	46
105°	160	276	1201	1553	1533	169
115°	292	373	964	1829	2039	289
125°	416	479	837	1454	1708	371
135°	511	571	803	1147	1319	395
145°	604	649	788	975	1051	378
155°	693	723	798	863	895	320
165°	766	778	808	820	832	216
175°	810	807	810	803	802	77
180°	802	802	802	802	802	



TEST NUMBER: P520961

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.6	111.9	263.5	128.1	86.9
95°	40.8	206.8	708.1	460.5	322.6
97.5°	72.3	229.1	932.6	898.5	771.3
100°	96.8	242.9	1056.2	1115.0	1010.4
102.5°	119.9	255.4	1137.7	1295.3	1233.2
105°	159.6	275.8	1200.6	1553.3	1533.4
107.5°	198.7	300.0	1163.5	1760.3	1807.1
110°	225.8	320.5	1103.8	1849.6	1937.6

TEST NUMBER: P520961

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	253.0	341.0	1050.8	1871.3	2021.8
115°	292.1	373.4	964.5	1828.6	2039.4
117.5°	330.8	407.5	913.9	1730.2	1977.3
120°	356.6	428.0	881.3	1653.1	1912.1
122.5°	383.8	449.9	860.9	1574.2	1829.2
125°	416.0	479.1	837.2	1454.3	1708.3
127.5°	448.0	507.4	820.5	1352.7	1575.9
130°	467.0	525.1	815.1	1282.0	1501.1
132.5°	484.6	545.4	806.9	1230.9	1416.9
135°	511.1	570.9	803.2	1146.8	1319.4
137.5°	536.3	596.4	791.3	1089.8	1219.9
140°	555.3	610.1	791.3	1048.8	1168.3
142.5°	574.3	629.1	784.5	1013.0	1114.0
145°	604.5	649.4	787.9	974.8	1051.1
147.5°	632.7	676.2	785.9	930.6	993.7
150°	650.4	688.6	791.3	911.3	961.1
152.5°	669.4	706.3	790.0	890.8	935.3
155°	692.8	722.7	798.1	863.4	894.9
157.5°	721.0	746.6	796.4	852.9	871.5
160°	731.9	753.5	803.2	839.2	852.5
162.5°	749.5	768.5	800.5	835.0	842.9
165°	765.9	777.5	808.3	820.5	832.1
167.5°	785.9	793.5	806.3	819.5	819.9
170°	791.3	796.3	811.7	810.2	818.5
172.5°	800.8	804.5	807.6	811.2	806.3
175°	810.0	806.7	810.0	803.2	801.5
177.5°	808.3	808.3	805.6	802.7	796.1
180°	801.5	801.5	801.5	801.5	801.5

(END OF REPORT)