

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520933

Luminaire Tested: **SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520933
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3057.0 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520933
CATALOG NUMBER: SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P520933

CATALOG NUMBER: SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520933

CATALOG NUMBER: SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	243.4	8.0
100°-110°	588.2	19.2
110°-120°	627.4	20.5
120°-130°	508.1	16.6
130°-140°	393.4	12.9
140°-150°	300.1	9.8
150°-160°	217.3	7.1
160°-170°	133.8	4.4
170°-180°	45.3	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1459.0	47.7
90°-150°	2660.7	87.0
90°-180°	3057.0	100.0
0°-180°	3057.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	24	122	417	271	190	27
105°	94	162	707	915	903	99
115°	172	220	568	1077	1201	170
125°	245	282	493	856	1006	219
135°	301	336	473	675	777	232
145°	356	382	464	574	619	223
155°	408	426	470	508	527	188
165°	451	458	476	483	490	127
175°	477	475	477	473	472	45
180°	472	472	472	472	472	



TEST NUMBER: P520933

CATALOG NUMBER: SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	65.9	155.2	75.4	51.2
95°	24.0	121.8	417.0	271.2	190.0
97.5°	42.6	134.9	549.2	529.1	454.2
100°	57.0	143.0	622.0	656.6	595.0
102.5°	70.6	150.4	670.0	762.8	726.2
105°	94.0	162.4	707.0	914.7	903.0
107.5°	117.0	176.6	685.2	1036.6	1064.2
110°	133.0	188.7	650.0	1089.2	1141.0



TEST NUMBER: P520933

CATALOG NUMBER: SQ4-075U-0D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	149.0	200.8	618.8	1102.0	1190.6
115°	172.0	219.9	568.0	1076.8	1201.0
117.5°	194.8	240.0	538.2	1018.9	1164.4
120°	210.0	252.0	519.0	973.5	1126.0
122.5°	226.0	264.9	507.0	927.0	1077.2
125°	245.0	282.2	493.0	856.4	1006.0
127.5°	263.8	298.8	483.2	796.6	928.0
130°	275.0	309.2	480.0	754.9	884.0
132.5°	285.4	321.2	475.2	724.9	834.4
135°	301.0	336.2	473.0	675.3	777.0
137.5°	315.8	351.2	466.0	641.7	718.4
140°	327.0	359.3	466.0	617.6	688.0
142.5°	338.2	370.5	462.0	596.6	656.0
145°	356.0	382.4	464.0	574.0	619.0
147.5°	372.6	398.2	462.8	548.0	585.2
150°	383.0	405.5	466.0	536.7	566.0
152.5°	394.2	415.9	465.2	524.6	550.8
155°	408.0	425.6	470.0	508.4	527.0
157.5°	424.6	439.7	469.0	502.2	513.2
160°	431.0	443.7	473.0	494.2	502.0
162.5°	441.4	452.5	471.4	491.7	496.4
165°	451.0	457.8	476.0	483.2	490.0
167.5°	462.8	467.3	474.8	482.6	482.8
170°	466.0	468.9	478.0	477.1	482.0
172.5°	471.6	473.8	475.6	477.7	474.8
175°	477.0	475.0	477.0	473.0	472.0
177.5°	476.0	476.0	474.4	472.7	468.8
180°	472.0	472.0	472.0	472.0	472.0

(END OF REPORT)