

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520960

Luminaire Tested: **SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P520960
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5154.8 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 41.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P520960
CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P520960

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P520960

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	410.4	8.0
100°-110°	991.9	19.2
110°-120°	1057.9	20.5
120°-130°	856.8	16.6
130°-140°	663.4	12.9
140°-150°	506.1	9.8
150°-160°	366.3	7.1
160°-170°	225.6	4.4
170°-180°	76.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2460.2	47.7
90°-150°	4486.5	87.0
90°-180°	5155.0	100.0
0°-180°	5154.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	40	205	703	457	320	45
105°	158	274	1192	1542	1523	167
115°	290	371	958	1816	2025	287
125°	413	476	831	1444	1696	369
135°	508	567	798	1139	1310	392
145°	600	645	782	968	1044	375
155°	688	718	792	857	889	318
165°	760	772	803	815	826	215
175°	804	801	804	798	796	76
180°	796	796	796	796	796	



TEST NUMBER: P520960

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.5	111.1	261.7	127.2	86.3
95°	40.5	205.3	703.1	457.2	320.4
97.5°	71.8	227.5	926.1	892.2	765.9
100°	96.1	241.2	1048.8	1107.2	1003.3
102.5°	119.0	253.6	1129.8	1286.2	1224.5
105°	158.5	273.9	1192.1	1542.4	1522.6
107.5°	197.3	297.9	1155.4	1748.0	1794.5
110°	224.3	318.2	1096.0	1836.6	1924.0



TEST NUMBER: P520960

CATALOG NUMBER: SQ4-125U-0D-93050-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	251.2	338.6	1043.4	1858.2	2007.6
115°	290.0	370.8	957.8	1815.7	2025.1
117.5°	328.5	404.6	907.5	1718.1	1963.4
120°	354.1	425.0	875.1	1641.5	1898.7
122.5°	381.1	446.7	854.9	1563.1	1816.4
125°	413.1	475.8	831.3	1444.1	1696.3
127.5°	444.8	503.8	814.8	1343.2	1564.8
130°	463.7	521.4	809.4	1273.0	1490.6
132.5°	481.2	541.6	801.3	1222.3	1407.0
135°	507.5	566.9	797.6	1138.7	1310.2
137.5°	532.5	592.2	785.8	1082.1	1211.4
140°	551.4	605.8	785.8	1041.4	1160.1
142.5°	570.3	624.7	779.0	1005.9	1106.1
145°	600.3	644.8	782.4	967.9	1043.8
147.5°	628.3	671.5	780.4	924.1	986.8
150°	645.8	683.7	785.8	904.9	954.4
152.5°	664.7	701.3	784.4	884.6	928.8
155°	688.0	717.6	792.5	857.3	888.6
157.5°	716.0	741.4	790.8	846.9	865.4
160°	726.8	748.2	797.6	833.3	846.5
162.5°	744.3	763.1	794.9	829.1	837.0
165°	760.5	772.0	802.6	814.7	826.2
167.5°	780.4	788.0	800.6	813.8	814.1
170°	785.8	790.7	806.0	804.5	812.7
172.5°	795.2	798.8	802.0	805.6	800.6
175°	804.3	801.0	804.3	797.5	795.9
177.5°	802.6	802.6	799.9	797.1	790.5
180°	795.9	795.9	795.9	795.9	795.9

(END OF REPORT)