

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521064

Luminaire Tested: **SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521064
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4577.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521064
CATALOG NUMBER: SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521064

CATALOG NUMBER: SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	101	97	94	91	94	91	88	85	78	76	74	67	65	64	56	55	55	50
2	93	87	82	78	87	81	77	73	71	68	65	61	59	57	52	50	49	45
3	87	78	72	67	80	74	68	64	64	60	57	56	53	51	48	46	44	41
4	80	71	64	59	75	67	61	56	59	54	51	51	48	45	44	42	40	37
5	75	64	57	52	69	61	54	50	54	49	45	47	43	41	41	38	36	33
6	69	59	51	46	65	55	49	44	49	44	41	43	40	37	38	35	33	30
7	65	54	47	42	60	51	44	40	45	40	37	40	36	33	35	32	30	28
8	61	49	42	38	57	47	41	36	42	37	33	37	33	31	33	30	28	26
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24
10	53	42	36	31	50	40	34	30	36	31	28	33	29	26	29	26	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19286	19286	19286
5°	18976	18929	19069
10°	17755	17992	18494
15°	16141	16653	17581
20°	14328	15073	16394
25°	12478	13466	15062
30°	10688	11863	13802
35°	8862	10069	12279
40°	6808	8051	10463
45°	4922	6096	8418
50°	3353	4543	6677
55°	2180	3286	5189
60°	1251	2314	3751
65°	332	1412	1899
70°	165	437	545
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P521064

CATALOG NUMBER: SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	4.2
10°-20°	487.9	10.7
20°-30°	610.8	13.3
30°-40°	564.1	12.3
40°-50°	379.1	8.3
50°-60°	195.8	4.3
60°-70°	61.3	1.3
70°-80°	3.9	0.1
80°-90°	0.1	0.0
90°-100°	165.9	3.6
100°-110°	400.9	8.8
110°-120°	427.6	9.3
120°-130°	346.3	7.6
130°-140°	268.1	5.9
140°-150°	204.5	4.5
150°-160°	148.0	3.2
160°-170°	91.2	2.0
170°-180°	30.9	0.7
0°-30°	1289.4	28.2
0°-40°	1853.5	40.5
0°-60°	2428.4	53.1
0°-90°	2493.6	54.5
90°-120°	994.3	21.7
90°-150°	1813.2	39.6
90°-180°	2083.0	45.5
0°-180°	4577.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2049	2028	2044	2051	2059	190
15°	1690	1684	1744	1802	1841	471
25°	1226	1236	1323	1413	1480	562
35°	787	807	894	999	1090	487
45°	377	400	467	558	645	296
55°	136	158	204	262	323	126
65°	15	29	65	78	87	26
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	16	83	284	185	130	18
105°	64	111	482	623	615	68
115°	117	150	387	734	818	116
125°	167	192	336	584	686	149
135°	205	229	322	460	530	158
145°	243	261	316	391	422	152
155°	278	290	320	346	359	128
165°	307	312	324	329	334	87
175°	325	324	325	322	322	31
180°	322	322	322	322	322	



TEST NUMBER: P521064

CATALOG NUMBER: SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2090.4	2090.4	2090.4	2090.4	2090.4
2.5°	2095.2	2075.5	2080.7	2080.6	2075.0
5°	2048.9	2028.2	2043.9	2051.1	2059.0
7.5°	1962.4	1946.1	1976.3	1998.9	2015.3
10°	1895.2	1881.4	1920.5	1951.3	1974.1
12.5°	1817.5	1806.9	1854.1	1896.5	1925.5
15°	1689.9	1684.0	1743.5	1802.0	1840.6
17.5°	1553.2	1553.0	1620.9	1693.6	1740.1
20°	1459.3	1462.3	1535.2	1615.3	1669.7
22.5°	1365.5	1372.4	1450.2	1533.8	1596.1
25°	1225.7	1235.6	1322.8	1413.3	1479.6
27.5°	1091.4	1105.8	1197.6	1291.7	1372.4
30°	1003.2	1020.0	1113.5	1212.4	1295.5
32.5°	916.7	936.6	1027.7	1132.4	1217.0
35°	786.8	806.6	894.0	999.2	1090.2
37.5°	652.7	672.1	757.5	861.0	959.3
40°	565.3	587.1	668.5	768.8	868.7
42.5°	486.0	507.8	584.3	683.0	777.3
45°	377.2	400.0	467.2	558.2	645.2
47.5°	287.0	311.7	370.7	453.1	532.4
50°	233.6	258.3	316.5	389.1	465.2
52.5°	190.7	214.7	267.2	335.5	405.3
55°	135.5	158.3	204.3	262.3	322.6
57.5°	93.6	113.2	154.5	202.9	250.2
60°	67.8	86.5	125.4	164.7	203.3
62.5°	45.1	62.3	100.3	130.4	156.3
65°	15.2	29.0	64.7	78.1	87.0
67.5°	7.7	9.3	34.0	35.9	38.8
70°	6.1	6.1	16.2	17.3	20.2
72.5°	4.4	4.4	6.5	8.3	8.9
75°	2.0	2.0	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	44.9	105.8	51.4	34.9
95°	16.4	83.0	284.2	184.8	129.5
97.5°	29.0	91.9	374.3	360.6	309.5
100°	38.8	97.5	423.9	447.5	405.5
102.5°	48.1	102.5	456.6	519.8	494.9
105°	64.1	110.7	481.8	623.4	615.4
107.5°	79.7	120.4	466.9	706.4	725.2
110°	90.6	128.6	443.0	742.3	777.6

TEST NUMBER: P521064

CATALOG NUMBER: SQ4-BB-050U-100D-93050-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.5	136.9	421.7	751.0	811.4
115°	117.2	149.9	387.1	733.8	818.5
117.5°	132.8	163.5	366.8	694.4	793.5
120°	143.1	171.8	353.7	663.4	767.3
122.5°	154.0	180.5	345.5	631.7	734.1
125°	167.0	192.3	336.0	583.6	685.6
127.5°	179.8	203.6	329.3	542.9	632.4
130°	187.4	210.7	327.1	514.5	602.4
132.5°	194.5	218.9	323.8	494.0	568.6
135°	205.1	229.1	322.3	460.2	529.5
137.5°	215.2	239.3	317.6	437.3	489.6
140°	222.8	244.8	317.6	420.9	468.9
142.5°	230.5	252.5	314.8	406.5	447.0
145°	242.6	260.6	316.2	391.2	421.8
147.5°	253.9	271.4	315.4	373.5	398.8
150°	261.0	276.3	317.6	365.7	385.7
152.5°	268.6	283.4	317.0	357.5	375.4
155°	278.0	290.0	320.3	346.5	359.1
157.5°	289.4	299.6	319.6	342.3	349.7
160°	293.7	302.4	322.3	336.8	342.1
162.5°	300.8	308.4	321.2	335.1	338.3
165°	307.3	312.0	324.4	329.3	333.9
167.5°	315.4	318.5	323.6	328.9	329.0
170°	317.6	319.6	325.7	325.1	328.5
172.5°	321.4	322.9	324.1	325.6	323.6
175°	325.1	323.7	325.1	322.3	321.7
177.5°	324.4	324.4	323.3	322.1	319.5
180°	321.7	321.7	321.7	321.7	321.7

(END OF REPORT)