

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521167

Luminaire Tested: **SQ4-BB-0U-100D-93050-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521167
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-0U-100D-93050-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2467.4 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521167
CATALOG NUMBER: SQ4-BB-0U-100D-93050-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521167

CATALOG NUMBER: SQ4-BB-0U-100D-93050-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82				82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74				74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67				67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	53	62	57	53	61	56	53	51				51
8	72	61	54	50	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44				44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19083	19083	19083
5°	18776	18729	18869
10°	17568	17803	18300
15°	15971	16478	17395
20°	14178	14914	16221
25°	12346	13325	14904
30°	10576	11737	13657
35°	8768	9963	12150
40°	6737	7966	10353
45°	4869	6032	8330
50°	3319	4495	6607
55°	2157	3251	5134
60°	1236	2290	3711
65°	327	1397	1880
70°	162	432	540
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P521167

CATALOG NUMBER: SQ4-BB-0U-100D-93050-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.8	7.7
10°-20°	482.7	19.6
20°-30°	604.3	24.5
30°-40°	558.2	22.6
40°-50°	375.1	15.2
50°-60°	193.7	7.9
60°-70°	60.7	2.5
70°-80°	3.8	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.8	51.7
0°-40°	1834.0	74.3
0°-60°	2402.8	97.4
0°-90°	2467.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2467.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2068	2068	2068	2068	2068	
5°	2027	2007	2022	2030	2037	188
15°	1672	1666	1725	1783	1821	466
25°	1213	1223	1309	1398	1464	556
35°	778	798	885	989	1079	482
45°	373	396	462	552	638	293
55°	134	157	202	260	319	125
65°	15	29	64	77	86	25
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P521167

CATALOG NUMBER: SQ4-BB-0U-100D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.4	2068.4	2068.4	2068.4	2068.4
2.5°	2073.2	2053.6	2058.8	2058.6	2053.2
5°	2027.3	2006.8	2022.3	2029.5	2037.4
7.5°	1941.7	1925.6	1955.5	1977.9	1994.1
10°	1875.2	1861.5	1900.3	1930.8	1953.3
12.5°	1798.4	1787.8	1834.6	1876.5	1905.3
15°	1672.1	1666.2	1725.1	1783.1	1821.2
17.5°	1536.8	1536.6	1603.9	1675.8	1721.7
20°	1444.0	1446.9	1519.0	1598.3	1652.1
22.5°	1351.1	1357.9	1435.0	1517.6	1579.3
25°	1212.8	1222.6	1308.9	1398.4	1464.0
27.5°	1079.9	1094.2	1185.0	1278.1	1357.9
30°	992.7	1009.3	1101.7	1199.7	1281.9
32.5°	907.0	926.8	1016.9	1120.4	1204.2
35°	778.5	798.1	884.6	988.7	1078.7
37.5°	645.8	665.0	749.5	852.0	949.2
40°	559.4	580.9	661.4	760.8	859.6
42.5°	480.9	502.4	578.2	675.8	769.1
45°	373.2	395.8	462.3	552.3	638.4
47.5°	284.0	308.4	366.8	448.3	526.8
50°	231.2	255.6	313.2	385.0	460.3
52.5°	188.7	212.4	264.4	332.0	401.1
55°	134.1	156.6	202.1	259.5	319.2
57.5°	92.7	112.0	152.9	200.8	247.6
60°	67.0	85.6	124.1	163.0	201.1
62.5°	44.6	61.7	99.3	129.1	154.7
65°	15.0	28.7	64.0	77.3	86.1
67.5°	7.6	9.2	33.6	35.5	38.4
70°	6.0	6.0	16.0	17.1	20.0
72.5°	4.4	4.4	6.4	8.2	8.8
75°	2.0	2.0	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)