

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521325

Luminaire Tested: **SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521325
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8756.7 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 93.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521325
CATALOG NUMBER: SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521325

CATALOG NUMBER: SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29				
1	94	90	87	84	84	81	78	76	64	62	61	48	47	46	34	33	33	26				
2	86	80	75	70	77	72	68	64	57	54	52	44	42	40	31	30	29	24				
3	80	71	65	60	71	64	59	55	51	48	45	40	37	35	29	27	26	21				
4	73	64	57	51	66	58	52	47	46	42	39	36	33	31	26	25	23	19				
5	68	57	50	45	61	52	46	41	42	38	34	33	30	28	24	22	21	18				
6	62	52	44	39	56	47	41	36	38	34	30	30	27	25	22	21	19	16				
7	58	47	40	35	52	43	37	32	35	30	27	28	25	22	21	19	17	15				
8	54	43	36	31	49	39	33	29	32	28	24	25	22	20	19	17	16	14				
9	50	39	32	28	45	36	30	26	30	25	22	24	21	18	18	16	15	13				
10	47	36	29	25	42	33	27	23	27	23	20	22	19	17	17	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19423	19423	19423
5°	19110	19063	19205
10°	17881	18120	18625
15°	16255	16771	17705
20°	14429	15179	16510
25°	12566	13561	15168
30°	10763	11946	13899
35°	8925	10140	12366
40°	6857	8108	10537
45°	4957	6139	8478
50°	3377	4576	6725
55°	2196	3309	5226
60°	1258	2331	3777
65°	334	1423	1912
70°	165	440	550
75°	71	36	0
80°	53	0	0
85°	0	0	0



TEST NUMBER: P521325

CATALOG NUMBER: SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.1	2.2
10°-20°	491.3	5.6
20°-30°	615.1	7.0
30°-40°	568.1	6.5
40°-50°	381.8	4.4
50°-60°	197.2	2.3
60°-70°	61.8	0.7
70°-80°	3.9	0.0
80°-90°	0.1	0.0
90°-100°	497.2	5.7
100°-110°	1201.7	13.7
110°-120°	1281.7	14.6
120°-130°	1038.1	11.9
130°-140°	803.7	9.2
140°-150°	613.1	7.0
150°-160°	443.8	5.1
160°-170°	273.4	3.1
170°-180°	92.6	1.1
0°-30°	1298.5	14.8
0°-40°	1866.6	21.3
0°-60°	2445.5	27.9
0°-90°	2511.3	28.7
90°-120°	2980.7	34.0
90°-150°	5435.7	62.1
90°-180°	6245.0	71.3
0°-180°	8756.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2105	2105	2105	2105	2105	
5°	2063	2042	2058	2066	2074	191
15°	1702	1696	1756	1815	1854	474
25°	1234	1244	1332	1423	1490	566
35°	792	812	900	1006	1098	491
45°	380	403	470	562	650	298
55°	136	159	206	264	325	127
65°	15	29	65	79	88	26
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	49	249	852	554	388	55
105°	192	332	1444	1869	1845	203
115°	351	449	1160	2200	2454	347
125°	500	576	1007	1750	2055	447
135°	615	687	966	1380	1587	475
145°	727	781	948	1173	1265	455
155°	834	870	960	1039	1077	385
165°	921	935	972	987	1001	260
175°	974	970	974	966	964	92
180°	964	964	964	964	964	

TEST NUMBER: P521325

CATALOG NUMBER: SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2105.2	2105.2	2105.2	2105.2	2105.2
2.5°	2110.0	2090.1	2095.4	2095.3	2089.7
5°	2063.4	2042.5	2058.3	2065.6	2073.6
7.5°	1976.2	1959.9	1990.3	2013.1	2029.6
10°	1908.6	1894.7	1934.1	1965.1	1988.0
12.5°	1830.4	1819.6	1867.2	1909.9	1939.1
15°	1701.8	1695.9	1755.8	1814.8	1853.6
17.5°	1564.2	1564.0	1632.4	1705.6	1752.4
20°	1469.6	1472.6	1546.0	1626.7	1681.5
22.5°	1375.1	1382.1	1460.5	1544.6	1607.3
25°	1234.4	1244.3	1332.1	1423.3	1490.0
27.5°	1099.1	1113.7	1206.1	1300.8	1382.1
30°	1010.3	1027.2	1121.3	1221.0	1304.6
32.5°	923.1	943.2	1035.0	1140.4	1225.6
35°	792.4	812.3	900.3	1006.3	1097.9
37.5°	657.3	676.8	762.8	867.1	966.1
40°	569.3	591.2	673.2	774.3	874.9
42.5°	489.5	511.4	588.5	687.8	782.8
45°	379.9	402.8	470.5	562.1	649.8
47.5°	289.0	313.9	373.4	456.3	536.1
50°	235.3	260.2	318.8	391.8	468.5
52.5°	192.1	216.2	269.1	337.9	408.2
55°	136.5	159.4	205.7	264.1	324.9
57.5°	94.3	114.0	155.6	204.4	252.0
60°	68.2	87.2	126.3	165.9	204.7
62.5°	45.4	62.8	101.0	131.4	157.5
65°	15.3	29.2	65.2	78.6	87.6
67.5°	7.7	9.3	34.2	36.1	39.1
70°	6.1	6.1	16.3	17.4	20.4
72.5°	4.5	4.5	6.5	8.4	9.0
75°	2.0	2.0	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.3	134.6	317.1	154.1	104.6
95°	49.0	248.8	851.9	554.0	388.2
97.5°	87.0	275.6	1122.0	1080.9	927.9
100°	116.4	292.2	1270.7	1341.4	1215.6
102.5°	144.2	307.2	1368.8	1558.3	1483.6
105°	192.0	331.9	1444.4	1868.8	1844.8
107.5°	239.0	360.9	1399.8	2117.8	2174.1
110°	271.7	385.6	1327.9	2225.2	2331.0



TEST NUMBER: P521325

CATALOG NUMBER: SQ4-BB-150U-100D-93050-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	304.4	410.3	1264.2	2251.4	2432.4
115°	351.4	449.3	1160.4	2199.9	2453.6
117.5°	398.0	490.3	1099.5	2081.6	2378.8
120°	429.0	514.9	1060.3	1988.8	2300.4
122.5°	461.7	541.2	1035.8	1893.9	2200.7
125°	500.5	576.4	1007.2	1749.6	2055.2
127.5°	538.9	610.4	987.2	1627.4	1895.9
130°	561.8	631.7	980.6	1542.3	1806.0
132.5°	583.1	656.2	970.8	1480.9	1704.7
135°	614.9	686.8	966.3	1379.6	1587.4
137.5°	645.2	717.5	952.0	1311.1	1467.7
140°	668.1	734.0	952.0	1261.7	1405.6
142.5°	690.9	756.9	943.9	1218.7	1340.2
145°	727.3	781.2	947.9	1172.7	1264.6
147.5°	761.2	813.5	945.5	1119.6	1195.5
150°	782.5	828.4	952.0	1096.4	1156.3
152.5°	805.3	849.7	950.4	1071.7	1125.3
155°	833.5	869.5	960.2	1038.7	1076.6
157.5°	867.4	898.2	958.2	1026.1	1048.5
160°	880.5	906.5	966.3	1009.6	1025.6
162.5°	901.8	924.5	963.1	1004.5	1014.1
165°	921.4	935.4	972.5	987.1	1001.1
167.5°	945.5	954.7	970.0	985.9	986.3
170°	952.0	958.0	976.5	974.7	984.7
172.5°	963.5	967.9	971.6	976.0	970.0
175°	974.5	970.5	974.5	966.3	964.3
177.5°	972.5	972.5	969.2	965.7	957.7
180°	964.3	964.3	964.3	964.3	964.3

(END OF REPORT)