

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936256

Luminaire Tested: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936256
REPORT IS A COMBINATION OF REPORTS P933429 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7107.5 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936256
CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P936256

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1776	1776	1776
5°	1736	2053	2388
10°	1575	2994	3958
15°	1339	3913	4780
20°	1091	4535	4871
25°	910	4747	4772
30°	768	4778	4763
35°	679	4700	4886
40°	592	4599	5013
45°	537	4524	5033
50°	493	4458	4950
55°	472	4360	4730
60°	484	4171	4384
65°	505	3882	3908
70°	538	3388	3301
75°	599	2764	2576
80°	660	1920	1736
85°	596	1020	888

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5033 cd/sqm



TEST NUMBER: P936256

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.3	1.0
10°-20°	329.2	4.6
20°-30°	575.9	8.1
30°-40°	741.3	10.4
40°-50°	828.0	11.6
50°-60°	793.1	11.2
60°-70°	628.5	8.8
70°-80°	369.6	5.2
80°-90°	104.2	1.5
90°-100°	200.3	2.8
100°-110°	526.5	7.4
110°-120°	546.0	7.7
120°-130°	437.9	6.2
130°-140°	343.6	4.8
140°-150°	263.7	3.7
150°-160°	189.9	2.7
160°-170°	116.2	1.6
170°-180°	39.3	0.6
0°-30°	979.4	13.8
0°-40°	1720.7	24.2
0°-60°	3341.8	47.0
0°-90°	4444.1	62.5
90°-120°	1272.7	17.9
90°-150°	2318.0	32.6
90°-180°	2663.0	37.5
0°-180°	7107.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	560	600	676	764	792	52
15°	419	774	1304	1581	1630	117
25°	268	877	1553	1621	1623	123
35°	181	838	1462	1546	1606	113
45°	124	668	1293	1481	1547	96
55°	89	425	1097	1274	1309	81
65°	70	225	814	916	929	70
75°	52	138	447	491	493	54
85°	18	42	111	122	124	20
90°	3	8	21	10	10	4
95°	26	104	345	178	121	29
105°	95	144	582	884	824	101
115°	168	205	466	930	1062	166
125°	234	263	424	717	845	208
135°	279	307	411	578	656	216
145°	324	345	406	494	532	203
155°	366	376	406	445	458	168
165°	395	400	406	422	427	112
175°	411	411	408	414	414	39
180°	411	411	411	411	411	



TEST NUMBER: P936256
 CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3
2.5°	574.3	574.3	578.0	579.8	583.5	585.3	589.1	592.7	603.8	605.7	609.3
5°	559.5	566.9	590.9	600.1	626.0	661.0	675.8	699.8	749.7	764.4	773.7
7.5°	537.3	553.9	613.0	627.8	692.5	784.8	823.5	875.3	954.7	993.4	1024.8
10°	502.3	537.3	642.6	677.7	782.9	923.3	995.2	1067.3	1187.3	1240.9	1261.2
12.5°	463.4	520.7	674.0	722.0	873.4	1078.4	1165.2	1244.6	1381.2	1453.3	1464.3
15°	419.2	496.7	703.5	773.7	969.5	1207.6	1303.7	1401.5	1529.0	1580.6	1593.6
17.5°	380.4	478.2	731.2	805.1	1043.3	1324.0	1421.8	1503.1	1606.5	1641.6	1650.8
20°	332.4	448.8	749.7	845.7	1120.9	1408.9	1503.1	1565.9	1636.1	1658.2	1661.9
22.5°	297.3	417.3	760.8	860.5	1172.5	1460.6	1540.0	1589.9	1637.9	1645.2	1647.1
25°	267.8	382.2	758.9	877.1	1216.9	1492.0	1552.9	1589.9	1617.5	1621.3	1621.3
27.5°	240.1	343.5	751.5	880.8	1250.1	1499.4	1547.4	1573.2	1586.1	1593.6	1593.6
30°	216.0	306.5	733.1	873.4	1264.9	1492.0	1530.8	1543.7	1556.6	1567.7	1573.2
32.5°	197.6	271.5	705.3	858.6	1266.7	1473.5	1501.3	1508.6	1527.0	1552.9	1562.2
35°	181.0	236.4	674.0	838.3	1255.7	1444.0	1462.4	1469.9	1506.8	1545.6	1558.4
37.5°	164.4	210.5	633.4	803.3	1239.0	1408.9	1421.8	1434.7	1492.0	1538.1	1552.9
40°	147.7	188.3	585.3	764.4	1213.2	1366.4	1377.6	1397.8	1473.5	1527.0	1541.8
42.5°	134.8	169.9	533.6	723.9	1180.0	1318.5	1335.1	1364.6	1451.3	1508.6	1525.2
45°	123.7	151.4	478.2	668.4	1137.5	1268.5	1292.6	1333.2	1425.5	1480.9	1495.7
47.5°	112.6	138.5	421.0	611.2	1091.3	1218.7	1250.1	1296.2	1390.4	1444.0	1456.9
50°	103.4	125.5	363.8	550.2	1041.4	1165.2	1202.1	1250.1	1346.2	1396.0	1412.6
52.5°	96.0	114.5	310.2	489.3	984.2	1109.8	1152.3	1202.1	1292.6	1340.6	1351.7
55°	88.6	105.3	264.0	424.7	925.1	1050.7	1096.8	1144.8	1233.5	1274.1	1281.5
57.5°	85.0	97.8	225.3	363.8	862.4	984.2	1035.9	1080.2	1163.3	1194.7	1202.1
60°	79.4	92.3	195.7	312.1	794.0	921.5	965.8	1010.0	1080.2	1106.1	1111.6
62.5°	73.9	88.6	173.5	262.2	723.9	847.6	891.9	932.5	991.6	1010.0	1017.4
65°	70.2	85.0	156.9	225.3	651.8	770.0	814.4	849.4	897.4	915.9	919.5
67.5°	66.4	81.2	144.0	193.9	579.8	692.5	725.7	758.9	795.8	814.4	816.2
70°	60.9	77.5	133.0	171.7	505.9	603.8	631.6	666.6	696.2	705.3	710.9
72.5°	57.3	72.0	125.5	155.1	430.2	518.9	544.7	565.0	590.9	600.1	600.1
75°	51.7	64.6	118.2	138.5	352.7	424.7	446.8	467.2	487.5	491.2	485.6
77.5°	46.2	57.3	101.6	116.4	275.1	336.1	354.5	365.6	382.2	385.9	387.7
80°	38.8	49.8	79.4	90.5	199.4	247.4	260.4	269.6	284.4	284.4	288.1
82.5°	29.5	38.8	57.3	64.6	134.8	169.9	181.0	186.5	195.7	195.7	195.7
85°	18.4	24.0	36.9	42.5	81.2	103.4	110.8	112.6	120.0	121.9	121.9
87.5°	9.3	12.9	24.0	25.9	42.5	53.6	53.6	57.3	57.3	55.4	53.6
90°	2.8	5.0	7.2	7.7	12.1	18.0	20.9	18.6	13.9	10.5	10.5
92.5°	11.0	29.7	48.5	53.2	74.8	103.6	118.0	103.4	74.2	52.4	50.3
95°	26.4	60.8	95.1	103.7	184.1	291.4	345.0	307.8	233.6	177.8	171.5
97.5°	45.8	76.1	106.4	113.9	248.0	426.8	516.2	492.7	445.8	410.6	398.6
100°	60.7	88.1	115.5	122.4	271.3	469.7	568.9	570.6	574.0	576.6	562.3
102.5°	73.3	98.9	124.5	131.0	281.9	483.2	583.7	613.7	673.4	718.3	706.0
105°	94.9	116.5	138.2	143.6	289.8	484.6	582.1	649.1	783.2	883.7	877.1
107.5°	116.9	137.1	157.4	162.4	291.3	463.1	549.0	642.5	829.5	969.8	971.4
110°	131.8	150.0	168.3	172.9	289.1	444.0	521.4	626.0	835.0	991.8	998.7



TEST NUMBER: P936256

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	146.5	163.8	181.2	185.6	289.2	427.3	496.4	603.4	817.3	977.8	988.4
115°	168.5	184.5	200.6	204.6	291.8	408.1	466.3	569.3	775.5	930.1	944.7
117.5°	190.2	204.8	219.4	223.1	297.2	396.2	445.6	538.7	724.7	864.2	880.4
120°	202.9	216.7	230.4	233.8	301.6	392.0	437.3	522.3	692.3	819.8	835.6
122.5°	215.4	229.2	243.0	246.5	308.0	389.9	430.9	507.5	660.6	775.4	790.9
125°	234.4	247.0	259.7	262.8	316.6	388.3	424.1	489.0	619.1	716.6	730.9
127.5°	249.8	262.6	275.3	278.5	325.1	387.3	418.3	474.1	585.8	669.5	681.6
130°	258.1	271.8	285.6	289.0	331.4	387.8	416.1	465.8	565.2	639.7	650.9
132.5°	266.7	280.4	294.1	297.5	336.4	388.3	414.2	458.7	547.7	614.4	624.4
135°	279.3	291.8	304.3	307.4	341.9	387.9	410.9	448.1	522.6	578.5	587.1
137.5°	292.3	304.7	317.0	320.1	350.2	390.3	410.3	441.8	504.7	552.0	559.1
140°	303.0	314.4	325.9	328.7	355.2	390.7	408.4	435.5	490.0	530.8	537.4
142.5°	311.3	321.8	332.4	335.1	359.5	392.0	408.4	432.2	480.0	515.9	521.6
145°	324.0	333.2	342.4	344.7	365.0	392.0	405.6	425.2	464.3	493.5	497.8
147.5°	336.7	345.6	354.6	356.8	373.0	394.8	405.6	421.0	451.8	474.8	478.4
150°	345.0	353.0	361.1	363.1	377.3	396.2	405.6	418.7	444.6	464.1	466.9
152.5°	353.5	359.6	365.7	367.3	380.0	397.1	405.6	416.7	438.9	455.5	457.7
155°	366.2	370.7	375.2	376.3	386.1	399.1	405.6	414.4	432.1	445.4	446.8
157.5°	375.5	379.9	384.4	385.5	392.2	401.1	405.6	412.5	426.2	436.5	437.5
160°	381.9	385.3	388.8	389.7	395.0	402.0	405.6	411.5	423.2	432.1	432.6
162.5°	388.3	390.8	393.4	394.1	397.9	403.1	405.6	410.6	420.5	427.9	428.5
165°	395.2	397.5	399.8	400.4	402.1	404.4	405.6	409.2	416.3	421.6	422.1
167.5°	401.5	402.6	403.7	404.0	405.4	407.4	408.4	410.7	415.3	418.8	419.1
170°	405.6	406.7	407.8	408.1	408.2	408.3	408.4	410.7	415.3	418.8	418.8
172.5°	407.8	408.1	408.3	408.4	408.4	408.4	408.4	410.2	413.9	416.6	416.4
175°	410.9	410.9	410.9	410.9	410.0	408.9	408.4	409.6	411.9	413.6	413.6
177.5°	410.9	410.9	410.9	410.9	410.2	409.4	408.9	409.8	411.7	413.1	412.8
180°	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9



TEST NUMBER: P936256

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	574.3	574.3
2.5°	613.0	609.3
5°	788.5	792.2
7.5°	1061.8	1059.9
10°	1320.3	1336.9
12.5°	1508.6	1512.3
15°	1623.1	1630.5
17.5°	1667.5	1669.3
20°	1669.3	1665.6
22.5°	1648.9	1645.2
25°	1625.0	1623.1
27.5°	1602.8	1604.7
30°	1593.6	1599.1
32.5°	1593.6	1602.8
35°	1597.2	1606.5
37.5°	1595.4	1606.5
40°	1588.0	1600.9
42.5°	1567.7	1577.0
45°	1536.3	1547.4
47.5°	1495.7	1503.1
50°	1444.0	1451.3
52.5°	1379.4	1381.2
55°	1301.8	1309.2
57.5°	1218.7	1220.5
60°	1126.4	1131.9
62.5°	1028.6	1028.6
65°	925.1	928.8
67.5°	818.0	827.2
70°	709.1	710.9
72.5°	602.0	602.0
75°	491.2	493.0
77.5°	385.9	385.9
80°	286.2	288.1
82.5°	197.6	201.3
85°	123.7	123.7
87.5°	57.3	51.7
90°	10.5	10.5
92.5°	42.0	33.7
95°	146.3	121.0
97.5°	350.6	302.5
100°	505.1	447.8
102.5°	657.0	608.0
105°	850.8	824.5
107.5°	977.8	984.1
110°	1026.2	1053.6



TEST NUMBER: P936256

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1030.5	1072.6
115°	1003.1	1061.6
117.5°	945.2	1010.0
120°	898.5	961.5
122.5°	853.1	915.2
125°	788.1	845.4
127.5°	729.8	778.1
130°	695.5	740.1
132.5°	664.3	704.2
135°	621.6	656.0
137.5°	587.2	615.5
140°	563.7	590.1
142.5°	544.3	567.0
145°	515.0	532.2
147.5°	492.6	506.8
150°	478.5	490.0
152.5°	466.4	475.1
155°	452.5	458.3
157.5°	441.6	445.6
160°	435.0	437.3
162.5°	430.7	432.9
165°	424.5	426.8
167.5°	420.0	421.0
170°	418.8	418.8
172.5°	415.5	414.7
175°	413.6	413.6
177.5°	411.9	410.9
180°	410.9	410.9



TEST NUMBER: P936256
 CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.07	5.11	4.90	5.97	7.05	17.26	18.30	18.10	19.16	20.24
	3H	4.79	5.72	5.63	6.59	7.70	19.12	20.06	19.97	20.93	22.03
	4H	5.10	5.98	5.96	6.86	7.97	19.78	20.66	20.64	21.54	22.65
	6H	5.36	6.17	6.23	7.06	8.19	20.22	21.04	21.10	21.92	23.05
	8H	5.43	6.21	6.31	7.11	8.24	20.35	21.13	21.23	22.03	23.16
	12H	5.45	6.19	6.34	7.09	8.25	20.43	21.17	21.32	22.07	23.22
4H	2H	11.32	12.20	12.18	13.08	14.19	17.56	18.44	18.42	19.32	20.43
	3H	12.90	13.64	13.78	14.55	15.68	19.63	20.37	20.50	21.28	22.41
	4H	13.00	13.68	13.89	14.59	15.74	20.40	21.08	21.29	21.99	23.14
	6H	13.02	13.61	13.93	14.54	15.70	20.96	21.55	21.86	22.48	23.63
	8H	13.00	13.55	13.91	14.48	15.65	21.13	21.68	22.04	22.60	23.77
	12H	12.97	13.47	13.90	14.41	15.59	21.23	21.73	22.16	22.67	23.85
8H	4H	14.47	15.01	15.37	15.94	17.11	20.48	21.03	21.39	21.95	23.12
	6H	14.72	15.17	15.65	16.14	17.31	21.12	21.58	22.06	22.54	23.71
	8H	14.74	15.14	15.68	16.10	17.29	21.35	21.75	22.29	22.71	23.90
	12H	14.71	15.07	15.66	16.02	17.26	21.50	21.86	22.45	22.81	24.05
12H	4H	14.62	15.11	15.55	16.06	17.24	20.44	20.94	21.37	21.88	23.06
	6H	14.98	15.38	15.92	16.34	17.53	21.11	21.51	22.05	22.47	23.66
	8H	15.06	15.41	16.01	16.36	17.60	21.35	21.70	22.30	22.65	23.89