

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936259

Luminaire Tested: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936259
REPORT IS A COMBINATION OF REPORTS P933437 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2337.1 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 22
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936259
CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	29
5	68	56	47	41	64	52	45	39	46	40	35	40	35	31	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1752	1752	1752
5°	1710	2023	2355
10°	1550	2948	3905
15°	1316	3849	4715
20°	1070	4457	4805
25°	892	4660	4708
30°	751	4686	4699
35°	662	4604	4821
40°	577	4500	4945
45°	520	4422	4966
50°	477	4351	4883
55°	455	4249	4666
60°	464	4057	4325
65°	481	3766	3855
70°	508	3277	3257
75°	557	2665	2541
80°	599	1842	1714
85°	505	974	875

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4966 cd/sqm



TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	1.0
10°-20°	108.3	4.6
20°-30°	189.4	8.1
30°-40°	243.8	10.4
40°-50°	272.3	11.7
50°-60°	260.8	11.2
60°-70°	206.7	8.8
70°-80°	121.5	5.2
80°-90°	34.3	1.5
90°-100°	65.8	2.8
100°-110°	173.1	7.4
110°-120°	179.5	7.7
120°-130°	144.0	6.2
130°-140°	113.0	4.8
140°-150°	86.7	3.7
150°-160°	62.4	2.7
160°-170°	38.2	1.6
170°-180°	12.9	0.6
0°-30°	322.1	13.8
0°-40°	565.9	24.2
0°-60°	1099.0	47.0
0°-90°	1461.4	62.5
90°-120°	418.5	17.9
90°-150°	762.1	32.6
90°-180°	876.0	37.5
0°-180°	2337.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	189	189	189	189	189	
5°	184	197	222	251	260	17
15°	138	254	429	520	536	38
25°	88	288	511	533	534	41
35°	60	276	481	508	528	37
45°	41	220	425	487	509	31
55°	29	140	361	419	430	27
65°	23	74	268	301	305	23
75°	17	46	147	162	162	18
85°	6	14	36	40	41	6
90°	1	2	7	3	3	1
95°	9	34	113	58	40	10
105°	31	47	191	291	271	33
115°	55	67	153	306	349	55
125°	77	86	139	236	278	68
135°	92	101	135	190	216	71
145°	106	113	133	162	175	67
155°	120	124	133	146	151	55
165°	130	132	133	139	140	37
175°	135	135	134	136	136	13
180°	135	135	135	135	135	



TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8
2.5°	188.8	188.8	190.1	190.6	191.9	192.5	193.7	194.9	198.6	199.1	200.4
5°	184.0	186.5	194.3	197.3	205.8	217.4	222.2	230.2	246.6	251.4	254.4
7.5°	176.7	182.2	201.6	206.5	227.7	258.1	270.8	287.8	313.9	326.7	337.0
10°	165.2	176.7	211.4	222.9	257.4	303.6	327.3	351.0	390.5	408.0	414.7
12.5°	152.4	171.3	221.7	237.4	287.2	354.6	383.2	409.3	454.2	477.9	481.5
15°	137.9	163.4	231.4	254.4	318.8	397.1	428.7	460.9	502.8	519.7	524.0
17.5°	125.1	157.3	240.5	264.8	343.1	435.4	467.6	494.3	528.3	539.8	542.8
20°	109.3	147.5	246.6	278.2	368.6	463.4	494.3	514.9	538.0	545.3	546.5
22.5°	97.8	137.2	250.2	283.0	385.6	480.3	506.4	522.8	538.6	541.0	541.6
25°	88.1	125.7	249.6	288.5	400.2	490.6	510.7	522.8	532.0	533.1	533.1
27.5°	78.9	113.0	247.1	289.7	411.1	493.0	508.9	517.4	521.6	524.0	524.0
30°	71.1	100.8	241.0	287.2	415.9	490.6	503.4	507.6	511.9	515.6	517.4
32.5°	65.0	89.2	232.0	282.3	416.6	484.5	493.7	496.1	502.2	510.7	513.7
35°	59.5	77.8	221.7	275.7	412.9	474.8	480.9	483.4	495.5	508.2	512.5
37.5°	54.0	69.2	208.3	264.1	407.4	463.4	467.6	471.9	490.6	505.8	510.7
40°	48.6	61.9	192.5	251.4	399.0	449.3	453.0	459.6	484.5	502.2	507.1
42.5°	44.4	55.8	175.5	238.1	388.0	433.6	439.0	448.8	477.3	496.1	501.5
45°	40.6	49.8	157.3	219.8	374.0	417.2	425.1	438.5	468.8	487.0	491.9
47.5°	37.0	45.5	138.5	201.0	358.9	400.8	411.1	426.2	457.3	474.8	479.1
50°	34.0	41.3	119.7	180.9	342.5	383.2	395.3	411.1	442.7	459.1	464.5
52.5°	31.6	37.7	102.0	160.9	323.7	365.0	378.9	395.3	425.1	440.8	444.5
55°	29.1	34.6	86.8	139.7	304.2	345.5	360.7	376.5	405.6	419.0	421.4
57.5°	28.0	32.2	74.0	119.7	283.6	323.7	340.6	355.2	382.5	392.8	395.3
60°	26.1	30.3	64.4	102.6	261.1	303.0	317.6	332.2	355.2	363.7	365.6
62.5°	24.3	29.1	57.1	86.3	238.1	278.7	293.3	306.7	326.0	332.2	334.5
65°	23.1	28.0	51.6	74.0	214.3	253.2	267.7	279.3	295.1	301.1	302.4
67.5°	21.9	26.7	47.3	63.7	190.6	227.7	238.6	249.6	261.7	267.7	268.4
70°	20.0	25.5	43.7	56.5	166.4	198.6	207.6	219.2	228.9	232.0	233.8
72.5°	18.8	23.7	41.3	51.1	141.5	170.6	179.1	185.8	194.3	197.3	197.3
75°	17.0	21.3	38.8	45.5	116.0	139.7	146.9	153.6	160.3	161.5	159.7
77.5°	15.2	18.8	33.4	38.3	90.5	110.5	116.6	120.2	125.7	126.9	127.5
80°	12.8	16.4	26.1	29.8	65.6	81.4	85.6	88.6	93.5	93.5	94.8
82.5°	9.7	12.8	18.8	21.3	44.4	55.8	59.5	61.4	64.4	64.4	64.4
85°	6.1	7.9	12.1	13.9	26.7	34.0	36.5	37.0	39.5	40.1	40.1
87.5°	3.1	4.3	7.9	8.5	13.9	17.7	17.7	18.8	18.8	18.2	17.7
90°	0.9	1.6	2.4	2.5	4.0	5.9	6.9	6.2	4.6	3.4	3.4
92.5°	3.6	9.8	15.9	17.5	24.6	34.1	38.8	34.0	24.4	17.2	16.5
95°	8.7	20.0	31.3	34.1	60.6	95.8	113.4	101.2	76.8	58.5	56.4
97.5°	15.0	25.0	34.9	37.5	81.6	140.3	169.7	162.0	146.5	135.0	131.0
100°	19.9	29.0	38.0	40.3	89.2	154.4	187.0	187.5	188.7	189.5	184.8
102.5°	24.1	32.5	41.0	43.1	92.7	158.9	191.9	201.8	221.4	236.2	232.1
105°	31.2	38.4	45.4	47.2	95.3	159.3	191.4	213.4	257.5	290.6	288.4
107.5°	38.5	45.1	51.8	53.4	95.8	152.2	180.5	211.3	272.7	318.9	319.4
110°	43.4	49.3	55.3	56.8	95.0	146.0	171.4	205.8	274.5	326.1	328.4



TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	48.2	53.9	59.6	61.0	95.0	140.5	163.2	198.4	268.7	321.5	325.0
115°	55.4	60.6	65.9	67.3	95.9	134.2	153.3	187.2	255.0	305.8	310.6
117.5°	62.5	67.3	72.1	73.3	97.8	130.3	146.5	177.1	238.2	284.1	289.5
120°	66.7	71.2	75.8	76.8	99.1	128.9	143.7	171.7	227.6	269.6	274.7
122.5°	70.8	75.3	79.8	81.0	101.2	128.2	141.7	166.8	217.1	254.9	260.0
125°	77.0	81.2	85.4	86.4	104.1	127.6	139.4	160.8	203.6	235.6	240.3
127.5°	82.1	86.4	90.5	91.6	106.9	127.3	137.5	155.9	192.6	220.1	224.1
130°	84.8	89.3	93.9	95.0	109.0	127.5	136.8	153.2	185.8	210.4	214.0
132.5°	87.7	92.2	96.8	97.8	110.6	127.6	136.1	150.8	180.0	202.0	205.3
135°	91.9	95.9	100.1	101.1	112.4	127.5	135.1	147.3	171.8	190.2	193.0
137.5°	96.1	100.2	104.3	105.3	115.1	128.3	134.9	145.2	165.9	181.5	183.8
140°	99.7	103.4	107.2	108.1	116.8	128.4	134.2	143.2	161.1	174.5	176.7
142.5°	102.4	105.8	109.3	110.2	118.2	128.9	134.2	142.1	157.9	169.6	171.5
145°	106.5	109.5	112.6	113.3	120.0	128.9	133.3	139.8	152.6	162.3	163.7
147.5°	110.7	113.6	116.6	117.3	122.6	129.8	133.3	138.4	148.5	156.1	157.3
150°	113.4	116.0	118.8	119.4	124.0	130.3	133.3	137.6	146.2	152.6	153.5
152.5°	116.2	118.2	120.2	120.7	124.9	130.5	133.3	137.0	144.3	149.8	150.5
155°	120.4	121.8	123.4	123.7	126.9	131.2	133.3	136.2	142.1	146.5	146.9
157.5°	123.5	124.9	126.4	126.7	128.9	131.9	133.3	135.6	140.1	143.5	143.8
160°	125.5	126.6	127.8	128.1	129.8	132.2	133.3	135.2	139.1	142.0	142.2
162.5°	127.6	128.4	129.3	129.5	130.8	132.5	133.3	135.0	138.2	140.7	140.8
165°	129.9	130.6	131.4	131.6	132.2	133.0	133.3	134.5	136.9	138.6	138.8
167.5°	132.0	132.3	132.7	132.8	133.2	133.9	134.2	135.0	136.5	137.7	137.8
170°	133.3	133.7	134.1	134.1	134.1	134.2	134.2	135.0	136.5	137.7	137.7
172.5°	134.1	134.1	134.2	134.2	134.2	134.2	134.2	134.9	136.0	137.0	136.9
175°	135.1	135.1	135.1	135.1	134.8	134.4	134.2	134.6	135.4	136.0	136.0
177.5°	135.1	135.1	135.1	135.1	134.9	134.6	134.4	134.7	135.3	135.8	135.7
180°	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1



TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	188.8	188.8
2.5°	201.6	200.4
5°	259.3	260.5
7.5°	349.1	348.6
10°	434.2	439.6
12.5°	496.1	497.3
15°	533.8	536.2
17.5°	548.3	549.0
20°	549.0	547.7
22.5°	542.3	541.0
25°	534.4	533.8
27.5°	527.1	527.7
30°	524.0	525.9
32.5°	524.0	527.1
35°	525.3	528.3
37.5°	524.6	528.3
40°	522.2	526.4
42.5°	515.6	518.6
45°	505.2	508.9
47.5°	491.9	494.3
50°	474.8	477.3
52.5°	453.6	454.2
55°	428.1	430.5
57.5°	400.8	401.3
60°	370.4	372.2
62.5°	338.3	338.3
65°	304.2	305.4
67.5°	269.0	272.0
70°	233.2	233.8
72.5°	198.0	198.0
75°	161.5	162.1
77.5°	126.9	126.9
80°	94.1	94.8
82.5°	65.0	66.2
85°	40.6	40.6
87.5°	18.8	17.0
90°	3.4	3.4
92.5°	13.8	11.0
95°	48.2	39.8
97.5°	115.2	99.5
100°	166.1	147.3
102.5°	216.0	199.9
105°	279.8	271.1
107.5°	321.5	323.6
110°	337.4	346.4



TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	338.8	352.7
115°	329.8	349.0
117.5°	310.7	332.1
120°	295.4	316.1
122.5°	280.4	300.9
125°	259.1	278.0
127.5°	240.0	255.8
130°	228.6	243.3
132.5°	218.4	231.5
135°	204.4	215.7
137.5°	193.1	202.4
140°	185.3	194.0
142.5°	179.0	186.4
145°	169.4	175.0
147.5°	161.9	166.6
150°	157.3	161.1
152.5°	153.3	156.2
155°	148.8	150.7
157.5°	145.2	146.5
160°	143.0	143.7
162.5°	141.6	142.3
165°	139.6	140.3
167.5°	138.0	138.4
170°	137.7	137.7
172.5°	136.6	136.3
175°	136.0	136.0
177.5°	135.4	135.1
180°	135.1	135.1



TEST NUMBER: P936259

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.00	5.04	4.83	5.90	6.98	17.14	18.18	17.98	19.04	20.12
	3H	4.72	5.65	5.56	6.53	7.63	18.98	19.92	19.83	20.79	21.89
	4H	5.03	5.91	5.89	6.79	7.90	19.62	20.51	20.49	21.39	22.50
	6H	5.29	6.11	6.16	6.99	8.12	20.05	20.87	20.93	21.75	22.88
	8H	5.36	6.14	6.24	7.05	8.17	20.17	20.95	21.05	21.86	22.98
	12H	5.39	6.13	6.28	7.03	8.18	20.24	20.98	21.13	21.88	23.03
4H	2H	11.22	12.10	12.08	12.98	14.09	17.44	18.33	18.31	19.20	20.32
	3H	12.80	13.54	13.68	14.45	15.58	19.49	20.23	20.37	21.14	22.27
	4H	12.91	13.58	13.80	14.49	15.64	20.25	20.93	21.14	21.84	22.99
	6H	12.93	13.51	13.83	14.44	15.60	20.79	21.38	21.70	22.31	23.46
	8H	12.91	13.46	13.82	14.38	15.55	20.95	21.50	21.86	22.42	23.60
	12H	12.87	13.37	13.80	14.31	15.49	21.04	21.54	21.97	22.48	23.66
8H	4H	14.36	14.90	15.26	15.83	17.00	20.33	20.88	21.24	21.80	22.97
	6H	14.61	15.06	15.54	16.03	17.20	20.95	21.41	21.89	22.38	23.55
	8H	14.63	15.03	15.57	15.99	17.18	21.17	21.57	22.11	22.53	23.72
	12H	14.60	14.96	15.55	15.91	17.15	21.31	21.67	22.26	22.62	23.86
12H	4H	14.50	15.00	15.43	15.94	17.12	20.29	20.79	21.22	21.73	22.91
	6H	14.86	15.27	15.81	16.23	17.41	20.94	21.34	21.88	22.30	23.49
	8H	14.94	15.30	15.89	16.25	17.49	21.17	21.53	22.12	22.48	23.71