

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936267

Luminaire Tested: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936267
REPORT IS A COMBINATION OF REPORTS P933453 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4673.4 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936267
CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1751	1751	1751
5°	1712	2025	2355
10°	1552	2952	3904
15°	1319	3856	4714
20°	1074	4469	4804
25°	896	4676	4706
30°	755	4705	4698
35°	668	4628	4819
40°	582	4526	4945
45°	528	4452	4964
50°	484	4385	4882
55°	463	4286	4665
60°	474	4099	4323
65°	494	3812	3854
70°	526	3324	3256
75°	582	2711	2540
80°	636	1880	1712
85°	564	998	877

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4964 cd/sqm



TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	1.0
10°-20°	216.5	4.6
20°-30°	378.6	8.1
30°-40°	487.4	10.4
40°-50°	544.4	11.6
50°-60°	521.4	11.2
60°-70°	413.2	8.8
70°-80°	243.0	5.2
80°-90°	68.5	1.5
90°-100°	131.7	2.8
100°-110°	346.2	7.4
110°-120°	359.0	7.7
120°-130°	288.0	6.2
130°-140°	225.9	4.8
140°-150°	173.4	3.7
150°-160°	124.9	2.7
160°-170°	76.4	1.6
170°-180°	25.8	0.6
0°-30°	643.9	13.8
0°-40°	1131.4	24.2
0°-60°	2197.2	47.0
0°-90°	2922.0	62.5
90°-120°	836.9	17.9
90°-150°	1524.3	32.6
90°-180°	1751.0	37.5
0°-180°	4673.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	378	378	378	378	378	
5°	368	395	444	503	521	34
15°	276	509	857	1039	1072	77
25°	176	577	1021	1066	1067	81
35°	119	551	962	1016	1056	74
45°	81	440	850	974	1017	63
55°	58	279	721	838	861	53
65°	46	148	535	602	611	46
75°	34	91	294	323	324	36
85°	12	28	73	80	81	13
90°	2	5	14	7	7	2
95°	17	68	227	117	80	19
105°	62	94	383	581	542	66
115°	111	134	307	612	698	109
125°	154	173	279	471	556	137
135°	184	202	270	380	431	142
145°	213	227	267	325	350	133
155°	241	248	267	293	301	111
165°	260	263	267	277	281	73
175°	270	270	269	272	272	26
180°	270	270	270	270	270	



TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	377.5	377.5	377.5	377.5	377.5	377.5	377.5	377.5	377.5	377.5	377.5
2.5°	377.5	377.5	380.0	381.3	383.6	384.9	387.3	389.8	397.0	398.2	400.6
5°	367.9	372.7	388.5	394.6	411.6	434.7	444.3	460.1	493.0	502.6	508.7
7.5°	353.3	364.2	403.1	412.8	455.3	515.9	541.5	575.5	627.6	653.2	673.8
10°	330.2	353.3	422.5	445.6	514.8	607.0	654.4	701.8	780.6	815.8	829.2
12.5°	304.8	342.3	443.2	474.7	574.2	709.0	766.1	818.3	908.1	955.5	962.7
15°	275.6	326.6	462.5	508.7	637.4	794.0	857.2	921.5	1005.3	1039.2	1047.7
17.5°	250.1	314.5	480.8	529.3	685.9	870.5	934.9	988.3	1056.2	1079.3	1085.4
20°	218.5	295.0	493.0	556.0	737.0	926.3	988.3	1029.5	1075.7	1090.3	1092.7
22.5°	195.4	274.4	500.2	565.7	770.9	960.4	1012.5	1045.4	1076.9	1081.8	1082.9
25°	176.1	251.3	499.0	576.7	800.1	981.0	1021.0	1045.4	1063.6	1066.0	1066.0
27.5°	157.9	225.8	494.1	579.1	822.0	985.8	1017.4	1034.4	1042.9	1047.7	1047.7
30°	142.0	201.6	482.0	574.2	831.7	981.0	1006.4	1015.0	1023.5	1030.8	1034.4
32.5°	129.9	178.5	463.8	564.5	832.8	968.8	987.1	991.9	1004.0	1021.0	1027.1
35°	118.9	155.4	443.2	551.2	825.6	949.4	961.6	966.4	990.7	1016.2	1024.6
37.5°	108.1	138.4	416.5	528.2	814.6	926.3	934.9	943.4	981.0	1011.3	1021.0
40°	97.1	123.8	384.9	502.6	797.6	898.5	905.7	919.1	968.8	1004.0	1013.8
42.5°	88.6	111.7	350.8	475.9	775.8	866.9	877.8	897.2	954.3	991.9	1002.8
45°	81.4	99.6	314.5	439.5	747.8	834.1	849.9	876.6	937.3	973.7	983.4
47.5°	74.0	91.1	276.8	401.9	717.5	801.3	822.0	852.3	914.2	949.4	957.9
50°	68.0	82.6	239.1	361.8	684.8	766.1	790.4	822.0	885.1	917.8	928.8
52.5°	63.1	75.3	203.9	321.7	647.1	729.7	757.6	790.4	849.9	881.4	888.7
55°	58.3	69.2	173.6	279.2	608.3	690.8	721.1	752.7	811.0	837.7	842.6
57.5°	55.8	64.4	148.1	239.1	567.0	647.1	681.1	710.3	764.9	785.5	790.4
60°	52.2	60.7	128.7	205.2	522.1	605.8	635.0	664.1	710.3	727.2	730.9
62.5°	48.6	58.3	114.1	172.4	475.9	557.3	586.4	613.2	652.0	664.1	669.0
65°	46.2	55.8	103.2	148.1	428.6	506.3	535.4	558.5	590.1	602.2	604.6
67.5°	43.7	53.4	94.7	127.4	381.3	455.3	477.1	499.0	523.3	535.4	536.6
70°	40.1	51.0	87.4	112.9	332.6	397.0	415.2	438.3	457.7	463.8	467.4
72.5°	37.7	47.3	82.6	102.0	282.9	341.2	358.2	371.5	388.5	394.6	394.6
75°	34.0	42.5	77.7	91.1	231.9	279.2	293.8	307.1	320.5	323.0	319.3
77.5°	30.3	37.7	66.8	76.5	180.9	220.9	233.1	240.4	251.3	253.7	255.0
80°	25.5	32.8	52.2	59.5	131.2	162.7	171.2	177.2	187.0	187.0	189.4
82.5°	19.5	25.5	37.7	42.5	88.6	111.7	118.9	122.6	128.7	128.7	128.7
85°	12.1	15.7	24.3	27.9	53.4	68.0	72.9	74.0	78.9	80.1	80.1
87.5°	6.1	8.5	15.7	17.0	27.9	35.2	35.2	37.7	37.7	36.4	35.2
90°	1.8	3.3	4.7	5.1	8.0	11.9	13.8	12.2	9.1	6.9	6.9
92.5°	7.2	19.6	32.0	35.0	49.2	68.2	77.6	68.0	48.9	34.5	33.1
95°	17.4	39.9	62.5	68.2	121.0	191.5	226.8	202.4	153.6	116.9	112.8
97.5°	30.1	50.1	69.9	74.9	163.0	280.6	339.4	324.0	293.2	270.0	262.1
100°	39.9	57.9	75.9	80.5	178.3	308.8	374.0	375.2	377.5	379.2	369.8
102.5°	48.2	65.1	81.9	86.1	185.4	317.7	383.9	403.5	442.8	472.3	464.3
105°	62.4	76.7	91.0	94.5	190.6	318.7	382.8	426.9	515.0	581.1	576.8
107.5°	76.8	90.2	103.5	106.8	191.5	304.5	361.0	422.4	545.5	637.7	638.8
110°	86.7	98.7	110.7	113.7	190.1	291.9	342.9	411.6	549.1	652.2	656.7



TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	96.3	107.7	119.1	122.0	190.2	281.0	326.4	396.7	537.4	642.9	649.9
115°	110.8	121.3	131.9	134.5	191.9	268.4	306.6	374.4	510.0	611.6	621.2
117.5°	125.1	134.7	144.3	146.7	195.5	260.5	293.0	354.2	476.5	568.3	578.9
120°	133.4	142.5	151.5	153.8	198.4	257.9	287.6	343.4	455.2	539.0	549.3
122.5°	141.6	150.7	159.9	162.1	202.6	256.4	283.4	333.7	434.4	509.9	520.1
125°	154.1	162.5	170.7	172.8	208.2	255.3	278.9	321.6	407.1	471.2	480.6
127.5°	164.3	172.6	181.0	183.1	213.8	254.6	275.1	311.8	385.2	440.3	448.2
130°	169.7	178.8	187.7	190.0	217.9	255.1	273.6	306.3	371.7	420.6	428.0
132.5°	175.3	184.4	193.3	195.6	221.2	255.3	272.4	301.6	360.1	404.0	410.6
135°	183.7	191.9	200.1	202.2	224.8	255.1	270.2	294.7	343.7	380.4	386.1
137.5°	192.2	200.3	208.5	210.5	230.3	256.6	269.8	290.6	331.9	363.0	367.6
140°	199.2	206.7	214.3	216.2	233.6	256.9	268.6	286.5	322.2	349.0	353.4
142.5°	204.7	211.6	218.6	220.3	236.4	257.9	268.6	284.3	315.7	339.3	343.0
145°	213.1	219.1	225.1	226.7	240.0	257.9	266.8	279.6	305.3	324.6	327.4
147.5°	221.4	227.3	233.2	234.6	245.3	259.6	266.8	276.9	297.1	312.2	314.5
150°	226.8	232.2	237.4	238.8	248.1	260.5	266.8	275.3	292.4	305.1	307.0
152.5°	232.4	236.4	240.5	241.5	249.9	261.1	266.8	274.0	288.6	299.5	301.0
155°	240.8	243.8	246.7	247.5	253.9	262.5	266.8	272.5	284.1	292.8	293.7
157.5°	246.9	249.8	252.7	253.4	257.9	263.8	266.8	271.3	280.2	287.0	287.7
160°	251.1	253.4	255.6	256.2	259.7	264.4	266.8	270.6	278.3	284.1	284.5
162.5°	255.3	257.0	258.6	259.1	261.6	265.0	266.8	270.0	276.5	281.4	281.8
165°	259.9	261.4	262.9	263.3	264.5	266.0	266.8	269.1	273.7	277.3	277.6
167.5°	264.0	264.8	265.5	265.7	266.7	267.9	268.6	270.1	273.2	275.4	275.6
170°	266.8	267.5	268.2	268.4	268.5	268.6	268.6	270.1	273.2	275.4	275.4
172.5°	268.2	268.4	268.6	268.6	268.6	268.6	268.6	269.7	272.2	274.0	273.8
175°	270.2	270.2	270.2	270.2	269.6	268.9	268.6	269.3	270.8	272.0	272.0
177.5°	270.2	270.2	270.2	270.2	269.7	269.2	268.9	269.6	270.7	271.6	271.5
180°	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2	270.2



TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	377.5	377.5
2.5°	403.1	400.6
5°	518.4	520.8
7.5°	698.1	696.9
10°	868.0	879.0
12.5°	991.9	994.3
15°	1067.2	1072.1
17.5°	1096.3	1097.5
20°	1097.5	1095.1
22.5°	1084.2	1081.8
25°	1068.4	1067.2
27.5°	1053.8	1055.1
30°	1047.7	1051.4
32.5°	1047.7	1053.8
35°	1050.2	1056.2
37.5°	1049.0	1056.2
40°	1044.1	1052.6
42.5°	1030.8	1036.9
45°	1010.2	1017.4
47.5°	983.4	988.3
50°	949.4	954.3
52.5°	906.9	908.1
55°	855.9	860.8
57.5°	801.3	802.5
60°	740.6	744.2
62.5°	676.2	676.2
65°	608.3	610.7
67.5°	537.8	543.9
70°	466.2	467.4
72.5°	395.8	395.8
75°	323.0	324.1
77.5°	253.7	253.7
80°	188.2	189.4
82.5°	129.9	132.3
85°	81.4	81.4
87.5°	37.7	34.0
90°	6.9	6.9
92.5°	27.6	22.1
95°	96.2	79.6
97.5°	230.5	198.9
100°	332.1	294.4
102.5°	432.0	399.8
105°	559.5	542.1
107.5°	642.9	647.1
110°	674.7	692.8



TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	677.6	705.3
115°	659.7	698.1
117.5°	621.6	664.2
120°	590.8	632.3
122.5°	560.9	601.8
125°	518.3	555.9
127.5°	479.9	511.7
130°	457.3	486.6
132.5°	436.8	463.1
135°	408.7	431.3
137.5°	386.1	404.7
140°	370.7	388.0
142.5°	357.9	372.7
145°	338.7	349.9
147.5°	323.9	333.3
150°	314.6	322.2
152.5°	306.7	312.4
155°	297.5	301.3
157.5°	290.4	293.0
160°	286.0	287.6
162.5°	283.2	284.7
165°	279.2	280.7
167.5°	276.3	276.9
170°	275.4	275.4
172.5°	273.3	272.7
175°	272.0	272.0
177.5°	270.8	270.2
180°	270.2	270.2



TEST NUMBER: P936267

CATALOG NUMBER: SQ4-FB-025U-050D-93050-1D-UNV-STD-W-8-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.02	5.06	4.85	5.92	6.99	17.20	18.23	18.03	19.10	20.17
	3H	4.74	5.67	5.58	6.54	7.65	19.05	19.98	19.89	20.86	21.96
	4H	5.04	5.93	5.90	6.81	7.92	19.70	20.59	20.56	21.47	22.58
	6H	5.30	6.12	6.18	7.00	8.13	20.14	20.96	21.02	21.84	22.97
	8H	5.38	6.16	6.26	7.06	8.19	20.27	21.05	21.15	21.95	23.08
	12H	5.40	6.14	6.29	7.04	8.20	20.34	21.09	21.23	21.98	23.14
4H	2H	11.25	12.14	12.12	13.02	14.13	17.49	18.38	18.36	19.26	20.37
	3H	12.84	13.58	13.72	14.49	15.62	19.55	20.30	20.43	21.21	22.34
	4H	12.94	13.62	13.83	14.52	15.68	20.33	21.01	21.22	21.91	23.07
	6H	12.96	13.55	13.87	14.48	15.64	20.88	21.47	21.78	22.40	23.55
	8H	12.94	13.49	13.85	14.42	15.59	21.05	21.59	21.95	22.52	23.69
	12H	12.91	13.41	13.84	14.35	15.53	21.15	21.64	22.08	22.59	23.76
8H	4H	14.40	14.95	15.31	15.87	17.05	20.40	20.95	21.31	21.88	23.05
	6H	14.65	15.11	15.59	16.07	17.24	21.04	21.50	21.98	22.46	23.63
	8H	14.67	15.08	15.62	16.03	17.22	21.26	21.67	22.21	22.63	23.81
	12H	14.65	15.01	15.60	15.96	17.19	21.42	21.77	22.37	22.72	23.96
12H	4H	14.55	15.05	15.48	15.99	17.17	20.37	20.86	21.30	21.81	22.98
	6H	14.91	15.32	15.86	16.27	17.46	21.03	21.43	21.97	22.39	23.58
	8H	14.99	15.35	15.94	16.30	17.53	21.27	21.62	22.22	22.57	23.81