

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936364

Luminaire Tested: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936364  
REPORT IS A COMBINATION OF REPORTS P933446 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4644.4 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936364  
CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P936364

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2648	2648	2648
5°	2586	3060	3559
10°	2345	4460	5901
15°	1992	5825	7127
20°	1621	6749	7263
25°	1352	7061	7116
30°	1140	7103	7102
35°	1007	6984	7286
40°	877	6828	7476
45°	793	6714	7505
50°	728	6610	7381
55°	696	6461	7053
60°	712	6174	6536
65°	739	5740	5827
70°	785	5002	4923
75°	866	4075	3841
80°	941	2823	2588
85°	823	1495	1324

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 7505 cd/sqm



TEST NUMBER: P936364

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.4	1.2
10°-20°	245.4	5.3
20°-30°	429.3	9.2
30°-40°	552.7	11.9
40°-50°	617.3	13.3
50°-60°	591.2	12.7
60°-70°	468.5	10.1
70°-80°	275.5	5.9
80°-90°	77.3	1.7
90°-100°	100.1	2.2
100°-110°	263.3	5.7
110°-120°	273.0	5.9
120°-130°	219.0	4.7
130°-140°	171.8	3.7
140°-150°	131.9	2.8
150°-160°	95.0	2.0
160°-170°	58.1	1.3
170°-180°	19.6	0.4
0°-30°	730.1	15.7
0°-40°	1282.8	27.6
0°-60°	2491.3	53.6
0°-90°	3312.7	71.3
90°-120°	636.3	13.7
90°-150°	1159.0	25.0
90°-180°	1332.0	28.7
0°-180°	4644.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	428	428	428	428	428	
5°	417	447	504	570	590	38
15°	312	577	972	1178	1216	87
25°	200	654	1158	1209	1210	92
35°	135	625	1090	1152	1198	84
45°	92	498	964	1104	1154	71
55°	66	317	818	950	976	60
65°	52	168	607	683	692	52
75°	38	103	333	366	368	40
85°	14	32	83	91	92	15
90°	1	4	10	5	5	2
95°	13	52	172	89	61	15
105°	47	72	291	442	412	50
115°	84	102	233	465	531	83
125°	117	131	212	358	423	104
135°	140	154	206	289	328	108
145°	162	172	203	247	266	101
155°	183	188	203	223	229	84
165°	198	200	203	211	214	56
175°	206	206	204	207	207	20
180°	206	206	206	206	206	



TEST NUMBER: P936364

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1
2.5°	428.1	428.1	430.9	432.2	435.0	436.4	439.1	441.9	450.1	451.5	454.3
5°	417.1	422.6	440.5	447.4	466.6	492.8	503.8	521.7	558.9	569.9	576.8
7.5°	400.6	413.0	457.0	468.0	516.2	585.0	613.9	652.5	711.7	740.6	764.0
10°	374.4	400.6	479.0	505.2	583.7	688.3	742.0	795.6	885.1	925.0	940.2
12.5°	345.5	388.2	502.4	538.2	651.1	803.9	868.6	927.8	1029.7	1083.4	1091.7
15°	312.5	370.3	524.5	576.8	722.7	900.3	971.8	1044.9	1139.9	1178.4	1188.0
17.5°	283.6	356.5	545.1	600.2	777.7	987.0	1060.0	1120.6	1197.7	1223.8	1230.7
20°	247.8	334.5	558.9	630.5	835.6	1050.4	1120.6	1167.4	1219.7	1236.2	1239.0
22.5°	221.6	311.1	567.1	641.5	874.1	1088.9	1148.1	1185.3	1221.1	1226.6	1228.0
25°	199.6	284.9	565.8	653.9	907.1	1112.3	1157.8	1185.3	1205.9	1208.7	1208.7
27.5°	179.0	256.0	560.3	656.6	931.9	1117.8	1153.6	1172.9	1182.5	1188.0	1188.0
30°	161.1	228.5	546.5	651.1	942.9	1112.3	1141.2	1150.9	1160.5	1168.8	1172.9
32.5°	147.3	202.4	525.8	640.1	944.3	1098.6	1119.2	1124.7	1138.5	1157.8	1164.6
35°	134.9	176.2	502.4	625.0	936.0	1076.5	1090.3	1095.8	1123.4	1152.3	1161.9
37.5°	122.5	156.9	472.2	598.8	923.7	1050.4	1060.0	1069.7	1112.3	1146.8	1157.8
40°	110.1	140.4	436.4	569.9	904.4	1018.6	1026.9	1042.0	1098.6	1138.5	1149.5
42.5°	100.5	126.6	397.8	539.6	879.6	982.9	995.2	1017.3	1082.1	1124.7	1137.1
45°	92.2	112.9	356.5	498.3	848.0	945.7	963.6	993.9	1062.8	1104.1	1115.1
47.5°	84.0	103.2	313.9	455.6	813.5	908.5	931.9	966.3	1036.5	1076.5	1086.2
50°	77.1	93.6	271.2	410.2	776.4	868.6	896.1	931.9	1003.5	1040.7	1053.1
52.5°	71.6	85.3	231.3	364.8	733.7	827.3	859.0	896.1	963.6	999.4	1007.6
55°	66.1	78.5	196.8	316.6	689.6	783.3	817.7	853.5	919.5	949.8	955.3
57.5°	63.3	73.0	167.9	271.2	642.8	733.7	772.2	805.3	867.2	890.6	896.1
60°	59.2	68.8	145.9	232.6	591.9	686.9	719.9	753.0	805.3	824.5	828.7
62.5°	55.1	66.1	129.4	195.5	539.6	631.8	664.9	695.2	739.2	753.0	758.5
65°	52.3	63.3	117.0	167.9	485.9	574.0	607.1	633.2	669.0	682.8	685.5
67.5°	49.6	60.6	107.4	144.5	432.2	516.2	541.0	565.8	593.3	607.1	608.4
70°	45.4	57.8	99.1	128.0	377.2	450.1	470.8	496.9	519.0	525.8	530.0
72.5°	42.7	53.7	93.6	115.6	320.7	386.8	406.1	421.2	440.5	447.4	447.4
75°	38.5	48.2	88.1	103.2	262.9	316.6	333.1	348.3	363.4	366.2	362.0
77.5°	34.4	42.7	75.7	86.7	205.1	250.5	264.3	272.6	284.9	287.7	289.1
80°	28.9	37.2	59.2	67.5	148.7	184.5	194.1	201.0	212.0	212.0	214.7
82.5°	22.0	28.9	42.7	48.2	100.5	126.6	134.9	139.0	145.9	145.9	145.9
85°	13.8	17.9	27.5	31.7	60.6	77.1	82.6	84.0	89.5	90.9	90.9
87.5°	6.9	9.6	17.9	19.3	31.7	39.9	39.9	42.7	42.7	41.3	39.9
90°	1.4	2.5	3.6	3.9	6.1	9.0	10.5	9.3	7.0	5.2	5.2
92.5°	5.5	14.9	24.2	26.6	37.4	51.8	59.0	51.7	37.1	26.2	25.1
95°	13.2	30.4	47.5	51.8	92.0	145.6	172.4	153.9	116.7	88.9	85.8
97.5°	22.9	38.0	53.1	56.9	124.0	213.4	258.1	246.3	222.9	205.3	199.3
100°	30.4	44.0	57.8	61.2	135.6	234.8	284.4	285.2	287.0	288.2	281.1
102.5°	36.7	49.6	62.3	65.5	141.0	241.5	291.8	306.8	336.7	359.2	353.0
105°	47.4	58.3	69.1	71.9	144.9	242.3	291.0	324.5	391.6	441.9	438.6
107.5°	58.5	68.6	78.6	81.2	145.6	231.5	274.5	321.3	414.8	484.9	485.7
110°	65.9	75.1	84.2	86.4	144.5	222.0	260.7	313.0	417.6	495.9	499.3



TEST NUMBER: P936364

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	73.2	82.0	90.6	92.8	144.5	213.6	248.1	301.6	408.6	488.9	494.1
115°	84.2	92.3	100.3	102.3	145.9	204.0	233.1	284.7	387.7	465.0	472.3
117.5°	95.2	102.4	109.7	111.5	148.6	198.0	222.8	269.3	362.3	432.1	440.1
120°	101.5	108.4	115.2	116.9	150.9	196.1	218.7	261.2	346.2	409.9	417.8
122.5°	107.6	114.6	121.5	123.2	154.0	195.0	215.5	253.7	330.3	387.7	395.5
125°	117.2	123.5	129.9	131.4	158.3	194.2	212.1	244.6	309.6	358.4	365.5
127.5°	124.9	131.2	137.7	139.2	162.5	193.6	209.1	237.0	292.9	334.8	340.8
130°	129.0	135.9	142.7	144.4	165.6	193.9	208.0	232.9	282.6	319.8	325.4
132.5°	133.3	140.2	147.0	148.8	168.2	194.2	207.1	229.3	273.8	307.2	312.1
135°	139.7	145.9	152.2	153.7	171.0	194.0	205.5	224.1	261.4	289.3	293.6
137.5°	146.2	152.3	158.5	160.0	175.1	195.2	205.2	221.0	252.5	276.0	279.5
140°	151.5	157.2	162.9	164.4	177.7	195.4	204.2	217.8	245.0	265.4	268.7
142.5°	155.6	160.9	166.2	167.5	179.7	196.0	204.2	216.1	240.1	258.0	260.8
145°	162.0	166.6	171.2	172.3	182.5	196.0	202.8	212.5	232.1	246.8	248.9
147.5°	168.3	172.8	177.3	178.4	186.6	197.4	202.8	210.5	225.8	237.4	239.2
150°	172.4	176.5	180.6	181.6	188.7	198.1	202.8	209.3	222.3	232.0	233.5
152.5°	176.7	179.8	182.9	183.6	190.1	198.6	202.8	208.3	219.4	227.8	228.9
155°	183.1	185.4	187.7	188.2	193.1	199.6	202.8	207.2	216.0	222.6	223.4
157.5°	187.8	190.0	192.2	192.7	196.1	200.6	202.8	206.2	213.1	218.2	218.8
160°	191.0	192.7	194.4	194.8	197.5	201.1	202.8	205.7	211.6	216.0	216.3
162.5°	194.1	195.4	196.7	197.0	199.0	201.5	202.8	205.3	210.2	214.0	214.3
165°	197.6	198.7	199.9	200.1	201.1	202.3	202.8	204.6	208.1	210.8	211.1
167.5°	200.7	201.3	201.8	202.0	202.7	203.7	204.2	205.4	207.7	209.4	209.5
170°	202.8	203.4	203.9	204.0	204.1	204.2	204.2	205.4	207.7	209.4	209.4
172.5°	203.9	204.0	204.2	204.2	204.2	204.2	204.2	205.1	206.9	208.3	208.2
175°	205.5	205.5	205.5	205.5	205.0	204.5	204.2	204.7	205.9	206.8	206.8
177.5°	205.5	205.5	205.5	205.5	205.1	204.6	204.5	204.9	205.8	206.6	206.5
180°	205.5	205.5	205.5	205.5	205.5	205.5	205.5	205.5	205.5	205.5	205.5



TEST NUMBER: P936364

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	428.1	428.1
2.5°	457.0	454.3
5°	587.8	590.5
7.5°	791.5	790.1
10°	984.2	996.6
12.5°	1124.7	1127.5
15°	1210.1	1215.6
17.5°	1243.1	1244.5
20°	1244.5	1241.7
22.5°	1229.3	1226.6
25°	1211.4	1210.1
27.5°	1194.9	1196.3
30°	1188.0	1192.2
32.5°	1188.0	1194.9
35°	1190.8	1197.7
37.5°	1189.4	1197.7
40°	1183.9	1193.6
42.5°	1168.8	1175.7
45°	1145.4	1153.6
47.5°	1115.1	1120.6
50°	1076.5	1082.1
52.5°	1028.3	1029.7
55°	970.5	976.0
57.5°	908.5	909.9
60°	839.7	843.8
62.5°	766.7	766.7
65°	689.6	692.4
67.5°	609.8	616.7
70°	528.6	530.0
72.5°	448.8	448.8
75°	366.2	367.5
77.5°	287.7	287.7
80°	213.4	214.7
82.5°	147.3	150.0
85°	92.2	92.2
87.5°	42.7	38.5
90°	5.2	5.2
92.5°	20.9	16.8
95°	73.1	60.6
97.5°	175.3	151.2
100°	252.5	223.9
102.5°	328.5	304.0
105°	425.4	412.2
107.5°	488.9	492.1
110°	513.1	526.8





TEST NUMBER: P936364  
CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	515.2	536.3
115°	501.5	530.8
117.5°	472.6	505.0
120°	449.3	480.8
122.5°	426.5	457.6
125°	394.1	422.7
127.5°	365.0	389.1
130°	347.7	370.0
132.5°	332.1	352.1
135°	310.7	328.0
137.5°	293.7	307.7
140°	281.8	295.0
142.5°	272.1	283.5
145°	257.5	266.1
147.5°	246.3	253.4
150°	239.2	245.0
152.5°	233.2	237.6
155°	226.2	229.1
157.5°	220.8	222.8
160°	217.5	218.7
162.5°	215.4	216.5
165°	212.3	213.5
167.5°	210.1	210.5
170°	209.4	209.4
172.5°	207.8	207.4
175°	206.8	206.8
177.5°	205.9	205.5
180°	205.5	205.5



TEST NUMBER: P936364

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-6-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.12	7.28	6.86	8.05	8.97	19.29	20.44	20.03	21.21	22.14
	3H	6.85	7.89	7.60	8.67	9.63	21.15	22.19	21.90	22.97	23.92
	4H	7.16	8.15	7.93	8.94	9.90	21.80	22.78	22.57	23.57	24.54
	6H	7.43	8.34	8.21	9.14	10.12	22.24	23.15	23.03	23.95	24.93
	8H	7.51	8.37	8.30	9.19	10.18	22.37	23.24	23.16	24.05	25.04
	12H	7.53	8.36	8.34	9.17	10.19	22.44	23.27	23.25	24.08	25.10
4H	2H	13.37	14.35	14.14	15.14	16.11	19.60	20.58	20.37	21.37	22.34
	3H	14.96	15.79	15.75	16.61	17.60	21.67	22.49	22.45	23.31	24.30
	4H	15.07	15.82	15.87	16.64	17.66	22.44	23.20	23.25	24.02	25.03
	6H	15.10	15.75	15.92	16.60	17.62	22.99	23.65	23.82	24.50	25.51
	8H	15.08	15.69	15.91	16.54	17.57	23.16	23.77	23.99	24.62	25.65
	12H	15.05	15.61	15.90	16.47	17.51	23.27	23.82	24.11	24.68	25.72
8H	4H	16.54	17.15	17.36	17.99	19.02	22.53	23.14	23.35	23.98	25.01
	6H	16.79	17.30	17.64	18.18	19.22	23.17	23.68	24.02	24.56	25.59
	8H	16.81	17.27	17.68	18.15	19.19	23.39	23.84	24.25	24.72	25.77
	12H	16.80	17.20	17.66	18.07	19.17	23.54	23.94	24.41	24.81	25.92
12H	4H	16.69	17.25	17.54	18.11	19.15	22.50	23.05	23.34	23.91	24.95
	6H	17.05	17.51	17.92	18.39	19.43	23.15	23.61	24.02	24.49	25.54
	8H	17.14	17.54	18.00	18.41	19.51	23.40	23.80	24.26	24.67	25.77