

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936359

Luminaire Tested: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936359
REPORT IS A COMBINATION OF REPORTS P933438 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3053.9 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 30
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936359
CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2612	2612	2612
5°	2549	3017	3511
10°	2310	4395	5821
15°	1961	5737	7029
20°	1594	6643	7164
25°	1328	6946	7017
30°	1119	6986	7005
35°	987	6864	7186
40°	859	6708	7373
45°	776	6591	7401
50°	711	6486	7280
55°	678	6333	6957
60°	692	6047	6447
65°	717	5616	5747
70°	759	4888	4855
75°	830	3974	3789
80°	889	2746	2553
85°	754	1449	1306

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7401 cd/sqm



TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.4	1.2
10°-20°	161.4	5.3
20°-30°	282.3	9.2
30°-40°	363.4	11.9
40°-50°	405.9	13.3
50°-60°	388.8	12.7
60°-70°	308.1	10.1
70°-80°	181.2	5.9
80°-90°	50.8	1.7
90°-100°	65.8	2.2
100°-110°	173.1	5.7
110°-120°	179.5	5.9
120°-130°	144.0	4.7
130°-140°	113.0	3.7
140°-150°	86.7	2.8
150°-160°	62.4	2.0
160°-170°	38.2	1.3
170°-180°	12.9	0.4
0°-30°	480.1	15.7
0°-40°	843.5	27.6
0°-60°	1638.1	53.6
0°-90°	2178.3	71.3
90°-120°	418.5	13.7
90°-150°	762.1	25.0
90°-180°	876.0	28.7
0°-180°	3053.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	282	282	282	282	282	
5°	274	294	331	375	388	25
15°	206	379	639	775	799	57
25°	131	430	761	795	796	60
35°	89	411	717	758	788	55
45°	61	328	634	726	758	47
55°	43	208	538	625	642	40
65°	34	110	399	449	455	34
75°	25	68	219	241	242	27
85°	9	21	54	60	61	10
90°	1	2	7	3	3	1
95°	9	34	113	58	40	10
105°	31	47	191	291	271	33
115°	55	67	153	306	349	55
125°	77	86	139	236	278	68
135°	92	101	135	190	216	71
145°	106	113	133	162	175	67
155°	120	124	133	146	151	55
165°	130	132	133	139	140	37
175°	135	135	134	136	136	13
180°	135	135	135	135	135	



TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	281.5	281.5	281.5	281.5	281.5	281.5	281.5	281.5	281.5	281.5	281.5
2.5°	281.5	281.5	283.3	284.2	286.0	286.9	288.7	290.6	296.0	296.9	298.7
5°	274.3	277.9	289.7	294.2	306.8	324.0	331.3	343.1	367.5	374.7	379.3
7.5°	263.4	271.5	300.5	307.8	339.4	384.7	403.7	429.0	468.0	487.0	502.4
10°	246.2	263.4	315.0	332.2	383.8	452.6	487.9	523.2	582.0	608.3	618.2
12.5°	227.2	255.3	330.4	353.9	428.1	528.6	571.2	610.1	677.1	712.4	717.8
15°	205.5	243.5	344.9	379.3	475.2	592.0	639.0	687.0	749.5	774.8	781.2
17.5°	186.5	234.4	358.4	394.7	511.4	649.0	697.0	736.8	787.5	804.7	809.2
20°	162.9	220.0	367.5	414.6	549.4	690.6	736.8	767.6	802.0	812.8	814.6
22.5°	145.7	204.6	372.9	421.8	574.8	716.0	754.9	779.3	802.9	806.5	807.4
25°	131.2	187.4	372.0	430.0	596.5	731.4	761.2	779.3	792.9	794.7	794.7
27.5°	117.7	168.4	368.4	431.8	612.8	735.0	758.5	771.2	777.5	781.2	781.2
30°	105.9	150.3	359.3	428.1	620.0	731.4	750.4	756.7	763.1	768.5	771.2
32.5°	96.9	133.1	345.8	420.9	620.9	722.3	735.9	739.5	748.6	761.2	765.8
35°	88.7	115.9	330.4	410.9	615.5	707.8	716.9	720.5	738.6	757.6	764.0
37.5°	80.6	103.2	310.5	393.7	607.4	690.6	697.0	703.3	731.4	754.0	761.2
40°	72.4	92.3	286.9	374.7	594.7	669.8	675.3	685.2	722.3	748.6	755.8
42.5°	66.1	83.3	261.6	354.8	578.4	646.3	654.4	668.9	711.5	739.5	747.7
45°	60.6	74.2	234.4	327.7	557.6	621.8	633.6	653.5	698.8	725.9	733.2
47.5°	55.2	67.9	206.4	299.6	535.0	597.4	612.8	635.4	681.6	707.8	714.2
50°	50.7	61.6	178.3	269.7	510.5	571.2	589.3	612.8	659.9	684.3	692.4
52.5°	47.1	56.1	152.1	239.9	482.5	544.0	564.8	589.3	633.6	657.1	662.6
55°	43.4	51.6	129.4	208.2	453.5	515.0	537.7	561.2	604.6	624.6	628.2
57.5°	41.6	48.0	110.4	178.3	422.7	482.5	507.8	529.5	570.3	585.6	589.3
60°	38.9	45.3	95.9	153.0	389.2	451.7	473.4	495.1	529.5	542.2	544.9
62.5°	36.2	43.4	85.1	128.5	354.8	415.5	437.2	457.1	486.1	495.1	498.7
65°	34.4	41.6	76.9	110.4	319.5	377.5	399.2	416.4	439.9	449.0	450.8
67.5°	32.6	39.8	70.6	95.0	284.2	339.4	355.7	372.0	390.1	399.2	400.1
70°	29.9	38.0	65.2	84.2	248.0	296.0	309.6	326.8	341.2	345.8	348.5
72.5°	28.1	35.3	61.6	76.0	210.9	254.4	267.0	277.0	289.7	294.2	294.2
75°	25.3	31.7	57.9	67.9	172.9	208.2	219.0	229.0	239.0	240.8	238.1
77.5°	22.6	28.1	49.8	57.0	134.9	164.7	173.8	179.2	187.4	189.2	190.1
80°	19.0	24.4	38.9	44.4	97.8	121.3	127.6	132.2	139.4	139.4	141.2
82.5°	14.5	19.0	28.1	31.7	66.1	83.3	88.7	91.4	95.9	95.9	95.9
85°	9.1	11.8	18.1	20.8	39.8	50.7	54.3	55.2	58.8	59.7	59.7
87.5°	4.5	6.3	11.8	12.7	20.8	26.2	26.2	28.1	28.1	27.2	26.2
90°	0.9	1.6	2.4	2.5	4.0	5.9	6.9	6.2	4.6	3.4	3.4
92.5°	3.6	9.8	15.9	17.5	24.6	34.1	38.8	34.0	24.4	17.2	16.5
95°	8.7	20.0	31.3	34.1	60.6	95.8	113.4	101.2	76.8	58.5	56.4
97.5°	15.0	25.0	34.9	37.5	81.6	140.3	169.7	162.0	146.5	135.0	131.0
100°	19.9	29.0	38.0	40.3	89.2	154.4	187.0	187.5	188.7	189.5	184.8
102.5°	24.1	32.5	41.0	43.1	92.7	158.9	191.9	201.8	221.4	236.2	232.1
105°	31.2	38.4	45.4	47.2	95.3	159.3	191.4	213.4	257.5	290.6	288.4
107.5°	38.5	45.1	51.8	53.4	95.8	152.2	180.5	211.3	272.7	318.9	319.4
110°	43.4	49.3	55.3	56.8	95.0	146.0	171.4	205.8	274.5	326.1	328.4



TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	48.2	53.9	59.6	61.0	95.0	140.5	163.2	198.4	268.7	321.5	325.0
115°	55.4	60.6	65.9	67.3	95.9	134.2	153.3	187.2	255.0	305.8	310.6
117.5°	62.5	67.3	72.1	73.3	97.8	130.3	146.5	177.1	238.2	284.1	289.5
120°	66.7	71.2	75.8	76.8	99.1	128.9	143.7	171.7	227.6	269.6	274.7
122.5°	70.8	75.3	79.8	81.0	101.2	128.2	141.7	166.8	217.1	254.9	260.0
125°	77.0	81.2	85.4	86.4	104.1	127.6	139.4	160.8	203.6	235.6	240.3
127.5°	82.1	86.4	90.5	91.6	106.9	127.3	137.5	155.9	192.6	220.1	224.1
130°	84.8	89.3	93.9	95.0	109.0	127.5	136.8	153.2	185.8	210.4	214.0
132.5°	87.7	92.2	96.8	97.8	110.6	127.6	136.1	150.8	180.0	202.0	205.3
135°	91.9	95.9	100.1	101.1	112.4	127.5	135.1	147.3	171.8	190.2	193.0
137.5°	96.1	100.2	104.3	105.3	115.1	128.3	134.9	145.2	165.9	181.5	183.8
140°	99.7	103.4	107.2	108.1	116.8	128.4	134.2	143.2	161.1	174.5	176.7
142.5°	102.4	105.8	109.3	110.2	118.2	128.9	134.2	142.1	157.9	169.6	171.5
145°	106.5	109.5	112.6	113.3	120.0	128.9	133.3	139.8	152.6	162.3	163.7
147.5°	110.7	113.6	116.6	117.3	122.6	129.8	133.3	138.4	148.5	156.1	157.3
150°	113.4	116.0	118.8	119.4	124.0	130.3	133.3	137.6	146.2	152.6	153.5
152.5°	116.2	118.2	120.2	120.7	124.9	130.5	133.3	137.0	144.3	149.8	150.5
155°	120.4	121.8	123.4	123.7	126.9	131.2	133.3	136.2	142.1	146.5	146.9
157.5°	123.5	124.9	126.4	126.7	128.9	131.9	133.3	135.6	140.1	143.5	143.8
160°	125.5	126.6	127.8	128.1	129.8	132.2	133.3	135.2	139.1	142.0	142.2
162.5°	127.6	128.4	129.3	129.5	130.8	132.5	133.3	135.0	138.2	140.7	140.8
165°	129.9	130.6	131.4	131.6	132.2	133.0	133.3	134.5	136.9	138.6	138.8
167.5°	132.0	132.3	132.7	132.8	133.2	133.9	134.2	135.0	136.5	137.7	137.8
170°	133.3	133.7	134.1	134.1	134.1	134.2	134.2	135.0	136.5	137.7	137.7
172.5°	134.1	134.1	134.2	134.2	134.2	134.2	134.2	134.9	136.0	137.0	136.9
175°	135.1	135.1	135.1	135.1	134.8	134.4	134.2	134.6	135.4	136.0	136.0
177.5°	135.1	135.1	135.1	135.1	134.9	134.6	134.4	134.7	135.3	135.8	135.7
180°	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1	135.1



TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	281.5	281.5
2.5°	300.5	298.7
5°	386.5	388.3
7.5°	520.5	519.6
10°	647.2	655.3
12.5°	739.5	741.3
15°	795.6	799.3
17.5°	817.4	818.3
20°	818.3	816.5
22.5°	808.3	806.5
25°	796.5	795.6
27.5°	785.7	786.6
30°	781.2	783.9
32.5°	781.2	785.7
35°	783.0	787.5
37.5°	782.1	787.5
40°	778.4	784.8
42.5°	768.5	773.0
45°	753.1	758.5
47.5°	733.2	736.8
50°	707.8	711.5
52.5°	676.2	677.1
55°	638.1	641.8
57.5°	597.4	598.3
60°	552.1	554.9
62.5°	504.2	504.2
65°	453.5	455.3
67.5°	401.0	405.5
70°	347.6	348.5
72.5°	295.1	295.1
75°	240.8	241.7
77.5°	189.2	189.2
80°	140.3	141.2
82.5°	96.9	98.7
85°	60.6	60.6
87.5°	28.1	25.3
90°	3.4	3.4
92.5°	13.8	11.0
95°	48.2	39.8
97.5°	115.2	99.5
100°	166.1	147.3
102.5°	216.0	199.9
105°	279.8	271.1
107.5°	321.5	323.6
110°	337.4	346.4



TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	338.8	352.7
115°	329.8	349.0
117.5°	310.7	332.1
120°	295.4	316.1
122.5°	280.4	300.9
125°	259.1	278.0
127.5°	240.0	255.8
130°	228.6	243.3
132.5°	218.4	231.5
135°	204.4	215.7
137.5°	193.1	202.4
140°	185.3	194.0
142.5°	179.0	186.4
145°	169.4	175.0
147.5°	161.9	166.6
150°	157.3	161.1
152.5°	153.3	156.2
155°	148.8	150.7
157.5°	145.2	146.5
160°	143.0	143.7
162.5°	141.6	142.3
165°	139.6	140.3
167.5°	138.0	138.4
170°	137.7	137.7
172.5°	136.6	136.3
175°	136.0	136.0
177.5°	135.4	135.1
180°	135.1	135.1



TEST NUMBER: P936359

CATALOG NUMBER: SQ4-FB-025U-075D-93050-1D-UNV-STD-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.07	7.22	6.81	7.99	8.92	19.21	20.36	19.95	21.13	22.06
	3H	6.79	7.83	7.55	8.61	9.57	21.05	22.09	21.81	22.87	23.83
	4H	7.11	8.09	7.88	8.88	9.85	21.70	22.68	22.47	23.47	24.44
	6H	7.37	8.28	8.16	9.08	10.06	22.13	23.04	22.92	23.84	24.82
	8H	7.45	8.32	8.24	9.13	10.12	22.26	23.13	23.05	23.94	24.93
	12H	7.48	8.31	8.28	9.12	10.13	22.33	23.16	23.13	23.97	24.98
4H	2H	13.29	14.28	14.07	15.07	16.03	19.52	20.50	20.29	21.29	22.26
	3H	14.89	15.72	15.68	16.54	17.52	21.57	22.40	22.36	23.22	24.21
	4H	15.00	15.75	15.80	16.57	17.59	22.34	23.10	23.15	23.92	24.93
	6H	15.03	15.68	15.85	16.53	17.54	22.89	23.54	23.71	24.39	25.41
	8H	15.01	15.62	15.83	16.46	17.50	23.05	23.66	23.87	24.50	25.54
	12H	14.98	15.53	15.83	16.40	17.44	23.15	23.70	24.00	24.57	25.60
8H	4H	16.46	17.07	17.28	17.91	18.94	22.43	23.04	23.25	23.88	24.92
	6H	16.71	17.22	17.57	18.11	19.14	23.06	23.57	23.91	24.45	25.49
	8H	16.74	17.19	17.60	18.07	19.12	23.28	23.73	24.14	24.61	25.66
	12H	16.72	17.12	17.59	17.99	19.09	23.43	23.83	24.30	24.70	25.80
12H	4H	16.61	17.16	17.46	18.03	19.07	22.40	22.95	23.24	23.81	24.85
	6H	16.97	17.43	17.84	18.30	19.35	23.05	23.50	23.91	24.38	25.43
	8H	17.06	17.46	17.92	18.33	19.43	23.28	23.68	24.15	24.55	25.66