

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936465

Luminaire Tested: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936465
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7284.7 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936465
CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P936465

CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63			63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51			51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42			42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35			35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30			30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26			26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22			22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20			20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20	17			17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16			16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3349	3349	3349
5°	3272	3871	4502
10°	2968	5643	7463
15°	2522	7372	9012
20°	2053	8543	9184
25°	1713	8940	8998
30°	1445	8996	8981
35°	1277	8847	9213
40°	1113	8653	9453
45°	1008	8511	9490
50°	925	8382	9333
55°	885	8195	8919
60°	906	7835	8266
65°	943	7288	7368
70°	1005	6356	6225
75°	1113	5182	4858
80°	1215	3594	3273
85°	1081	1907	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9490 cd/sqm



TEST NUMBER: P936465

CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.4	1.3
10°-20°	413.8	5.7
20°-30°	723.9	9.9
30°-40°	931.8	12.8
40°-50°	1040.8	14.3
50°-60°	996.9	13.7
60°-70°	790.0	10.8
70°-80°	464.6	6.4
80°-90°	130.1	1.8
90°-100°	127.8	1.8
100°-110°	336.0	4.6
110°-120°	348.3	4.8
120°-130°	279.4	3.8
130°-140°	219.2	3.0
140°-150°	168.3	2.3
150°-160°	121.2	1.7
160°-170°	74.2	1.0
170°-180°	25.1	0.3
0°-30°	1231.1	16.9
0°-40°	2162.9	29.7
0°-60°	4200.6	57.7
0°-90°	5585.2	76.7
90°-120°	812.1	11.1
90°-150°	1479.0	20.3
90°-180°	1699.0	23.3
0°-180°	7284.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	722	722	722	722	722	
5°	703	754	850	961	996	65
15°	527	972	1639	1987	2050	147
25°	337	1102	1952	2038	2040	155
35°	228	1054	1838	1943	2019	142
45°	156	840	1625	1862	1945	120
55°	111	534	1379	1602	1646	102
65°	88	283	1024	1151	1168	87
75°	65	174	562	617	620	68
85°	23	53	139	153	156	25
90°	2	5	13	7	7	3
95°	17	66	220	114	77	19
105°	60	92	371	564	526	64
115°	108	130	298	594	677	106
125°	150	168	271	457	540	133
135°	178	196	262	369	418	138
145°	207	220	259	315	340	130
155°	234	240	259	284	292	107
165°	252	256	259	269	272	71
175°	262	262	261	264	264	25
180°	262	262	262	262	262	



TEST NUMBER: P936465

CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	721.9	721.9	721.9	721.9	721.9	721.9	721.9	721.9	721.9	721.9	721.9
2.5°	721.9	721.9	726.5	728.8	733.5	735.8	740.4	745.1	759.0	761.3	766.0
5°	703.3	712.6	742.8	754.4	786.9	831.0	849.5	879.7	942.3	960.9	972.5
7.5°	675.4	696.3	770.6	789.2	870.4	986.4	1035.2	1100.2	1200.0	1248.8	1288.2
10°	631.3	675.4	807.8	851.9	984.1	1160.5	1251.1	1341.6	1492.4	1559.8	1585.2
12.5°	582.6	654.5	847.2	907.5	1097.9	1355.5	1464.6	1564.4	1736.1	1826.7	1840.6
15°	526.9	624.4	884.4	972.5	1218.6	1518.0	1638.6	1761.7	1921.8	1986.8	2003.1
17.5°	478.1	601.2	919.1	1012.0	1311.4	1664.2	1787.3	1889.3	2019.3	2063.4	2075.1
20°	417.8	564.0	942.3	1063.0	1408.9	1771.0	1889.3	1968.3	2056.5	2084.3	2089.0
22.5°	373.7	524.5	956.3	1081.6	1473.9	1836.0	1935.8	1998.4	2058.8	2068.0	2070.4
25°	336.6	480.4	953.9	1102.5	1529.6	1875.4	1952.0	1998.4	2033.3	2037.9	2037.9
27.5°	301.7	431.7	944.7	1107.2	1571.4	1884.7	1945.1	1977.6	1993.8	2003.1	2003.1
30°	271.6	385.3	921.4	1097.9	1589.9	1875.4	1924.2	1940.4	1956.7	1970.6	1977.6
32.5°	248.4	341.2	886.6	1079.3	1592.3	1852.2	1887.0	1896.3	1919.5	1952.0	1963.6
35°	227.5	297.1	847.2	1053.8	1578.3	1815.1	1838.3	1847.6	1894.0	1942.7	1959.0
37.5°	206.6	264.6	796.1	1009.7	1557.4	1771.0	1787.3	1803.5	1875.4	1933.4	1952.0
40°	185.7	236.8	735.8	960.9	1524.9	1717.6	1731.5	1757.0	1852.2	1919.5	1938.1
42.5°	169.4	213.5	670.8	909.8	1483.2	1657.3	1678.2	1715.2	1824.3	1896.3	1917.2
45°	155.5	190.3	601.2	840.2	1429.8	1594.6	1624.8	1675.8	1791.8	1861.5	1880.1
47.5°	141.6	174.1	529.2	768.2	1371.7	1531.9	1571.4	1629.4	1747.7	1815.1	1831.3
50°	130.0	157.8	457.2	691.7	1309.1	1464.6	1511.0	1571.4	1692.0	1754.8	1775.6
52.5°	120.7	143.9	390.0	615.1	1237.1	1394.9	1448.3	1511.0	1624.8	1685.1	1699.0
55°	111.4	132.3	331.9	533.8	1162.9	1320.7	1378.7	1439.1	1550.5	1601.5	1610.8
57.5°	106.8	123.0	283.2	457.2	1083.9	1237.1	1302.1	1357.9	1462.3	1501.7	1511.0
60°	99.8	116.0	246.0	392.2	998.1	1158.2	1213.9	1269.6	1357.9	1390.4	1397.3
62.5°	92.8	111.4	218.2	329.6	909.8	1065.4	1121.1	1172.2	1246.4	1269.6	1278.9
65°	88.2	106.8	197.3	283.2	819.4	967.9	1023.6	1067.7	1128.0	1151.3	1155.9
67.5°	83.5	102.1	181.0	243.7	728.8	870.4	912.2	953.9	1000.4	1023.6	1025.9
70°	76.6	97.5	167.1	215.9	636.0	759.0	793.8	837.9	875.1	886.6	893.6
72.5°	71.9	90.6	157.8	195.0	540.8	652.2	684.7	710.3	742.8	754.4	754.4
75°	65.0	81.2	148.5	174.1	443.4	533.8	561.7	587.2	612.8	617.4	610.4
77.5°	58.1	71.9	127.6	146.2	345.9	422.5	445.6	459.5	480.4	485.1	487.5
80°	48.7	62.7	99.8	113.7	250.7	311.0	327.3	338.8	357.5	357.5	362.1
82.5°	37.2	48.7	71.9	81.2	169.4	213.5	227.5	234.4	246.0	246.0	246.0
85°	23.2	30.2	46.5	53.4	102.1	130.0	139.3	141.6	150.9	153.2	153.2
87.5°	11.6	16.2	30.2	32.5	53.4	67.3	67.3	71.9	71.9	69.6	67.3
90°	1.8	3.2	4.6	4.9	7.7	11.5	13.4	11.9	8.9	6.7	6.7
92.5°	7.0	19.0	31.0	34.0	47.8	66.1	75.3	66.0	47.4	33.5	32.1
95°	16.9	38.7	60.7	66.1	117.4	185.8	220.1	196.4	149.0	113.5	109.4
97.5°	29.2	48.6	67.8	72.6	158.2	272.3	329.4	314.4	284.5	262.0	254.4
100°	38.7	56.2	73.7	78.1	173.0	299.6	362.9	364.1	366.3	367.9	358.8
102.5°	46.8	63.1	79.5	83.5	179.9	308.3	372.5	391.5	429.7	458.3	450.5
105°	60.5	74.4	88.3	91.7	185.0	309.2	371.4	414.2	499.8	563.9	559.7
107.5°	74.6	87.5	100.4	103.6	185.8	295.5	350.3	409.9	529.3	618.8	619.8
110°	84.1	95.7	107.4	110.3	184.4	283.3	332.7	399.4	532.8	632.8	637.2



TEST NUMBER: P936465

CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	93.5	104.5	115.6	118.4	184.5	272.6	316.7	385.0	521.4	623.9	630.6
115°	107.5	117.7	128.0	130.5	186.2	260.4	297.5	363.3	494.8	593.5	602.8
117.5°	121.4	130.7	140.0	142.4	189.7	252.8	284.3	343.7	462.3	551.4	561.8
120°	129.5	138.2	147.0	149.2	192.5	250.2	279.0	333.2	441.7	523.0	533.0
122.5°	137.4	146.2	155.1	157.3	196.6	248.8	275.0	323.8	421.5	494.7	504.7
125°	149.6	157.7	165.6	167.7	202.0	247.8	270.6	312.1	395.1	457.2	466.4
127.5°	159.4	167.5	175.7	177.7	207.5	247.1	266.9	302.6	373.8	427.2	434.9
130°	164.7	173.5	182.2	184.4	211.4	247.5	265.5	297.2	360.6	408.1	415.3
132.5°	170.1	178.9	187.6	189.8	214.7	247.8	264.3	292.6	349.4	392.0	398.4
135°	178.2	186.2	194.2	196.2	218.2	247.5	262.2	286.0	333.5	369.1	374.6
137.5°	186.5	194.4	202.3	204.3	223.4	249.0	261.8	281.9	322.1	352.2	356.7
140°	193.3	200.6	207.9	209.7	226.7	249.3	260.6	278.0	312.7	338.7	342.9
142.5°	198.7	205.3	212.1	213.8	229.4	250.2	260.6	275.9	306.4	329.2	332.8
145°	206.8	212.6	218.4	219.9	232.9	250.2	258.8	271.3	296.3	315.0	317.7
147.5°	214.8	220.5	226.3	227.7	238.0	251.9	258.8	268.7	288.3	302.9	305.2
150°	220.1	225.3	230.4	231.7	240.7	252.8	258.8	267.1	283.7	296.1	297.9
152.5°	225.5	229.4	233.4	234.3	242.5	253.4	258.8	265.9	280.0	290.6	292.0
155°	233.6	236.5	239.4	240.1	246.4	254.7	258.8	264.5	275.7	284.1	285.0
157.5°	239.6	242.4	245.2	245.9	250.2	255.9	258.8	263.2	271.9	278.5	279.1
160°	243.6	245.8	248.0	248.6	252.0	256.6	258.8	262.6	270.1	275.7	276.1
162.5°	247.7	249.3	250.9	251.4	253.8	257.2	258.8	262.0	268.3	273.1	273.4
165°	252.2	253.7	255.1	255.5	256.6	258.1	258.8	261.1	265.6	269.0	269.4
167.5°	256.2	256.9	257.6	257.8	258.7	260.0	260.6	262.1	265.1	267.3	267.4
170°	258.8	259.5	260.2	260.4	260.5	260.6	260.6	262.1	265.1	267.3	267.3
172.5°	260.2	260.4	260.6	260.6	260.6	260.6	260.6	261.7	264.1	265.9	265.7
175°	262.2	262.2	262.2	262.2	261.6	260.9	260.6	261.3	262.8	263.9	263.9
177.5°	262.2	262.2	262.2	262.2	261.7	261.2	260.9	261.6	262.7	263.6	263.4
180°	262.2	262.2	262.2	262.2	262.2	262.2	262.2	262.2	262.2	262.2	262.2



TEST NUMBER: P936465

CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	721.9	721.9
2.5°	770.6	766.0
5°	991.1	995.7
7.5°	1334.6	1332.3
10°	1659.5	1680.5
12.5°	1896.3	1901.0
15°	2040.2	2049.5
17.5°	2095.9	2098.3
20°	2098.3	2093.6
22.5°	2072.7	2068.0
25°	2042.6	2040.2
27.5°	2014.6	2017.0
30°	2003.1	2010.1
32.5°	2003.1	2014.6
35°	2007.7	2019.3
37.5°	2005.4	2019.3
40°	1996.1	2012.4
42.5°	1970.6	1982.1
45°	1931.1	1945.1
47.5°	1880.1	1889.3
50°	1815.1	1824.3
52.5°	1733.9	1736.1
55°	1636.4	1645.7
57.5°	1531.9	1534.2
60°	1415.8	1422.8
62.5°	1292.9	1292.9
65°	1162.9	1167.5
67.5°	1028.2	1039.8
70°	891.3	893.6
72.5°	756.7	756.7
75°	617.4	619.7
77.5°	485.1	485.1
80°	359.8	362.1
82.5°	248.4	253.0
85°	155.5	155.5
87.5°	71.9	65.0
90°	6.7	6.7
92.5°	26.8	21.4
95°	93.4	77.2
97.5°	223.6	193.0
100°	322.2	285.7
102.5°	419.2	387.9
105°	542.9	526.0
107.5°	623.9	627.9
110°	654.7	672.3



TEST NUMBER: P936465
CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	657.5	684.4
115°	640.1	677.3
117.5°	603.1	644.5
120°	573.3	613.5
122.5°	544.3	583.9
125°	502.9	539.5
127.5°	465.7	496.5
130°	443.7	472.2
132.5°	423.9	449.3
135°	396.6	418.5
137.5°	374.7	392.7
140°	359.7	376.5
142.5°	347.3	361.7
145°	328.7	339.6
147.5°	314.3	323.4
150°	305.3	312.7
152.5°	297.6	303.1
155°	288.7	292.4
157.5°	281.8	284.3
160°	277.5	279.0
162.5°	274.8	276.2
165°	270.9	272.4
167.5°	268.1	268.7
170°	267.3	267.3
172.5°	265.2	264.6
175°	263.9	263.9
177.5°	262.8	262.2
180°	262.2	262.2



TEST NUMBER: P936465
 CATALOG NUMBER: SQ4-FB-025U-100D-93050-1D-UNV-STD-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.34	8.57	8.02	9.28	10.10	20.51	21.75	21.19	22.45	23.28
	3H	8.07	9.18	8.76	9.90	10.76	22.38	23.49	23.07	24.21	25.07
	4H	8.38	9.44	9.10	10.16	11.03	23.04	24.10	23.75	24.82	25.69
	6H	8.65	9.63	9.38	10.36	11.25	23.49	24.47	24.22	25.20	26.09
	8H	8.73	9.66	9.47	10.42	11.31	23.62	24.55	24.36	25.31	26.20
	12H	8.76	9.65	9.51	10.40	11.32	23.70	24.59	24.45	25.34	26.26
4H	2H	14.59	15.65	15.31	16.37	17.25	20.83	21.89	21.55	22.61	23.48
	3H	16.19	17.08	16.92	17.84	18.73	22.91	23.80	23.64	24.56	25.45
	4H	16.31	17.11	17.05	17.88	18.80	23.69	24.50	24.44	25.26	26.18
	6H	16.34	17.04	17.10	17.83	18.76	24.26	24.96	25.02	25.75	26.67
	8H	16.33	16.98	17.09	17.77	18.71	24.43	25.08	25.20	25.87	26.81
	12H	16.30	16.89	17.09	17.70	18.65	24.54	25.13	25.33	25.94	26.89
8H	4H	17.78	18.44	18.55	19.22	20.16	23.79	24.44	24.55	25.23	26.17
	6H	18.04	18.59	18.84	19.41	20.36	24.43	24.98	25.23	25.81	26.75
	8H	18.07	18.55	18.88	19.38	20.34	24.66	25.15	25.47	25.97	26.93
	12H	18.05	18.48	18.87	19.30	20.31	24.82	25.25	25.63	26.07	27.08
12H	4H	17.94	18.54	18.73	19.34	20.29	23.76	24.35	24.55	25.16	26.10
	6H	18.31	18.79	19.12	19.62	20.58	24.42	24.91	25.23	25.73	26.69
	8H	18.39	18.82	19.21	19.64	20.65	24.67	25.10	25.48	25.92	26.93