

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936556

Luminaire Tested: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936556
REPORT IS A COMBINATION OF REPORTS P933432 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13873.7 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 148.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936556
CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P936556

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4482	4482	4482
5°	4380	5181	6024
10°	3974	7554	9987
15°	3379	9872	12059
20°	2752	11443	12290
25°	2296	11977	12040
30°	1938	12056	12017
35°	1714	11859	12328
40°	1494	11602	12649
45°	1354	11415	12699
50°	1243	11247	12489
55°	1192	11000	11935
60°	1221	10522	11061
65°	1273	9792	9860
70°	1359	8546	8329
75°	1511	6974	6500
80°	1663	4843	4380
85°	1510	2574	2242

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12699 cd/sqm



TEST NUMBER: P936556

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.4	1.4
10°-20°	830.7	6.0
20°-30°	1453.0	10.5
30°-40°	1870.4	13.5
40°-50°	2089.2	15.1
50°-60°	2000.9	14.4
60°-70°	1585.7	11.4
70°-80°	932.5	6.7
80°-90°	260.6	1.9
90°-100°	200.3	1.4
100°-110°	526.5	3.8
110°-120°	546.0	3.9
120°-130°	437.9	3.2
130°-140°	343.6	2.5
140°-150°	263.7	1.9
150°-160°	189.9	1.4
160°-170°	116.2	0.8
170°-180°	39.3	0.3
0°-30°	2471.0	17.8
0°-40°	4341.4	31.3
0°-60°	8431.5	60.8
0°-90°	11210.3	80.8
90°-120°	1272.7	9.2
90°-150°	2318.0	16.7
90°-180°	2663.0	19.2
0°-180°	13873.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1449	1449	1449	1449	1449	
5°	1412	1514	1705	1929	1999	130
15°	1058	1952	3289	3988	4114	294
25°	676	2213	3918	4090	4095	311
35°	457	2115	3690	3900	4053	285
45°	312	1686	3261	3736	3904	241
55°	224	1072	2767	3215	3303	204
65°	177	568	2054	2311	2343	175
75°	130	350	1128	1239	1244	137
85°	47	107	280	308	312	49
90°	3	8	21	10	10	5
95°	26	104	345	178	121	29
105°	95	144	582	884	824	101
115°	168	205	466	930	1062	166
125°	234	263	424	717	845	208
135°	279	307	411	578	656	216
145°	324	345	406	494	532	203
155°	366	376	406	445	458	168
165°	395	400	406	422	427	112
175°	411	411	408	414	414	39
180°	411	411	411	411	411	



TEST NUMBER: P936556

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1448.9	1448.9	1448.9	1448.9	1448.9	1448.9	1448.9	1448.9	1448.9	1448.9	1448.9
2.5°	1448.9	1448.9	1458.2	1462.9	1472.2	1476.8	1486.2	1495.5	1523.5	1528.1	1537.4
5°	1411.6	1430.2	1490.8	1514.1	1579.4	1667.9	1705.2	1765.7	1891.5	1928.8	1952.0
7.5°	1355.7	1397.6	1546.8	1584.0	1747.1	1980.0	2077.8	2208.3	2408.7	2506.5	2585.7
10°	1267.2	1355.7	1621.3	1709.8	1975.3	2329.4	2511.1	2692.8	2995.6	3130.7	3182.0
12.5°	1169.4	1313.8	1700.5	1821.6	2203.7	2720.8	2939.7	3140.1	3484.9	3666.6	3694.5
15°	1057.6	1253.2	1775.0	1952.0	2445.9	3046.9	3289.1	3536.1	3857.5	3988.0	4020.6
17.5°	959.7	1206.7	1844.9	2031.2	2632.2	3340.4	3587.4	3792.3	4053.2	4141.7	4165.1
20°	838.6	1132.1	1891.5	2133.7	2828.0	3554.7	3792.3	3950.7	4127.8	4183.7	4192.9
22.5°	750.0	1052.9	1919.5	2171.0	2958.4	3685.2	3885.5	4011.2	4132.4	4151.0	4155.7
25°	675.5	964.4	1914.8	2212.9	3070.1	3764.4	3918.1	4011.2	4081.2	4090.4	4090.4
27.5°	605.7	866.6	1896.1	2222.3	3154.0	3783.0	3904.1	3969.3	4002.0	4020.6	4020.6
30°	545.1	773.3	1849.5	2203.7	3191.3	3764.4	3862.2	3894.8	3927.5	3955.4	3969.3
32.5°	498.5	684.9	1779.7	2166.4	3196.0	3717.8	3787.7	3806.3	3852.9	3918.1	3941.4
35°	456.6	596.3	1700.5	2115.1	3168.1	3643.2	3689.8	3708.5	3801.6	3899.5	3932.0
37.5°	414.6	531.1	1598.0	2026.6	3126.1	3554.7	3587.4	3619.9	3764.4	3880.8	3918.1
40°	372.7	475.2	1476.8	1928.8	3060.9	3447.6	3475.5	3526.8	3717.8	3852.9	3890.1
42.5°	340.1	428.7	1346.4	1826.3	2977.0	3326.5	3368.4	3442.9	3661.9	3806.3	3848.3
45°	312.1	382.0	1206.7	1686.5	2869.8	3200.6	3261.2	3363.7	3596.6	3736.4	3773.7
47.5°	284.2	349.5	1062.2	1542.1	2753.4	3074.8	3154.0	3270.5	3508.2	3643.2	3675.8
50°	260.9	316.8	917.8	1388.4	2627.6	2939.7	3032.9	3154.0	3396.3	3522.1	3564.1
52.5°	242.3	288.9	782.7	1234.6	2483.2	2800.0	2907.2	3032.9	3261.2	3382.3	3410.2
55°	223.6	265.6	666.2	1071.5	2334.1	2650.9	2767.4	2888.5	3112.1	3214.6	3233.2
57.5°	214.3	247.0	568.4	917.8	2175.7	2483.2	2613.6	2725.5	2935.1	3014.3	3032.9
60°	200.3	232.9	493.8	787.4	2003.3	2324.8	2436.6	2548.4	2725.5	2790.6	2804.7
62.5°	186.4	223.6	437.9	661.6	1826.3	2138.4	2250.2	2352.7	2501.8	2548.4	2567.1
65°	177.0	214.3	396.0	568.4	1644.6	1942.8	2054.5	2143.1	2264.2	2310.8	2320.1
67.5°	167.8	205.0	363.4	489.2	1462.9	1747.1	1830.9	1914.8	2008.0	2054.5	2059.2
70°	153.7	195.7	335.4	433.2	1276.5	1523.5	1593.3	1681.9	1756.4	1779.7	1793.6
72.5°	144.4	181.7	316.8	391.3	1085.5	1309.2	1374.3	1425.6	1490.8	1514.1	1514.1
75°	130.4	163.1	298.2	349.5	889.8	1071.5	1127.5	1178.7	1229.9	1239.3	1225.3
77.5°	116.5	144.4	256.2	293.5	694.1	848.0	894.5	922.5	964.4	973.7	978.4
80°	97.8	125.8	200.3	228.3	503.2	624.3	656.9	680.2	717.5	717.5	726.8
82.5°	74.5	97.8	144.4	163.1	340.1	428.7	456.6	470.5	493.8	493.8	493.8
85°	46.6	60.6	93.1	107.2	205.0	260.9	279.5	284.2	302.8	307.5	307.5
87.5°	23.3	32.6	60.6	65.2	107.2	135.1	135.1	144.4	144.4	139.8	135.1
90°	2.8	5.0	7.2	7.7	12.1	18.0	20.9	18.6	13.9	10.5	10.5
92.5°	11.0	29.7	48.5	53.2	74.8	103.6	118.0	103.4	74.2	52.4	50.3
95°	26.4	60.8	95.1	103.7	184.1	291.4	345.0	307.8	233.6	177.8	171.5
97.5°	45.8	76.1	106.4	113.9	248.0	426.8	516.2	492.7	445.8	410.6	398.6
100°	60.7	88.1	115.5	122.4	271.3	469.7	568.9	570.6	574.0	576.6	562.3
102.5°	73.3	98.9	124.5	131.0	281.9	483.2	583.7	613.7	673.4	718.3	706.0
105°	94.9	116.5	138.2	143.6	289.8	484.6	582.1	649.1	783.2	883.7	877.1
107.5°	116.9	137.1	157.4	162.4	291.3	463.1	549.0	642.5	829.5	969.8	971.4
110°	131.8	150.0	168.3	172.9	289.1	444.0	521.4	626.0	835.0	991.8	998.7



TEST NUMBER: P936556

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	146.5	163.8	181.2	185.6	289.2	427.3	496.4	603.4	817.3	977.8	988.4
115°	168.5	184.5	200.6	204.6	291.8	408.1	466.3	569.3	775.5	930.1	944.7
117.5°	190.2	204.8	219.4	223.1	297.2	396.2	445.6	538.7	724.7	864.2	880.4
120°	202.9	216.7	230.4	233.8	301.6	392.0	437.3	522.3	692.3	819.8	835.6
122.5°	215.4	229.2	243.0	246.5	308.0	389.9	430.9	507.5	660.6	775.4	790.9
125°	234.4	247.0	259.7	262.8	316.6	388.3	424.1	489.0	619.1	716.6	730.9
127.5°	249.8	262.6	275.3	278.5	325.1	387.3	418.3	474.1	585.8	669.5	681.6
130°	258.1	271.8	285.6	289.0	331.4	387.8	416.1	465.8	565.2	639.7	650.9
132.5°	266.7	280.4	294.1	297.5	336.4	388.3	414.2	458.7	547.7	614.4	624.4
135°	279.3	291.8	304.3	307.4	341.9	387.9	410.9	448.1	522.6	578.5	587.1
137.5°	292.3	304.7	317.0	320.1	350.2	390.3	410.3	441.8	504.7	552.0	559.1
140°	303.0	314.4	325.9	328.7	355.2	390.7	408.4	435.5	490.0	530.8	537.4
142.5°	311.3	321.8	332.4	335.1	359.5	392.0	408.4	432.2	480.0	515.9	521.6
145°	324.0	333.2	342.4	344.7	365.0	392.0	405.6	425.2	464.3	493.5	497.8
147.5°	336.7	345.6	354.6	356.8	373.0	394.8	405.6	421.0	451.8	474.8	478.4
150°	345.0	353.0	361.1	363.1	377.3	396.2	405.6	418.7	444.6	464.1	466.9
152.5°	353.5	359.6	365.7	367.3	380.0	397.1	405.6	416.7	438.9	455.5	457.7
155°	366.2	370.7	375.2	376.3	386.1	399.1	405.6	414.4	432.1	445.4	446.8
157.5°	375.5	379.9	384.4	385.5	392.2	401.1	405.6	412.5	426.2	436.5	437.5
160°	381.9	385.3	388.8	389.7	395.0	402.0	405.6	411.5	423.2	432.1	432.6
162.5°	388.3	390.8	393.4	394.1	397.9	403.1	405.6	410.6	420.5	427.9	428.5
165°	395.2	397.5	399.8	400.4	402.1	404.4	405.6	409.2	416.3	421.6	422.1
167.5°	401.5	402.6	403.7	404.0	405.4	407.4	408.4	410.7	415.3	418.8	419.1
170°	405.6	406.7	407.8	408.1	408.2	408.3	408.4	410.7	415.3	418.8	418.8
172.5°	407.8	408.1	408.3	408.4	408.4	408.4	408.4	410.2	413.9	416.6	416.4
175°	410.9	410.9	410.9	410.9	410.0	408.9	408.4	409.6	411.9	413.6	413.6
177.5°	410.9	410.9	410.9	410.9	410.2	409.4	408.9	409.8	411.7	413.1	412.8
180°	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9	410.9



TEST NUMBER: P936556

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1448.9	1448.9
2.5°	1546.8	1537.4
5°	1989.4	1998.6
7.5°	2678.8	2674.2
10°	3331.0	3373.0
12.5°	3806.3	3815.6
15°	4095.1	4113.8
17.5°	4207.0	4211.6
20°	4211.6	4202.3
22.5°	4160.4	4151.0
25°	4099.8	4095.1
27.5°	4043.9	4048.6
30°	4020.6	4034.6
32.5°	4020.6	4043.9
35°	4029.9	4053.2
37.5°	4025.3	4053.2
40°	4006.7	4039.2
42.5°	3955.4	3978.7
45°	3876.2	3904.1
47.5°	3773.7	3792.3
50°	3643.2	3661.9
52.5°	3480.2	3484.9
55°	3284.5	3303.2
57.5°	3074.8	3079.5
60°	2841.9	2855.9
62.5°	2595.0	2595.0
65°	2334.1	2343.4
67.5°	2063.9	2087.2
70°	1789.0	1793.6
72.5°	1518.8	1518.8
75°	1239.3	1243.9
77.5°	973.7	973.7
80°	722.1	726.8
82.5°	498.5	507.9
85°	312.1	312.1
87.5°	144.4	130.4
90°	10.5	10.5
92.5°	42.0	33.7
95°	146.3	121.0
97.5°	350.6	302.5
100°	505.1	447.8
102.5°	657.0	608.0
105°	850.8	824.5
107.5°	977.8	984.1
110°	1026.2	1053.6



TEST NUMBER: P936556

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1030.5	1072.6
115°	1003.1	1061.6
117.5°	945.2	1010.0
120°	898.5	961.5
122.5°	853.1	915.2
125°	788.1	845.4
127.5°	729.8	778.1
130°	695.5	740.1
132.5°	664.3	704.2
135°	621.6	656.0
137.5°	587.2	615.5
140°	563.7	590.1
142.5°	544.3	567.0
145°	515.0	532.2
147.5°	492.6	506.8
150°	478.5	490.0
152.5°	466.4	475.1
155°	452.5	458.3
157.5°	441.6	445.6
160°	435.0	437.3
162.5°	430.7	432.9
165°	424.5	426.8
167.5°	420.0	421.0
170°	418.8	418.8
172.5°	415.5	414.7
175°	413.6	413.6
177.5°	411.9	410.9
180°	410.9	410.9



TEST NUMBER: P936556
 CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.65	9.95	9.28	10.60	11.35	21.84	23.14	22.47	23.79	24.54
	3H	9.38	10.56	10.03	11.22	12.00	23.71	24.89	24.36	25.55	26.33
	4H	9.70	10.81	10.36	11.49	12.28	24.38	25.50	25.05	26.17	26.96
	6H	9.97	11.00	10.65	11.69	12.50	24.84	25.87	25.52	26.55	27.36
	8H	10.05	11.04	10.74	11.74	12.56	24.98	25.96	25.66	26.66	27.48
	12H	10.09	11.03	10.78	11.73	12.57	25.06	26.00	25.76	26.70	27.54
4H	2H	15.92	17.03	16.59	17.71	18.50	22.16	23.28	22.83	23.95	24.74
	3H	17.53	18.46	18.21	19.17	19.99	24.25	25.19	24.93	25.90	26.71
	4H	17.64	18.49	18.34	19.20	20.05	25.04	25.89	25.74	26.61	27.45
	6H	17.68	18.42	18.39	19.16	20.01	25.61	26.35	26.33	27.09	27.94
	8H	17.66	18.36	18.39	19.10	19.96	25.79	26.48	26.51	27.22	28.08
	12H	17.64	18.27	18.39	19.03	19.90	25.91	26.53	26.65	27.29	28.16
8H	4H	19.13	19.82	19.85	20.56	21.42	25.14	25.83	25.86	26.57	27.44
	6H	19.39	19.97	20.14	20.74	21.61	25.79	26.37	26.55	27.15	28.02
	8H	19.41	19.93	20.18	20.71	21.59	26.02	26.54	26.79	27.32	28.20
	12H	19.40	19.86	20.17	20.63	21.57	26.19	26.65	26.96	27.42	28.36
12H	4H	19.29	19.92	20.04	20.68	21.55	25.11	25.74	25.86	26.50	27.37
	6H	19.65	20.17	20.42	20.95	21.83	25.78	26.30	26.55	27.08	27.96
	8H	19.75	20.20	20.51	20.97	21.91	26.04	26.49	26.81	27.26	28.21