

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936555

Luminaire Tested: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936555
REPORT IS A COMBINATION OF REPORTS P933432 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13684.2 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 148.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936555
CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P936555

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4421	4421	4421
5°	4320	5110	5942
10°	3920	7451	9850
15°	3333	9737	11894
20°	2714	11286	12122
25°	2265	11814	11876
30°	1911	11891	11853
35°	1690	11697	12160
40°	1474	11443	12477
45°	1335	11259	12525
50°	1226	11094	12318
55°	1176	10850	11772
60°	1205	10378	10910
65°	1255	9659	9725
70°	1340	8429	8216
75°	1491	6879	6411
80°	1641	4776	4320
85°	1491	2539	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12525 cd/sqm



TEST NUMBER: P936555

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.4
10°-20°	819.3	6.0
20°-30°	1433.1	10.5
30°-40°	1844.8	13.5
40°-50°	2060.6	15.1
50°-60°	1973.6	14.4
60°-70°	1564.1	11.4
70°-80°	919.7	6.7
80°-90°	257.1	1.9
90°-100°	197.5	1.4
100°-110°	519.3	3.8
110°-120°	538.5	3.9
120°-130°	431.9	3.2
130°-140°	338.9	2.5
140°-150°	260.1	1.9
150°-160°	187.3	1.4
160°-170°	114.6	0.8
170°-180°	38.7	0.3
0°-30°	2437.3	17.8
0°-40°	4282.1	31.3
0°-60°	8316.3	60.8
0°-90°	11057.2	80.8
90°-120°	1255.4	9.2
90°-150°	2286.3	16.7
90°-180°	2627.0	19.2
0°-180°	13684.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1392	1493	1682	1902	1971	129
15°	1043	1925	3244	3934	4058	290
25°	666	2183	3865	4035	4039	307
35°	450	2086	3639	3846	3998	281
45°	308	1664	3217	3685	3851	238
55°	221	1057	2730	3171	3258	201
65°	175	561	2026	2279	2311	173
75°	129	345	1112	1222	1227	135
85°	46	106	276	303	308	49
90°	3	8	21	10	10	5
95°	26	102	340	175	119	29
105°	94	142	574	872	813	99
115°	166	202	460	917	1047	164
125°	231	259	418	707	834	205
135°	276	303	405	571	647	213
145°	320	340	400	487	525	200
155°	361	371	400	439	452	166
165°	390	395	400	416	421	110
175°	405	405	403	408	408	38
180°	405	405	405	405	405	



TEST NUMBER: P936555

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2
2.5°	1429.2	1429.2	1438.3	1442.9	1452.1	1456.7	1465.9	1475.1	1502.7	1507.3	1516.4
5°	1392.3	1410.7	1470.4	1493.4	1557.8	1645.1	1681.9	1741.6	1865.6	1902.5	1925.4
7.5°	1337.2	1378.6	1525.6	1562.4	1723.2	1953.0	2049.5	2178.2	2375.8	2472.3	2550.4
10°	1249.9	1337.2	1599.1	1686.4	1948.4	2297.6	2476.8	2656.0	2954.7	3088.0	3138.6
12.5°	1153.4	1295.8	1677.3	1796.7	2173.6	2683.6	2899.6	3097.2	3437.3	3616.5	3644.0
15°	1043.1	1236.1	1750.8	1925.4	2412.5	3005.3	3244.2	3487.8	3804.8	3933.6	3965.7
17.5°	946.6	1190.2	1819.7	2003.5	2596.3	3294.8	3538.4	3740.5	3997.8	4085.2	4108.2
20°	827.1	1116.6	1865.6	2104.6	2789.3	3506.1	3740.5	3896.7	4071.4	4126.5	4135.7
22.5°	739.8	1038.5	1893.2	2141.3	2918.0	3634.9	3832.5	3956.5	4075.9	4094.3	4098.9
25°	666.3	951.2	1888.6	2182.7	3028.2	3713.0	3864.6	3956.5	4025.4	4034.6	4034.6
27.5°	597.4	854.7	1870.2	2191.9	3110.9	3731.3	3850.8	3915.1	3947.3	3965.7	3965.7
30°	537.7	762.8	1824.3	2173.6	3147.7	3713.0	3809.5	3841.6	3873.8	3901.3	3915.1
32.5°	491.7	675.5	1755.4	2136.8	3152.3	3667.0	3736.0	3754.3	3800.2	3864.6	3887.6
35°	450.3	588.2	1677.3	2086.2	3124.8	3593.5	3639.4	3657.8	3749.7	3846.2	3878.3
37.5°	409.0	523.8	1576.2	1999.0	3083.4	3506.1	3538.4	3570.5	3713.0	3827.8	3864.6
40°	367.6	468.7	1456.7	1902.5	3019.1	3400.5	3428.0	3478.6	3667.0	3800.2	3837.0
42.5°	335.5	422.8	1328.1	1801.4	2936.3	3281.0	3322.4	3395.9	3611.9	3754.3	3795.7
45°	307.8	376.8	1190.2	1663.5	2830.6	3156.9	3216.7	3317.8	3547.5	3685.4	3722.1
47.5°	280.3	344.7	1047.7	1521.0	2715.8	3032.8	3110.9	3225.8	3460.2	3593.5	3625.6
50°	257.3	312.5	905.3	1369.4	2591.7	2899.6	2991.5	3110.9	3349.9	3474.0	3515.4
52.5°	239.0	284.9	772.0	1217.7	2449.3	2761.7	2867.5	2991.5	3216.7	3336.2	3363.7
55°	220.6	262.0	657.1	1056.9	2302.2	2614.6	2729.6	2849.1	3069.6	3170.7	3189.1
57.5°	211.4	243.6	560.7	905.3	2146.0	2449.3	2577.9	2688.2	2895.0	2973.1	2991.5
60°	197.6	229.7	487.1	776.6	1976.0	2293.0	2403.3	2513.6	2688.2	2752.5	2766.4
62.5°	183.8	220.6	431.9	652.5	1801.4	2109.2	2219.5	2320.6	2467.6	2513.6	2532.0
65°	174.6	211.4	390.6	560.7	1622.1	1916.2	2026.5	2113.8	2233.3	2279.2	2288.4
67.5°	165.5	202.2	358.4	482.5	1442.9	1723.2	1805.9	1888.6	1980.6	2026.5	2031.1
70°	151.6	193.0	330.8	427.3	1259.1	1502.7	1571.5	1658.9	1732.4	1755.4	1769.1
72.5°	142.5	179.2	312.5	386.0	1070.7	1291.3	1355.6	1406.2	1470.4	1493.4	1493.4
75°	128.6	160.8	294.1	344.7	877.6	1056.9	1112.1	1162.6	1213.1	1222.3	1208.6
77.5°	114.9	142.5	252.7	289.5	684.7	836.4	882.3	909.9	951.2	960.4	965.0
80°	96.5	124.1	197.6	225.2	496.3	615.8	647.9	670.9	707.7	707.7	716.9
82.5°	73.5	96.5	142.5	160.8	335.5	422.8	450.3	464.1	487.1	487.1	487.1
85°	46.0	59.7	91.9	105.7	202.2	257.3	275.7	280.3	298.7	303.3	303.3
87.5°	23.0	32.1	59.7	64.4	105.7	133.2	133.2	142.5	142.5	137.9	133.2
90°	2.7	4.9	7.1	7.6	11.9	17.7	20.6	18.4	13.8	10.3	10.3
92.5°	10.9	29.3	47.9	52.5	73.8	102.2	116.4	102.0	73.2	51.7	49.6
95°	26.1	59.9	93.8	102.3	181.6	287.4	340.3	303.6	230.4	175.4	169.2
97.5°	45.2	75.0	104.9	112.3	244.6	421.0	509.2	486.0	439.7	405.0	393.1
100°	59.8	86.9	114.0	120.7	267.6	463.3	561.1	562.8	566.2	568.7	554.6
102.5°	72.3	97.6	122.8	129.2	278.1	476.6	575.8	605.3	664.2	708.5	696.3
105°	93.6	115.0	136.3	141.7	285.8	478.0	574.1	640.2	772.5	871.7	865.2
107.5°	115.3	135.2	155.2	160.2	287.3	456.7	541.5	633.7	818.2	956.6	958.1
110°	130.0	148.0	166.0	170.5	285.1	437.9	514.3	617.4	823.6	978.3	985.1



TEST NUMBER: P936555

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	144.5	161.6	178.8	183.0	285.2	421.4	489.6	595.1	806.1	964.4	974.9
115°	166.2	182.0	197.9	201.9	287.8	402.5	459.9	561.6	764.9	917.4	931.8
117.5°	187.6	202.0	216.4	220.0	293.2	390.8	439.5	531.3	714.8	852.4	868.4
120°	200.1	213.7	227.3	230.6	297.5	386.7	431.3	515.1	682.9	808.6	824.1
122.5°	212.4	226.1	239.7	243.1	303.8	384.6	425.1	500.6	651.5	764.8	780.1
125°	231.2	243.7	256.2	259.2	312.3	383.0	418.3	482.4	610.6	706.8	721.0
127.5°	246.4	259.0	271.5	274.7	320.7	382.0	412.6	467.6	577.8	660.3	672.3
130°	254.5	268.1	281.7	285.0	326.9	382.5	410.4	459.5	557.5	631.0	642.0
132.5°	263.0	276.5	290.1	293.5	331.8	383.0	408.5	452.4	540.2	606.0	615.9
135°	275.5	287.8	300.2	303.2	337.3	382.6	405.2	442.0	515.5	570.6	579.1
137.5°	288.3	300.5	312.6	315.7	345.4	385.0	404.7	435.7	497.8	544.5	551.4
140°	298.9	310.1	321.4	324.2	350.4	385.3	402.8	429.6	483.3	523.5	530.1
142.5°	307.0	317.4	327.8	330.5	354.6	386.7	402.8	426.3	473.5	508.9	514.5
145°	319.6	328.7	337.7	340.0	360.0	386.7	400.1	419.4	457.9	486.8	491.0
147.5°	332.1	340.9	349.8	351.9	367.9	389.4	400.1	415.3	445.6	468.3	471.9
150°	340.3	348.2	356.2	358.2	372.1	390.8	400.1	412.9	438.6	457.7	460.5
152.5°	348.7	354.7	360.7	362.2	374.8	391.7	400.1	411.0	432.9	449.3	451.5
155°	361.2	365.6	370.1	371.2	380.8	393.7	400.1	408.8	426.2	439.3	440.7
157.5°	370.4	374.7	379.2	380.3	386.9	395.6	400.1	406.9	420.4	430.5	431.5
160°	376.7	380.1	383.5	384.3	389.6	396.6	400.1	405.9	417.5	426.1	426.7
162.5°	383.0	385.5	388.0	388.7	392.5	397.5	400.1	405.0	414.7	422.1	422.6
165°	389.8	392.0	394.4	394.9	396.6	398.9	400.1	403.6	410.6	415.8	416.4
167.5°	396.0	397.1	398.2	398.5	399.9	401.8	402.8	405.1	409.7	413.1	413.4
170°	400.1	401.2	402.3	402.5	402.6	402.7	402.8	405.1	409.7	413.1	413.1
172.5°	402.3	402.5	402.7	402.8	402.8	402.8	402.8	404.6	408.2	410.9	410.8
175°	405.2	405.2	405.2	405.2	404.4	403.3	402.8	404.0	406.2	408.0	408.0
177.5°	405.2	405.2	405.2	405.2	404.6	403.8	403.3	404.2	406.1	407.4	407.1
180°	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2



TEST NUMBER: P936555
CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1429.2	1429.2
2.5°	1525.6	1516.4
5°	1962.2	1971.4
7.5°	2642.3	2637.6
10°	3285.6	3326.9
12.5°	3754.3	3763.5
15°	4039.2	4057.6
17.5°	4149.5	4154.1
20°	4154.1	4144.9
22.5°	4103.5	4094.3
25°	4043.8	4039.2
27.5°	3988.7	3993.3
30°	3965.7	3979.4
32.5°	3965.7	3988.7
35°	3974.8	3997.8
37.5°	3970.3	3997.8
40°	3951.9	3984.1
42.5°	3901.3	3924.3
45°	3823.2	3850.8
47.5°	3722.1	3740.5
50°	3593.5	3611.9
52.5°	3432.6	3437.3
55°	3239.7	3258.0
57.5°	3032.8	3037.4
60°	2803.1	2816.9
62.5°	2559.5	2559.5
65°	2302.2	2311.4
67.5°	2035.7	2058.7
70°	1764.6	1769.1
72.5°	1498.0	1498.0
75°	1222.3	1226.9
77.5°	960.4	960.4
80°	712.3	716.9
82.5°	491.7	500.9
85°	307.8	307.8
87.5°	142.5	128.6
90°	10.3	10.3
92.5°	41.5	33.2
95°	144.3	119.4
97.5°	345.8	298.3
100°	498.2	441.7
102.5°	648.0	599.7
105°	839.2	813.2
107.5°	964.4	970.7
110°	1012.2	1039.2



TEST NUMBER: P936555

CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1016.4	1058.0
115°	989.4	1047.1
117.5°	932.3	996.2
120°	886.2	948.3
122.5°	841.4	902.7
125°	777.4	833.8
127.5°	719.9	767.5
130°	686.0	730.0
132.5°	655.2	694.6
135°	613.1	647.0
137.5°	579.2	607.1
140°	556.0	582.0
142.5°	536.9	559.2
145°	508.0	524.9
147.5°	485.9	499.9
150°	472.0	483.3
152.5°	460.0	468.6
155°	446.3	452.0
157.5°	435.6	439.5
160°	429.0	431.3
162.5°	424.8	427.0
165°	418.7	421.0
167.5°	414.3	415.3
170°	413.1	413.1
172.5°	409.9	409.0
175°	408.0	408.0
177.5°	406.2	405.2
180°	405.2	405.2



TEST NUMBER: P936555
 CATALOG NUMBER: SQ4-FB-025U-125D-93050-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.60	9.90	9.23	10.55	11.30	21.79	23.09	22.42	23.74	24.49
	3H	9.34	10.51	9.98	11.17	11.95	23.67	24.84	24.31	25.50	26.29
	4H	9.65	10.77	10.32	11.44	12.23	24.33	25.45	25.00	26.12	26.91
	6H	9.93	10.96	10.60	11.64	12.45	24.79	25.82	25.47	26.51	27.32
	8H	10.01	10.99	10.70	11.70	12.51	24.93	25.91	25.62	26.62	27.43
	12H	10.04	10.98	10.73	11.68	12.52	25.01	25.95	25.71	26.65	27.50
4H	2H	15.87	16.99	16.54	17.66	18.45	22.11	23.23	22.78	23.90	24.69
	3H	17.48	18.41	18.16	19.12	19.94	24.20	25.14	24.88	25.85	26.66
	4H	17.59	18.44	18.29	19.16	20.00	24.99	25.85	25.69	26.56	27.40
	6H	17.63	18.37	18.35	19.11	19.96	25.56	26.31	26.28	27.04	27.90
	8H	17.62	18.31	18.34	19.05	19.91	25.74	26.43	26.46	27.17	28.04
	12H	17.60	18.22	18.34	18.98	19.85	25.86	26.49	26.60	27.25	28.12
8H	4H	19.08	19.77	19.80	20.51	21.37	25.09	25.79	25.81	26.52	27.39
	6H	19.34	19.92	20.09	20.70	21.57	25.75	26.32	26.50	27.10	27.97
	8H	19.37	19.88	20.13	20.66	21.54	25.98	26.49	26.74	27.27	28.15
	12H	19.36	19.81	20.12	20.58	21.52	26.14	26.60	26.91	27.37	28.31
12H	4H	19.24	19.87	19.99	20.63	21.50	25.07	25.69	25.81	26.45	27.32
	6H	19.61	20.12	20.37	20.90	21.79	25.73	26.25	26.50	27.03	27.91
	8H	19.70	20.15	20.47	20.92	21.87	25.99	26.45	26.76	27.21	28.16