

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936861

Luminaire Tested: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936861
REPORT IS A COMBINATION OF REPORTS P933479 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6812.1 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936861
CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61		
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55	50		
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45	41		
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38	34		
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	28		
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27	24		
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23	21		
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21	18		
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18	16		
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16	14		
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3349	3349	3349
5°	3270	3869	4501
10°	2965	5639	7462
15°	2519	7366	9010
20°	2050	8534	9184
25°	1710	8928	8997
30°	1441	8982	8979
35°	1273	8831	9212
40°	1109	8634	9452
45°	1003	8490	9489
50°	920	8359	9332
55°	880	8169	8918
60°	899	7807	8265
65°	934	7258	7367
70°	993	6325	6224
75°	1096	5152	4857
80°	1188	3569	3274
85°	1037	1890	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9489 cd/sqm



TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.0
10°-20°	310.3	4.6
20°-30°	542.8	8.0
30°-40°	698.8	10.3
40°-50°	780.5	11.5
50°-60°	747.6	11.0
60°-70°	592.5	8.7
70°-80°	348.4	5.1
80°-90°	98.3	1.4
90°-100°	197.2	2.9
100°-110°	518.5	7.6
110°-120°	537.6	7.9
120°-130°	431.2	6.3
130°-140°	338.4	5.0
140°-150°	259.7	3.8
150°-160°	187.0	2.7
160°-170°	114.4	1.7
170°-180°	38.7	0.6
0°-30°	923.2	13.6
0°-40°	1622.0	23.8
0°-60°	3150.1	46.2
0°-90°	4189.3	61.5
90°-120°	1253.4	18.4
90°-150°	2282.7	33.5
90°-180°	2623.0	38.5
0°-180°	6812.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	541	541	541	541	541	
5°	527	566	637	721	747	49
15°	395	729	1229	1490	1537	110
25°	252	827	1464	1528	1530	116
35°	171	790	1379	1457	1514	107
45°	117	630	1218	1396	1459	90
55°	84	400	1034	1201	1234	76
65°	66	212	768	863	876	66
75°	49	130	421	463	465	51
85°	17	40	104	115	117	18
90°	3	8	21	10	10	3
95°	26	102	340	175	119	29
105°	94	142	573	870	812	99
115°	166	202	459	916	1045	164
125°	231	259	418	706	832	205
135°	275	303	405	570	646	213
145°	319	340	400	486	524	200
155°	361	371	400	438	451	166
165°	389	394	400	415	420	110
175°	405	405	402	407	407	38
180°	405	405	405	405	405	



TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	541.3	541.3	541.3	541.3	541.3	541.3	541.3	541.3	541.3	541.3	541.3
2.5°	541.3	541.3	544.8	546.6	550.0	551.7	555.3	558.8	569.1	570.9	574.4
5°	527.4	534.4	557.0	565.7	590.0	623.2	637.0	659.7	706.7	720.6	729.3
7.5°	506.5	522.1	577.9	591.8	652.8	739.8	776.3	825.1	899.9	936.4	966.0
10°	473.4	506.5	605.8	638.8	738.0	870.3	938.2	1006.1	1119.2	1169.7	1188.9
12.5°	436.9	490.9	635.4	680.6	823.3	1016.5	1098.3	1173.1	1302.0	1369.9	1380.3
15°	395.1	468.2	663.2	729.3	913.8	1138.4	1228.9	1321.1	1441.2	1489.9	1502.2
17.5°	358.6	450.8	689.3	758.9	983.4	1248.1	1340.3	1416.9	1514.4	1547.4	1556.1
20°	313.3	423.0	706.7	797.2	1056.6	1328.1	1416.9	1476.1	1542.2	1563.1	1566.5
22.5°	280.3	393.4	717.1	811.1	1105.3	1376.8	1451.7	1498.6	1544.0	1550.9	1552.7
25°	252.4	360.3	715.4	826.8	1147.1	1406.4	1463.9	1498.6	1524.8	1528.2	1528.2
27.5°	226.3	323.7	708.4	830.3	1178.4	1413.4	1458.6	1483.0	1495.2	1502.2	1502.2
30°	203.7	289.0	691.0	823.3	1192.3	1406.4	1443.0	1455.2	1467.4	1477.7	1483.0
32.5°	186.3	255.8	664.9	809.4	1194.1	1389.0	1415.1	1422.1	1439.4	1463.9	1472.6
35°	170.6	222.8	635.4	790.2	1183.6	1361.2	1378.6	1385.5	1420.3	1456.9	1469.0
37.5°	154.9	198.4	597.1	757.2	1168.0	1328.1	1340.3	1352.5	1406.4	1449.9	1463.9
40°	139.2	177.5	551.7	720.6	1143.5	1288.0	1298.5	1317.6	1389.0	1439.4	1453.4
42.5°	127.1	160.1	503.0	682.4	1112.3	1242.8	1258.4	1286.3	1368.1	1422.1	1437.8
45°	116.6	142.7	450.8	630.1	1072.2	1195.8	1218.5	1256.8	1343.7	1396.0	1409.9
47.5°	106.2	130.5	396.9	576.2	1028.7	1148.8	1178.4	1221.9	1310.7	1361.2	1373.3
50°	97.5	118.4	342.9	518.7	981.7	1098.3	1133.2	1178.4	1268.9	1315.9	1331.6
52.5°	90.6	107.9	292.4	461.3	927.7	1046.1	1086.1	1133.2	1218.5	1263.7	1274.2
55°	83.5	99.2	248.9	400.3	872.1	990.4	1033.9	1079.2	1162.7	1201.0	1208.0
57.5°	80.1	92.2	212.4	342.9	812.9	927.7	976.5	1018.3	1096.6	1126.2	1133.2
60°	74.8	87.0	184.5	294.1	748.5	868.6	910.4	952.1	1018.3	1042.6	1047.8
62.5°	69.6	83.5	163.6	247.2	682.4	798.9	840.7	879.0	934.7	952.1	959.1
65°	66.1	80.1	148.0	212.4	614.5	725.8	767.6	800.7	846.0	863.4	866.8
67.5°	62.6	76.6	135.8	182.8	546.6	652.8	684.0	715.4	750.2	767.6	769.4
70°	57.4	73.1	125.3	161.9	476.9	569.1	595.3	628.3	656.2	664.9	670.1
72.5°	53.9	67.9	118.4	146.2	405.6	489.1	513.5	532.6	557.0	565.7	565.7
75°	48.7	61.0	111.4	130.5	332.4	400.3	421.2	440.4	459.5	463.0	457.8
77.5°	43.5	53.9	95.7	109.7	259.4	316.8	334.2	344.6	360.3	363.8	365.5
80°	36.5	47.0	74.8	85.3	188.0	233.3	245.4	254.1	268.1	268.1	271.6
82.5°	27.8	36.5	53.9	61.0	127.1	160.1	170.6	175.8	184.5	184.5	184.5
85°	17.4	22.7	34.8	40.1	76.6	97.5	104.4	106.2	113.1	114.9	114.9
87.5°	8.7	12.2	22.7	24.3	40.1	50.5	50.5	53.9	53.9	52.3	50.5
90°	2.7	4.9	7.1	7.6	11.9	17.7	20.6	18.4	13.7	10.3	10.3
92.5°	10.9	29.3	47.8	52.4	73.7	102.1	116.2	101.8	73.1	51.6	49.5
95°	26.1	59.8	93.6	102.1	181.3	286.9	339.7	303.2	230.0	175.1	168.9
97.5°	45.1	74.9	104.7	112.2	244.3	420.4	508.4	485.3	439.0	404.3	392.4
100°	59.7	86.8	113.8	120.6	267.1	462.5	560.2	561.8	565.3	567.8	553.8
102.5°	72.2	97.5	122.7	129.0	277.6	475.8	574.8	604.3	663.2	707.4	695.4
105°	93.5	114.8	136.1	141.5	285.4	477.3	573.2	639.2	771.2	870.3	863.8
107.5°	115.1	135.1	154.9	159.9	286.9	456.0	540.6	632.6	816.8	955.0	956.6
110°	129.8	147.7	165.7	170.2	284.7	437.2	513.5	616.4	822.4	976.8	983.5



TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	144.2	161.3	178.5	182.8	284.7	420.8	488.8	594.2	804.9	962.9	973.2
115°	165.9	181.7	197.5	201.5	287.4	401.9	459.2	560.7	763.7	915.9	930.3
117.5°	187.3	201.7	216.1	219.7	292.7	390.1	438.8	530.4	713.6	851.0	867.0
120°	199.8	213.3	226.9	230.3	297.0	386.1	430.6	514.3	681.7	807.2	822.8
122.5°	212.1	225.7	239.3	242.8	303.3	384.0	424.4	499.8	650.6	763.6	778.9
125°	230.8	243.2	255.7	258.7	311.7	382.3	417.6	481.7	609.7	705.7	719.8
127.5°	246.0	258.6	271.1	274.3	320.1	381.4	411.9	466.9	576.8	659.3	671.1
130°	254.2	267.7	281.2	284.6	326.3	381.9	409.7	458.6	556.6	630.0	641.0
132.5°	262.6	276.1	289.7	293.0	331.3	382.3	407.9	451.7	539.3	605.0	614.8
135°	275.1	287.4	299.7	302.8	336.7	382.0	404.6	441.3	514.7	569.7	578.2
137.5°	287.8	300.0	312.1	315.2	344.8	384.3	404.0	435.0	497.0	543.6	550.5
140°	298.4	309.7	320.8	323.7	349.8	384.7	402.2	429.0	482.5	522.7	529.2
142.5°	306.5	316.9	327.3	329.9	354.0	386.1	402.2	425.7	472.7	508.0	513.6
145°	319.1	328.1	337.2	339.5	359.5	386.1	399.5	418.7	457.2	486.1	490.3
147.5°	331.6	340.3	349.2	351.4	367.4	388.7	399.5	414.6	444.9	467.6	471.1
150°	339.7	347.7	355.6	357.6	371.6	390.1	399.5	412.3	437.8	457.0	459.8
152.5°	348.1	354.1	360.2	361.7	374.2	391.0	399.5	410.3	432.2	448.5	450.7
155°	360.6	365.1	369.5	370.6	380.2	393.0	399.5	408.1	425.5	438.5	439.9
157.5°	369.9	374.2	378.5	379.6	386.2	395.1	399.5	406.2	419.7	429.8	430.8
160°	376.1	379.4	382.8	383.6	388.9	395.9	399.5	405.2	416.8	425.5	426.1
162.5°	382.3	384.9	387.4	388.0	391.8	396.9	399.5	404.4	414.1	421.4	421.9
165°	389.1	391.4	393.7	394.3	396.0	398.3	399.5	403.0	409.9	415.2	415.8
167.5°	395.3	396.4	397.5	397.8	399.3	401.2	402.2	404.5	409.0	412.5	412.7
170°	399.5	400.5	401.6	401.9	402.0	402.1	402.2	404.5	409.0	412.5	412.5
172.5°	401.6	401.9	402.1	402.2	402.2	402.2	402.2	403.9	407.5	410.3	410.1
175°	404.6	404.6	404.6	404.6	403.8	402.7	402.2	403.3	405.6	407.3	407.3
177.5°	404.6	404.6	404.6	404.6	404.0	403.1	402.7	403.6	405.4	406.7	406.5
180°	404.6	404.6	404.6	404.6	404.6	404.6	404.6	404.6	404.6	404.6	404.6



TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	541.3	541.3
2.5°	577.9	574.4
5°	743.2	746.7
7.5°	1000.8	999.2
10°	1244.6	1260.2
12.5°	1422.1	1425.6
15°	1530.0	1536.9
17.5°	1571.8	1573.5
20°	1573.5	1570.1
22.5°	1554.3	1550.9
25°	1531.8	1530.0
27.5°	1510.9	1512.6
30°	1502.2	1507.3
32.5°	1502.2	1510.9
35°	1505.7	1514.4
37.5°	1503.9	1514.4
40°	1496.9	1509.1
42.5°	1477.7	1486.5
45°	1448.2	1458.6
47.5°	1409.9	1416.9
50°	1361.2	1368.1
52.5°	1300.2	1302.0
55°	1227.2	1234.1
57.5°	1148.8	1150.6
60°	1061.8	1067.0
62.5°	969.6	969.6
65°	872.1	875.5
67.5°	771.1	779.8
70°	668.4	670.1
72.5°	567.5	567.5
75°	463.0	464.7
77.5°	363.8	363.8
80°	269.8	271.6
82.5°	186.3	189.7
85°	116.6	116.6
87.5°	53.9	48.7
90°	10.3	10.3
92.5°	41.3	33.1
95°	144.0	119.2
97.5°	345.2	297.9
100°	497.4	441.0
102.5°	647.0	598.7
105°	837.9	811.9
107.5°	962.8	969.1
110°	1010.5	1037.5



TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1014.8	1056.2
115°	987.8	1045.4
117.5°	930.8	994.7
120°	884.8	946.9
122.5°	840.1	901.2
125°	776.2	832.5
127.5°	718.7	766.3
130°	684.9	728.8
132.5°	654.2	693.5
135°	612.1	646.0
137.5°	578.4	606.1
140°	555.1	581.1
142.5°	535.9	558.2
145°	507.2	524.1
147.5°	485.1	499.1
150°	471.2	482.5
152.5°	459.3	467.9
155°	445.6	451.3
157.5°	434.8	438.8
160°	428.3	430.6
162.5°	424.1	426.3
165°	418.1	420.4
167.5°	413.7	414.6
170°	412.5	412.5
172.5°	409.2	408.4
175°	407.3	407.3
177.5°	405.6	404.6
180°	404.6	404.6



TEST NUMBER: P936861

CATALOG NUMBER: SQ4-FB-050U-100D-93050-1D-UNV-STD-W-6-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.18	7.21	7.03	8.08	9.17	19.35	20.37	20.19	21.25	22.34
	3H	6.90	7.82	7.76	8.71	9.83	21.19	22.12	22.05	23.00	24.12
	4H	7.21	8.08	8.08	8.97	10.10	21.84	22.72	22.72	23.61	24.73
	6H	7.47	8.27	8.35	9.17	10.31	22.28	23.09	23.16	23.98	25.12
	8H	7.54	8.31	8.43	9.22	10.36	22.40	23.17	23.29	24.09	25.23
	12H	7.56	8.30	8.46	9.20	10.37	22.47	23.21	23.37	24.11	25.28
4H	2H	13.41	14.28	14.29	15.17	16.30	19.64	20.52	20.52	21.40	22.53
	3H	14.99	15.73	15.88	16.64	17.79	21.70	22.43	22.59	23.35	24.50
	4H	15.09	15.76	15.99	16.68	17.85	22.47	23.14	23.37	24.05	25.22
	6H	15.12	15.70	16.03	16.63	17.81	23.01	23.59	23.93	24.53	25.70
	8H	15.10	15.64	16.01	16.57	17.76	23.18	23.72	24.10	24.65	25.84
	12H	15.06	15.55	16.00	16.50	17.70	23.28	23.77	24.21	24.72	25.91
8H	4H	16.55	17.09	17.47	18.03	19.21	22.54	23.09	23.46	24.02	25.21
	6H	16.80	17.25	17.75	18.23	19.41	23.18	23.63	24.12	24.60	25.79
	8H	16.82	17.22	17.78	18.19	19.39	23.40	23.80	24.35	24.76	25.96
	12H	16.80	17.15	17.76	18.11	19.36	23.55	23.90	24.50	24.86	26.11
12H	4H	16.70	17.19	17.64	18.14	19.34	22.50	22.99	23.44	23.95	25.14
	6H	17.06	17.46	18.01	18.42	19.63	23.16	23.56	24.12	24.53	25.73
	8H	17.14	17.49	18.10	18.45	19.70	23.40	23.75	24.36	24.71	25.96