

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937053

Luminaire Tested: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937053
REPORT IS A COMBINATION OF REPORTS P933493 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12146.1 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937053
CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P937053

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35			35
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35	29			29
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	23			23
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24	19			19
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20	16			16
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14			14
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15	12			12
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10			10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12	9			9
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10	8			8
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9	7			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1700	1700	1700
5°	1661	1965	2285
10°	1508	2865	3788
15°	1282	3745	4574
20°	1044	4341	4662
25°	871	4543	4567
30°	735	4573	4558
35°	650	4499	4677
40°	567	4401	4798
45°	514	4330	4817
50°	472	4266	4737
55°	452	4173	4527
60°	463	3991	4196
65°	483	3715	3740
70°	515	3242	3160
75°	573	2645	2465
80°	633	1837	1662
85°	574	976	850

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4817 cd/sqm



TEST NUMBER: P937053

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.1	0.6
10°-20°	315.1	2.6
20°-30°	551.2	4.5
30°-40°	709.5	5.8
40°-50°	792.5	6.5
50°-60°	759.0	6.2
60°-70°	601.5	5.0
70°-80°	353.7	2.9
80°-90°	102.9	0.8
90°-100°	593.2	4.9
100°-110°	1559.7	12.8
110°-120°	1617.2	13.3
120°-130°	1297.2	10.7
130°-140°	1017.8	8.4
140°-150°	781.2	6.4
150°-160°	562.6	4.6
160°-170°	344.2	2.8
170°-180°	116.3	1.0
0°-30°	937.4	7.7
0°-40°	1646.9	13.6
0°-60°	3198.4	26.3
0°-90°	4256.5	35.0
90°-120°	3770.1	31.0
90°-150°	6866.4	56.5
90°-180°	7890.0	65.0
0°-180°	12146.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	550	550	550	550	550	
5°	536	574	647	732	758	49
15°	401	740	1248	1513	1560	112
25°	256	840	1486	1552	1554	118
35°	173	802	1400	1479	1538	108
45°	118	640	1237	1417	1481	92
55°	85	406	1050	1219	1253	77
65°	67	216	779	876	889	67
75°	49	132	428	470	472	52
85°	18	41	106	117	118	19
90°	8	23	62	31	31	8
95°	78	307	1022	527	359	87
105°	281	426	1724	2618	2442	298
115°	499	606	1381	2755	3145	493
125°	694	778	1256	2123	2504	616
135°	827	911	1217	1714	1943	640
145°	960	1021	1202	1462	1576	601
155°	1085	1115	1202	1319	1358	498
165°	1170	1186	1202	1249	1264	330
175°	1217	1217	1210	1225	1225	116
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P937053

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	549.6	549.6	553.2	554.9	558.4	560.2	563.8	567.3	577.9	579.7	583.2
5°	535.5	542.5	565.5	574.3	599.1	632.6	646.8	669.8	717.5	731.6	740.5
7.5°	514.2	530.1	586.7	600.8	662.8	751.1	788.2	837.7	913.7	950.8	980.8
10°	480.7	514.2	615.0	648.6	749.3	883.7	952.5	1021.5	1136.3	1187.6	1207.0
12.5°	443.5	498.3	645.0	691.0	835.9	1032.1	1115.2	1191.2	1321.9	1390.9	1401.4
15°	401.2	475.4	673.3	740.5	927.8	1155.8	1247.7	1341.3	1463.3	1512.8	1525.2
17.5°	364.1	457.7	699.8	770.5	998.5	1267.1	1360.8	1438.6	1537.6	1571.1	1580.0
20°	318.1	429.5	717.5	809.4	1072.8	1348.5	1438.6	1498.6	1565.8	1587.0	1590.5
22.5°	284.6	399.4	728.1	823.6	1122.2	1397.9	1473.9	1521.7	1567.6	1574.6	1576.4
25°	256.3	365.8	726.4	839.5	1164.6	1427.9	1486.3	1521.7	1548.1	1551.7	1551.7
27.5°	229.8	328.7	719.2	843.0	1196.4	1435.1	1481.0	1505.7	1518.1	1525.2	1525.2
30°	206.8	293.4	701.6	835.9	1210.6	1427.9	1465.1	1477.5	1489.8	1500.4	1505.7
32.5°	189.1	259.8	675.1	821.7	1212.3	1410.3	1436.8	1443.8	1461.5	1486.3	1495.1
35°	173.2	226.3	645.0	802.3	1201.8	1382.0	1399.7	1406.8	1442.1	1479.2	1491.5
37.5°	157.3	201.5	606.2	768.8	1185.8	1348.5	1360.8	1373.1	1427.9	1472.1	1486.3
40°	141.4	180.2	560.2	731.6	1161.1	1307.8	1318.4	1337.8	1410.3	1461.5	1475.6
42.5°	129.0	162.6	510.7	692.8	1129.3	1261.9	1277.8	1306.0	1389.0	1443.8	1459.7
45°	118.4	144.9	457.7	639.8	1088.7	1214.1	1237.1	1276.0	1364.4	1417.3	1431.5
47.5°	107.8	132.5	403.0	584.9	1044.5	1166.4	1196.4	1240.6	1330.7	1382.0	1394.4
50°	99.0	120.2	348.2	526.6	996.7	1115.2	1150.5	1196.4	1288.4	1336.1	1352.0
52.5°	91.9	109.6	296.9	468.3	942.0	1062.1	1102.8	1150.5	1237.1	1283.0	1293.6
55°	84.8	100.7	252.7	406.5	885.4	1005.6	1049.7	1095.7	1180.5	1219.4	1226.5
57.5°	81.3	93.6	215.6	348.2	825.3	942.0	991.4	1033.8	1113.3	1143.5	1150.5
60°	76.0	88.4	187.3	298.7	759.9	881.9	924.3	966.7	1033.8	1058.6	1063.9
62.5°	70.7	84.8	166.1	250.9	692.8	811.2	853.6	892.4	949.0	966.7	973.8
65°	67.2	81.3	150.2	215.6	623.9	737.0	779.4	813.0	858.9	876.5	880.1
67.5°	63.6	77.7	137.8	185.6	554.9	662.8	694.6	726.4	761.7	779.4	781.2
70°	58.3	74.2	127.3	164.3	484.2	577.9	604.4	638.0	666.3	675.1	680.4
72.5°	54.8	68.9	120.2	148.4	411.7	496.6	521.4	540.8	565.5	574.3	574.3
75°	49.4	61.8	113.1	132.5	337.5	406.5	427.6	447.1	466.6	470.1	464.8
77.5°	44.2	54.8	97.2	111.4	263.3	321.6	339.3	349.9	365.8	369.3	371.1
80°	37.2	47.7	76.0	86.6	190.9	236.8	249.2	258.0	272.2	272.2	275.7
82.5°	28.3	37.2	54.8	61.8	129.0	162.6	173.2	178.5	187.3	187.3	187.3
85°	17.7	23.0	35.3	40.7	77.7	99.0	106.0	107.8	114.9	116.6	116.6
87.5°	8.9	12.4	23.0	24.8	40.7	51.3	51.3	54.8	54.8	53.0	51.3
90°	8.2	14.7	21.2	22.8	35.9	53.4	62.1	55.2	41.4	31.0	31.0
92.5°	32.7	88.2	143.8	157.7	221.6	306.9	349.6	306.4	220.0	155.2	149.0
95°	78.4	180.1	281.8	307.1	545.3	863.0	1021.8	911.9	691.8	526.8	508.1
97.5°	135.6	225.3	315.0	337.4	734.6	1264.2	1529.0	1459.5	1320.4	1216.2	1180.6
100°	179.7	261.0	342.4	362.7	803.5	1391.1	1685.0	1690.1	1700.3	1707.9	1665.5
102.5°	217.3	293.2	369.0	387.9	835.0	1431.1	1729.2	1817.7	1994.9	2127.8	2091.5
105°	281.0	345.3	409.5	425.5	858.5	1435.7	1724.3	1922.9	2320.0	2617.9	2598.4
107.5°	346.3	406.2	466.1	481.1	862.8	1371.8	1626.3	1903.3	2457.2	2872.7	2877.4
110°	390.4	444.5	498.6	512.1	856.3	1315.2	1544.6	1854.3	2473.6	2938.0	2958.3



TEST NUMBER: P937053

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	433.7	485.3	536.8	549.7	856.6	1265.7	1470.3	1787.2	2421.0	2896.4	2927.6
115°	499.1	546.6	594.2	606.0	864.4	1209.0	1381.2	1686.5	2297.1	2755.1	2798.4
117.5°	563.6	606.8	649.9	660.7	880.5	1173.4	1319.9	1595.4	2146.5	2559.8	2607.9
120°	601.2	641.9	682.4	692.6	893.6	1161.5	1295.4	1547.1	2050.7	2428.3	2475.0
122.5°	637.9	678.9	719.9	730.2	912.4	1155.2	1276.6	1503.3	1956.8	2296.8	2342.9
125°	694.3	731.7	769.1	778.4	937.7	1150.0	1256.2	1448.8	1834.0	2122.9	2165.3
127.5°	740.1	777.8	815.6	825.0	963.1	1147.1	1239.1	1404.5	1735.2	1983.2	2019.0
130°	764.6	805.2	845.8	856.0	981.5	1148.8	1232.5	1379.7	1674.1	1894.9	1928.0
132.5°	789.9	830.5	871.1	881.3	996.4	1150.0	1226.8	1358.6	1622.1	1819.8	1849.4
135°	827.4	864.4	901.5	910.7	1012.9	1149.0	1217.1	1327.4	1548.1	1713.7	1739.1
137.5°	865.8	902.5	939.2	948.3	1037.4	1156.0	1215.4	1308.7	1495.3	1635.2	1656.1
140°	897.6	931.4	965.2	973.6	1052.3	1157.2	1209.7	1290.3	1451.5	1572.3	1591.8
142.5°	922.1	953.4	984.6	992.4	1064.9	1161.4	1209.7	1280.5	1422.1	1528.2	1545.0
145°	959.7	986.9	1014.2	1021.0	1081.2	1161.4	1201.5	1259.4	1375.2	1462.1	1474.8
147.5°	997.3	1023.8	1050.4	1056.9	1105.2	1169.4	1201.5	1247.1	1338.2	1406.5	1417.1
150°	1021.8	1045.8	1069.8	1075.7	1117.6	1173.6	1201.5	1240.0	1316.9	1374.6	1383.1
152.5°	1047.1	1065.3	1083.4	1088.0	1125.8	1176.3	1201.5	1234.4	1300.1	1349.3	1355.7
155°	1084.7	1098.1	1111.6	1114.9	1143.8	1182.3	1201.5	1227.7	1279.9	1319.1	1323.4
157.5°	1112.5	1125.5	1138.6	1141.9	1161.7	1188.3	1201.5	1221.8	1262.5	1292.9	1295.9
160°	1131.3	1141.4	1151.6	1154.2	1170.0	1191.0	1201.5	1218.9	1253.8	1279.9	1281.7
162.5°	1150.0	1157.7	1165.2	1167.2	1178.6	1193.9	1201.5	1216.2	1245.6	1267.7	1269.3
165°	1170.5	1177.4	1184.2	1186.0	1191.2	1198.1	1201.5	1212.1	1233.0	1248.9	1250.6
167.5°	1189.2	1192.5	1195.8	1196.6	1201.0	1206.8	1209.7	1216.5	1230.3	1240.7	1241.4
170°	1201.5	1204.8	1208.1	1208.9	1209.2	1209.5	1209.7	1216.5	1230.3	1240.7	1240.7
172.5°	1208.0	1208.7	1209.5	1209.7	1209.7	1209.7	1209.7	1215.1	1226.0	1234.2	1233.6
175°	1217.1	1217.1	1217.1	1217.1	1214.6	1211.4	1209.7	1213.1	1220.0	1225.2	1225.2
177.5°	1217.1	1217.1	1217.1	1217.1	1215.1	1212.6	1211.4	1214.1	1219.5	1223.6	1222.9
180°	1217.1	1217.1	1217.1	1217.1	1217.1	1217.1	1217.1	1217.1	1217.1	1217.1	1217.1



TEST NUMBER: P937053

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	549.6	549.6
2.5°	586.7	583.2
5°	754.6	758.1
7.5°	1016.2	1014.4
10°	1263.6	1279.5
12.5°	1443.8	1447.4
15°	1553.5	1560.5
17.5°	1595.9	1597.6
20°	1597.6	1594.1
22.5°	1578.1	1574.6
25°	1555.2	1553.5
27.5°	1534.0	1535.8
30°	1525.2	1530.4
32.5°	1525.2	1534.0
35°	1528.7	1537.6
37.5°	1526.9	1537.6
40°	1519.8	1532.2
42.5°	1500.4	1509.3
45°	1470.4	1481.0
47.5°	1431.5	1438.6
50°	1382.0	1389.0
52.5°	1320.2	1321.9
55°	1246.0	1253.0
57.5°	1166.4	1168.1
60°	1078.0	1083.3
62.5°	984.4	984.4
65°	885.4	888.9
67.5°	782.9	791.7
70°	678.7	680.4
72.5°	576.2	576.2
75°	470.1	471.8
77.5°	369.3	369.3
80°	273.9	275.7
82.5°	189.1	192.6
85°	118.4	118.4
87.5°	54.8	49.4
90°	31.0	31.0
92.5°	124.4	99.7
95°	433.4	358.6
97.5°	1038.3	896.0
100°	1496.0	1326.5
102.5°	1946.2	1801.0
105°	2520.3	2442.2
107.5°	2896.3	2915.2
110°	3039.6	3121.0



TEST NUMBER: P937053

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3052.4	3177.3
115°	2971.5	3144.7
117.5°	2799.8	2991.9
120°	2661.6	2848.2
122.5°	2526.9	2711.0
125°	2334.8	2504.3
127.5°	2162.0	2305.0
130°	2060.1	2192.3
132.5°	1967.7	2086.1
135°	1841.2	1943.2
137.5°	1739.6	1823.1
140°	1669.9	1747.9
142.5°	1612.2	1679.3
145°	1525.6	1576.4
147.5°	1459.1	1501.3
150°	1417.3	1451.5
152.5°	1381.6	1407.3
155°	1340.5	1357.5
157.5°	1308.0	1319.9
160°	1288.6	1295.4
162.5°	1275.8	1282.4
165°	1257.5	1264.4
167.5°	1244.4	1247.3
170°	1240.7	1240.7
172.5°	1231.0	1228.5
175°	1225.2	1225.2
177.5°	1220.0	1217.1
180°	1217.1	1217.1



TEST NUMBER: P937053
 CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.30	2.07	2.37	3.14	4.61	14.50	15.26	15.56	16.34	17.80
	3H	2.00	2.69	3.08	3.77	5.26	16.33	17.02	17.41	18.10	19.59
	4H	2.29	2.95	3.38	4.03	5.52	16.98	17.63	18.07	18.72	20.21
	6H	2.54	3.14	3.64	4.23	5.73	17.41	18.01	18.51	19.10	20.60
	8H	2.60	3.18	3.71	4.28	5.78	17.53	18.10	18.63	19.20	20.70
	12H	2.62	3.16	3.73	4.26	5.78	17.59	18.14	18.70	19.24	20.76
4H	2H	8.52	9.17	9.61	10.25	11.74	14.76	15.41	15.85	16.50	17.99
	3H	10.07	10.62	11.18	11.73	13.24	16.80	17.34	17.90	18.46	19.96
	4H	10.16	10.66	11.27	11.77	13.29	17.57	18.07	18.67	19.17	20.69
	6H	10.17	10.60	11.28	11.72	13.24	18.10	18.53	19.22	19.66	21.18
	8H	10.14	10.54	11.26	11.66	13.20	18.27	18.67	19.38	19.79	21.32
	12H	10.09	10.46	11.23	11.59	13.13	18.36	18.72	19.49	19.85	21.39
8H	4H	11.60	12.01	12.72	13.12	14.66	17.62	18.02	18.73	19.14	20.67
	6H	11.84	12.17	12.98	13.33	14.86	18.25	18.58	19.38	19.74	21.27
	8H	11.86	12.15	13.00	13.29	14.84	18.47	18.76	19.61	19.90	21.45
	12H	11.82	12.08	12.97	13.21	14.80	18.61	18.87	19.76	20.00	21.59
12H	4H	11.74	12.11	12.88	13.24	14.78	17.56	17.93	18.70	19.06	20.60
	6H	12.10	12.39	13.24	13.53	15.08	18.23	18.52	19.37	19.66	21.21
	8H	12.16	12.42	13.31	13.56	15.14	18.46	18.71	19.60	19.85	21.43