

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937260

Luminaire Tested: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P937260  
REPORT IS A COMBINATION OF REPORTS P933503 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5666.8 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 51.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937260  
CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3499	3499	3499
5°	3415	4041	4704
10°	3094	5887	7798
15°	2626	7686	9416
20°	2135	8900	9596
25°	1779	9305	9402
30°	1499	9358	9383
35°	1323	9195	9627
40°	1151	8986	9877
45°	1040	8830	9916
50°	952	8688	9752
55°	909	8484	9319
60°	927	8101	8636
65°	961	7522	7698
70°	1015	6547	6503
75°	1115	5325	5076
80°	1189	3680	3419
85°	1002	1943	1750

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 9916 cd/sqm



TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.8	0.9
10°-20°	216.2	3.8
20°-30°	378.2	6.7
30°-40°	486.8	8.6
40°-50°	543.8	9.6
50°-60°	520.8	9.2
60°-70°	412.7	7.3
70°-80°	242.7	4.3
80°-90°	69.0	1.2
90°-100°	206.6	3.6
100°-110°	543.2	9.6
110°-120°	563.2	9.9
120°-130°	451.8	8.0
130°-140°	354.5	6.3
140°-150°	272.1	4.8
150°-160°	195.9	3.5
160°-170°	119.9	2.1
170°-180°	40.5	0.7
0°-30°	643.1	11.3
0°-40°	1130.0	19.9
0°-60°	2194.5	38.7
0°-90°	2919.0	51.5
90°-120°	1313.1	23.2
90°-150°	2391.5	42.2
90°-180°	2748.0	48.5
0°-180°	5666.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	377	377	377	377	377	
5°	367	394	444	502	520	34
15°	275	508	856	1038	1071	77
25°	176	576	1020	1065	1066	81
35°	119	550	960	1015	1055	74
45°	81	439	849	972	1016	63
55°	58	279	720	837	860	53
65°	46	148	535	602	610	46
75°	34	91	294	323	324	36
85°	12	28	73	80	81	13
90°	3	8	22	11	11	3
95°	27	107	356	183	125	30
105°	98	148	600	912	851	104
115°	174	211	481	960	1095	172
125°	242	271	438	739	872	215
135°	288	317	424	597	677	223
145°	334	356	418	509	549	209
155°	378	388	418	459	473	174
165°	408	413	418	435	440	115
175°	424	424	421	427	427	40
180°	424	424	424	424	424	



TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1
2.5°	377.1	377.1	379.6	380.8	383.1	384.4	386.8	389.2	396.5	397.7	400.1
5°	367.4	372.3	388.0	394.1	411.0	434.1	443.8	459.6	492.3	502.0	508.0
7.5°	352.9	363.8	402.6	412.3	454.7	515.4	540.8	574.8	626.9	652.4	672.9
10°	329.8	352.9	422.0	445.0	514.1	606.3	653.6	700.8	779.7	814.8	828.2
12.5°	304.4	341.9	442.6	474.1	573.6	708.2	765.2	817.3	907.0	954.3	961.6
15°	275.2	326.1	462.0	508.0	636.6	793.1	856.1	920.4	1004.1	1038.0	1046.4
17.5°	249.8	314.0	480.1	528.7	685.2	869.4	933.7	987.1	1055.0	1078.0	1084.1
20°	218.2	294.7	492.3	555.4	736.1	925.2	987.1	1028.3	1074.3	1088.9	1091.3
22.5°	195.2	274.0	499.6	565.0	769.9	959.2	1011.3	1044.1	1075.5	1080.4	1081.6
25°	175.8	251.0	498.4	575.9	799.1	979.7	1019.7	1044.1	1062.2	1064.6	1064.6
27.5°	157.7	225.6	493.5	578.4	820.9	984.6	1016.2	1033.1	1041.6	1046.4	1046.4
30°	141.9	201.3	481.4	573.6	830.6	979.7	1005.2	1013.7	1022.2	1029.5	1033.1
32.5°	129.8	178.2	463.3	563.8	831.8	967.6	985.8	990.7	1002.8	1019.7	1025.9
35°	118.8	155.2	442.6	550.5	824.5	948.3	960.4	965.2	989.5	1015.0	1023.4
37.5°	107.9	138.2	415.9	527.5	813.6	925.2	933.7	942.2	979.7	1010.1	1019.7
40°	97.0	123.7	384.4	502.0	796.7	897.3	904.6	918.0	967.6	1002.8	1012.5
42.5°	88.6	111.6	350.5	475.4	774.8	865.8	876.7	896.1	953.1	990.7	1001.6
45°	81.2	99.4	314.0	438.9	746.9	833.1	848.8	875.5	936.1	972.5	982.2
47.5°	74.0	90.9	276.5	401.4	716.6	800.3	820.9	851.3	913.1	948.3	956.7
50°	67.9	82.5	238.9	361.4	683.9	765.2	789.4	820.9	884.0	916.7	927.6
52.5°	63.0	75.2	203.7	321.4	646.3	728.7	756.6	789.4	848.8	880.3	887.6
55°	58.2	69.1	173.4	278.9	607.5	689.9	720.3	751.8	810.0	836.7	841.5
57.5°	55.8	64.2	147.9	238.9	566.3	646.3	680.3	709.4	763.9	784.5	789.4
60°	52.1	60.7	128.6	204.9	521.4	605.0	634.2	663.3	709.4	726.4	729.9
62.5°	48.5	58.2	114.0	172.2	475.4	556.6	585.7	612.4	651.2	663.3	668.2
65°	46.1	55.8	103.1	147.9	428.0	505.6	534.7	557.8	589.3	601.5	603.8
67.5°	43.7	53.3	94.6	127.3	380.8	454.7	476.6	498.4	522.6	534.7	535.9
70°	40.0	50.9	87.3	112.8	332.2	396.5	414.7	437.7	457.1	463.3	466.8
72.5°	37.6	47.3	82.5	101.9	282.6	340.7	357.7	371.0	388.0	394.1	394.1
75°	34.0	42.4	77.6	90.9	231.6	278.9	293.5	306.8	320.1	322.6	318.9
77.5°	30.3	37.6	66.7	76.4	180.7	220.7	232.8	240.1	251.0	253.5	254.7
80°	25.4	32.8	52.1	59.4	131.0	162.5	171.0	177.0	186.8	186.8	189.1
82.5°	19.4	25.4	37.6	42.4	88.6	111.6	118.8	122.5	128.6	128.6	128.6
85°	12.1	15.8	24.2	27.9	53.3	67.9	72.8	74.0	78.8	80.0	80.0
87.5°	6.1	8.4	15.8	17.0	27.9	35.1	35.1	37.6	37.6	36.3	35.1
90°	2.8	5.1	7.4	8.0	12.6	18.6	21.7	19.3	14.4	10.8	10.8
92.5°	11.4	30.7	50.0	54.9	77.2	106.9	121.8	106.7	76.6	54.1	51.9
95°	27.3	62.8	98.2	107.0	190.0	300.5	355.9	317.5	240.9	183.4	176.9
97.5°	47.3	78.5	109.7	117.5	255.9	440.3	532.5	508.3	459.9	423.6	411.2
100°	62.6	90.9	119.2	126.3	279.8	484.5	586.9	588.6	592.2	594.8	580.1
102.5°	75.7	102.1	128.5	135.1	290.8	498.5	602.3	633.1	694.8	741.0	728.4
105°	97.8	120.2	142.6	148.2	299.0	500.1	600.5	669.7	808.0	911.7	904.9
107.5°	120.6	141.5	162.3	167.6	300.5	477.8	566.4	662.9	855.8	1000.5	1002.1
110°	136.0	154.8	173.7	178.4	298.3	458.0	538.0	645.8	861.4	1023.2	1030.3



TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	151.1	169.0	186.9	191.4	298.3	440.9	512.1	622.5	843.2	1008.7	1019.7
115°	173.8	190.3	206.9	211.1	301.1	421.0	481.1	587.4	800.0	959.5	974.6
117.5°	196.3	211.3	226.4	230.2	306.7	408.6	459.7	555.7	747.6	891.5	908.2
120°	209.4	223.6	237.7	241.3	311.2	404.5	451.1	538.9	714.2	845.7	862.0
122.5°	222.2	236.5	250.7	254.3	317.7	402.3	444.6	523.5	681.5	800.0	816.0
125°	241.8	254.8	267.9	271.1	326.6	400.6	437.6	504.6	638.8	739.4	754.2
127.5°	257.8	270.9	284.0	287.3	335.4	399.6	431.6	489.2	604.4	690.7	703.2
130°	266.3	280.4	294.6	298.2	341.8	400.1	429.3	480.6	583.1	660.0	671.5
132.5°	275.1	289.3	303.4	307.0	347.1	400.6	427.3	473.2	565.0	633.9	644.1
135°	288.2	301.0	313.9	317.2	352.8	400.2	423.9	462.3	539.2	596.9	605.8
137.5°	301.6	314.3	327.1	330.3	361.3	402.7	423.3	455.8	520.8	569.5	576.8
140°	312.7	324.4	336.2	339.1	366.5	403.1	421.3	449.4	505.5	547.6	554.4
142.5°	321.2	332.0	342.9	345.6	370.8	404.5	421.3	446.0	495.3	532.3	538.1
145°	334.2	343.8	353.2	355.6	376.5	404.5	418.5	438.7	478.9	509.2	513.6
147.5°	347.3	356.5	365.8	368.1	384.9	407.3	418.5	434.3	466.1	489.9	493.5
150°	355.9	364.2	372.6	374.7	389.3	408.7	418.5	431.9	458.7	478.8	481.7
152.5°	364.7	371.0	377.4	378.9	392.1	409.7	418.5	429.9	452.8	470.0	472.2
155°	377.8	382.5	387.1	388.3	398.4	411.8	418.5	427.6	445.7	459.4	460.9
157.5°	387.5	392.0	396.6	397.7	404.6	413.9	418.5	425.5	439.7	450.3	451.3
160°	394.0	397.5	401.0	402.0	407.5	414.8	418.5	424.5	436.7	445.8	446.4
162.5°	400.6	403.2	405.9	406.5	410.5	415.8	418.5	423.6	433.8	441.5	442.1
165°	407.6	410.0	412.4	413.1	414.9	417.3	418.5	422.1	429.5	435.0	435.6
167.5°	414.2	415.3	416.4	416.7	418.3	420.3	421.3	423.7	428.6	432.1	432.4
170°	418.5	419.6	420.8	421.0	421.1	421.2	421.3	423.7	428.6	432.1	432.1
172.5°	420.8	421.0	421.2	421.3	421.3	421.3	421.3	423.2	427.0	429.8	429.7
175°	423.9	423.9	423.9	423.9	423.1	421.9	421.3	422.5	424.9	426.7	426.7
177.5°	423.9	423.9	423.9	423.9	423.2	422.3	421.9	422.8	424.7	426.2	425.9
180°	423.9	423.9	423.9	423.9	423.9	423.9	423.9	423.9	423.9	423.9	423.9



TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	377.1	377.1
2.5°	402.6	400.1
5°	517.8	520.2
7.5°	697.3	696.0
10°	867.0	877.9
12.5°	990.7	993.1
15°	1065.9	1070.7
17.5°	1095.0	1096.2
20°	1096.2	1093.7
22.5°	1082.9	1080.4
25°	1067.1	1065.9
27.5°	1052.5	1053.7
30°	1046.4	1050.1
32.5°	1046.4	1052.5
35°	1048.9	1055.0
37.5°	1047.6	1055.0
40°	1042.9	1051.3
42.5°	1029.5	1035.5
45°	1008.9	1016.2
47.5°	982.2	987.1
50°	948.3	953.1
52.5°	905.8	907.0
55°	854.8	859.7
57.5°	800.3	801.5
60°	739.7	743.3
62.5°	675.4	675.4
65°	607.5	609.9
67.5°	537.2	543.3
70°	465.6	466.8
72.5°	395.3	395.3
75°	322.6	323.8
77.5°	253.5	253.5
80°	187.9	189.1
82.5°	129.8	132.1
85°	81.2	81.2
87.5°	37.6	34.0
90°	10.8	10.8
92.5°	43.3	34.7
95°	151.0	124.9
97.5°	361.7	312.1
100°	521.1	462.0
102.5°	677.8	627.2
105°	877.8	850.6
107.5°	1008.7	1015.3
110°	1058.7	1087.0





TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1063.1	1106.6
115°	1035.0	1095.3
117.5°	975.1	1042.0
120°	927.0	991.9
122.5°	880.1	944.2
125°	813.2	872.2
127.5°	753.0	802.8
130°	717.5	763.5
132.5°	685.3	726.5
135°	641.3	676.8
137.5°	605.9	635.0
140°	581.6	608.8
142.5°	561.4	584.8
145°	531.3	549.1
147.5°	508.2	522.9
150°	493.6	505.6
152.5°	481.1	490.1
155°	466.8	472.8
157.5°	455.5	459.7
160°	448.8	451.1
162.5°	444.3	446.6
165°	438.0	440.4
167.5°	433.4	434.4
170°	432.1	432.1
172.5°	428.7	427.8
175°	426.7	426.7
177.5°	424.9	423.9
180°	423.9	423.9



TEST NUMBER: P937260

CATALOG NUMBER: SQ4-FB-075U-100D-93050-1D-UNV-STD-W-4-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.48	6.39	6.41	7.35	8.60	18.62	19.53	19.55	20.49	21.74
	3H	6.19	7.01	7.14	7.98	9.25	20.45	21.27	21.39	22.24	23.51
	4H	6.49	7.27	7.45	8.24	9.52	21.08	21.86	22.05	22.84	24.11
	6H	6.74	7.46	7.72	8.44	9.73	21.51	22.23	22.48	23.20	24.49
	8H	6.81	7.50	7.79	8.49	9.78	21.62	22.31	22.60	23.30	24.59
	12H	6.83	7.49	7.82	8.47	9.79	21.68	22.34	22.67	23.33	24.64
4H	2H	12.68	13.46	13.64	14.43	15.71	18.90	19.68	19.87	20.65	21.93
	3H	14.25	14.90	15.23	15.91	17.20	20.94	21.59	21.91	22.59	23.88
	4H	14.35	14.95	15.34	15.94	17.26	21.70	22.29	22.68	23.29	24.60
	6H	14.36	14.88	15.36	15.90	17.21	22.23	22.74	23.22	23.76	25.07
	8H	14.34	14.82	15.34	15.84	17.17	22.38	22.87	23.38	23.88	25.21
	12H	14.30	14.74	15.32	15.77	17.10	22.47	22.91	23.49	23.93	25.27
8H	4H	15.79	16.27	16.79	17.28	18.61	21.76	22.24	22.76	23.26	24.59
	6H	16.03	16.43	17.06	17.49	18.81	22.38	22.78	23.41	23.83	25.16
	8H	16.05	16.41	17.09	17.45	18.79	22.59	22.95	23.63	23.99	25.33
	12H	16.02	16.33	17.06	17.37	18.76	22.73	23.04	23.77	24.08	25.47
12H	4H	15.93	16.37	16.95	17.40	18.73	21.72	22.15	22.74	23.18	24.52
	6H	16.29	16.64	17.32	17.68	19.03	22.37	22.72	23.40	23.76	25.10
	8H	16.36	16.67	17.40	17.71	19.10	22.59	22.90	23.63	23.94	25.32