

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937455

Luminaire Tested: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937455
REPORT IS A COMBINATION OF REPORTS P933557 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15298.2 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 123.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937455
CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P937455

CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	11	9	7
10	43	31	24	19	38	28	22	18	22	18	14	17	14	11	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1752	1752	1752
5°	1712	2025	2355
10°	1554	2953	3904
15°	1321	3859	4714
20°	1076	4474	4805
25°	898	4682	4707
30°	757	4713	4698
35°	670	4636	4820
40°	584	4536	4945
45°	529	4462	4965
50°	486	4397	4882
55°	466	4300	4666
60°	477	4114	4324
65°	498	3828	3854
70°	531	3341	3256
75°	591	2726	2541
80°	651	1893	1712
85°	590	1006	876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4965 cd/sqm



TEST NUMBER: P937455

CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	0.5
10°-20°	324.7	2.1
20°-30°	568.0	3.7
30°-40°	731.2	4.8
40°-50°	816.7	5.3
50°-60°	782.2	5.1
60°-70°	619.9	4.1
70°-80°	364.5	2.4
80°-90°	107.7	0.7
90°-100°	820.3	5.4
100°-110°	2156.7	14.1
110°-120°	2236.3	14.6
120°-130°	1793.8	11.7
130°-140°	1407.5	9.2
140°-150°	1080.3	7.1
150°-160°	778.0	5.1
160°-170°	476.0	3.1
170°-180°	160.8	1.1
0°-30°	966.0	6.3
0°-40°	1697.2	11.1
0°-60°	3296.2	21.5
0°-90°	4388.3	28.7
90°-120°	5213.4	34.1
90°-150°	9495.0	62.1
90°-180°	10910.0	71.3
0°-180°	15298.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	552	592	667	754	781	51
15°	414	763	1286	1559	1608	115
25°	264	865	1532	1599	1601	122
35°	178	827	1442	1524	1585	111
45°	122	659	1275	1461	1526	94
55°	87	419	1082	1257	1291	80
65°	69	222	803	903	916	69
75°	51	137	441	484	486	53
85°	18	42	109	120	122	19
90°	11	32	86	43	43	11
95°	108	425	1413	728	496	120
105°	389	588	2384	3620	3377	412
115°	690	838	1910	3810	4348	682
125°	960	1076	1737	2936	3463	852
135°	1144	1259	1683	2370	2687	885
145°	1327	1412	1662	2022	2180	831
155°	1500	1542	1662	1824	1877	689
165°	1618	1640	1662	1727	1748	457
175°	1683	1683	1673	1694	1694	160
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P937455

CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	566.4	566.4	566.4	566.4	566.4	566.4	566.4	566.4	566.4	566.4	566.4
2.5°	566.4	566.4	570.1	571.9	575.5	577.3	581.0	584.6	595.6	597.4	601.0
5°	551.9	559.1	582.8	591.9	617.4	652.0	666.6	690.3	739.4	754.0	763.1
7.5°	530.0	546.4	604.6	619.2	683.0	774.1	812.3	863.3	941.6	979.8	1010.8
10°	495.4	530.0	633.8	668.5	772.2	910.7	981.6	1052.7	1171.1	1224.0	1244.0
12.5°	457.1	513.6	664.8	712.1	861.4	1063.7	1149.3	1227.6	1362.4	1433.4	1444.3
15°	413.5	490.0	693.9	763.1	956.2	1191.1	1285.9	1382.4	1508.1	1559.0	1571.8
17.5°	375.2	471.7	721.2	794.1	1029.1	1305.9	1402.4	1482.6	1584.6	1619.2	1628.3
20°	327.8	442.6	739.4	834.2	1105.6	1389.7	1482.6	1544.5	1613.7	1635.5	1639.2
22.5°	293.3	411.6	750.4	848.8	1156.5	1440.7	1519.0	1568.2	1615.5	1622.8	1624.6
25°	264.1	377.0	748.6	865.2	1200.2	1471.6	1531.7	1568.2	1595.4	1599.1	1599.1
27.5°	236.8	338.8	741.2	868.8	1233.0	1478.9	1526.3	1551.7	1564.5	1571.8	1571.8
30°	213.1	302.3	723.0	861.4	1247.6	1471.6	1509.9	1522.7	1535.3	1546.3	1551.7
32.5°	194.9	267.7	695.7	846.9	1249.4	1453.4	1480.8	1488.0	1506.2	1531.7	1540.9
35°	178.5	233.2	664.8	826.9	1238.5	1424.3	1442.5	1449.8	1486.2	1524.5	1537.1
37.5°	162.1	207.6	624.7	792.3	1222.1	1389.7	1402.4	1415.1	1471.6	1517.1	1531.7
40°	145.7	185.7	577.3	754.0	1196.6	1347.8	1358.7	1378.7	1453.4	1506.2	1520.8
42.5°	133.0	167.5	526.4	714.0	1163.9	1300.4	1316.8	1346.0	1431.5	1488.0	1504.4
45°	122.0	149.4	471.7	659.3	1121.9	1251.2	1274.9	1315.0	1406.1	1460.7	1475.2
47.5°	111.1	136.6	415.3	602.8	1076.4	1202.1	1233.0	1278.5	1371.4	1424.3	1437.0
50°	102.0	123.8	358.8	542.7	1027.2	1149.3	1185.7	1233.0	1327.8	1376.9	1393.3
52.5°	94.7	113.0	305.9	482.6	970.8	1094.6	1136.5	1185.7	1274.9	1322.3	1333.2
55°	87.4	103.8	260.4	418.9	912.5	1036.3	1081.8	1129.2	1216.6	1256.7	1264.0
57.5°	83.8	96.5	222.2	358.8	850.6	970.8	1021.7	1065.5	1147.4	1178.4	1185.7
60°	78.3	91.1	193.1	307.8	783.1	908.9	952.6	996.2	1065.5	1091.0	1096.4
62.5°	72.9	87.4	171.2	258.6	714.0	836.0	879.7	919.7	978.0	996.2	1003.6
65°	69.2	83.8	154.8	222.2	642.9	759.5	803.2	837.8	885.2	903.4	907.0
67.5°	65.5	80.1	142.0	191.3	571.9	683.0	715.8	748.6	785.0	803.2	805.1
70°	60.1	76.5	131.2	169.4	499.0	595.6	622.9	657.5	686.7	695.7	701.2
72.5°	56.5	71.1	123.8	153.0	424.3	511.8	537.3	557.3	582.8	591.9	591.9
75°	51.0	63.7	116.6	136.6	347.9	418.9	440.7	460.8	480.8	484.4	479.0
77.5°	45.5	56.5	100.2	114.8	271.4	331.5	349.7	360.6	377.0	380.6	382.4
80°	38.3	49.2	78.3	89.2	196.7	244.0	256.8	265.9	280.5	280.5	284.1
82.5°	29.1	38.3	56.5	63.7	133.0	167.5	178.5	183.9	193.1	193.1	193.1
85°	18.2	23.7	36.4	41.9	80.1	102.0	109.3	111.1	118.4	120.2	120.2
87.5°	9.1	12.8	23.7	25.5	41.9	52.9	52.9	56.5	56.5	54.7	52.9
90°	11.3	20.4	29.3	31.6	49.7	73.8	85.8	76.3	57.2	42.9	42.9
92.5°	45.2	121.9	198.8	218.0	306.5	424.4	483.4	423.7	304.2	214.6	206.1
95°	108.4	249.0	389.6	424.7	754.1	1193.4	1413.0	1260.9	956.7	728.5	702.6
97.5°	187.5	311.5	435.5	466.5	1015.8	1748.1	2114.4	2018.2	1826.0	1681.8	1632.6
100°	248.5	360.9	473.3	501.5	1111.0	1923.7	2330.2	2337.2	2351.2	2361.7	2303.2
102.5°	300.4	405.3	510.2	536.5	1154.7	1979.0	2391.2	2513.6	2758.6	2942.3	2892.1
105°	388.6	477.4	566.3	588.4	1187.1	1985.3	2384.4	2659.0	3208.2	3620.0	3593.0
107.5°	478.9	561.7	644.6	665.3	1193.1	1896.9	2248.8	2631.8	3397.9	3972.4	3978.9
110°	539.9	614.7	689.5	708.2	1184.0	1818.6	2135.8	2564.0	3420.4	4062.7	4090.9



TEST NUMBER: P937455

CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	599.8	671.1	742.3	760.2	1184.5	1750.2	2033.1	2471.4	3347.8	4005.2	4048.3
115°	690.1	755.9	821.6	838.1	1195.4	1671.7	1910.0	2332.1	3176.5	3809.7	3869.6
117.5°	779.3	839.1	898.8	913.8	1217.6	1622.7	1825.3	2206.2	2968.3	3539.8	3606.2
120°	831.3	887.5	943.8	957.8	1235.7	1606.2	1791.4	2139.5	2835.8	3358.0	3422.5
122.5°	882.2	938.9	995.6	1009.8	1261.7	1597.5	1765.4	2078.9	2705.9	3176.1	3239.8
125°	960.1	1011.8	1063.5	1076.4	1296.6	1590.4	1737.2	2003.5	2536.1	2935.5	2994.1
127.5°	1023.3	1075.5	1127.7	1140.8	1331.7	1586.2	1713.5	1942.1	2399.4	2742.4	2791.8
130°	1057.2	1113.4	1169.6	1183.7	1357.3	1588.7	1704.4	1908.0	2315.1	2620.4	2666.2
132.5°	1092.3	1148.5	1204.7	1218.7	1377.9	1590.3	1696.5	1878.7	2243.2	2516.5	2557.4
135°	1144.2	1195.4	1246.6	1259.4	1400.6	1588.8	1683.0	1835.6	2140.7	2369.6	2404.9
137.5°	1197.3	1247.9	1298.6	1311.3	1434.4	1598.6	1680.7	1809.7	2067.7	2261.3	2290.1
140°	1241.3	1288.0	1334.7	1346.3	1455.1	1600.2	1672.7	1784.2	2007.1	2174.3	2201.3
142.5°	1275.2	1318.4	1361.5	1372.3	1472.4	1605.9	1672.7	1770.7	1966.5	2113.3	2136.5
145°	1327.1	1364.8	1402.5	1411.9	1495.1	1606.0	1661.5	1741.5	1901.7	2021.8	2039.3
147.5°	1379.1	1415.8	1452.4	1461.6	1528.2	1617.1	1661.5	1724.5	1850.5	1945.0	1959.6
150°	1413.0	1446.1	1479.2	1487.5	1545.6	1622.9	1661.5	1714.7	1821.1	1900.9	1912.7
152.5°	1448.0	1473.1	1498.2	1504.5	1556.8	1626.6	1661.5	1707.0	1797.7	1865.9	1874.8
155°	1499.9	1518.5	1537.1	1541.8	1581.7	1634.9	1661.5	1697.6	1769.9	1824.1	1830.0
157.5°	1538.3	1556.4	1574.5	1579.1	1606.6	1643.2	1661.5	1689.6	1745.8	1788.0	1792.1
160°	1564.3	1578.4	1592.4	1596.0	1617.8	1646.9	1661.5	1685.6	1733.7	1769.9	1772.2
162.5°	1590.3	1600.8	1611.4	1614.0	1629.8	1650.9	1661.5	1681.8	1722.4	1752.9	1755.2
165°	1618.5	1628.0	1637.6	1640.0	1647.1	1656.7	1661.5	1676.1	1705.1	1727.0	1729.3
167.5°	1644.5	1649.0	1653.5	1654.7	1660.7	1668.8	1672.7	1682.3	1701.4	1715.7	1716.7
170°	1661.5	1666.0	1670.6	1671.7	1672.0	1672.5	1672.7	1682.3	1701.4	1715.7	1715.7
172.5°	1670.5	1671.5	1672.5	1672.7	1672.7	1672.7	1672.7	1680.3	1695.4	1706.7	1705.8
175°	1683.0	1683.0	1683.0	1683.0	1679.5	1675.0	1672.7	1677.5	1687.0	1694.2	1694.2
177.5°	1683.0	1683.0	1683.0	1683.0	1680.3	1676.8	1675.0	1678.8	1686.3	1691.9	1690.9
180°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0



TEST NUMBER: P937455

CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	566.4	566.4
2.5°	604.6	601.0
5°	777.7	781.3
7.5°	1047.3	1045.5
10°	1302.3	1318.6
12.5°	1488.0	1491.6
15°	1601.0	1608.2
17.5°	1644.7	1646.5
20°	1646.5	1642.9
22.5°	1626.4	1622.8
25°	1602.8	1601.0
27.5°	1580.9	1582.8
30°	1571.8	1577.2
32.5°	1571.8	1580.9
35°	1575.4	1584.6
37.5°	1573.6	1584.6
40°	1566.3	1579.1
42.5°	1546.3	1555.4
45°	1515.3	1526.3
47.5°	1475.2	1482.6
50°	1424.3	1431.5
52.5°	1360.5	1362.4
55°	1284.1	1291.3
57.5°	1202.1	1203.9
60°	1111.0	1116.4
62.5°	1014.5	1014.5
65°	912.5	916.1
67.5°	806.9	815.9
70°	699.4	701.2
72.5°	593.8	593.8
75°	484.4	486.3
77.5°	380.6	380.6
80°	282.3	284.1
82.5°	194.9	198.5
85°	122.0	122.0
87.5°	56.5	51.0
90°	42.9	42.9
92.5°	171.9	137.8
95°	599.2	495.8
97.5°	1435.9	1239.1
100°	2068.7	1834.3
102.5°	2691.3	2490.6
105°	3485.1	3377.2
107.5°	4005.1	4031.1
110°	4203.3	4315.8



TEST NUMBER: P937455

CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4221.0	4393.7
115°	4109.1	4348.5
117.5°	3871.7	4137.3
120°	3680.5	3938.5
122.5°	3494.2	3748.7
125°	3228.5	3463.0
127.5°	2989.7	3187.4
130°	2848.8	3031.6
132.5°	2721.1	2884.7
135°	2545.9	2687.1
137.5°	2405.6	2521.1
140°	2309.2	2417.1
142.5°	2229.3	2322.2
145°	2109.7	2179.9
147.5°	2017.8	2076.0
150°	1959.9	2007.1
152.5°	1910.4	1946.1
155°	1853.6	1877.2
157.5°	1808.7	1825.3
160°	1781.8	1791.4
162.5°	1764.2	1773.3
165°	1738.9	1748.4
167.5°	1720.7	1724.7
170°	1715.7	1715.7
172.5°	1702.2	1698.7
175°	1694.2	1694.2
177.5°	1686.9	1683.0
180°	1683.0	1683.0



TEST NUMBER: P937455
 CATALOG NUMBER: SQ4-FB-100U-050D-93050-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.59	1.30	1.70	2.42	3.96	13.78	14.49	14.89	15.61	17.15
	3H	1.28	1.92	2.40	3.04	4.60	15.61	16.25	16.73	17.38	18.94
	4H	1.57	2.18	2.70	3.30	4.87	16.25	16.86	17.39	17.99	19.55
	6H	1.81	2.38	2.96	3.50	5.08	16.68	17.24	17.82	18.37	19.94
	8H	1.88	2.41	3.02	3.55	5.12	16.80	17.33	17.94	18.48	20.05
	12H	1.89	2.40	3.04	3.53	5.13	16.86	17.37	18.01	18.51	20.10
4H	2H	7.79	8.40	8.93	9.52	11.09	14.03	14.64	15.17	15.77	17.33
	3H	9.34	9.86	10.49	11.00	12.58	16.07	16.58	17.22	17.73	19.31
	4H	9.43	9.90	10.58	11.04	12.64	16.83	17.30	17.98	18.44	20.04
	6H	9.43	9.84	10.59	11.00	12.58	17.37	17.77	18.53	18.93	20.52
	8H	9.41	9.78	10.56	10.94	12.54	17.53	17.91	18.69	19.06	20.66
	12H	9.36	9.70	10.53	10.86	12.47	17.62	17.96	18.79	19.12	20.73
8H	4H	10.87	11.24	12.02	12.40	14.00	16.88	17.26	18.04	18.41	20.02
	6H	11.10	11.41	12.28	12.61	14.21	17.51	17.82	18.68	19.01	20.62
	8H	11.12	11.39	12.30	12.56	14.18	17.73	18.00	18.91	19.17	20.79
	12H	11.08	11.32	12.27	12.49	14.14	17.87	18.11	19.06	19.28	20.93
12H	4H	11.00	11.35	12.18	12.51	14.12	16.83	17.17	18.00	18.33	19.94
	6H	11.36	11.63	12.54	12.81	14.43	17.49	17.76	18.67	18.93	20.56
	8H	11.42	11.66	12.61	12.83	14.49	17.72	17.95	18.90	19.12	20.78