

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937759

Luminaire Tested: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937759
REPORT IS A COMBINATION OF REPORTS P933568 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7323.7 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 68.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937759
CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	56	56	56	50
1	97	93	89	85	90	86	82	79	72	70	67	60	58	57	49	48	47	49	48	47	41
2	88	80	74	68	81	74	69	64	63	59	55	52	49	46	42	40	38	42	40	38	34
3	80	70	62	56	73	65	58	53	55	50	45	46	42	39	37	34	32	37	34	32	28
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	30	27	33	30	27	23
5	67	54	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23	29	26	23	20
6	61	49	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20	26	23	20	17
7	56	44	35	30	52	40	33	28	34	29	24	29	24	21	24	20	17	24	20	17	15
8	52	39	31	26	48	37	29	24	31	25	21	26	22	18	22	18	15	22	18	15	13
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	20	16	14	20	16	14	11
10	45	33	25	20	41	30	24	19	26	21	17	22	18	15	18	15	12	18	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4420	4420	4420
5°	4314	5105	5941
10°	3908	7435	9850
15°	3318	9707	11893
20°	2698	11242	12121
25°	2248	11755	11875
30°	1893	11820	11852
35°	1671	11614	12159
40°	1455	11350	12475
45°	1314	11154	12524
50°	1203	10974	12318
55°	1148	10716	11771
60°	1172	10232	10909
65°	1213	9501	9724
70°	1282	8270	8216
75°	1407	6726	6412
80°	1502	4648	4321
85°	1267	2453	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12524 cd/sqm



TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.6	0.8
10°-20°	273.1	3.7
20°-30°	477.7	6.5
30°-40°	614.9	8.4
40°-50°	686.8	9.4
50°-60°	657.8	9.0
60°-70°	521.3	7.1
70°-80°	306.5	4.2
80°-90°	87.3	1.2
90°-100°	273.4	3.7
100°-110°	718.9	9.8
110°-120°	745.4	10.2
120°-130°	597.9	8.2
130°-140°	469.2	6.4
140°-150°	360.1	4.9
150°-160°	259.3	3.5
160°-170°	158.7	2.2
170°-180°	53.6	0.7
0°-30°	812.4	11.1
0°-40°	1427.3	19.5
0°-60°	2771.9	37.8
0°-90°	3687.1	50.3
90°-120°	1737.8	23.7
90°-150°	3165.0	43.2
90°-180°	3637.0	49.7
0°-180°	7323.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	476	476	476	476	476	
5°	464	498	561	634	657	43
15°	348	642	1081	1311	1352	97
25°	222	728	1288	1345	1346	102
35°	150	695	1213	1282	1332	94
45°	103	554	1072	1228	1284	79
55°	74	352	910	1057	1086	67
65°	58	187	675	760	770	58
75°	43	115	371	407	409	45
85°	15	35	92	101	103	16
90°	4	10	29	14	14	4
95°	36	142	471	243	165	40
105°	130	196	795	1207	1126	137
115°	230	279	637	1270	1450	227
125°	320	359	579	978	1154	284
135°	381	420	561	790	896	295
145°	442	471	554	674	727	277
155°	500	514	554	608	626	230
165°	540	547	554	576	583	152
175°	561	561	558	565	565	53
180°	561	561	561	561	561	



TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3	476.3
2.5°	476.3	476.3	479.4	480.9	484.0	485.5	488.6	491.7	500.8	502.4	505.4
5°	464.1	470.2	490.1	497.7	519.2	548.3	560.6	580.5	621.8	634.1	641.8
7.5°	445.7	459.5	508.5	520.7	574.3	650.9	683.1	726.0	791.8	824.0	850.0
10°	416.6	445.7	533.0	562.1	649.4	765.8	825.5	885.2	984.8	1029.3	1046.1
12.5°	384.4	431.9	559.0	598.9	724.5	894.5	966.4	1032.3	1145.7	1205.4	1214.5
15°	347.7	412.0	583.6	641.8	804.1	1001.7	1081.3	1162.5	1268.2	1311.0	1321.8
17.5°	315.5	396.7	606.5	667.8	865.3	1098.1	1179.3	1246.8	1332.5	1361.6	1369.2
20°	275.7	372.2	621.8	701.5	929.7	1168.7	1246.8	1298.8	1357.0	1375.4	1378.5
22.5°	246.6	346.1	631.0	713.7	972.6	1211.5	1277.4	1318.7	1358.6	1364.7	1366.2
25°	222.1	317.1	629.5	727.5	1009.3	1237.5	1288.1	1318.7	1341.7	1344.8	1344.8
27.5°	199.1	284.9	623.4	730.6	1036.9	1243.7	1283.5	1305.0	1315.7	1321.8	1321.8
30°	179.2	254.3	608.1	724.5	1049.2	1237.5	1269.7	1280.4	1291.1	1300.4	1305.0
32.5°	163.9	225.1	585.1	712.2	1050.7	1222.2	1245.2	1251.3	1266.7	1288.1	1295.7
35°	150.1	196.1	559.0	695.3	1041.5	1197.7	1213.0	1219.2	1249.8	1282.0	1292.7
37.5°	136.3	174.6	525.4	666.3	1027.7	1168.7	1179.3	1190.1	1237.5	1275.8	1288.1
40°	122.6	156.2	485.5	634.1	1006.3	1133.4	1142.6	1159.4	1222.2	1266.7	1278.9
42.5°	111.8	140.9	442.6	600.4	978.7	1093.6	1107.4	1131.9	1203.9	1251.3	1265.1
45°	102.6	125.6	396.7	554.4	943.4	1052.2	1072.2	1105.8	1182.4	1228.4	1240.6
47.5°	93.4	114.9	349.2	507.0	905.2	1010.9	1036.9	1075.2	1153.3	1197.7	1208.5
50°	85.8	104.2	301.7	456.4	863.8	966.4	997.1	1036.9	1116.5	1157.9	1171.7
52.5°	79.7	95.0	257.3	405.9	816.4	920.5	955.8	997.1	1072.2	1112.0	1121.1
55°	73.5	87.3	219.0	352.3	767.3	871.5	909.8	949.6	1023.1	1056.8	1062.9
57.5°	70.4	81.2	186.8	301.7	715.3	816.4	859.3	896.0	964.9	991.0	997.1
60°	65.9	76.6	162.4	258.9	658.6	764.3	801.1	837.8	896.0	917.5	922.0
62.5°	61.3	73.5	144.0	217.5	600.4	703.0	739.8	773.5	822.5	837.8	843.9
65°	58.2	70.4	130.2	186.8	540.7	638.7	675.4	704.6	744.4	759.7	762.8
67.5°	55.1	67.4	119.5	160.8	480.9	574.3	601.9	629.5	660.1	675.4	677.0
70°	50.5	64.4	110.2	142.5	419.6	500.8	523.8	552.9	577.4	585.1	589.7
72.5°	47.5	59.7	104.2	128.6	356.9	430.4	451.9	468.7	490.1	497.7	497.7
75°	42.9	53.6	98.0	114.9	292.5	352.3	370.7	387.5	404.3	407.4	402.8
77.5°	38.3	47.5	84.3	96.5	228.2	278.8	294.1	303.2	317.1	320.1	321.6
80°	32.1	41.4	65.9	75.0	165.4	205.2	216.0	223.6	235.9	235.9	239.0
82.5°	24.5	32.1	47.5	53.6	111.8	140.9	150.1	154.7	162.4	162.4	162.4
85°	15.3	19.9	30.6	35.2	67.4	85.8	91.9	93.4	99.6	101.1	101.1
87.5°	7.7	10.7	19.9	21.5	35.2	44.4	44.4	47.5	47.5	46.0	44.4
90°	3.8	6.8	9.8	10.5	16.6	24.6	28.6	25.4	19.1	14.3	14.3
92.5°	15.0	40.6	66.3	72.7	102.2	141.5	161.1	141.2	101.4	71.5	68.7
95°	36.1	83.0	129.9	141.6	251.4	397.7	471.0	420.3	318.9	242.9	234.3
97.5°	62.5	103.8	145.2	155.5	338.6	582.7	704.8	672.7	608.6	560.6	544.2
100°	82.8	120.3	157.8	167.2	370.4	641.3	776.7	779.1	783.7	787.2	767.7
102.5°	100.1	135.1	170.1	178.9	385.0	659.7	797.1	837.9	919.6	980.7	964.0
105°	129.5	159.1	188.7	196.1	395.7	661.8	794.8	886.3	1069.4	1206.7	1197.7
107.5°	159.7	187.3	214.9	221.8	397.7	632.3	749.6	877.3	1132.6	1324.2	1326.3
110°	179.9	204.9	229.8	236.1	394.7	606.2	711.9	854.7	1140.1	1354.2	1363.6



TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	200.0	223.7	247.4	253.4	394.8	583.4	677.7	823.8	1115.9	1335.0	1349.4
115°	230.0	251.9	273.8	279.3	398.5	557.3	636.7	777.4	1058.9	1269.9	1289.9
117.5°	259.8	279.7	299.6	304.6	405.9	540.9	608.4	735.4	989.4	1180.0	1202.1
120°	277.1	295.8	314.5	319.3	411.8	535.4	597.1	713.2	945.3	1119.3	1140.9
122.5°	294.1	313.0	331.9	336.6	420.5	532.5	588.4	692.9	901.9	1058.7	1079.9
125°	320.1	337.3	354.5	358.8	432.2	530.1	579.0	667.8	845.3	978.5	998.0
127.5°	341.1	358.4	375.9	380.3	443.9	528.7	571.2	647.4	799.8	914.1	930.6
130°	352.4	371.1	389.9	394.6	452.4	529.6	568.2	636.1	771.7	873.5	888.7
132.5°	364.1	382.8	401.5	406.2	459.3	530.1	565.5	626.2	747.7	838.8	852.5
135°	381.4	398.5	415.6	419.8	466.9	529.6	561.0	611.9	713.5	789.8	801.6
137.5°	399.1	416.0	432.8	437.1	478.1	532.9	560.2	603.2	689.2	753.7	763.3
140°	413.7	429.3	444.9	448.8	485.1	533.4	557.6	594.7	669.0	724.8	733.7
142.5°	425.1	439.5	453.8	457.5	490.9	535.3	557.6	590.2	655.4	704.4	712.2
145°	442.4	454.9	467.4	470.6	498.4	535.4	553.9	580.6	633.9	673.9	679.8
147.5°	459.7	472.0	484.1	487.2	509.4	539.0	553.9	574.9	616.9	648.4	653.3
150°	471.0	482.0	493.0	495.8	515.2	541.0	553.9	571.6	607.0	633.6	637.5
152.5°	482.6	491.0	499.4	501.5	518.9	542.2	553.9	569.0	599.2	621.9	624.9
155°	500.0	506.2	512.4	514.0	527.3	545.0	553.9	565.9	590.0	608.0	610.0
157.5°	512.8	518.8	524.8	526.4	535.5	547.7	553.9	563.2	581.9	596.0	597.3
160°	521.5	526.2	530.8	532.0	539.3	549.0	553.9	561.9	577.9	590.0	590.8
162.5°	530.1	533.6	537.1	538.0	543.3	550.3	553.9	560.7	574.1	584.3	585.0
165°	539.5	542.6	545.8	546.6	549.1	552.2	553.9	558.8	568.4	575.7	576.5
167.5°	548.2	549.7	551.2	551.6	553.6	556.2	557.6	560.7	567.1	571.9	572.2
170°	553.9	555.3	556.9	557.2	557.3	557.5	557.6	560.7	567.1	571.9	571.9
172.5°	556.9	557.2	557.5	557.6	557.6	557.6	557.6	560.1	565.1	568.9	568.6
175°	561.0	561.0	561.0	561.0	559.8	558.3	557.6	559.2	562.4	564.7	564.7
177.5°	561.0	561.0	561.0	561.0	560.1	558.9	558.3	559.6	562.1	564.0	563.6
180°	561.0	561.0	561.0	561.0	561.0	561.0	561.0	561.0	561.0	561.0	561.0



TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	476.3	476.3
2.5°	508.5	505.4
5°	654.0	657.1
7.5°	880.7	879.2
10°	1095.1	1108.9
12.5°	1251.3	1254.4
15°	1346.3	1352.4
17.5°	1383.1	1384.6
20°	1384.6	1381.5
22.5°	1367.7	1364.7
25°	1347.8	1346.3
27.5°	1329.4	1330.9
30°	1321.8	1326.4
32.5°	1321.8	1329.4
35°	1324.9	1332.5
37.5°	1323.3	1332.5
40°	1317.2	1327.9
42.5°	1300.4	1308.0
45°	1274.3	1283.5
47.5°	1240.6	1246.8
50°	1197.7	1203.9
52.5°	1144.1	1145.7
55°	1079.8	1085.9
57.5°	1010.9	1012.4
60°	934.3	938.9
62.5°	853.1	853.1
65°	767.3	770.4
67.5°	678.5	686.2
70°	588.2	589.7
72.5°	499.3	499.3
75°	407.4	409.0
77.5°	320.1	320.1
80°	237.4	239.0
82.5°	163.9	166.9
85°	102.6	102.6
87.5°	47.5	42.9
90°	14.3	14.3
92.5°	57.3	45.9
95°	199.8	165.3
97.5°	478.6	413.0
100°	689.6	611.4
102.5°	897.1	830.2
105°	1161.7	1125.7
107.5°	1335.0	1343.7
110°	1401.1	1438.6



TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1407.0	1464.6
115°	1369.7	1449.5
117.5°	1290.6	1379.1
120°	1226.9	1312.8
122.5°	1164.8	1249.6
125°	1076.1	1154.4
127.5°	996.6	1062.5
130°	949.6	1010.5
132.5°	907.0	961.6
135°	848.6	895.7
137.5°	801.9	840.4
140°	769.7	805.7
142.5°	743.1	774.1
145°	703.2	726.7
147.5°	672.6	692.0
150°	653.3	669.0
152.5°	636.8	648.7
155°	617.9	625.7
157.5°	602.9	608.4
160°	594.0	597.1
162.5°	588.1	591.1
165°	579.7	582.8
167.5°	573.5	574.9
170°	571.9	571.9
172.5°	567.4	566.3
175°	564.7	564.7
177.5°	562.4	561.0
180°	561.0	561.0



TEST NUMBER: P937759

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.19	7.09	7.13	8.06	9.32	19.33	20.23	20.27	21.20	22.46
	3H	6.90	7.71	7.85	8.68	9.97	21.15	21.96	22.11	22.94	24.23
	4H	7.20	7.96	8.17	8.95	10.24	21.79	22.56	22.76	23.54	24.83
	6H	7.45	8.16	8.43	9.14	10.45	22.21	22.92	23.19	23.91	25.21
	8H	7.52	8.19	8.51	9.20	10.50	22.33	23.00	23.31	24.01	25.31
	12H	7.54	8.18	8.53	9.18	10.51	22.39	23.03	23.38	24.03	25.36
4H	2H	13.38	14.15	14.36	15.13	16.43	19.61	20.38	20.58	21.36	22.65
	3H	14.96	15.60	15.94	16.61	17.92	21.64	22.29	22.63	23.30	24.60
	4H	15.05	15.64	16.05	16.65	17.98	22.40	22.99	23.40	23.99	25.32
	6H	15.07	15.58	16.07	16.60	17.93	22.93	23.44	23.94	24.46	25.79
	8H	15.04	15.52	16.05	16.54	17.89	23.08	23.56	24.09	24.58	25.93
	12H	15.00	15.43	16.03	16.47	17.82	23.17	23.60	24.20	24.64	25.99
8H	4H	16.49	16.97	17.50	17.99	19.33	22.46	22.94	23.47	23.96	25.30
	6H	16.74	17.13	17.77	18.19	19.53	23.08	23.48	24.12	24.54	25.88
	8H	16.75	17.10	17.80	18.15	19.51	23.30	23.64	24.34	24.69	26.05
	12H	16.72	17.03	17.77	18.07	19.48	23.43	23.74	24.48	24.78	26.19
12H	4H	16.63	17.06	17.66	18.10	19.45	22.42	22.85	23.45	23.89	25.24
	6H	16.99	17.34	18.03	18.39	19.75	23.07	23.42	24.11	24.46	25.82
	8H	17.06	17.37	18.11	18.41	19.81	23.29	23.60	24.34	24.64	26.04