

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937764

Luminaire Tested: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937764
REPORT IS A COMBINATION OF REPORTS P933576 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11138.1 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937764
CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	56	56	56	50
1	97	93	89	85	90	86	82	79	72	70	67	60	58	57	49	48	47	49	48	47	41
2	88	80	74	68	81	74	69	64	63	59	55	52	49	46	42	40	38	42	40	38	34
3	80	70	62	56	73	65	58	53	55	50	45	46	42	39	37	34	32	37	34	32	28
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	30	27	33	30	27	23
5	67	54	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23	29	26	23	20
6	61	49	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20	26	23	20	17
7	56	44	35	30	52	40	33	28	34	29	24	29	24	21	24	20	17	24	20	17	15
8	52	39	31	26	48	37	29	24	31	25	21	26	22	18	22	18	15	22	18	15	13
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	20	16	14	20	16	14	11
10	45	33	25	20	41	30	24	19	26	21	17	22	18	15	18	15	12	18	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4481	4481	4481
5°	4376	5178	6024
10°	3968	7547	9987
15°	3372	9857	12059
20°	2744	11420	12290
25°	2288	11948	12040
30°	1929	12020	12017
35°	1704	11817	12328
40°	1485	11554	12649
45°	1343	11361	12698
50°	1231	11187	12488
55°	1178	10933	11935
60°	1204	10448	11060
65°	1252	9713	9860
70°	1330	8465	8330
75°	1467	6895	6500
80°	1592	4776	4380
85°	1389	2530	2242

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12698 cd/sqm



TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	0.8
10°-20°	415.3	3.7
20°-30°	726.5	6.5
30°-40°	935.2	8.4
40°-50°	1044.6	9.4
50°-60°	1000.5	9.0
60°-70°	792.9	7.1
70°-80°	466.2	4.2
80°-90°	132.8	1.2
90°-100°	415.8	3.7
100°-110°	1093.3	9.8
110°-120°	1133.6	10.2
120°-130°	909.3	8.2
130°-140°	713.5	6.4
140°-150°	547.6	4.9
150°-160°	394.4	3.5
160°-170°	241.3	2.2
170°-180°	81.5	0.7
0°-30°	1235.5	11.1
0°-40°	2170.7	19.5
0°-60°	4215.7	37.8
0°-90°	5607.6	50.3
90°-120°	2642.8	23.7
90°-150°	4813.2	43.2
90°-180°	5530.0	49.6
0°-180°	11138.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	724	724	724	724	724	
5°	706	757	852	964	999	65
15°	529	976	1645	1994	2057	147
25°	338	1106	1959	2045	2048	156
35°	228	1058	1845	1950	2027	143
45°	156	843	1631	1868	1952	121
55°	112	536	1384	1607	1652	102
65°	89	284	1027	1155	1172	88
75°	65	175	564	620	622	68
85°	23	54	140	154	156	25
90°	6	16	44	22	22	6
95°	55	215	716	369	251	61
105°	197	298	1209	1835	1712	209
115°	350	425	968	1931	2204	346
125°	487	546	881	1488	1756	432
135°	580	638	853	1201	1362	449
145°	673	716	842	1025	1105	421
155°	760	782	842	925	952	349
165°	820	831	842	876	886	232
175°	853	853	848	859	859	81
180°	853	853	853	853	853	



TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	724.4	724.4	724.4	724.4	724.4	724.4	724.4	724.4	724.4	724.4	724.4
2.5°	724.4	724.4	729.1	731.4	736.1	738.5	743.1	747.7	761.7	764.1	768.8
5°	705.8	715.2	745.4	757.1	789.7	833.9	852.5	882.8	945.8	964.4	976.1
7.5°	677.9	698.8	773.3	792.0	873.6	990.0	1038.9	1104.2	1204.3	1253.2	1292.8
10°	633.6	677.9	810.6	854.9	987.7	1164.7	1255.6	1346.4	1497.9	1565.4	1591.0
12.5°	584.7	656.9	850.2	910.8	1101.8	1360.4	1469.9	1570.0	1742.4	1833.3	1847.2
15°	528.8	626.6	887.5	976.1	1222.9	1523.5	1644.6	1768.0	1928.8	1994.0	2010.3
17.5°	479.9	603.3	922.5	1015.6	1316.2	1670.2	1793.6	1896.1	2026.6	2070.9	2082.5
20°	419.3	566.0	945.8	1066.9	1414.0	1777.4	1896.1	1975.3	2063.9	2091.8	2096.5
22.5°	375.1	526.5	959.7	1085.5	1479.2	1842.5	1942.8	2005.6	2066.2	2075.6	2077.8
25°	337.8	482.2	957.4	1106.5	1535.1	1882.2	1959.1	2005.6	2040.6	2045.3	2045.3
27.5°	302.8	433.2	948.1	1111.1	1577.1	1891.5	1952.0	1984.7	2000.9	2010.3	2010.3
30°	272.6	386.7	924.8	1101.8	1595.7	1882.2	1931.1	1947.4	1963.7	1977.7	1984.7
32.5°	249.2	342.4	889.8	1083.2	1598.0	1858.9	1893.8	1903.1	1926.4	1959.1	1970.7
35°	228.3	298.2	850.2	1057.6	1584.0	1821.6	1844.9	1854.2	1900.8	1949.7	1966.1
37.5°	207.3	265.6	799.0	1013.3	1563.0	1777.4	1793.6	1810.0	1882.2	1940.4	1959.1
40°	186.4	237.6	738.5	964.4	1530.4	1723.8	1737.7	1763.4	1858.9	1926.4	1945.1
42.5°	170.0	214.3	673.2	913.1	1488.5	1663.2	1684.2	1721.4	1830.9	1903.1	1924.1
45°	156.1	191.0	603.3	843.3	1434.9	1600.3	1630.6	1681.9	1798.3	1868.2	1886.9
47.5°	142.1	174.7	531.1	771.0	1376.7	1537.4	1577.1	1635.2	1754.1	1821.6	1838.0
50°	130.4	158.4	458.9	694.1	1313.8	1469.9	1516.5	1577.1	1698.2	1761.1	1782.0
52.5°	121.1	144.4	391.3	617.3	1241.5	1399.9	1453.5	1516.5	1630.6	1691.1	1705.2
55°	111.8	132.8	333.1	535.8	1167.0	1325.4	1383.7	1444.3	1556.0	1607.3	1616.6
57.5°	107.2	123.4	284.2	458.9	1087.8	1241.5	1306.8	1362.7	1467.6	1507.1	1516.5
60°	100.1	116.5	247.0	393.7	1001.7	1162.4	1218.3	1274.2	1362.7	1395.4	1402.3
62.5°	93.1	111.8	219.0	330.7	913.1	1069.2	1125.1	1176.4	1250.9	1274.2	1283.5
65°	88.6	107.2	198.0	284.2	822.3	971.4	1027.3	1071.5	1132.1	1155.4	1160.1
67.5°	83.9	102.5	181.7	244.6	731.4	873.6	915.5	957.4	1004.0	1027.3	1029.7
70°	76.9	97.8	167.8	216.7	638.3	761.7	796.7	840.9	878.2	889.8	896.9
72.5°	72.2	90.9	158.4	195.7	542.7	654.6	687.2	712.8	745.4	757.1	757.1
75°	65.2	81.5	149.1	174.7	444.9	535.8	563.7	589.3	614.9	619.6	612.7
77.5°	58.3	72.2	128.1	146.7	347.1	424.0	447.3	461.2	482.2	486.8	489.2
80°	48.9	62.9	100.1	114.2	251.5	312.1	328.4	340.1	358.7	358.7	363.4
82.5°	37.3	48.9	72.2	81.5	170.0	214.3	228.3	235.3	247.0	247.0	247.0
85°	23.3	30.3	46.6	53.6	102.5	130.4	139.8	142.1	151.4	153.7	153.7
87.5°	11.7	16.3	30.3	32.6	53.6	67.5	67.5	72.2	72.2	69.9	67.5
90°	5.7	10.3	14.9	16.1	25.2	37.4	43.5	38.6	29.0	21.7	21.7
92.5°	22.9	61.9	100.8	110.5	155.4	215.1	245.0	214.7	154.2	108.7	104.4
95°	55.0	126.2	197.5	215.3	382.3	604.9	716.3	639.2	484.9	369.3	356.2
97.5°	95.1	157.9	220.8	236.5	514.9	886.2	1071.9	1023.1	925.7	852.5	827.6
100°	126.0	183.0	240.0	254.2	563.2	975.1	1181.2	1184.7	1191.9	1197.2	1167.5
102.5°	152.3	205.6	258.7	272.0	585.4	1003.2	1212.1	1274.2	1398.4	1491.5	1466.1
105°	196.9	242.0	287.1	298.3	601.8	1006.4	1208.7	1347.9	1626.2	1835.0	1821.3
107.5°	242.7	284.8	326.8	337.3	604.9	961.6	1140.0	1334.1	1722.4	2013.7	2017.0
110°	273.7	311.6	349.6	359.0	600.3	921.9	1082.7	1299.7	1733.9	2059.5	2073.7



TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	304.0	340.2	376.3	385.3	600.4	887.2	1030.6	1252.7	1697.1	2030.3	2052.1
115°	349.8	383.1	416.4	424.8	606.0	847.4	968.2	1182.2	1610.3	1931.3	1961.7
117.5°	395.1	425.4	455.6	463.2	617.1	822.5	925.2	1118.4	1504.7	1794.4	1828.0
120°	421.4	449.9	478.4	485.6	626.4	814.2	908.1	1084.5	1437.5	1702.2	1734.9
122.5°	447.2	475.9	504.7	511.9	639.5	809.8	894.9	1053.9	1371.7	1610.0	1642.3
125°	486.7	512.9	539.1	545.7	657.3	806.2	880.6	1015.6	1285.6	1488.1	1517.9
127.5°	518.8	545.2	571.7	578.3	675.1	804.1	868.6	984.5	1216.3	1390.2	1415.3
130°	535.9	564.5	592.9	600.1	688.1	805.4	864.0	967.2	1173.5	1328.4	1351.5
132.5°	553.6	582.2	610.6	617.8	698.5	806.2	860.0	952.4	1137.1	1275.7	1296.4
135°	580.0	606.0	631.9	638.4	710.0	805.4	853.1	930.5	1085.2	1201.3	1219.2
137.5°	606.9	632.6	658.4	664.8	727.2	810.4	852.0	917.4	1048.2	1146.3	1160.9
140°	629.3	652.9	676.6	682.5	737.6	811.2	848.0	904.5	1017.4	1102.2	1115.8
142.5°	646.4	668.4	690.2	695.7	746.5	814.1	848.0	897.6	996.8	1071.2	1083.0
145°	672.8	691.9	710.9	715.7	757.9	814.2	842.3	882.8	964.0	1024.9	1033.8
147.5°	699.1	717.6	736.2	740.9	774.6	819.7	842.3	874.2	938.1	986.0	993.3
150°	716.3	733.1	749.8	754.1	783.4	822.6	842.3	869.2	923.1	963.6	969.5
152.5°	734.1	746.8	759.5	762.7	789.2	824.5	842.3	865.3	911.4	945.9	950.4
155°	760.4	769.8	779.1	781.5	801.8	828.8	842.3	860.6	897.2	924.7	927.7
157.5°	779.9	789.0	798.1	800.4	814.4	833.0	842.3	856.5	885.0	906.4	908.5
160°	793.0	800.1	807.3	809.0	820.1	834.9	842.3	854.5	878.9	897.2	898.4
162.5°	806.2	811.5	816.8	818.2	826.2	836.9	842.3	852.5	873.2	888.6	889.7
165°	820.5	825.3	830.1	831.3	835.0	839.9	842.3	849.6	864.4	875.5	876.7
167.5°	833.6	835.9	838.2	838.8	841.8	845.9	848.0	852.8	862.4	869.7	870.3
170°	842.3	844.6	846.8	847.4	847.6	847.9	848.0	852.8	862.4	869.7	869.7
172.5°	846.8	847.3	847.9	848.0	848.0	848.0	848.0	851.8	859.4	865.1	864.7
175°	853.1	853.1	853.1	853.1	851.3	849.1	848.0	850.3	855.2	858.9	858.9
177.5°	853.1	853.1	853.1	853.1	851.8	850.1	849.1	851.1	854.8	857.7	857.1
180°	853.1	853.1	853.1	853.1	853.1	853.1	853.1	853.1	853.1	853.1	853.1



TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	724.4	724.4
2.5°	773.3	768.8
5°	994.7	999.4
7.5°	1339.5	1337.1
10°	1665.5	1686.5
12.5°	1903.1	1907.8
15°	2047.6	2056.9
17.5°	2103.4	2105.8
20°	2105.8	2101.2
22.5°	2080.1	2075.6
25°	2049.9	2047.6
27.5°	2022.0	2024.3
30°	2010.3	2017.3
32.5°	2010.3	2022.0
35°	2015.0	2026.6
37.5°	2012.6	2026.6
40°	2003.3	2019.6
42.5°	1977.7	1989.4
45°	1938.1	1952.0
47.5°	1886.9	1896.1
50°	1821.6	1830.9
52.5°	1740.0	1742.4
55°	1642.2	1651.6
57.5°	1537.4	1539.7
60°	1421.0	1427.9
62.5°	1297.5	1297.5
65°	1167.0	1171.7
67.5°	1031.9	1043.6
70°	894.5	896.9
72.5°	759.4	759.4
75°	619.6	621.9
77.5°	486.8	486.8
80°	361.0	363.4
82.5°	249.2	253.9
85°	156.1	156.1
87.5°	72.2	65.2
90°	21.7	21.7
92.5°	87.1	69.8
95°	303.8	251.4
97.5°	727.8	628.1
100°	1048.7	929.8
102.5°	1364.2	1262.5
105°	1766.7	1712.0
107.5°	2030.3	2043.5
110°	2130.8	2187.8



TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2139.7	2227.2
115°	2083.0	2204.4
117.5°	1962.7	2097.3
120°	1865.8	1996.5
122.5°	1771.3	1900.4
125°	1636.6	1755.5
127.5°	1515.6	1615.8
130°	1444.2	1536.8
132.5°	1379.4	1462.3
135°	1290.6	1362.1
137.5°	1219.4	1278.0
140°	1170.6	1225.3
142.5°	1130.1	1177.2
145°	1069.5	1105.1
147.5°	1022.9	1052.4
150°	993.5	1017.4
152.5°	968.4	986.5
155°	939.6	951.6
157.5°	916.9	925.2
160°	903.3	908.1
162.5°	894.3	898.9
165°	881.5	886.3
167.5°	872.3	874.3
170°	869.7	869.7
172.5°	862.9	861.2
175°	858.9	858.9
177.5°	855.1	853.1
180°	853.1	853.1



TEST NUMBER: P937764

CATALOG NUMBER: SQ4-FB-100U-125D-93050-1D-UNV-STD-W-6-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.24	7.15	7.19	8.12	9.38	19.41	20.31	20.36	21.28	22.54
	3H	6.95	7.76	7.91	8.74	10.03	21.25	22.06	22.20	23.04	24.32
	4H	7.25	8.02	8.22	9.00	10.30	21.89	22.66	22.86	23.64	24.93
	6H	7.51	8.22	8.49	9.20	10.51	22.32	23.03	23.30	24.01	25.32
	8H	7.58	8.25	8.56	9.26	10.56	22.44	23.12	23.43	24.12	25.42
	12H	7.59	8.24	8.59	9.24	10.57	22.51	23.15	23.50	24.15	25.48
4H	2H	13.46	14.23	14.43	15.21	16.50	19.69	20.46	20.67	21.44	22.73
	3H	15.03	15.67	16.02	16.68	17.99	21.73	22.38	22.72	23.39	24.70
	4H	15.13	15.72	16.12	16.72	18.05	22.50	23.09	23.49	24.09	25.42
	6H	15.14	15.65	16.15	16.68	18.00	23.04	23.55	24.04	24.57	25.90
	8H	15.12	15.59	16.13	16.61	17.96	23.20	23.67	24.21	24.69	26.04
	12H	15.08	15.51	16.10	16.54	17.89	23.29	23.72	24.32	24.76	26.11
8H	4H	16.57	17.05	17.58	18.07	19.41	22.56	23.04	23.57	24.06	25.40
	6H	16.81	17.21	17.85	18.27	19.61	23.19	23.59	24.22	24.65	25.99
	8H	16.83	17.18	17.88	18.23	19.59	23.41	23.76	24.45	24.80	26.16
	12H	16.80	17.11	17.85	18.15	19.56	23.55	23.86	24.60	24.90	26.30
12H	4H	16.71	17.15	17.74	18.18	19.53	22.52	22.95	23.55	23.98	25.33
	6H	17.07	17.42	18.11	18.47	19.83	23.17	23.52	24.22	24.57	25.93
	8H	17.14	17.45	18.19	18.49	19.90	23.40	23.71	24.45	24.75	26.16