

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937657

Luminaire Tested: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937657
REPORT IS A COMBINATION OF REPORTS P933567 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6322.8 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937657
CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42	36
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34	30
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29	24
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24	20
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3349	3349	3349
5°	3269	3867	4502
10°	2962	5634	7463
15°	2514	7356	9011
20°	2044	8518	9184
25°	1703	8907	8998
30°	1434	8956	8980
35°	1266	8800	9213
40°	1101	8599	9453
45°	995	8450	9490
50°	911	8315	9333
55°	870	8120	8919
60°	888	7753	8266
65°	919	7200	7368
70°	972	6266	6225
75°	1066	5097	4858
80°	1137	3521	3272
85°	961	1858	1674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9490 cd/sqm



TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	0.7
10°-20°	206.9	3.3
20°-30°	361.9	5.7
30°-40°	465.9	7.4
40°-50°	520.4	8.2
50°-60°	498.4	7.9
60°-70°	395.0	6.2
70°-80°	232.3	3.7
80°-90°	66.6	1.1
90°-100°	265.3	4.2
100°-110°	697.6	11.0
110°-120°	723.3	11.4
120°-130°	580.2	9.2
130°-140°	455.2	7.2
140°-150°	349.4	5.5
150°-160°	251.6	4.0
160°-170°	154.0	2.4
170°-180°	52.0	0.8
0°-30°	615.5	9.7
0°-40°	1081.5	17.1
0°-60°	2100.3	33.2
0°-90°	2794.2	44.2
90°-120°	1686.2	26.7
90°-150°	3071.0	48.6
90°-180°	3529.0	55.8
0°-180°	6322.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	361	361	361	361	361	
5°	352	377	425	480	498	32
15°	263	486	819	993	1025	73
25°	168	551	976	1019	1020	78
35°	114	527	919	971	1010	71
45°	78	420	812	931	972	60
55°	56	267	689	801	823	51
65°	44	142	512	576	584	44
75°	32	87	281	309	310	34
85°	12	27	70	77	78	12
90°	4	10	28	14	14	4
95°	35	137	457	236	160	39
105°	126	190	771	1171	1092	133
115°	223	271	618	1232	1406	220
125°	311	348	562	949	1120	276
135°	370	407	544	766	869	286
145°	429	457	537	654	705	269
155°	485	499	537	590	607	223
165°	524	530	537	559	566	148
175°	544	544	541	548	548	52
180°	544	544	544	544	544	



TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.9
2.5°	360.9	360.9	363.3	364.4	366.7	367.9	370.2	372.5	379.5	380.7	382.9
5°	351.7	356.3	371.3	377.1	393.4	415.4	424.7	439.9	471.2	480.4	486.2
7.5°	337.7	348.2	385.3	394.6	435.2	493.3	517.6	550.1	600.0	624.4	644.1
10°	315.7	337.7	403.8	425.9	492.0	580.3	625.5	670.8	746.2	779.8	792.7
12.5°	291.3	327.3	423.6	453.7	548.9	677.8	732.3	782.2	868.1	913.3	920.3
15°	263.4	312.1	442.1	486.2	609.3	759.0	819.4	880.8	960.9	993.4	1001.5
17.5°	239.1	300.6	459.5	506.0	655.7	832.1	893.6	944.7	1009.7	1031.7	1037.5
20°	208.9	282.0	471.2	531.5	704.5	885.5	944.7	984.1	1028.2	1042.2	1044.5
22.5°	186.8	262.3	478.1	540.8	736.9	918.0	967.9	999.2	1029.4	1034.0	1035.2
25°	168.3	240.2	477.0	551.2	764.8	937.7	976.0	999.2	1016.6	1018.9	1018.9
27.5°	150.9	215.9	472.4	553.6	785.6	942.3	972.5	988.8	996.9	1001.5	1001.5
30°	135.8	192.6	460.8	548.9	795.0	937.7	962.1	970.2	978.3	985.3	988.8
32.5°	124.2	170.6	443.4	539.6	796.1	926.1	943.5	948.1	959.7	976.0	981.9
35°	113.7	148.5	423.6	526.9	789.2	907.5	919.1	923.8	947.0	971.4	979.5
37.5°	103.3	132.3	398.0	504.8	778.7	885.5	893.6	901.8	937.7	966.7	976.0
40°	92.8	118.4	367.9	480.4	762.5	858.8	865.7	878.6	926.1	959.7	969.0
42.5°	84.8	106.8	335.4	455.0	741.5	828.6	839.0	857.7	912.2	948.1	958.6
45°	77.7	95.1	300.6	420.1	714.8	797.3	812.3	837.9	896.0	930.7	940.0
47.5°	70.8	87.0	264.6	384.2	685.9	766.0	785.6	814.7	873.9	907.5	915.6
50°	65.0	79.0	228.6	345.9	654.5	732.3	755.5	785.6	846.1	877.3	887.8
52.5°	60.3	71.9	195.0	307.6	618.6	697.5	724.2	755.5	812.3	842.6	849.5
55°	55.7	66.1	166.0	266.9	581.4	660.3	689.4	719.5	775.3	800.7	805.4
57.5°	53.4	61.5	141.6	228.6	542.0	618.6	651.1	678.9	731.1	750.9	755.5
60°	49.9	58.1	123.0	196.1	499.1	579.1	607.0	634.8	678.9	695.2	698.6
62.5°	46.5	55.7	109.1	164.8	455.0	532.7	560.5	586.1	623.2	634.8	639.5
65°	44.1	53.4	98.6	141.6	409.6	483.9	511.8	533.8	564.0	575.6	577.9
67.5°	41.8	51.0	90.6	121.8	364.4	435.2	456.1	477.0	500.2	511.8	512.9
70°	38.3	48.7	83.5	107.9	317.9	379.5	396.9	418.9	437.5	443.4	446.8
72.5°	36.0	45.2	79.0	97.5	270.4	326.1	342.4	355.1	371.3	377.1	377.1
75°	32.5	40.6	74.3	87.0	221.7	266.9	280.9	293.6	306.4	308.7	305.2
77.5°	29.0	36.0	63.9	73.1	172.9	211.2	222.8	229.8	240.2	242.6	243.7
80°	24.3	31.4	49.9	56.8	125.3	155.5	163.6	169.4	178.7	178.7	181.0
82.5°	18.5	24.3	36.0	40.6	84.8	106.8	113.7	117.3	123.0	123.0	123.0
85°	11.6	15.1	23.2	26.7	51.0	65.0	69.6	70.8	75.4	76.6	76.6
87.5°	5.8	8.1	15.1	16.2	26.7	33.6	33.6	36.0	36.0	34.8	33.6
90°	3.7	6.6	9.5	10.2	16.1	23.9	27.8	24.7	18.5	13.9	13.9
92.5°	14.6	39.4	64.3	70.5	99.2	137.3	156.3	137.0	98.4	69.4	66.7
95°	35.0	80.5	126.0	137.4	243.9	385.9	457.0	407.8	309.4	235.6	227.3
97.5°	60.6	100.7	140.9	150.9	328.6	565.5	683.8	652.8	590.6	543.9	528.0
100°	80.4	116.7	153.1	162.2	359.4	622.3	753.7	756.0	760.4	763.9	744.9
102.5°	97.1	131.1	165.0	173.6	373.5	640.1	773.4	813.0	892.3	951.6	935.4
105°	125.7	154.4	183.1	190.3	384.0	642.1	771.2	860.0	1037.6	1170.9	1162.2
107.5°	154.9	181.7	208.5	215.2	385.9	613.5	727.3	851.2	1099.0	1284.9	1287.0
110°	174.6	198.8	223.0	229.1	382.9	588.2	690.8	829.3	1106.3	1314.0	1323.2



TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	194.0	217.0	240.0	245.8	383.1	566.1	657.6	799.3	1082.8	1295.4	1309.4
115°	223.2	244.4	265.7	271.0	386.6	540.8	617.8	754.4	1027.4	1232.3	1251.6
117.5°	252.1	271.4	290.7	295.5	393.8	524.9	590.4	713.6	960.1	1145.0	1166.4
120°	268.8	287.0	305.2	309.8	399.6	519.5	579.4	692.0	917.2	1086.1	1107.0
122.5°	285.4	303.7	322.1	326.6	408.1	516.7	571.0	672.3	875.1	1027.3	1047.8
125°	310.6	327.3	343.9	348.2	419.4	514.3	561.8	648.0	820.2	949.4	968.4
127.5°	330.9	347.8	364.8	369.0	430.7	513.0	554.2	628.2	776.1	887.0	903.0
130°	341.9	360.1	378.3	382.9	439.0	513.9	551.3	617.2	748.8	847.6	862.3
132.5°	353.3	371.4	389.6	394.2	445.6	514.3	548.7	607.6	725.5	813.9	827.2
135°	370.1	386.6	403.2	407.4	453.0	513.9	544.4	593.7	692.4	766.4	777.8
137.5°	387.2	403.7	420.0	424.1	463.9	517.1	543.6	585.3	668.7	731.4	740.7
140°	401.5	416.6	431.7	435.5	470.7	517.6	541.0	577.0	649.2	703.3	712.0
142.5°	412.5	426.4	440.4	443.9	476.3	519.4	541.0	572.7	636.0	683.5	691.0
145°	429.2	441.4	453.6	456.6	483.6	519.5	537.4	563.3	615.1	653.9	659.6
147.5°	446.1	457.9	469.7	472.7	494.3	523.0	537.4	557.8	598.6	629.1	633.9
150°	457.0	467.7	478.4	481.1	499.9	525.0	537.4	554.6	589.0	614.8	618.6
152.5°	468.3	476.4	484.6	486.6	503.5	526.1	537.4	552.1	581.4	603.5	606.4
155°	485.2	491.1	497.2	498.7	511.6	528.8	537.4	549.1	572.5	590.0	591.9
157.5°	497.6	503.4	509.2	510.7	519.6	531.5	537.4	546.5	564.7	578.3	579.6
160°	506.0	510.6	515.0	516.2	523.3	532.7	537.4	545.2	560.8	572.5	573.3
162.5°	514.3	517.8	521.2	522.1	527.2	534.0	537.4	544.0	557.1	566.9	567.6
165°	523.5	526.5	529.6	530.4	532.8	535.9	537.4	542.2	551.6	558.6	559.4
167.5°	531.9	533.4	534.9	535.2	537.2	539.7	541.0	544.1	550.3	554.9	555.3
170°	537.4	538.8	540.3	540.7	540.8	540.9	541.0	544.1	550.3	554.9	554.9
172.5°	540.3	540.7	540.9	541.0	541.0	541.0	541.0	543.5	548.3	552.0	551.7
175°	544.4	544.4	544.4	544.4	543.2	541.7	541.0	542.6	545.7	548.0	548.0
177.5°	544.4	544.4	544.4	544.4	543.5	542.4	541.7	543.0	545.4	547.3	546.9
180°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4



TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	360.9	360.9
2.5°	385.3	382.9
5°	495.5	497.9
7.5°	667.3	666.1
10°	829.8	840.2
12.5°	948.1	950.5
15°	1020.1	1024.7
17.5°	1048.0	1049.1
20°	1049.1	1046.8
22.5°	1036.4	1034.0
25°	1021.3	1020.1
27.5°	1007.3	1008.5
30°	1001.5	1005.0
32.5°	1001.5	1007.3
35°	1003.9	1009.7
37.5°	1002.7	1009.7
40°	998.1	1006.2
42.5°	985.3	991.1
45°	965.6	972.5
47.5°	940.0	944.7
50°	907.5	912.2
52.5°	866.9	868.1
55°	818.1	822.8
57.5°	766.0	767.1
60°	707.9	711.4
62.5°	646.4	646.4
65°	581.4	583.7
67.5°	514.2	520.0
70°	445.6	446.8
72.5°	378.4	378.4
75°	308.7	309.9
77.5°	242.6	242.6
80°	179.9	181.0
82.5°	124.2	126.5
85°	77.7	77.7
87.5°	36.0	32.5
90°	13.9	13.9
92.5°	55.6	44.5
95°	193.8	160.4
97.5°	464.4	400.8
100°	669.1	593.3
102.5°	870.5	805.6
105°	1127.2	1092.3
107.5°	1295.4	1303.8
110°	1359.5	1395.9



TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1365.2	1421.1
115°	1329.0	1406.5
117.5°	1252.3	1338.2
120°	1190.4	1273.9
122.5°	1130.2	1212.5
125°	1044.2	1120.1
127.5°	967.0	1030.9
130°	921.4	980.5
132.5°	880.1	933.0
135°	823.4	869.1
137.5°	778.1	815.4
140°	746.9	781.8
142.5°	721.1	751.1
145°	682.4	705.1
147.5°	652.7	671.5
150°	633.9	649.2
152.5°	617.9	629.5
155°	599.5	607.2
157.5°	585.0	590.4
160°	576.3	579.4
162.5°	570.6	573.5
165°	562.5	565.5
167.5°	556.5	557.8
170°	554.9	554.9
172.5°	550.6	549.5
175°	548.0	548.0
177.5°	545.7	544.4
180°	544.4	544.4



TEST NUMBER: P937657

CATALOG NUMBER: SQ4-FB-100U-100D-93050-1D-UNV-STD-W-4-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.64	5.48	5.63	6.49	7.84	17.77	18.62	18.77	19.63	20.98
	3H	5.34	6.10	6.35	7.12	8.49	19.60	20.36	20.61	21.38	22.75
	4H	5.64	6.36	6.66	7.38	8.76	20.23	20.95	21.25	21.98	23.35
	6H	5.89	6.55	6.92	7.58	8.97	20.65	21.31	21.68	22.34	23.73
	8H	5.95	6.59	6.99	7.63	9.02	20.76	21.39	21.80	22.44	23.83
	12H	5.97	6.57	7.01	7.61	9.02	20.82	21.42	21.87	22.47	23.88
4H	2H	11.82	12.54	12.85	13.57	14.95	18.05	18.77	19.08	19.79	21.17
	3H	13.39	13.99	14.43	15.05	16.44	20.08	20.68	21.11	21.73	23.12
	4H	13.49	14.04	14.53	15.08	16.50	20.83	21.39	21.88	22.43	23.84
	6H	13.50	13.97	14.55	15.04	16.45	21.36	21.83	22.41	22.90	24.31
	8H	13.47	13.92	14.53	14.98	16.40	21.51	21.96	22.57	23.02	24.44
	12H	13.43	13.83	14.50	14.91	16.34	21.60	22.00	22.67	23.08	24.51
8H	4H	14.92	15.36	15.97	16.43	17.85	20.89	21.34	21.95	22.40	23.82
	6H	15.16	15.53	16.24	16.63	18.05	21.51	21.88	22.59	22.98	24.40
	8H	15.18	15.50	16.27	16.59	18.03	21.72	22.05	22.81	23.13	24.57
	12H	15.15	15.43	16.24	16.51	17.99	21.86	22.14	22.95	23.22	24.70
12H	4H	15.06	15.46	16.13	16.54	17.97	20.85	21.25	21.92	22.32	23.75
	6H	15.42	15.74	16.50	16.83	18.27	21.49	21.82	22.58	22.90	24.34
	8H	15.48	15.77	16.58	16.85	18.33	21.71	22.00	22.80	23.08	24.56