

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938154

Luminaire Tested: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938154
REPORT IS A COMBINATION OF REPORTS P933592 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24375.8 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 225.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938154
CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P938154

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4372	4372	4372
5°	4273	5055	5877
10°	3877	7370	9743
15°	3297	9631	11765
20°	2685	11164	11990
25°	2240	11685	11746
30°	1890	11762	11724
35°	1672	11570	12027
40°	1458	11319	12341
45°	1321	11137	12389
50°	1213	10973	12184
55°	1163	10732	11644
60°	1192	10265	10791
65°	1242	9554	9620
70°	1326	8337	8126
75°	1474	6804	6342
80°	1623	4725	4273
85°	1474	2511	2187

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12389 cd/sqm



TEST NUMBER: P938154

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.9	0.8
10°-20°	810.4	3.3
20°-30°	1417.5	5.8
30°-40°	1824.8	7.5
40°-50°	2038.2	8.4
50°-60°	1952.1	8.0
60°-70°	1547.1	6.3
70°-80°	909.7	3.7
80°-90°	260.6	1.1
90°-100°	1010.0	4.1
100°-110°	2655.4	10.9
110°-120°	2753.4	11.3
120°-130°	2208.6	9.1
130°-140°	1733.0	7.1
140°-150°	1330.1	5.5
150°-160°	957.9	3.9
160°-170°	586.1	2.4
170°-180°	198.0	0.8
0°-30°	2410.8	9.9
0°-40°	4235.5	17.4
0°-60°	8225.8	33.7
0°-90°	10943.3	44.9
90°-120°	6418.9	26.3
90°-150°	11690.5	48.0
90°-180°	13433.0	55.1
0°-180°	24375.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1414	1414	1414	1414	1414	
5°	1377	1477	1664	1882	1950	127
15°	1032	1904	3209	3891	4013	287
25°	659	2159	3822	3991	3995	304
35°	445	2064	3600	3804	3954	278
45°	304	1645	3182	3645	3809	236
55°	218	1045	2700	3136	3223	199
65°	173	555	2004	2254	2286	171
75°	127	341	1100	1209	1214	133
85°	46	105	273	300	304	48
90°	14	39	106	53	53	15
95°	134	523	1740	897	610	148
105°	478	725	2936	4457	4158	507
115°	850	1032	2352	4691	5354	839
125°	1182	1325	2139	3614	4264	1049
135°	1409	1551	2072	2918	3308	1090
145°	1634	1738	2046	2489	2684	1024
155°	1847	1898	2046	2246	2311	849
165°	1993	2019	2046	2126	2153	562
175°	2072	2072	2060	2086	2086	197
180°	2072	2072	2072	2072	2072	



TEST NUMBER: P938154
 CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1413.6	1413.6	1413.6	1413.6	1413.6	1413.6	1413.6	1413.6	1413.6	1413.6	1413.6
2.5°	1413.6	1413.6	1422.7	1427.2	1436.3	1440.8	1450.0	1459.0	1486.3	1490.9	1499.9
5°	1377.2	1395.3	1454.4	1477.2	1540.8	1627.2	1663.6	1722.7	1845.3	1881.8	1904.4
7.5°	1322.6	1363.6	1509.0	1545.4	1704.5	1931.7	2027.2	2154.5	2349.9	2445.4	2522.6
10°	1236.3	1322.6	1581.7	1668.1	1927.2	2272.6	2449.8	2627.1	2922.6	3054.4	3104.4
12.5°	1140.9	1281.7	1659.0	1777.2	2149.9	2654.4	2868.0	3063.5	3399.9	3577.1	3604.3
15°	1031.8	1222.6	1731.7	1904.4	2386.3	2972.6	3208.9	3449.8	3763.4	3890.8	3922.5
17.5°	936.3	1177.2	1799.9	1981.7	2568.0	3258.9	3499.9	3699.8	3954.3	4040.7	4063.5
20°	818.1	1104.5	1845.3	2081.7	2759.0	3468.0	3699.8	3854.3	4027.1	4081.6	4090.7
22.5°	731.7	1027.2	1872.6	2118.0	2886.2	3595.3	3790.8	3913.4	4031.6	4049.8	4054.3
25°	659.0	940.9	1868.1	2159.0	2995.3	3672.6	3822.5	3913.4	3981.6	3990.7	3990.7
27.5°	590.9	845.4	1849.9	2168.1	3077.1	3690.7	3808.9	3872.5	3904.4	3922.5	3922.5
30°	531.8	754.5	1804.4	2149.9	3113.4	3672.6	3768.0	3799.8	3831.7	3858.9	3872.5
32.5°	486.3	668.2	1736.3	2113.6	3118.0	3627.1	3695.3	3713.5	3758.9	3822.5	3845.3
35°	445.4	581.8	1659.0	2063.5	3090.8	3554.4	3599.8	3618.0	3708.9	3804.4	3836.1
37.5°	404.5	518.1	1559.0	1977.2	3049.9	3468.0	3499.9	3531.6	3672.6	3786.2	3822.5
40°	363.6	463.6	1440.8	1881.8	2986.2	3363.5	3390.7	3440.8	3627.1	3758.9	3795.2
42.5°	331.8	418.2	1313.6	1781.8	2904.4	3245.3	3286.2	3358.9	3572.6	3713.5	3754.4
45°	304.5	372.7	1177.2	1645.4	2799.8	3122.6	3181.7	3281.7	3508.9	3645.3	3681.6
47.5°	277.3	340.9	1036.3	1504.5	2686.2	2999.8	3077.1	3190.7	3422.6	3554.4	3586.2
50°	254.5	309.1	895.4	1354.5	2563.5	2868.0	2958.9	3077.1	3313.5	3436.2	3477.1
52.5°	236.4	281.8	763.6	1204.5	2422.6	2731.7	2836.3	2958.9	3181.7	3299.9	3327.1
55°	218.2	259.1	650.0	1045.4	2277.1	2586.2	2699.9	2818.1	3036.2	3136.2	3154.4
57.5°	209.1	240.9	554.6	895.4	2122.6	2422.6	2549.8	2659.0	2863.5	2940.7	2958.9
60°	195.4	227.2	481.8	768.2	1954.5	2268.1	2377.1	2486.3	2659.0	2722.6	2736.3
62.5°	181.8	218.2	427.2	645.4	1781.8	2086.3	2195.3	2295.3	2440.8	2486.3	2504.5
65°	172.7	209.1	386.3	554.6	1604.5	1895.4	2004.4	2090.8	2209.0	2254.4	2263.5
67.5°	163.7	200.0	354.5	477.3	1427.2	1704.5	1786.2	1868.1	1959.0	2004.4	2009.0
70°	150.0	190.9	327.2	422.7	1245.4	1486.3	1554.4	1640.8	1713.5	1736.3	1749.9
72.5°	140.9	177.3	309.1	381.8	1059.1	1277.3	1340.8	1390.9	1454.4	1477.2	1477.2
75°	127.2	159.1	290.9	340.9	868.1	1045.4	1100.0	1149.9	1199.9	1209.0	1195.4
77.5°	113.6	140.9	250.0	286.3	677.2	827.3	872.7	900.0	940.9	949.9	954.5
80°	95.4	122.7	195.4	222.8	490.9	609.1	640.9	663.6	700.0	700.0	709.1
82.5°	72.7	95.4	140.9	159.1	331.8	418.2	445.4	459.0	481.8	481.8	481.8
85°	45.5	59.1	90.9	104.6	200.0	254.5	272.7	277.3	295.5	300.0	300.0
87.5°	22.7	31.8	59.1	63.7	104.6	131.8	131.8	140.9	140.9	136.4	131.8
90°	13.9	25.0	36.2	38.9	61.1	90.8	105.6	93.9	70.5	52.8	52.8
92.5°	55.6	150.1	244.8	268.4	377.4	522.6	595.2	521.6	374.5	264.2	253.7
95°	133.5	306.6	479.6	522.9	928.4	1469.3	1739.7	1552.4	1177.9	897.0	865.1
97.5°	230.8	383.5	536.2	574.3	1250.7	2152.4	2603.3	2484.9	2248.2	2070.7	2010.1
100°	305.9	444.4	582.8	617.5	1367.9	2368.6	2868.9	2877.6	2894.9	2907.9	2835.7
102.5°	369.9	499.1	628.2	660.6	1421.8	2436.6	2944.1	3094.8	3396.5	3622.7	3560.9
105°	478.4	587.8	697.2	724.6	1461.6	2444.3	2935.6	3273.7	3949.9	4457.0	4423.8
107.5°	589.7	691.6	793.6	819.1	1469.0	2335.6	2768.8	3240.4	4183.5	4890.9	4899.0
110°	664.8	756.8	848.9	871.9	1457.8	2239.1	2629.7	3157.0	4211.4	5002.2	5036.8



TEST NUMBER: P938154

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	738.5	826.2	913.9	935.9	1458.3	2154.9	2503.2	3042.8	4121.9	4931.3	4984.5
115°	849.7	930.6	1011.6	1031.8	1471.8	2058.3	2351.6	2871.4	3911.0	4690.7	4764.4
117.5°	959.6	1033.1	1106.7	1125.0	1499.1	1997.9	2247.3	2716.5	3654.7	4358.3	4440.0
120°	1023.5	1092.7	1162.0	1179.3	1521.4	1977.6	2205.6	2634.3	3491.5	4134.5	4213.9
122.5°	1086.1	1155.9	1225.8	1243.2	1553.4	1966.9	2173.6	2559.6	3331.5	3910.5	3988.9
125°	1182.1	1245.7	1309.4	1325.3	1596.5	1958.0	2138.8	2466.7	3122.5	3614.3	3686.4
127.5°	1260.0	1324.3	1388.5	1404.6	1639.6	1952.9	2109.6	2391.1	2954.2	3376.5	3437.4
130°	1301.7	1370.9	1440.1	1457.4	1671.1	1956.1	2098.5	2349.1	2850.4	3226.3	3282.6
132.5°	1344.8	1414.0	1483.3	1500.5	1696.6	1958.0	2088.8	2313.1	2761.9	3098.4	3148.8
135°	1408.8	1471.8	1534.8	1550.6	1724.5	1956.3	2072.1	2260.0	2635.8	2917.6	2961.1
137.5°	1474.1	1536.5	1598.9	1614.5	1766.1	1968.3	2069.3	2228.2	2545.8	2784.1	2819.6
140°	1528.3	1585.8	1643.3	1657.7	1791.6	1970.2	2059.6	2196.7	2471.2	2677.0	2710.2
142.5°	1570.0	1623.2	1676.4	1689.6	1812.9	1977.4	2059.6	2180.1	2421.2	2602.0	2630.5
145°	1634.0	1680.4	1726.8	1738.3	1840.8	1977.4	2045.7	2144.3	2341.4	2489.2	2510.9
147.5°	1698.0	1743.1	1788.2	1799.5	1881.6	1991.0	2045.7	2123.2	2278.4	2394.7	2412.6
150°	1739.7	1780.5	1821.3	1831.5	1902.9	1998.1	2045.7	2111.2	2242.2	2340.4	2354.9
152.5°	1782.8	1813.7	1844.7	1852.4	1916.9	2002.7	2045.7	2101.7	2213.5	2297.4	2308.4
155°	1846.8	1869.7	1892.5	1898.2	1947.4	2012.9	2045.7	2090.2	2179.2	2245.9	2253.1
157.5°	1894.1	1916.3	1938.6	1944.2	1978.0	2023.1	2045.7	2080.3	2149.5	2201.4	2206.5
160°	1926.1	1943.4	1960.7	1965.0	1991.9	2027.8	2045.7	2075.3	2134.7	2179.2	2182.1
162.5°	1958.0	1971.0	1984.0	1987.2	2006.8	2032.7	2045.7	2070.8	2120.8	2158.3	2161.1
165°	1992.8	2004.5	2016.2	2019.2	2028.1	2039.8	2045.7	2063.6	2099.4	2126.3	2129.2
167.5°	2024.8	2030.4	2035.9	2037.3	2044.7	2054.7	2059.6	2071.3	2094.8	2112.4	2113.7
170°	2045.7	2051.2	2056.8	2058.1	2058.6	2059.2	2059.6	2071.3	2094.8	2112.4	2112.4
172.5°	2056.8	2058.1	2059.3	2059.6	2059.6	2059.6	2059.6	2068.9	2087.4	2101.3	2100.2
175°	2072.1	2072.1	2072.1	2072.1	2067.9	2062.4	2059.6	2065.5	2077.2	2086.0	2086.0
177.5°	2072.1	2072.1	2072.1	2072.1	2068.9	2064.5	2062.4	2067.0	2076.2	2083.2	2082.0
180°	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1



TEST NUMBER: P938154

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1413.6	1413.6
2.5°	1509.0	1499.9
5°	1940.9	1949.9
7.5°	2613.5	2608.9
10°	3249.8	3290.7
12.5°	3713.5	3722.5
15°	3995.2	4013.4
17.5°	4104.4	4108.9
20°	4108.9	4099.8
22.5°	4058.9	4049.8
25°	3999.8	3995.2
27.5°	3945.3	3949.8
30°	3922.5	3936.1
32.5°	3922.5	3945.3
35°	3931.6	3954.3
37.5°	3927.1	3954.3
40°	3908.9	3940.7
42.5°	3858.9	3881.6
45°	3781.6	3808.9
47.5°	3681.6	3699.8
50°	3554.4	3572.6
52.5°	3395.3	3399.9
55°	3204.4	3222.6
57.5°	2999.8	3004.4
60°	2772.6	2786.2
62.5°	2531.7	2531.7
65°	2277.1	2286.3
67.5°	2013.6	2036.3
70°	1745.4	1749.9
72.5°	1481.7	1481.7
75°	1209.0	1213.6
77.5°	949.9	949.9
80°	704.5	709.1
82.5°	486.3	495.5
85°	304.5	304.5
87.5°	140.9	127.2
90°	52.8	52.8
92.5°	211.7	169.7
95°	737.8	610.5
97.5°	1767.8	1525.5
100°	2547.1	2258.4
102.5°	3313.6	3066.4
105°	4291.0	4158.1
107.5°	4931.1	4963.3
110°	5175.3	5313.7



TEST NUMBER: P938154
CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5197.0	5409.7
115°	5059.2	5354.1
117.5°	4767.0	5094.0
120°	4531.5	4849.2
122.5°	4302.2	4615.6
125°	3975.1	4263.7
127.5°	3680.9	3924.4
130°	3507.6	3732.6
132.5°	3350.3	3551.7
135°	3134.7	3308.4
137.5°	2961.8	3104.0
140°	2843.2	2976.0
142.5°	2744.8	2859.2
145°	2597.4	2684.0
147.5°	2484.3	2556.0
150°	2413.1	2471.2
152.5°	2352.3	2396.1
155°	2282.2	2311.2
157.5°	2226.9	2247.3
160°	2193.9	2205.6
162.5°	2172.2	2183.3
165°	2141.0	2152.8
167.5°	2118.6	2123.5
170°	2112.4	2112.4
172.5°	2095.8	2091.5
175°	2086.0	2086.0
177.5°	2077.0	2072.1
180°	2072.1	2072.1



TEST NUMBER: P938154
 CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.65	6.50	6.64	7.51	8.85	18.84	19.69	19.83	20.70	22.04
	3H	6.36	7.12	7.36	8.14	9.50	20.69	21.45	21.69	22.47	23.83
	4H	6.65	7.38	7.67	8.40	9.77	21.34	22.06	22.35	23.08	24.45
	6H	6.90	7.57	7.93	8.60	9.98	21.77	22.44	22.80	23.46	24.84
	8H	6.97	7.61	8.00	8.65	10.03	21.89	22.53	22.92	23.57	24.95
	12H	6.99	7.59	8.03	8.63	10.03	21.96	22.57	23.00	23.60	25.01
4H	2H	12.87	13.60	13.89	14.62	15.99	19.12	19.84	20.14	20.86	22.23
	3H	14.44	15.05	15.47	16.10	17.48	21.16	21.77	22.20	22.82	24.20
	4H	14.53	15.09	15.57	16.13	17.53	21.93	22.49	22.97	23.53	24.94
	6H	14.54	15.02	15.59	16.09	17.49	22.48	22.96	23.53	24.02	25.42
	8H	14.52	14.97	15.57	16.02	17.44	22.64	23.09	23.69	24.15	25.56
	12H	14.48	14.88	15.54	15.95	17.37	22.74	23.14	23.81	24.22	25.64
8H	4H	15.98	16.43	17.03	17.49	18.90	21.99	22.44	23.04	23.50	24.91
	6H	16.22	16.59	17.30	17.69	19.10	22.63	23.00	23.70	24.10	25.51
	8H	16.24	16.57	17.32	17.65	19.08	22.85	23.18	23.93	24.26	25.69
	12H	16.21	16.49	17.29	17.57	19.04	23.00	23.28	24.08	24.36	25.83
12H	4H	16.12	16.53	17.19	17.60	19.02	21.95	22.35	23.01	23.42	24.84
	6H	16.48	16.81	17.56	17.89	19.32	22.61	22.94	23.69	24.02	25.45
	8H	16.55	16.84	17.64	17.92	19.39	22.84	23.13	23.93	24.21	25.68