

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938155

Luminaire Tested: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938155
REPORT IS A COMBINATION OF REPORTS P933592 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24643.9 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 225.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938155
CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P938155

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4421	4421	4421
5°	4320	5110	5942
10°	3920	7451	9850
15°	3333	9737	11894
20°	2714	11286	12122
25°	2265	11814	11876
30°	1911	11891	11853
35°	1690	11697	12160
40°	1474	11443	12477
45°	1335	11259	12525
50°	1226	11094	12318
55°	1176	10850	11772
60°	1205	10378	10910
65°	1255	9659	9725
70°	1340	8429	8216
75°	1491	6879	6411
80°	1641	4776	4320
85°	1491	2539	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12525 cd/sqm



TEST NUMBER: P938155

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	0.8
10°-20°	819.3	3.3
20°-30°	1433.1	5.8
30°-40°	1844.8	7.5
40°-50°	2060.6	8.4
50°-60°	1973.6	8.0
60°-70°	1564.1	6.3
70°-80°	919.7	3.7
80°-90°	263.5	1.1
90°-100°	1021.1	4.1
100°-110°	2684.7	10.9
110°-120°	2783.7	11.3
120°-130°	2232.9	9.1
130°-140°	1752.0	7.1
140°-150°	1344.7	5.5
150°-160°	968.4	3.9
160°-170°	592.5	2.4
170°-180°	200.2	0.8
0°-30°	2437.3	9.9
0°-40°	4282.1	17.4
0°-60°	8316.3	33.7
0°-90°	11063.6	44.9
90°-120°	6489.5	26.3
90°-150°	11819.1	48.0
90°-180°	13580.0	55.1
0°-180°	24643.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1392	1493	1682	1902	1971	129
15°	1043	1925	3244	3934	4058	290
25°	666	2183	3865	4035	4039	307
35°	450	2086	3639	3846	3998	281
45°	308	1664	3217	3685	3851	238
55°	221	1057	2730	3171	3258	201
65°	175	561	2026	2279	2311	173
75°	129	345	1112	1222	1227	135
85°	46	106	276	303	308	49
90°	14	39	107	53	53	15
95°	135	529	1759	907	617	150
105°	484	732	2968	4506	4204	513
115°	859	1043	2378	4742	5413	848
125°	1195	1340	2162	3654	4311	1061
135°	1424	1568	2095	2950	3345	1102
145°	1652	1758	2068	2517	2714	1035
155°	1867	1919	2068	2271	2337	858
165°	2015	2041	2068	2150	2176	569
175°	2095	2095	2082	2109	2109	199
180°	2095	2095	2095	2095	2095	



TEST NUMBER: P938155
 CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2
2.5°	1429.2	1429.2	1438.3	1442.9	1452.1	1456.7	1465.9	1475.1	1502.7	1507.3	1516.4
5°	1392.3	1410.7	1470.4	1493.4	1557.8	1645.1	1681.9	1741.6	1865.6	1902.5	1925.4
7.5°	1337.2	1378.6	1525.6	1562.4	1723.2	1953.0	2049.5	2178.2	2375.8	2472.3	2550.4
10°	1249.9	1337.2	1599.1	1686.4	1948.4	2297.6	2476.8	2656.0	2954.7	3088.0	3138.6
12.5°	1153.4	1295.8	1677.3	1796.7	2173.6	2683.6	2899.6	3097.2	3437.3	3616.5	3644.0
15°	1043.1	1236.1	1750.8	1925.4	2412.5	3005.3	3244.2	3487.8	3804.8	3933.6	3965.7
17.5°	946.6	1190.2	1819.7	2003.5	2596.3	3294.8	3538.4	3740.5	3997.8	4085.2	4108.2
20°	827.1	1116.6	1865.6	2104.6	2789.3	3506.1	3740.5	3896.7	4071.4	4126.5	4135.7
22.5°	739.8	1038.5	1893.2	2141.3	2918.0	3634.9	3832.5	3956.5	4075.9	4094.3	4098.9
25°	666.3	951.2	1888.6	2182.7	3028.2	3713.0	3864.6	3956.5	4025.4	4034.6	4034.6
27.5°	597.4	854.7	1870.2	2191.9	3110.9	3731.3	3850.8	3915.1	3947.3	3965.7	3965.7
30°	537.7	762.8	1824.3	2173.6	3147.7	3713.0	3809.5	3841.6	3873.8	3901.3	3915.1
32.5°	491.7	675.5	1755.4	2136.8	3152.3	3667.0	3736.0	3754.3	3800.2	3864.6	3887.6
35°	450.3	588.2	1677.3	2086.2	3124.8	3593.5	3639.4	3657.8	3749.7	3846.2	3878.3
37.5°	409.0	523.8	1576.2	1999.0	3083.4	3506.1	3538.4	3570.5	3713.0	3827.8	3864.6
40°	367.6	468.7	1456.7	1902.5	3019.1	3400.5	3428.0	3478.6	3667.0	3800.2	3837.0
42.5°	335.5	422.8	1328.1	1801.4	2936.3	3281.0	3322.4	3395.9	3611.9	3754.3	3795.7
45°	307.8	376.8	1190.2	1663.5	2830.6	3156.9	3216.7	3317.8	3547.5	3685.4	3722.1
47.5°	280.3	344.7	1047.7	1521.0	2715.8	3032.8	3110.9	3225.8	3460.2	3593.5	3625.6
50°	257.3	312.5	905.3	1369.4	2591.7	2899.6	2991.5	3110.9	3349.9	3474.0	3515.4
52.5°	239.0	284.9	772.0	1217.7	2449.3	2761.7	2867.5	2991.5	3216.7	3336.2	3363.7
55°	220.6	262.0	657.1	1056.9	2302.2	2614.6	2729.6	2849.1	3069.6	3170.7	3189.1
57.5°	211.4	243.6	560.7	905.3	2146.0	2449.3	2577.9	2688.2	2895.0	2973.1	2991.5
60°	197.6	229.7	487.1	776.6	1976.0	2293.0	2403.3	2513.6	2688.2	2752.5	2766.4
62.5°	183.8	220.6	431.9	652.5	1801.4	2109.2	2219.5	2320.6	2467.6	2513.6	2532.0
65°	174.6	211.4	390.6	560.7	1622.1	1916.2	2026.5	2113.8	2233.3	2279.2	2288.4
67.5°	165.5	202.2	358.4	482.5	1442.9	1723.2	1805.9	1888.6	1980.6	2026.5	2031.1
70°	151.6	193.0	330.8	427.3	1259.1	1502.7	1571.5	1658.9	1732.4	1755.4	1769.1
72.5°	142.5	179.2	312.5	386.0	1070.7	1291.3	1355.6	1406.2	1470.4	1493.4	1493.4
75°	128.6	160.8	294.1	344.7	877.6	1056.9	1112.1	1162.6	1213.1	1222.3	1208.6
77.5°	114.9	142.5	252.7	289.5	684.7	836.4	882.3	909.9	951.2	960.4	965.0
80°	96.5	124.1	197.6	225.2	496.3	615.8	647.9	670.9	707.7	707.7	716.9
82.5°	73.5	96.5	142.5	160.8	335.5	422.8	450.3	464.1	487.1	487.1	487.1
85°	46.0	59.7	91.9	105.7	202.2	257.3	275.7	280.3	298.7	303.3	303.3
87.5°	23.0	32.1	59.7	64.4	105.7	133.2	133.2	142.5	142.5	137.9	133.2
90°	14.0	25.3	36.6	39.4	61.8	91.8	106.8	95.0	71.2	53.4	53.4
92.5°	56.2	151.8	247.5	271.4	381.5	528.3	601.8	527.3	378.6	267.1	256.5
95°	135.0	309.9	484.9	528.6	938.7	1485.5	1758.8	1569.5	1190.8	906.9	874.7
97.5°	233.4	387.7	542.1	580.7	1264.4	2176.1	2631.9	2512.3	2272.9	2093.5	2032.2
100°	309.3	449.3	589.3	624.3	1383.0	2394.7	2900.5	2909.3	2926.7	2939.9	2866.9
102.5°	374.0	504.6	635.2	667.8	1437.4	2463.4	2976.4	3128.9	3433.8	3662.6	3600.1
105°	483.6	594.2	704.8	732.5	1477.7	2471.2	2967.9	3309.7	3993.4	4506.1	4472.5
107.5°	596.1	699.2	802.3	828.1	1485.2	2361.3	2799.3	3276.0	4229.5	4944.7	4952.9
110°	672.1	765.1	858.3	881.5	1473.9	2263.7	2658.6	3191.7	4257.7	5057.2	5092.3



TEST NUMBER: P938155

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	746.6	835.3	924.0	946.2	1474.3	2178.6	2530.7	3076.3	4167.3	4985.5	5039.3
115°	859.0	940.8	1022.7	1043.2	1488.0	2081.0	2377.5	2903.0	3954.0	4742.3	4816.8
117.5°	970.2	1044.5	1118.9	1137.4	1515.6	2019.9	2272.0	2746.3	3694.9	4406.2	4488.9
120°	1034.8	1104.7	1174.8	1192.3	1538.1	1999.3	2229.9	2663.3	3529.9	4179.9	4260.2
122.5°	1098.1	1168.7	1239.3	1256.9	1570.5	1988.5	2197.5	2587.8	3368.2	3953.6	4032.8
125°	1195.1	1259.4	1323.8	1339.9	1614.1	1979.6	2162.3	2493.8	3156.8	3654.0	3727.0
127.5°	1273.8	1338.8	1403.8	1420.0	1657.6	1974.4	2132.8	2417.4	2986.7	3413.6	3475.2
130°	1316.0	1386.0	1456.0	1473.4	1689.5	1977.6	2121.6	2375.0	2881.8	3261.8	3318.7
132.5°	1359.6	1429.5	1499.6	1517.0	1715.3	1979.6	2111.7	2338.6	2792.2	3132.5	3183.5
135°	1424.3	1488.0	1551.7	1567.6	1743.4	1977.8	2094.9	2284.9	2664.8	2949.7	2993.6
137.5°	1490.3	1553.4	1616.5	1632.3	1785.5	1989.9	2092.1	2252.7	2573.8	2814.7	2850.6
140°	1545.1	1603.2	1661.3	1675.9	1811.3	1991.9	2082.2	2220.9	2498.3	2706.4	2740.0
142.5°	1587.3	1641.1	1694.8	1708.2	1832.9	1999.1	2082.2	2204.1	2447.8	2630.6	2659.5
145°	1652.0	1698.9	1745.8	1757.5	1861.0	1999.1	2068.2	2167.9	2367.2	2516.6	2538.5
147.5°	1716.6	1762.3	1807.9	1819.3	1902.3	2012.9	2068.2	2146.6	2303.5	2421.0	2439.1
150°	1758.8	1800.1	1841.4	1851.7	1923.8	2020.0	2068.2	2134.5	2266.9	2366.2	2380.8
152.5°	1802.4	1833.7	1865.0	1872.8	1937.9	2024.8	2068.2	2124.8	2237.8	2322.6	2333.8
155°	1867.1	1890.2	1913.3	1919.1	1968.8	2035.1	2068.2	2113.2	2203.2	2270.6	2277.9
157.5°	1915.0	1937.4	1959.9	1965.6	1999.8	2045.4	2068.2	2103.1	2173.1	2225.6	2230.8
160°	1947.3	1964.7	1982.3	1986.6	2013.8	2050.1	2068.2	2098.2	2158.2	2203.2	2206.1
162.5°	1979.6	1992.7	2005.8	2009.1	2028.8	2055.1	2068.2	2093.5	2144.1	2182.1	2184.9
165°	2014.7	2026.6	2038.4	2041.4	2050.4	2062.2	2068.2	2086.3	2122.5	2149.7	2152.7
167.5°	2047.1	2052.7	2058.3	2059.7	2067.2	2077.3	2082.2	2094.1	2117.8	2135.6	2136.9
170°	2068.2	2073.8	2079.4	2080.8	2081.2	2081.9	2082.2	2094.1	2117.8	2135.6	2135.6
172.5°	2079.4	2080.7	2082.0	2082.2	2082.2	2082.2	2082.2	2091.6	2110.4	2124.4	2123.3
175°	2094.9	2094.9	2094.9	2094.9	2090.7	2085.0	2082.2	2088.2	2100.1	2108.9	2108.9
177.5°	2094.9	2094.9	2094.9	2094.9	2091.6	2087.2	2085.0	2089.7	2099.1	2106.1	2104.9
180°	2094.9	2094.9	2094.9	2094.9	2094.9	2094.9	2094.9	2094.9	2094.9	2094.9	2094.9



TEST NUMBER: P938155
CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1429.2	1429.2
2.5°	1525.6	1516.4
5°	1962.2	1971.4
7.5°	2642.3	2637.6
10°	3285.6	3326.9
12.5°	3754.3	3763.5
15°	4039.2	4057.6
17.5°	4149.5	4154.1
20°	4154.1	4144.9
22.5°	4103.5	4094.3
25°	4043.8	4039.2
27.5°	3988.7	3993.3
30°	3965.7	3979.4
32.5°	3965.7	3988.7
35°	3974.8	3997.8
37.5°	3970.3	3997.8
40°	3951.9	3984.1
42.5°	3901.3	3924.3
45°	3823.2	3850.8
47.5°	3722.1	3740.5
50°	3593.5	3611.9
52.5°	3432.6	3437.3
55°	3239.7	3258.0
57.5°	3032.8	3037.4
60°	2803.1	2816.9
62.5°	2559.5	2559.5
65°	2302.2	2311.4
67.5°	2035.7	2058.7
70°	1764.6	1769.1
72.5°	1498.0	1498.0
75°	1222.3	1226.9
77.5°	960.4	960.4
80°	712.3	716.9
82.5°	491.7	500.9
85°	307.8	307.8
87.5°	142.5	128.6
90°	53.4	53.4
92.5°	214.0	171.5
95°	745.9	617.2
97.5°	1787.2	1542.3
100°	2575.1	2283.3
102.5°	3350.1	3100.2
105°	4338.2	4203.8
107.5°	4985.4	5017.9
110°	5232.2	5372.1



TEST NUMBER: P938155

CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5254.2	5469.2
115°	5114.9	5413.0
117.5°	4819.4	5150.0
120°	4581.4	4902.5
122.5°	4349.6	4666.4
125°	4018.8	4310.6
127.5°	3721.4	3967.6
130°	3546.1	3773.6
132.5°	3387.1	3590.8
135°	3169.1	3344.8
137.5°	2994.4	3138.1
140°	2874.4	3008.8
142.5°	2775.0	2890.6
145°	2626.0	2713.5
147.5°	2511.6	2584.1
150°	2439.7	2498.4
152.5°	2378.1	2422.5
155°	2307.3	2336.7
157.5°	2251.4	2272.0
160°	2218.0	2229.9
162.5°	2196.1	2207.3
165°	2164.5	2176.5
167.5°	2141.9	2146.9
170°	2135.6	2135.6
172.5°	2118.9	2114.5
175°	2108.9	2108.9
177.5°	2099.9	2094.9
180°	2094.9	2094.9



TEST NUMBER: P938155
 CATALOG NUMBER: SQ4-FB-125U-125D-93050-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.69	6.54	6.68	7.55	8.89	18.88	19.73	19.87	20.74	22.08
	3H	6.39	7.16	7.40	8.18	9.54	20.73	21.49	21.73	22.51	23.87
	4H	6.69	7.42	7.71	8.44	9.80	21.37	22.10	22.39	23.12	24.49
	6H	6.94	7.61	7.97	8.64	10.02	21.81	22.48	22.83	23.50	24.88
	8H	7.01	7.65	8.04	8.69	10.06	21.93	22.57	22.96	23.61	24.99
	12H	7.03	7.63	8.06	8.67	10.07	22.00	22.61	23.04	23.64	25.04
4H	2H	12.91	13.64	13.93	14.66	16.02	19.15	19.88	20.18	20.90	22.27
	3H	14.48	15.08	15.51	16.13	17.51	21.20	21.81	22.23	22.86	24.24
	4H	14.57	15.13	15.61	16.17	17.57	21.97	22.53	23.01	23.57	24.97
	6H	14.58	15.06	15.63	16.13	17.52	22.52	23.00	23.56	24.06	25.46
	8H	14.56	15.01	15.61	16.06	17.48	22.68	23.13	23.73	24.19	25.60
	12H	14.51	14.92	15.58	15.99	17.41	22.78	23.18	23.84	24.25	25.67
8H	4H	16.02	16.47	17.07	17.52	18.94	22.03	22.48	23.08	23.54	24.95
	6H	16.26	16.63	17.33	17.73	19.14	22.67	23.04	23.74	24.14	25.55
	8H	16.28	16.60	17.36	17.69	19.12	22.89	23.21	23.97	24.30	25.73
	12H	16.25	16.53	17.33	17.61	19.08	23.04	23.32	24.12	24.40	25.87
12H	4H	16.16	16.57	17.23	17.64	19.06	21.98	22.39	23.05	23.46	24.88
	6H	16.52	16.85	17.60	17.93	19.36	22.65	22.98	23.73	24.06	25.49
	8H	16.59	16.88	17.67	17.95	19.43	22.88	23.17	23.97	24.25	25.72