

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937960

Luminaire Tested: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937960
REPORT IS A COMBINATION OF REPORTS P933598 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6800.1 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937960
CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	40	40	40	33
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	33	33	33	27
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	27	27	27	22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	23	23	23	18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	19	19	19	15
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	16	16	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	14	14	14	11
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	12	12	12	10
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	11	11	11	8
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	10	10	10	7
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2648	2648	2648
5°	2585	3059	3560
10°	2342	4455	5901
15°	1988	5817	7126
20°	1617	6735	7263
25°	1347	7043	7115
30°	1134	7082	7101
35°	1001	6959	7285
40°	871	6800	7475
45°	787	6683	7504
50°	721	6575	7380
55°	687	6421	7052
60°	703	6131	6536
65°	727	5693	5827
70°	769	4956	4922
75°	843	4030	3841
80°	903	2785	2589
85°	762	1471	1325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7504 cd/sqm



TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	0.5
10°-20°	163.6	2.4
20°-30°	286.2	4.2
30°-40°	368.4	5.4
40°-50°	411.5	6.1
50°-60°	394.1	5.8
60°-70°	312.4	4.6
70°-80°	183.7	2.7
80°-90°	53.7	0.8
90°-100°	345.1	5.1
100°-110°	907.3	13.3
110°-120°	940.8	13.8
120°-130°	754.6	11.1
130°-140°	592.1	8.7
140°-150°	454.5	6.7
150°-160°	327.3	4.8
160°-170°	200.3	2.9
170°-180°	67.7	1.0
0°-30°	486.7	7.2
0°-40°	855.2	12.6
0°-60°	1660.8	24.4
0°-90°	2210.6	32.5
90°-120°	2193.1	32.3
90°-150°	3994.3	58.7
90°-180°	4589.0	67.5
0°-180°	6800.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	285	285	285	285	285	
5°	278	298	336	380	394	26
15°	208	384	648	786	810	58
25°	133	436	772	806	807	61
35°	90	417	727	768	798	56
45°	62	332	642	736	769	48
55°	44	211	545	633	651	40
65°	35	112	405	455	462	35
75°	26	69	222	244	245	27
85°	9	21	55	61	62	10
90°	5	13	36	18	18	5
95°	46	179	594	306	209	51
105°	163	248	1003	1523	1421	173
115°	290	353	803	1603	1829	287
125°	404	453	731	1235	1457	359
135°	481	530	708	997	1130	372
145°	558	594	699	850	917	350
155°	631	648	699	767	790	290
165°	681	690	699	726	736	192
175°	708	708	704	713	713	67
180°	708	708	708	708	708	



TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4
2.5°	285.4	285.4	287.2	288.2	290.0	290.9	292.7	294.6	300.1	301.0	302.8
5°	278.1	281.7	293.7	298.3	311.1	328.5	335.9	347.8	372.6	379.9	384.5
7.5°	267.0	275.3	304.7	312.0	344.1	390.0	409.3	435.0	474.4	493.7	509.3
10°	249.6	267.0	319.4	336.8	389.1	458.8	494.6	530.4	590.1	616.7	626.8
12.5°	230.3	258.8	335.0	358.8	434.1	535.9	579.1	618.5	686.4	722.2	727.7
15°	208.3	246.9	349.6	384.5	481.8	600.2	647.9	696.5	759.9	785.5	792.0
17.5°	189.0	237.7	363.4	400.1	518.5	658.0	706.6	747.0	798.4	815.8	820.4
20°	165.2	223.0	372.6	420.3	557.0	700.2	747.0	778.2	813.1	824.1	825.9
22.5°	147.7	207.4	378.1	427.6	582.7	725.9	765.4	790.1	814.0	817.7	818.6
25°	133.1	190.0	377.2	435.9	604.8	741.5	771.8	790.1	803.9	805.7	805.7
27.5°	119.3	170.7	373.5	437.7	621.3	745.2	769.0	781.9	788.3	792.0	792.0
30°	107.4	152.3	364.3	434.1	628.6	741.5	760.8	767.2	773.6	779.1	781.9
32.5°	98.2	134.9	350.6	426.7	629.5	732.3	746.1	749.8	758.9	771.8	776.4
35°	89.9	117.5	335.0	416.6	624.0	717.6	726.8	730.5	748.8	768.1	774.5
37.5°	81.7	104.6	314.8	399.2	615.8	700.2	706.6	713.0	741.5	764.4	771.8
40°	73.4	93.6	290.9	379.9	602.9	679.1	684.6	694.7	732.3	758.9	766.3
42.5°	67.0	84.4	265.2	359.7	586.4	655.2	663.5	678.2	721.3	749.8	758.0
45°	61.5	75.3	237.7	332.2	565.3	630.5	642.4	662.6	708.5	736.0	743.3
47.5°	56.0	68.8	209.2	303.8	542.4	605.7	621.3	644.2	691.0	717.6	724.1
50°	51.4	62.4	180.8	273.5	517.6	579.1	597.4	621.3	669.0	693.8	702.0
52.5°	47.7	56.9	154.2	243.2	489.1	551.5	572.6	597.4	642.4	666.2	671.8
55°	44.0	52.3	131.2	211.1	459.8	522.2	545.1	569.0	613.0	633.2	636.9
57.5°	42.2	48.6	112.0	180.8	428.6	489.1	514.8	536.9	578.1	593.7	597.4
60°	39.5	45.9	97.3	155.1	394.6	457.9	480.0	502.0	536.9	549.7	552.5
62.5°	36.7	44.0	86.3	130.3	359.7	421.2	443.2	463.4	492.8	502.0	505.6
65°	34.9	42.2	78.0	112.0	323.9	382.7	404.7	422.1	446.0	455.2	457.0
67.5°	33.0	40.4	71.6	96.4	288.2	344.1	360.7	377.2	395.5	404.7	405.6
70°	30.3	38.5	66.1	85.3	251.4	300.1	313.9	331.3	346.0	350.6	353.3
72.5°	28.4	35.8	62.4	77.1	213.8	257.9	270.7	280.8	293.7	298.3	298.3
75°	25.7	32.1	58.7	68.8	175.3	211.1	222.1	232.2	242.3	244.1	241.4
77.5°	22.9	28.4	50.5	57.8	136.7	167.0	176.2	181.7	190.0	191.8	192.7
80°	19.3	24.8	39.5	45.0	99.1	123.0	129.4	134.0	141.3	141.3	143.2
82.5°	14.7	19.3	28.4	32.1	67.0	84.4	89.9	92.7	97.3	97.3	97.3
85°	9.2	11.9	18.4	21.1	40.4	51.4	55.1	56.0	59.7	60.6	60.6
87.5°	4.6	6.4	11.9	12.8	21.1	26.6	26.6	28.4	28.4	27.5	26.6
90°	4.8	8.5	12.4	13.3	20.9	31.0	36.1	32.0	24.0	18.1	18.1
92.5°	19.0	51.3	83.6	91.7	128.9	178.6	203.4	178.2	128.0	90.3	86.7
95°	45.6	104.7	163.9	178.7	317.2	502.0	594.4	530.4	402.5	306.5	295.6
97.5°	78.8	131.0	183.2	196.2	427.3	735.3	889.4	849.0	768.1	707.5	686.8
100°	104.5	151.9	199.1	211.0	467.4	809.2	980.2	983.1	989.1	993.5	968.8
102.5°	126.4	170.5	214.6	225.7	485.7	832.5	1005.9	1057.5	1160.5	1237.8	1216.7
105°	163.4	200.9	238.2	247.6	499.4	835.2	1003.0	1118.6	1349.6	1522.8	1511.4
107.5°	201.4	236.3	271.2	279.9	502.0	798.0	946.1	1107.2	1429.4	1671.0	1673.8
110°	227.1	258.6	290.0	297.9	498.1	765.1	898.5	1078.7	1438.9	1709.1	1721.0



TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	252.3	282.3	312.2	319.7	498.2	736.3	855.3	1039.7	1408.4	1684.9	1703.1
115°	290.3	318.0	345.7	352.6	502.9	703.2	803.4	981.0	1336.3	1602.7	1627.8
117.5°	327.9	353.0	378.2	384.4	512.3	682.7	767.8	928.1	1248.6	1489.1	1516.9
120°	349.7	373.4	397.1	403.0	519.9	675.7	753.6	900.1	1192.9	1412.6	1439.8
122.5°	371.1	395.0	418.8	424.8	530.8	672.0	742.7	874.6	1138.3	1336.1	1362.9
125°	403.9	425.6	447.4	452.8	545.5	669.0	730.8	842.8	1066.8	1234.9	1259.5
127.5°	430.5	452.4	474.4	479.9	560.2	667.3	720.8	816.9	1009.4	1153.6	1174.5
130°	444.7	468.4	492.1	497.9	571.0	668.4	717.0	802.6	973.9	1102.3	1121.5
132.5°	459.5	483.2	506.8	512.7	579.7	669.0	713.7	790.3	943.7	1058.7	1075.8
135°	481.3	502.9	524.4	529.8	589.2	668.4	708.0	772.2	900.6	996.9	1011.8
137.5°	503.6	524.9	546.3	551.6	603.4	672.5	707.0	761.2	869.8	951.2	963.3
140°	522.2	541.8	561.4	566.4	612.2	673.2	703.7	750.6	844.4	914.7	926.0
142.5°	536.4	554.6	572.7	577.3	619.4	675.6	703.7	744.9	827.2	889.0	898.7
145°	558.3	574.1	590.0	593.9	628.9	675.6	698.9	732.6	800.0	850.5	858.0
147.5°	580.2	595.6	611.0	614.9	642.8	680.2	698.9	725.4	778.5	818.2	824.4
150°	594.4	608.3	622.3	625.8	650.2	682.7	698.9	721.3	766.1	799.7	804.6
152.5°	609.2	619.7	630.3	632.9	655.0	684.2	698.9	718.0	756.3	784.9	788.7
155°	631.0	638.8	646.6	648.5	665.3	687.7	698.9	714.2	744.5	767.4	769.9
157.5°	647.2	654.8	662.3	664.2	675.8	691.2	698.9	710.8	734.4	752.1	753.9
160°	658.1	664.0	669.9	671.4	680.6	692.8	698.9	709.0	729.3	744.5	745.5
162.5°	669.0	673.4	677.9	679.0	685.6	694.5	698.9	707.5	724.6	737.5	738.4
165°	680.8	684.9	688.9	689.9	693.0	696.9	698.9	705.1	717.3	726.4	727.5
167.5°	691.9	693.7	695.6	696.1	698.6	702.0	703.7	707.7	715.7	721.8	722.2
170°	698.9	700.8	702.8	703.2	703.4	703.6	703.7	707.7	715.7	721.8	721.8
172.5°	702.8	703.1	703.6	703.7	703.7	703.7	703.7	706.8	713.1	717.9	717.5
175°	708.0	708.0	708.0	708.0	706.5	704.6	703.7	705.7	709.7	712.7	712.7
177.5°	708.0	708.0	708.0	708.0	706.9	705.3	704.6	706.2	709.4	711.8	711.3
180°	708.0	708.0	708.0	708.0	708.0	708.0	708.0	708.0	708.0	708.0	708.0



TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	285.4	285.4
2.5°	304.7	302.8
5°	391.9	393.7
7.5°	527.7	526.8
10°	656.2	664.4
12.5°	749.8	751.6
15°	806.7	810.3
17.5°	828.7	829.6
20°	829.6	827.8
22.5°	819.5	817.7
25°	807.6	806.7
27.5°	796.6	797.5
30°	792.0	794.7
32.5°	792.0	796.6
35°	793.8	798.4
37.5°	792.9	798.4
40°	789.2	795.6
42.5°	779.1	783.7
45°	763.5	769.0
47.5°	743.3	747.0
50°	717.6	721.3
52.5°	685.5	686.4
55°	647.0	650.6
57.5°	605.7	606.6
60°	559.8	562.5
62.5°	511.2	511.2
65°	459.8	461.6
67.5°	406.5	411.1
70°	352.4	353.3
72.5°	299.2	299.2
75°	244.1	245.0
77.5°	191.8	191.8
80°	142.2	143.2
82.5°	98.2	100.0
85°	61.5	61.5
87.5°	28.4	25.7
90°	18.1	18.1
92.5°	72.3	58.0
95°	252.1	208.6
97.5°	604.0	521.3
100°	870.3	771.6
102.5°	1132.2	1047.7
105°	1466.1	1420.7
107.5°	1684.8	1695.8
110°	1768.2	1815.5



TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1775.6	1848.3
115°	1728.6	1829.3
117.5°	1628.7	1740.4
120°	1548.2	1656.8
122.5°	1469.9	1577.0
125°	1358.1	1456.7
127.5°	1257.6	1340.8
130°	1198.4	1275.3
132.5°	1144.6	1213.5
135°	1071.0	1130.3
137.5°	1011.9	1060.5
140°	971.4	1016.8
142.5°	937.8	976.9
145°	887.5	917.1
147.5°	848.8	873.3
150°	824.5	844.4
152.5°	803.6	818.7
155°	779.8	789.7
157.5°	760.9	767.8
160°	749.6	753.6
162.5°	742.2	746.0
165°	731.5	735.5
167.5°	723.9	725.5
170°	721.8	721.8
172.5°	716.1	714.6
175°	712.7	712.7
177.5°	709.7	708.0
180°	708.0	708.0



TEST NUMBER: P937960

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-4-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.51	3.26	3.60	4.35	5.85	15.65	16.40	16.74	17.49	18.99
	3H	3.21	3.88	4.31	4.98	6.49	17.47	18.13	18.56	19.23	20.75
	4H	3.50	4.14	4.61	5.24	6.76	18.10	18.73	19.20	19.83	21.35
	6H	3.75	4.33	4.86	5.44	6.97	18.51	19.09	19.62	20.20	21.73
	8H	3.81	4.37	4.93	5.49	7.02	18.62	19.18	19.74	20.30	21.82
	12H	3.83	4.36	4.95	5.47	7.02	18.68	19.20	19.80	20.32	21.87
4H	2H	9.69	10.32	10.80	11.42	12.95	15.91	16.55	17.03	17.65	19.17
	3H	11.25	11.78	12.37	12.91	14.44	17.93	18.46	19.05	19.59	21.12
	4H	11.34	11.83	12.46	12.94	14.50	18.68	19.17	19.81	20.29	21.84
	6H	11.34	11.76	12.47	12.90	14.45	19.20	19.62	20.34	20.76	22.31
	8H	11.32	11.71	12.45	12.84	14.40	19.36	19.75	20.49	20.88	22.44
	12H	11.27	11.62	12.42	12.77	14.33	19.43	19.79	20.58	20.93	22.50
8H	4H	12.76	13.15	13.89	14.29	15.85	18.73	19.13	19.87	20.26	21.82
	6H	13.00	13.32	14.15	14.50	16.06	19.35	19.67	20.50	20.84	22.40
	8H	13.02	13.30	14.17	14.45	16.03	19.56	19.84	20.72	20.99	22.57
	12H	12.98	13.23	14.14	14.38	15.99	19.69	19.94	20.85	21.09	22.70
12H	4H	12.90	13.25	14.05	14.39	15.96	18.68	19.04	19.83	20.18	21.75
	6H	13.25	13.54	14.41	14.69	16.27	19.33	19.61	20.49	20.76	22.34
	8H	13.32	13.57	14.48	14.72	16.33	19.54	19.79	20.71	20.94	22.56