

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937962

Luminaire Tested: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937962
REPORT IS A COMBINATION OF REPORTS P933606 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9951.3 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 83.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937962
CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	27
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	15
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	11
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	10
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	8
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	7
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2584	2584	2584
5°	2523	2985	3473
10°	2288	4351	5758
15°	1944	5683	6953
20°	1582	6585	7086
25°	1319	6889	6942
30°	1111	6930	6929
35°	982	6813	7108
40°	855	6662	7293
45°	774	6550	7322
50°	710	6450	7201
55°	679	6303	6881
60°	694	6023	6376
65°	721	5599	5684
70°	766	4880	4802
75°	846	3975	3748
80°	918	2754	2525
85°	799	1459	1293

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7322 cd/sqm



TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	0.5
10°-20°	239.5	2.4
20°-30°	418.9	4.2
30°-40°	539.2	5.4
40°-50°	602.2	6.1
50°-60°	576.8	5.8
60°-70°	457.1	4.6
70°-80°	268.8	2.7
80°-90°	78.6	0.8
90°-100°	505.0	5.1
100°-110°	1327.7	13.3
110°-120°	1376.7	13.8
120°-130°	1104.3	11.1
130°-140°	866.5	8.7
140°-150°	665.1	6.7
150°-160°	478.9	4.8
160°-170°	293.0	2.9
170°-180°	99.0	1.0
0°-30°	712.3	7.2
0°-40°	1251.5	12.6
0°-60°	2430.6	24.4
0°-90°	3235.1	32.5
90°-120°	3209.4	32.3
90°-150°	5845.2	58.7
90°-180°	6716.0	67.5
0°-180°	9951.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	418	418	418	418	418	
5°	407	436	492	556	576	38
15°	305	563	948	1150	1186	85
25°	195	638	1130	1179	1181	90
35°	132	610	1064	1124	1168	82
45°	90	486	940	1077	1126	70
55°	64	309	798	927	952	59
65°	51	164	592	666	676	51
75°	38	101	325	357	359	39
85°	13	31	81	89	90	14
90°	7	19	53	26	26	7
95°	67	261	870	448	305	74
105°	239	362	1468	2228	2079	254
115°	425	516	1176	2345	2677	420
125°	591	663	1070	1807	2132	525
135°	704	775	1036	1459	1654	545
145°	817	869	1023	1245	1342	512
155°	923	949	1023	1123	1156	424
165°	996	1010	1023	1063	1076	281
175°	1036	1036	1030	1043	1043	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7
2.5°	417.7	417.7	420.3	421.7	424.4	425.7	428.4	431.1	439.2	440.5	443.2
5°	406.9	412.3	429.7	436.5	455.3	480.8	491.5	509.0	545.2	556.0	562.7
7.5°	390.8	402.9	445.9	456.6	503.6	570.8	599.0	636.6	694.3	722.5	745.3
10°	365.3	390.8	467.4	492.9	569.4	671.5	723.9	776.2	863.5	902.5	917.2
12.5°	337.1	378.7	490.2	525.1	635.2	784.3	847.4	905.2	1004.5	1057.0	1065.1
15°	304.9	361.3	511.7	562.7	705.1	878.3	948.1	1019.4	1112.1	1149.7	1159.1
17.5°	276.7	347.8	531.8	585.5	758.8	962.9	1034.2	1093.3	1168.5	1194.0	1200.7
20°	241.7	326.3	545.2	615.1	815.2	1024.8	1093.3	1138.9	1190.0	1206.1	1208.8
22.5°	216.2	303.5	553.3	625.8	852.8	1062.4	1120.1	1156.4	1191.3	1196.7	1198.0
25°	194.7	278.0	552.0	637.9	885.0	1085.2	1129.5	1156.4	1176.5	1179.2	1179.2
27.5°	174.6	249.8	546.6	640.6	909.2	1090.6	1125.5	1144.3	1153.7	1159.1	1159.1
30°	157.1	222.9	533.2	635.2	919.9	1085.2	1113.4	1122.8	1132.2	1140.3	1144.3
32.5°	143.7	197.4	513.0	624.5	921.3	1071.8	1091.9	1097.3	1110.7	1129.5	1136.2
35°	131.6	171.9	490.2	609.7	913.2	1050.3	1063.7	1069.1	1096.0	1124.2	1133.6
37.5°	119.5	153.1	460.6	584.2	901.1	1024.8	1034.2	1043.6	1085.2	1118.8	1129.5
40°	107.4	137.0	425.7	556.0	882.3	993.8	1001.9	1016.6	1071.8	1110.7	1121.5
42.5°	98.0	123.6	388.1	526.4	858.2	958.9	971.0	992.5	1055.7	1097.3	1109.4
45°	90.0	110.1	347.8	486.2	827.3	922.6	940.1	969.6	1036.9	1077.1	1087.9
47.5°	81.9	100.7	306.2	444.5	793.7	886.4	909.2	942.8	1011.3	1050.3	1059.7
50°	75.2	91.3	264.6	400.2	757.4	847.4	874.3	909.2	979.0	1015.3	1027.5
52.5°	69.8	83.3	225.6	355.9	715.8	807.1	838.0	874.3	940.1	975.0	983.1
55°	64.5	76.5	192.0	308.9	672.8	764.1	797.7	832.6	897.1	926.6	932.0
57.5°	61.8	71.2	163.8	264.6	627.2	715.8	753.4	785.6	846.1	868.9	874.3
60°	57.7	67.1	142.4	227.0	577.5	670.1	702.4	734.6	785.6	804.4	808.5
62.5°	53.7	64.5	126.2	190.7	526.4	616.4	648.7	678.2	721.2	734.6	740.0
65°	51.0	61.8	114.2	163.8	474.1	560.0	592.2	617.8	652.7	666.1	668.8
67.5°	48.3	59.1	104.8	141.0	421.7	503.6	527.8	552.0	578.8	592.2	593.6
70°	44.3	56.4	96.7	124.9	368.0	439.2	459.3	484.8	506.3	513.0	517.0
72.5°	41.6	52.4	91.3	112.8	312.9	377.4	396.2	410.9	429.7	436.5	436.5
75°	37.6	47.0	85.9	100.7	256.5	308.9	325.0	339.8	354.5	357.2	353.2
77.5°	33.6	41.6	73.9	84.6	200.1	244.4	257.8	265.9	278.0	280.7	282.0
80°	28.2	36.3	57.7	65.8	145.0	180.0	189.4	196.1	206.8	206.8	209.5
82.5°	21.5	28.2	41.6	47.0	98.0	123.6	131.6	135.6	142.4	142.4	142.4
85°	13.4	17.5	26.9	30.9	59.1	75.2	80.6	81.9	87.3	88.6	88.6
87.5°	6.7	9.4	17.5	18.8	30.9	38.9	38.9	41.6	41.6	40.3	38.9
90°	7.0	12.5	18.1	19.4	30.5	45.4	52.8	46.9	35.2	26.4	26.4
92.5°	27.8	75.1	122.4	134.2	188.6	261.3	297.6	260.8	187.3	132.1	126.9
95°	66.8	153.3	239.8	261.4	464.2	734.7	869.9	776.2	588.9	448.5	432.5
97.5°	115.4	191.7	268.1	287.1	625.3	1076.3	1301.7	1242.5	1124.2	1035.3	1005.1
100°	153.0	222.2	291.4	308.7	683.9	1184.3	1434.5	1438.8	1447.5	1453.9	1417.8
102.5°	185.0	249.5	314.2	330.3	710.9	1218.3	1472.0	1547.4	1698.2	1811.3	1780.4
105°	239.2	293.9	348.5	362.2	730.8	1222.2	1467.9	1636.9	1975.0	2228.5	2211.9
107.5°	294.8	345.8	396.8	409.5	734.5	1167.8	1384.4	1620.2	2091.8	2445.5	2449.5
110°	332.3	378.4	424.4	435.9	728.9	1119.5	1314.9	1578.4	2105.7	2501.1	2518.4



TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	369.2	413.1	457.0	468.0	729.1	1077.4	1251.6	1521.3	2060.9	2465.6	2492.2
115°	424.8	465.3	505.9	516.0	735.9	1029.2	1175.8	1435.7	1955.5	2345.4	2382.2
117.5°	479.8	516.6	553.3	562.5	749.6	998.9	1123.6	1358.2	1827.3	2179.2	2220.0
120°	511.8	546.4	581.0	589.7	760.7	988.7	1102.8	1317.1	1745.7	2067.2	2106.9
122.5°	543.1	578.0	612.9	621.6	776.7	983.4	1086.8	1279.8	1665.8	1955.3	1994.4
125°	591.0	622.9	654.7	662.6	798.3	979.0	1069.5	1233.4	1561.2	1807.2	1843.3
127.5°	629.9	662.1	694.2	702.3	819.8	976.5	1054.9	1195.6	1477.2	1688.3	1718.7
130°	650.8	685.5	720.0	728.7	835.5	977.9	1049.2	1174.6	1425.2	1613.2	1641.3
132.5°	672.4	707.0	741.6	750.3	848.3	979.0	1044.4	1156.6	1380.9	1549.2	1574.3
135°	704.3	735.9	767.4	775.3	862.2	978.1	1036.1	1130.0	1317.9	1458.8	1480.5
137.5°	737.0	768.3	799.5	807.3	883.0	984.1	1034.6	1114.0	1272.9	1392.0	1409.8
140°	764.1	792.9	821.6	828.8	895.8	985.1	1029.8	1098.4	1235.6	1338.5	1355.1
142.5°	785.0	811.6	838.2	844.8	906.5	988.7	1029.8	1090.0	1210.6	1301.0	1315.3
145°	817.0	840.2	863.3	869.2	920.4	988.7	1022.8	1072.1	1170.7	1244.7	1255.5
147.5°	849.0	871.6	894.1	899.8	940.8	995.5	1022.8	1061.6	1139.2	1197.4	1206.3
150°	869.9	890.3	910.6	915.7	951.4	999.0	1022.8	1055.6	1121.1	1170.3	1177.5
152.5°	891.4	906.9	922.4	926.2	958.4	1001.3	1022.8	1050.7	1106.7	1148.7	1154.1
155°	923.4	934.9	946.3	949.1	973.7	1006.4	1022.8	1045.1	1089.6	1123.0	1126.7
157.5°	947.1	958.2	969.3	972.0	989.0	1011.5	1022.8	1040.1	1074.7	1100.7	1103.2
160°	963.0	971.7	980.4	982.5	995.9	1013.9	1022.8	1037.7	1067.3	1089.6	1091.0
162.5°	979.0	985.5	992.0	993.6	1003.4	1016.4	1022.8	1035.3	1060.3	1079.1	1080.6
165°	996.4	1002.3	1008.2	1009.6	1014.0	1019.8	1022.8	1031.8	1049.8	1063.2	1064.6
167.5°	1012.4	1015.2	1018.0	1018.7	1022.4	1027.3	1029.8	1035.7	1047.4	1056.2	1056.8
170°	1022.8	1025.6	1028.4	1029.1	1029.3	1029.6	1029.8	1035.7	1047.4	1056.2	1056.2
172.5°	1028.4	1029.0	1029.6	1029.8	1029.8	1029.8	1029.8	1034.4	1043.7	1050.6	1050.1
175°	1036.1	1036.1	1036.1	1036.1	1034.0	1031.2	1029.8	1032.7	1038.7	1043.0	1043.0
177.5°	1036.1	1036.1	1036.1	1036.1	1034.4	1032.2	1031.1	1033.5	1038.1	1041.6	1041.0
180°	1036.1	1036.1	1036.1	1036.1	1036.1	1036.1	1036.1	1036.1	1036.1	1036.1	1036.1



TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	417.7	417.7
2.5°	445.9	443.2
5°	573.4	576.1
7.5°	772.2	770.9
10°	960.2	972.3
12.5°	1097.3	1100.0
15°	1180.6	1185.9
17.5°	1212.8	1214.1
20°	1214.1	1211.4
22.5°	1199.4	1196.7
25°	1181.9	1180.6
27.5°	1165.8	1167.1
30°	1159.1	1163.1
32.5°	1159.1	1165.8
35°	1161.8	1168.5
37.5°	1160.4	1168.5
40°	1155.0	1164.4
42.5°	1140.3	1147.0
45°	1117.4	1125.5
47.5°	1087.9	1093.3
50°	1050.3	1055.7
52.5°	1003.2	1004.5
55°	946.8	952.2
57.5°	886.4	887.7
60°	819.2	823.2
62.5°	748.0	748.0
65°	672.8	675.5
67.5°	594.9	601.6
70°	515.7	517.0
72.5°	437.8	437.8
75°	357.2	358.6
77.5°	280.7	280.7
80°	208.2	209.5
82.5°	143.7	146.4
85°	90.0	90.0
87.5°	41.6	37.6
90°	26.4	26.4
92.5°	105.8	84.8
95°	368.9	305.2
97.5°	883.9	762.8
100°	1273.6	1129.3
102.5°	1656.8	1533.2
105°	2145.4	2079.0
107.5°	2465.5	2481.6
110°	2587.6	2656.8



TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2598.5	2704.8
115°	2529.6	2677.0
117.5°	2383.5	2547.0
120°	2265.8	2424.6
122.5°	2151.1	2307.8
125°	1987.6	2131.9
127.5°	1840.5	1962.3
130°	1753.8	1866.3
132.5°	1675.1	1775.9
135°	1567.3	1654.2
137.5°	1480.8	1551.9
140°	1421.6	1488.0
142.5°	1372.4	1429.6
145°	1298.7	1342.0
147.5°	1242.2	1278.1
150°	1206.6	1235.6
152.5°	1176.1	1198.0
155°	1141.2	1155.7
157.5°	1113.4	1123.6
160°	1096.9	1102.8
162.5°	1086.1	1091.7
165°	1070.5	1076.3
167.5°	1059.2	1061.8
170°	1056.2	1056.2
172.5°	1048.0	1045.8
175°	1043.0	1043.0
177.5°	1038.6	1036.1
180°	1036.1	1036.1



TEST NUMBER: P937962

CATALOG NUMBER: SQ4-FB-125U-075D-93050-1D-UNV-STD-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.43	3.18	3.52	4.27	5.77	15.60	16.35	16.69	17.44	18.94
	3H	3.13	3.80	4.23	4.90	6.42	17.43	18.10	18.52	19.20	20.71
	4H	3.42	4.06	4.53	5.16	6.68	18.06	18.70	19.17	19.80	21.32
	6H	3.67	4.25	4.79	5.36	6.89	18.48	19.07	19.60	20.17	21.71
	8H	3.73	4.29	4.85	5.41	6.94	18.60	19.16	19.72	20.27	21.80
	12H	3.75	4.28	4.87	5.39	6.94	18.66	19.19	19.78	20.30	21.85
4H	2H	9.63	10.26	10.74	11.36	12.89	15.86	16.50	16.98	17.60	19.12
	3H	11.19	11.72	12.31	12.84	14.38	17.89	18.42	19.01	19.55	21.08
	4H	11.28	11.76	12.40	12.88	14.43	18.65	19.14	19.77	20.25	21.81
	6H	11.28	11.70	12.41	12.84	14.38	19.18	19.60	20.31	20.74	22.28
	8H	11.25	11.65	12.39	12.78	14.34	19.33	19.73	20.47	20.86	22.42
	12H	11.20	11.56	12.35	12.70	14.27	19.42	19.77	20.57	20.92	22.49
8H	4H	12.71	13.10	13.84	14.23	15.79	18.70	19.09	19.83	20.22	21.79
	6H	12.94	13.27	14.10	14.44	16.00	19.32	19.64	20.47	20.82	22.38
	8H	12.96	13.24	14.12	14.40	15.98	19.54	19.82	20.69	20.97	22.55
	12H	12.92	13.17	14.09	14.32	15.94	19.67	19.92	20.84	21.07	22.68
12H	4H	12.84	13.20	13.99	14.34	15.91	18.65	19.00	19.80	20.15	21.71
	6H	13.20	13.48	14.36	14.64	16.22	19.30	19.59	20.46	20.74	22.32
	8H	13.26	13.51	14.43	14.66	16.28	19.52	19.77	20.69	20.92	22.54