

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521726

Luminaire Tested: **SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521726
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4352.6 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521726

CATALOG NUMBER: SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P521726

CATALOG NUMBER: SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58				58
1	101	97	94	90	94	91	88	85	79	77	75	68	66	65	58	57	56	51				51
2	93	86	81	76	87	81	76	72	71	67	64	61	59	57	53	51	49	45				45
3	86	77	70	65	80	72	67	62	64	59	56	56	52	50	48	46	44	40				40
4	79	69	62	57	74	65	59	54	58	53	49	51	47	44	44	41	39	36				36
5	73	63	55	50	68	59	52	47	52	47	43	46	42	39	40	37	35	32				32
6	68	57	49	44	64	54	47	42	48	42	38	42	38	35	37	34	31	29				29
7	63	52	44	39	59	49	42	38	44	39	35	39	35	32	34	31	29	26				26
8	59	48	40	35	55	45	39	34	40	35	31	36	32	29	32	29	26	24				24
9	55	44	37	32	52	42	35	31	37	32	29	34	29	26	30	26	24	22				22
10	52	41	34	29	49	39	32	28	35	30	26	31	27	24	28	25	22	20				20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15936	15936	15936
5°	15738	15681	15773
10°	14869	15004	15351
15°	13726	14045	14674
20°	12464	12934	13789
25°	11180	11789	12847
30°	9996	10650	11870
35°	8741	9373	10713
40°	7358	7942	9275
45°	6072	6596	7744
50°	5070	5526	6452
55°	4303	4742	5327
60°	3678	4111	4251
65°	2930	3458	2746
70°	2598	2698	1678
75°	2406	2189	1027
80°	2216	2014	887
85°	2001	1842	720



TEST NUMBER: P521726

CATALOG NUMBER: SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	3.6
10°-20°	412.1	9.5
20°-30°	533.8	12.3
30°-40°	522.7	12.0
40°-50°	400.1	9.2
50°-60°	266.6	6.1
60°-70°	145.5	3.3
70°-80°	60.6	1.4
80°-90°	17.2	0.4
90°-100°	146.1	3.4
100°-110°	353.2	8.1
110°-120°	376.7	8.7
120°-130°	305.1	7.0
130°-140°	236.2	5.4
140°-150°	180.2	4.1
150°-160°	130.4	3.0
160°-170°	80.3	1.8
170°-180°	27.2	0.6
0°-30°	1104.3	25.4
0°-40°	1627.0	37.4
0°-60°	2293.7	52.7
0°-90°	2517.0	57.8
90°-120°	876.1	20.1
90°-150°	1597.6	36.7
90°-180°	1836.0	42.2
0°-180°	4352.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1727	1727	1727	1727	1727	
5°	1699	1682	1693	1697	1703	158
15°	1437	1432	1470	1510	1536	401
25°	1098	1101	1158	1209	1262	505
35°	776	780	832	888	951	482
45°	465	474	506	544	594	363
55°	268	279	295	306	331	243
65°	134	145	158	138	126	139
75°	68	68	61	42	29	72
85°	19	19	17	11	7	21
90°	0	0	0	0	0	2
95°	14	73	250	163	114	16
105°	56	98	424	549	542	60
115°	103	132	341	647	721	102
125°	147	169	296	514	604	131
135°	181	202	284	406	466	140
145°	214	230	279	345	372	134
155°	245	256	282	305	316	113
165°	271	275	286	290	294	76
175°	286	285	286	284	283	27
180°	283	283	283	283	283	

TEST NUMBER: P521726

CATALOG NUMBER: SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1727.3	1727.3	1727.3	1727.3	1727.3
2.5°	1731.6	1716.1	1720.0	1719.9	1715.2
5°	1699.3	1682.2	1693.2	1697.1	1703.1
7.5°	1636.2	1623.3	1643.3	1658.2	1670.2
10°	1587.1	1576.0	1601.5	1623.1	1638.6
12.5°	1530.1	1520.8	1552.4	1581.3	1601.7
15°	1437.0	1431.8	1470.4	1510.4	1536.3
17.5°	1337.4	1334.9	1379.1	1425.8	1459.0
20°	1269.5	1268.8	1317.3	1365.9	1404.4
22.5°	1201.0	1202.6	1253.6	1304.2	1348.1
25°	1098.2	1101.2	1158.1	1208.6	1262.0
27.5°	1003.2	1004.5	1063.4	1116.7	1173.6
30°	938.3	942.0	999.7	1054.9	1114.2
32.5°	873.4	877.7	934.2	991.2	1051.7
35°	776.1	779.8	832.2	888.2	951.2
37.5°	675.8	680.8	727.3	780.3	842.2
40°	610.9	618.3	659.4	709.3	770.1
42.5°	548.4	557.6	595.7	643.1	697.9
45°	465.4	474.3	505.5	543.8	593.5
47.5°	393.8	404.0	428.1	461.0	503.4
50°	353.2	362.8	385.0	409.4	449.5
52.5°	317.4	327.1	346.8	365.6	399.7
55°	267.5	278.7	294.8	306.0	331.2
57.5°	226.6	237.3	250.1	255.2	270.4
60°	199.3	211.2	222.8	222.3	230.4
62.5°	174.5	184.6	196.2	188.1	188.6
65°	134.2	145.3	158.4	138.4	125.8
67.5°	108.4	110.8	124.3	96.5	81.6
70°	96.3	96.3	100.0	74.7	62.2
72.5°	84.7	84.7	81.2	60.8	47.6
75°	67.5	67.5	61.4	42.1	28.8
77.5°	52.0	51.4	47.0	31.4	20.9
80°	41.7	41.7	37.9	24.8	16.7
82.5°	32.6	32.6	29.4	19.4	12.4
85°	18.9	18.9	17.4	11.3	6.8
87.5°	6.7	6.7	6.1	3.6	3.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.8	39.6	93.2	45.3	30.7
95°	14.4	73.1	250.4	162.8	114.1
97.5°	25.6	81.0	329.8	317.7	272.7
100°	34.2	85.9	373.5	394.3	357.3
102.5°	42.4	90.3	402.3	458.0	436.0
105°	56.4	97.5	424.5	549.3	542.2
107.5°	70.3	106.1	411.4	622.4	639.0
110°	79.9	113.3	390.3	654.0	685.1

TEST NUMBER: P521726

CATALOG NUMBER: SQ4-WB-025U-075D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	89.5	120.6	371.6	661.7	714.9
115°	103.3	132.0	341.1	646.6	721.1
117.5°	117.0	144.1	323.2	611.8	699.2
120°	126.1	151.3	311.6	584.5	676.1
122.5°	135.7	159.1	304.4	556.6	646.8
125°	147.1	169.4	296.0	514.2	604.1
127.5°	158.4	179.4	290.1	478.3	557.2
130°	165.1	185.7	288.2	453.3	530.8
132.5°	171.4	192.9	285.3	435.3	501.0
135°	180.7	201.9	284.0	405.5	466.5
137.5°	189.6	210.9	279.8	385.3	431.4
140°	196.3	215.7	279.8	370.8	413.1
142.5°	203.1	222.4	277.4	358.2	393.9
145°	213.8	229.6	278.6	344.7	371.7
147.5°	223.7	239.1	277.9	329.1	351.4
150°	230.0	243.5	279.8	322.2	339.9
152.5°	236.7	249.7	279.3	315.0	330.7
155°	245.0	255.6	282.2	305.3	316.4
157.5°	255.0	264.0	281.6	301.6	308.2
160°	258.8	266.4	284.0	296.7	301.4
162.5°	265.0	271.7	283.1	295.2	298.1
165°	270.8	274.9	285.8	290.1	294.2
167.5°	277.9	280.6	285.1	289.8	289.9
170°	279.8	281.6	287.0	286.5	289.4
172.5°	283.2	284.5	285.6	286.9	285.1
175°	286.4	285.2	286.4	284.0	283.4
177.5°	285.8	285.8	284.9	283.8	281.5
180°	283.4	283.4	283.4	283.4	283.4

(END OF REPORT)