

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521831

Luminaire Tested: **SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521831
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5633.4 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 55.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521831

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521831

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	46	46	40
2	90	83	78	73	82	77	72	68	65	61	58	53	51	49	43	41	40	35
3	83	74	67	62	76	68	63	58	58	54	50	48	45	43	39	37	35	31
4	76	66	59	54	70	61	55	50	52	48	44	44	40	38	36	33	31	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	46	41	60	50	44	39	43	38	34	36	33	30	30	27	25	23
7	61	49	42	36	56	46	39	35	39	34	31	33	30	27	28	25	23	20
8	56	45	38	33	52	42	35	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	33	28	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	29	25	31	26	23	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16106	16106	16106
5°	15906	15848	15941
10°	15027	15163	15515
15°	13872	14194	14831
20°	12597	13071	13936
25°	11299	11915	12984
30°	10103	10763	11996
35°	8835	9473	10827
40°	7436	8026	9374
45°	6136	6666	7826
50°	5124	5585	6519
55°	4349	4793	5384
60°	3718	4155	4298
65°	2960	3495	2777
70°	2625	2727	1694
75°	2431	2210	1037
80°	2237	2035	898
85°	2022	1863	730



TEST NUMBER: P521831

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.8
10°-20°	416.5	7.4
20°-30°	539.5	9.6
30°-40°	528.3	9.4
40°-50°	404.4	7.2
50°-60°	269.4	4.8
60°-70°	147.0	2.6
70°-80°	61.3	1.1
80°-90°	17.3	0.3
90°-100°	246.0	4.4
100°-110°	594.5	10.6
110°-120°	634.1	11.3
120°-130°	513.5	9.1
130°-140°	397.6	7.1
140°-150°	303.3	5.4
150°-160°	219.6	3.9
160°-170°	135.2	2.4
170°-180°	45.8	0.8
0°-30°	1116.1	19.8
0°-40°	1644.3	29.2
0°-60°	2318.2	41.2
0°-90°	2543.8	45.2
90°-120°	1474.5	26.2
90°-150°	2689.0	47.7
90°-180°	3090.0	54.9
0°-180°	5633.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1746	1746	1746	1746	1746	
5°	1717	1700	1711	1715	1721	160
15°	1452	1447	1486	1526	1553	406
25°	1110	1113	1170	1222	1275	510
35°	784	788	841	898	961	488
45°	470	479	511	550	600	367
55°	270	282	298	309	335	245
65°	136	147	160	140	127	141
75°	68	68	62	43	29	73
85°	19	19	18	11	7	21
90°	0	0	0	0	0	2
95°	24	123	421	274	192	27
105°	95	164	714	924	913	100
115°	174	222	574	1088	1214	172
125°	248	285	498	866	1017	221
135°	304	340	478	682	785	235
145°	360	386	469	580	626	225
155°	412	430	475	514	533	190
165°	456	463	481	488	495	129
175°	482	480	482	478	477	46
180°	477	477	477	477	477	

TEST NUMBER: P521831

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1745.7	1745.7	1745.7	1745.7	1745.7
2.5°	1750.0	1734.4	1738.3	1738.2	1733.4
5°	1717.4	1700.1	1711.2	1715.2	1721.2
7.5°	1653.6	1640.6	1660.8	1675.8	1687.9
10°	1604.0	1592.8	1618.5	1640.4	1656.1
12.5°	1546.4	1537.0	1568.9	1598.2	1618.7
15°	1452.3	1447.1	1486.0	1526.5	1552.7
17.5°	1351.7	1349.1	1393.8	1441.0	1474.5
20°	1283.0	1282.3	1331.3	1380.4	1419.4
22.5°	1213.8	1215.4	1267.0	1318.1	1362.4
25°	1109.9	1112.9	1170.4	1221.5	1275.4
27.5°	1013.9	1015.2	1074.7	1128.5	1186.1
30°	948.3	952.0	1010.3	1066.1	1126.0
32.5°	882.7	887.1	944.2	1001.8	1062.9
35°	784.4	788.1	841.1	897.7	961.3
37.5°	683.0	688.1	735.0	788.6	851.2
40°	617.4	624.9	666.4	716.8	778.3
42.5°	554.3	563.6	602.1	649.9	705.3
45°	470.3	479.3	510.9	549.6	599.8
47.5°	398.0	408.3	432.6	465.9	508.8
50°	357.0	366.7	389.1	413.8	454.2
52.5°	320.8	330.5	350.5	369.5	404.0
55°	270.4	281.6	298.0	309.3	334.7
57.5°	229.0	239.8	252.8	257.9	273.3
60°	201.5	213.4	225.2	224.6	232.9
62.5°	176.3	186.5	198.2	190.1	190.6
65°	135.6	146.8	160.1	139.9	127.2
67.5°	109.5	111.9	125.6	97.6	82.4
70°	97.3	97.3	101.1	75.5	62.8
72.5°	85.6	85.6	82.1	61.4	48.1
75°	68.2	68.2	62.0	42.6	29.1
77.5°	52.5	51.9	47.5	31.8	21.1
80°	42.1	42.1	38.3	25.1	16.9
82.5°	32.9	32.9	29.7	19.6	12.6
85°	19.1	19.1	17.6	11.4	6.9
87.5°	6.7	6.7	6.1	3.7	3.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.1	66.6	156.9	76.3	51.7
95°	24.3	123.1	421.4	274.0	192.0
97.5°	43.1	136.3	555.0	534.7	459.0
100°	57.6	144.6	628.6	663.6	601.3
102.5°	71.4	152.0	677.1	770.9	733.9
105°	95.0	164.2	714.5	924.5	912.6
107.5°	118.2	178.5	692.5	1047.7	1075.5
110°	134.4	190.7	656.9	1100.8	1153.1

TEST NUMBER: P521831

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	150.6	203.0	625.4	1113.7	1203.3
115°	173.8	222.3	574.0	1088.3	1213.8
117.5°	196.9	242.5	543.9	1029.8	1176.8
120°	212.2	254.7	524.5	983.8	1138.0
122.5°	228.4	267.7	512.4	936.9	1088.7
125°	247.6	285.2	498.2	865.5	1016.7
127.5°	266.6	302.0	488.3	805.1	937.9
130°	277.9	312.5	485.1	763.0	893.4
132.5°	288.4	324.6	480.3	732.6	843.3
135°	304.2	339.8	478.0	682.5	785.3
137.5°	319.2	354.9	471.0	648.6	726.0
140°	330.5	363.1	471.0	624.2	695.3
142.5°	341.8	374.4	466.9	602.9	663.0
145°	359.8	386.5	468.9	580.1	625.6
147.5°	376.6	402.5	467.7	553.9	591.4
150°	387.1	409.8	471.0	542.4	572.0
152.5°	398.4	420.3	470.2	530.2	556.7
155°	412.3	430.1	475.0	513.8	532.6
157.5°	429.1	444.3	474.0	507.6	518.7
160°	435.6	448.4	478.0	499.4	507.3
162.5°	446.1	457.4	476.4	496.9	501.7
165°	455.8	462.7	481.1	488.3	495.2
167.5°	467.7	472.3	479.9	487.7	487.9
170°	471.0	473.9	483.1	482.2	487.1
172.5°	476.6	478.8	480.7	482.8	479.9
175°	482.1	480.1	482.1	478.0	477.0
177.5°	481.1	481.1	479.4	477.7	473.8
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)