

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938455

Luminaire Tested: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938455
REPORT IS A COMBINATION OF REPORTS P933623 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25000.5 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 217.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938455
CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P938455

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	42	42	42	35
1	94	90	86	82	85	81	78	75	65	63	60	50	49	47	36	35	35	36	35	35	28
2	85	78	72	66	77	70	65	61	56	53	49	43	41	39	32	30	29	32	30	29	23
3	77	68	61	55	69	61	55	50	49	45	41	38	35	32	28	26	24	28	26	24	19
4	71	60	52	46	63	54	47	42	43	38	34	34	30	27	24	22	20	24	22	20	16
5	64	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	22	19	17	14
6	59	47	39	33	53	43	36	30	34	29	25	27	23	20	19	17	15	19	17	15	12
7	54	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	18	15	13	10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	13	11	16	13	11	9
9	47	35	27	22	42	31	25	20	26	20	17	20	16	14	15	12	10	15	12	10	8
10	43	31	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3451	3451	3451
5°	3373	3990	4639
10°	3061	5818	7691
15°	2602	7602	9287
20°	2119	8812	9464
25°	1768	9223	9272
30°	1492	9284	9254
35°	1320	9132	9494
40°	1151	8934	9741
45°	1043	8790	9779
50°	957	8661	9617
55°	918	8471	9191
60°	940	8103	8518
65°	980	7541	7593
70°	1047	6581	6415
75°	1165	5370	5006
80°	1281	3729	3373
85°	1160	1981	1727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9779 cd/sqm



TEST NUMBER: P938455

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	0.6
10°-20°	639.7	2.6
20°-30°	1118.9	4.5
30°-40°	1440.3	5.8
40°-50°	1608.8	6.4
50°-60°	1540.9	6.2
60°-70°	1221.1	4.9
70°-80°	718.1	2.9
80°-90°	209.1	0.8
90°-100°	1230.1	4.9
100°-110°	3234.0	12.9
110°-120°	3353.3	13.4
120°-130°	2689.8	10.8
130°-140°	2110.5	8.4
140°-150°	1619.9	6.5
150°-160°	1166.6	4.7
160°-170°	713.8	2.9
170°-180°	241.2	1.0
0°-30°	1902.9	7.6
0°-40°	3343.2	13.4
0°-60°	6492.9	26.0
0°-90°	8641.2	34.6
90°-120°	7817.5	31.3
90°-150°	14237.7	56.9
90°-180°	16359.0	65.4
0°-180°	25000.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1116	1116	1116	1116	1116	
5°	1087	1166	1313	1485	1539	100
15°	814	1503	2533	3071	3168	227
25°	520	1704	3017	3150	3154	240
35°	352	1629	2842	3003	3121	220
45°	240	1299	2511	2877	3006	186
55°	172	825	2131	2476	2544	157
65°	136	438	1582	1780	1805	135
75°	100	269	868	954	958	105
85°	36	83	215	237	240	38
90°	17	47	129	64	64	16
95°	163	637	2119	1092	744	181
105°	583	882	3575	5428	5064	618
115°	1035	1257	2864	5713	6521	1022
125°	1440	1614	2605	4402	5193	1278
135°	1716	1888	2524	3553	4029	1327
145°	1990	2117	2491	3032	3269	1247
155°	2249	2312	2491	2735	2815	1033
165°	2427	2459	2491	2590	2622	685
175°	2524	2524	2508	2540	2540	240
180°	2524	2524	2524	2524	2524	



TEST NUMBER: P938455

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1115.8	1115.8	1115.8	1115.8	1115.8	1115.8	1115.8	1115.8	1115.8	1115.8	1115.8
2.5°	1115.8	1115.8	1122.9	1126.6	1133.7	1137.3	1144.5	1151.6	1173.2	1176.8	1184.0
5°	1087.1	1101.4	1148.1	1166.0	1216.3	1284.4	1313.1	1359.7	1456.6	1485.3	1503.2
7.5°	1044.0	1076.3	1191.1	1219.8	1345.3	1524.7	1600.1	1700.5	1854.9	1930.2	1991.2
10°	975.9	1044.0	1248.5	1316.6	1521.2	1793.8	1933.8	2073.7	2306.9	2410.9	2450.4
12.5°	900.5	1011.7	1309.5	1402.8	1697.0	2095.2	2263.8	2418.1	2683.6	2823.6	2845.0
15°	814.4	965.1	1366.9	1503.2	1883.5	2346.4	2532.9	2723.1	2970.6	3071.0	3096.2
17.5°	739.1	929.2	1420.7	1564.2	2027.0	2572.4	2762.6	2920.4	3121.3	3189.4	3207.4
20°	645.7	871.9	1456.6	1643.1	2177.7	2737.4	2920.4	3042.3	3178.7	3221.7	3228.9
22.5°	577.6	810.8	1478.1	1671.8	2278.2	2837.9	2992.1	3089.0	3182.3	3196.7	3200.2
25°	520.2	742.7	1474.5	1704.1	2364.3	2898.9	3017.3	3089.0	3142.8	3150.0	3150.0
27.5°	466.4	667.3	1460.2	1711.3	2428.9	2913.2	3006.5	3056.7	3081.8	3096.2	3096.2
30°	419.7	595.6	1424.3	1697.0	2457.6	2898.9	2974.2	2999.3	3024.4	3046.0	3056.7
32.5°	383.9	527.3	1370.5	1668.3	2461.1	2863.0	2916.8	2931.2	2967.0	3017.3	3035.2
35°	351.6	459.2	1309.5	1628.8	2439.6	2805.5	2841.5	2855.8	2927.6	3002.9	3028.0
37.5°	319.3	409.0	1230.6	1560.7	2407.4	2737.4	2762.6	2787.6	2898.9	2988.6	3017.3
40°	287.0	366.0	1137.3	1485.3	2357.1	2654.9	2676.4	2715.8	2863.0	2967.0	2995.7
42.5°	261.9	330.1	1036.9	1406.3	2292.5	2561.6	2593.9	2651.3	2819.9	2931.2	2963.4
45°	240.4	294.2	929.2	1298.7	2210.0	2464.8	2511.4	2590.3	2769.7	2877.3	2906.0
47.5°	218.9	269.1	818.0	1187.6	2120.3	2367.9	2428.9	2518.5	2701.5	2805.5	2830.7
50°	200.9	243.9	706.7	1069.2	2023.5	2263.8	2335.6	2428.9	2615.5	2712.3	2744.6
52.5°	186.6	222.4	602.7	950.8	1912.2	2156.2	2238.7	2335.6	2511.4	2604.7	2626.2
55°	172.3	204.5	513.0	825.1	1797.5	2041.4	2131.1	2224.3	2396.6	2475.5	2489.8
57.5°	165.0	190.2	437.7	706.7	1675.5	1912.2	2012.7	2098.8	2260.3	2321.2	2335.6
60°	154.2	179.4	380.3	606.3	1542.7	1790.2	1876.4	1962.5	2098.8	2149.0	2159.8
62.5°	143.5	172.3	337.3	509.4	1406.3	1646.8	1732.8	1811.8	1926.6	1962.5	1976.8
65°	136.3	165.0	304.9	437.7	1266.5	1496.1	1582.1	1650.4	1743.6	1779.5	1786.7
67.5°	129.2	157.9	279.9	376.7	1126.6	1345.3	1410.0	1474.5	1546.3	1582.1	1585.8
70°	118.4	150.7	258.3	333.6	983.0	1173.2	1227.0	1295.2	1352.6	1370.5	1381.3
72.5°	111.2	139.9	243.9	301.3	835.9	1008.2	1058.4	1097.9	1148.1	1166.0	1166.0
75°	100.5	125.5	229.6	269.1	685.2	825.1	868.2	907.7	947.2	954.3	943.5
77.5°	89.7	111.2	197.3	226.0	534.6	653.0	688.8	710.4	742.7	749.8	753.5
80°	75.3	96.9	154.2	175.8	387.5	480.7	505.9	523.8	552.5	552.5	559.7
82.5°	57.4	75.3	111.2	125.5	261.9	330.1	351.6	362.3	380.3	380.3	380.3
85°	35.8	46.6	71.8	82.6	157.9	200.9	215.2	218.9	233.2	236.8	236.8
87.5°	17.9	25.1	46.6	50.2	82.6	104.0	104.0	111.2	111.2	107.6	104.0
90°	16.9	30.5	44.1	47.4	74.5	110.6	128.7	114.4	85.8	64.4	64.4
92.5°	67.7	182.8	298.1	326.9	459.6	636.4	724.9	635.2	456.1	321.8	309.0
95°	162.6	373.3	584.1	636.8	1130.8	1789.5	2118.8	1890.7	1434.6	1092.4	1053.7
97.5°	281.1	467.1	653.0	699.5	1523.2	2621.4	3170.5	3026.4	2738.1	2521.9	2448.1
100°	372.6	541.2	709.8	752.0	1666.0	2884.7	3494.0	3504.5	3525.6	3541.4	3453.6
102.5°	450.5	607.8	765.1	804.5	1731.5	2967.5	3585.5	3769.2	4136.5	4412.0	4336.7
105°	582.7	715.9	849.1	882.4	1780.1	2976.9	3575.3	3987.1	4810.6	5428.2	5387.7
107.5°	718.2	842.3	966.5	997.6	1789.1	2844.4	3372.1	3946.4	5095.1	5956.6	5966.4
110°	809.6	921.7	1033.9	1061.9	1775.6	2727.0	3202.7	3844.9	5129.0	6092.1	6134.3



TEST NUMBER: P938455

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	899.4	1006.3	1113.2	1139.9	1776.1	2624.4	3048.6	3705.7	5020.0	6005.7	6070.5
115°	1034.9	1133.4	1232.1	1256.7	1792.5	2506.8	2864.0	3497.1	4763.1	5712.7	5802.5
117.5°	1168.7	1258.2	1347.8	1370.1	1825.7	2433.2	2736.9	3308.3	4450.9	5308.0	5407.5
120°	1246.5	1330.9	1415.1	1436.2	1852.9	2408.4	2686.2	3208.2	4252.2	5035.2	5132.0
122.5°	1322.7	1407.8	1492.9	1514.2	1891.9	2395.4	2647.2	3117.3	4057.5	4762.6	4858.0
125°	1439.7	1517.1	1594.7	1614.1	1944.4	2384.7	2604.9	3004.2	3802.9	4401.8	4489.7
127.5°	1534.4	1612.7	1691.0	1710.6	1996.8	2378.5	2569.3	2912.2	3597.9	4112.2	4186.4
130°	1585.3	1669.6	1753.8	1774.9	2035.2	2382.2	2555.7	2860.9	3471.5	3929.3	3997.8
132.5°	1637.8	1722.1	1806.3	1827.4	2066.2	2384.6	2543.9	2817.1	3363.7	3773.5	3834.9
135°	1715.6	1792.4	1869.2	1888.4	2100.2	2382.5	2523.6	2752.4	3210.1	3553.3	3606.2
137.5°	1795.3	1871.3	1947.4	1966.4	2150.9	2397.0	2520.1	2713.6	3100.5	3390.7	3434.0
140°	1861.4	1931.3	2001.4	2018.9	2182.0	2399.5	2508.3	2675.4	3009.7	3260.3	3300.8
142.5°	1912.2	1976.9	2041.6	2057.8	2208.0	2408.2	2508.3	2655.1	2948.7	3168.9	3203.7
145°	1990.1	2046.6	2103.0	2117.1	2241.8	2408.2	2491.4	2611.4	2851.5	3031.7	3058.0
147.5°	2067.9	2122.9	2177.8	2191.6	2291.5	2424.7	2491.4	2585.9	2774.8	2916.5	2938.3
150°	2118.8	2168.5	2218.2	2230.6	2317.5	2433.4	2491.4	2571.2	2730.8	2850.4	2868.1
152.5°	2171.3	2209.0	2246.5	2255.9	2334.4	2439.0	2491.4	2559.5	2695.8	2797.9	2811.3
155°	2249.2	2277.1	2304.9	2311.9	2371.7	2451.4	2491.4	2545.6	2654.0	2735.3	2744.2
157.5°	2306.8	2333.9	2360.9	2367.7	2408.9	2463.8	2491.4	2533.5	2617.8	2681.1	2687.3
160°	2345.7	2366.8	2387.9	2393.2	2425.9	2469.6	2491.4	2527.5	2599.7	2653.9	2657.6
162.5°	2384.6	2400.5	2416.2	2420.2	2443.9	2475.5	2491.4	2521.9	2582.9	2628.6	2631.9
165°	2427.0	2441.3	2455.6	2459.2	2469.9	2484.2	2491.4	2513.2	2556.8	2589.6	2593.2
167.5°	2466.0	2472.8	2479.5	2481.2	2490.3	2502.3	2508.3	2522.6	2551.2	2572.6	2574.2
170°	2491.4	2498.2	2504.9	2506.7	2507.2	2507.9	2508.3	2522.6	2551.2	2572.6	2572.6
172.5°	2504.9	2506.4	2507.9	2508.3	2508.3	2508.3	2508.3	2519.6	2542.2	2559.2	2557.8
175°	2523.6	2523.6	2523.6	2523.6	2518.5	2511.7	2508.3	2515.4	2529.7	2540.5	2540.5
177.5°	2523.6	2523.6	2523.6	2523.6	2519.6	2514.4	2511.7	2517.3	2528.7	2537.1	2535.5
180°	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6



TEST NUMBER: P938455
 CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1115.8	<i>1115.8</i>
2.5°	1191.1	<i>1184.0</i>
5°	1532.0	<i>1539.1</i>
7.5°	2063.0	<i>2059.3</i>
10°	2565.2	<i>2597.5</i>
12.5°	2931.2	<i>2938.3</i>
15°	3153.6	<i>3168.0</i>
17.5°	3239.7	<i>3243.3</i>
20°	3243.3	<i>3236.1</i>
22.5°	3203.8	<i>3196.7</i>
25°	3157.2	<i>3153.6</i>
27.5°	3114.1	<i>3117.7</i>
30°	3096.2	<i>3107.0</i>
32.5°	3096.2	<i>3114.1</i>
35°	3103.3	<i>3121.3</i>
37.5°	3099.7	<i>3121.3</i>
40°	3085.4	<i>3110.5</i>
42.5°	3046.0	<i>3063.9</i>
45°	2984.9	<i>3006.5</i>
47.5°	2906.0	<i>2920.4</i>
50°	2805.5	<i>2819.9</i>
52.5°	2680.0	<i>2683.6</i>
55°	2529.3	<i>2543.7</i>
57.5°	2367.9	<i>2371.4</i>
60°	2188.5	<i>2199.3</i>
62.5°	1998.3	<i>1998.3</i>
65°	1797.5	<i>1804.6</i>
67.5°	1589.4	<i>1607.3</i>
70°	1377.7	<i>1381.3</i>
72.5°	1169.6	<i>1169.6</i>
75°	954.3	<i>957.9</i>
77.5°	749.8	<i>749.8</i>
80°	556.1	<i>559.7</i>
82.5°	383.9	<i>391.0</i>
85°	240.4	<i>240.4</i>
87.5°	111.2	<i>100.5</i>
90°	64.4	<i>64.4</i>
92.5°	257.8	<i>206.6</i>
95°	898.6	<i>743.5</i>
97.5°	2153.0	<i>1857.9</i>
100°	3102.1	<i>2750.5</i>
102.5°	4035.7	<i>3734.5</i>
105°	5225.9	<i>5064.1</i>
107.5°	6005.6	<i>6044.7</i>
110°	6302.9	<i>6471.5</i>



TEST NUMBER: P938455

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6329.4	6588.4
115°	6161.5	6520.6
117.5°	5805.7	6203.9
120°	5518.9	5905.8
122.5°	5239.7	5621.3
125°	4841.3	5192.8
127.5°	4483.0	4779.5
130°	4271.8	4545.8
132.5°	4080.2	4325.6
135°	3817.7	4029.2
137.5°	3607.2	3780.2
140°	3462.6	3624.4
142.5°	3342.9	3482.2
145°	3163.4	3268.8
147.5°	3025.7	3112.9
150°	2938.9	3009.7
152.5°	2864.7	2918.1
155°	2779.5	2814.9
157.5°	2712.1	2736.9
160°	2671.9	2686.2
162.5°	2645.5	2659.1
165°	2607.5	2621.8
167.5°	2580.2	2586.2
170°	2572.6	2572.6
172.5°	2552.6	2547.3
175°	2540.5	2540.5
177.5°	2529.6	2523.6
180°	2523.6	2523.6



TEST NUMBER: P938455
 CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.71	4.47	4.78	5.55	7.02	16.90	17.66	17.97	18.74	20.21
	3H	4.40	5.09	5.49	6.17	7.67	18.74	19.42	19.82	20.51	22.00
	4H	4.70	5.35	5.79	6.43	7.93	19.38	20.03	20.47	21.12	22.61
	6H	4.94	5.54	6.04	6.63	8.14	19.81	20.41	20.91	21.50	23.01
	8H	5.01	5.58	6.11	6.68	8.19	19.93	20.50	21.03	21.61	23.11
	12H	5.02	5.56	6.13	6.66	8.19	20.00	20.54	21.11	21.64	23.17
4H	2H	10.92	11.57	12.02	12.65	14.15	17.16	17.81	18.26	18.90	20.39
	3H	12.47	13.02	13.58	14.13	15.64	19.20	19.74	20.31	20.86	22.37
	4H	12.56	13.06	13.68	14.17	15.70	19.97	20.47	21.08	21.57	23.10
	6H	12.57	13.00	13.69	14.13	15.65	20.50	20.93	21.62	22.06	23.58
	8H	12.54	12.94	13.66	14.06	15.60	20.67	21.07	21.79	22.19	23.73
	12H	12.49	12.86	13.63	13.99	15.53	20.76	21.12	21.89	22.25	23.80
8H	4H	14.00	14.40	15.12	15.52	17.06	20.02	20.42	21.14	21.54	23.08
	6H	14.24	14.57	15.38	15.73	17.27	20.65	20.98	21.79	22.14	23.68
	8H	14.26	14.55	15.41	15.69	17.25	20.87	21.16	22.02	22.30	23.86
	12H	14.22	14.48	15.37	15.62	17.21	21.01	21.27	22.16	22.41	24.00
12H	4H	14.14	14.51	15.28	15.64	17.18	19.97	20.33	21.10	21.46	23.01
	6H	14.50	14.79	15.65	15.93	17.49	20.63	20.92	21.78	22.06	23.62
	8H	14.56	14.82	15.72	15.96	17.55	20.86	21.11	22.01	22.25	23.84