

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938456

Luminaire Tested: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938456  
REPORT IS A COMBINATION OF REPORTS P933623 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 25346.7 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 217.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938456  
CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P938456

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	42	42	42	35
1	94	90	86	82	85	81	78	75	65	63	60	50	49	47	36	35	35	36	35	35	28
2	85	78	72	66	77	70	65	61	56	53	49	43	41	39	32	30	29	32	30	29	23
3	77	68	61	55	69	61	55	50	49	45	41	38	35	32	28	26	24	28	26	24	19
4	71	60	52	46	63	54	47	42	43	38	34	34	30	27	24	22	20	24	22	20	16
5	64	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	22	19	17	14
6	59	47	39	33	53	43	36	30	34	29	25	27	23	20	19	17	15	19	17	15	12
7	54	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	18	15	13	10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	13	11	16	13	11	9
9	47	35	27	22	42	31	25	20	26	20	17	20	16	14	15	12	10	15	12	10	8
10	43	31	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3499	3499	3499
5°	3420	4045	4703
10°	3103	5898	7797
15°	2638	7707	9415
20°	2148	8934	9595
25°	1793	9351	9400
30°	1512	9413	9383
35°	1338	9259	9625
40°	1167	9058	9876
45°	1057	8912	9914
50°	971	8781	9750
55°	930	8588	9318
60°	954	8215	8636
65°	994	7645	7698
70°	1061	6672	6503
75°	1181	5445	5075
80°	1299	3781	3419
85°	1176	2009	1750

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 9914 cd/sqm



TEST NUMBER: P938456

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.3	0.6
10°-20°	648.5	2.6
20°-30°	1134.4	4.5
30°-40°	1460.3	5.8
40°-50°	1631.1	6.4
50°-60°	1562.2	6.2
60°-70°	1238.1	4.9
70°-80°	728.0	2.9
80°-90°	212.0	0.8
90°-100°	1247.1	4.9
100°-110°	3278.8	12.9
110°-120°	3399.8	13.4
120°-130°	2727.0	10.8
130°-140°	2139.7	8.4
140°-150°	1642.3	6.5
150°-160°	1182.8	4.7
160°-170°	723.7	2.9
170°-180°	244.5	1.0
0°-30°	1929.2	7.6
0°-40°	3389.5	13.4
0°-60°	6582.8	26.0
0°-90°	8760.9	34.6
90°-120°	7925.7	31.3
90°-150°	14434.9	56.9
90°-180°	16586.0	65.4
0°-180°	25346.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1131	1131	1131	1131	1131	
5°	1102	1182	1331	1506	1560	102
15°	826	1524	2568	3114	3212	230
25°	527	1728	3059	3194	3197	243
35°	356	1651	2881	3044	3164	223
45°	244	1317	2546	2917	3048	189
55°	175	837	2161	2510	2579	159
65°	138	444	1604	1804	1830	137
75°	102	273	880	968	971	107
85°	36	84	218	240	244	39
90°	17	48	130	65	65	17
95°	165	646	2148	1108	754	183
105°	591	895	3625	5503	5134	626
115°	1049	1274	2904	5792	6611	1036
125°	1460	1636	2641	4463	5265	1296
135°	1739	1915	2558	3602	4085	1346
145°	2018	2146	2526	3074	3314	1264
155°	2280	2344	2526	2773	2854	1048
165°	2461	2493	2526	2625	2658	694
175°	2558	2558	2543	2576	2576	243
180°	2558	2558	2558	2558	2558	



TEST NUMBER: P938456

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2
2.5°	1131.2	1131.2	1138.5	1142.2	1149.4	1153.1	1160.3	1167.6	1189.4	1193.1	1200.3
5°	1102.2	1116.7	1164.0	1182.2	1233.1	1302.2	1331.3	1378.6	1476.8	1505.8	1524.0
7.5°	1058.5	1091.2	1207.6	1236.7	1364.0	1545.9	1622.3	1724.1	1880.5	1956.9	2018.7
10°	989.4	1058.5	1265.8	1334.9	1542.3	1818.7	1960.6	2102.4	2338.8	2444.3	2484.3
12.5°	913.0	1025.7	1327.6	1422.2	1720.5	2124.2	2295.2	2451.6	2720.8	2862.7	2884.4
15°	825.7	978.4	1385.8	1524.0	1909.6	2378.8	2568.0	2760.8	3011.8	3113.6	3139.1
17.5°	749.3	942.1	1440.4	1585.9	2055.1	2608.0	2800.8	2960.9	3164.5	3233.6	3251.9
20°	654.7	883.9	1476.8	1665.9	2207.9	2775.3	2960.9	3084.5	3222.7	3266.4	3273.6
22.5°	585.6	822.1	1498.6	1695.0	2309.7	2877.2	3033.5	3131.8	3226.3	3240.9	3244.5
25°	527.4	753.0	1494.9	1727.7	2397.0	2939.0	3059.0	3131.8	3186.3	3193.6	3193.6
27.5°	472.9	676.5	1480.4	1735.0	2462.5	2953.5	3048.1	3099.1	3124.5	3139.1	3139.1
30°	425.5	603.8	1444.0	1720.5	2491.6	2939.0	3015.4	3040.9	3066.3	3088.1	3099.1
32.5°	389.2	534.6	1389.5	1691.4	2495.2	2902.7	2957.2	2971.8	3008.1	3059.0	3077.2
35°	356.4	465.5	1327.6	1651.4	2473.4	2844.4	2880.8	2895.3	2968.1	3044.5	3070.0
37.5°	323.8	414.7	1247.6	1582.3	2440.7	2775.3	2800.8	2826.2	2939.0	3030.0	3059.0
40°	291.0	371.0	1153.1	1505.8	2389.8	2691.7	2713.4	2753.5	2902.7	3008.1	3037.2
42.5°	265.5	334.7	1051.2	1425.8	2324.2	2597.1	2629.8	2688.0	2859.0	2971.8	3004.4
45°	243.7	298.3	942.1	1316.7	2240.6	2498.9	2546.1	2626.2	2808.1	2917.2	2946.3
47.5°	221.9	272.8	829.3	1204.0	2149.7	2400.7	2462.5	2553.4	2739.0	2844.4	2869.9
50°	203.7	247.3	716.5	1084.0	2051.5	2295.2	2367.9	2462.5	2651.7	2749.9	2782.6
52.5°	189.1	225.5	611.1	963.9	1938.7	2186.0	2269.7	2367.9	2546.1	2640.8	2662.6
55°	174.6	207.3	520.1	836.6	1822.4	2069.7	2160.6	2255.1	2429.8	2509.8	2524.3
57.5°	167.3	192.8	443.8	716.5	1698.7	1938.7	2040.6	2127.9	2291.6	2353.3	2367.9
60°	156.4	181.9	385.5	614.7	1564.0	1815.0	1902.4	1989.7	2127.9	2178.8	2189.7
62.5°	145.5	174.6	341.9	516.5	1425.8	1669.6	1756.8	1836.9	1953.3	1989.7	2004.2
65°	138.2	167.3	309.2	443.8	1284.0	1516.8	1604.0	1673.2	1767.8	1804.1	1811.4
67.5°	131.0	160.0	283.8	381.9	1142.2	1364.0	1429.5	1494.9	1567.7	1604.0	1607.7
70°	120.0	152.8	261.9	338.3	996.6	1189.4	1244.0	1313.1	1371.3	1389.5	1400.4
72.5°	112.8	141.9	247.3	305.5	847.5	1022.1	1073.1	1113.1	1164.0	1182.2	1182.2
75°	101.9	127.3	232.8	272.8	694.7	836.6	880.3	920.3	960.3	967.5	956.6
77.5°	90.9	112.8	200.1	229.1	542.0	662.0	698.4	720.2	753.0	760.2	763.9
80°	76.4	98.2	156.4	178.2	392.9	487.4	512.9	531.1	560.2	560.2	567.4
82.5°	58.2	76.4	112.8	127.3	265.5	334.7	356.4	367.4	385.5	385.5	385.5
85°	36.3	47.3	72.8	83.7	160.0	203.7	218.2	221.9	236.4	240.1	240.1
87.5°	18.2	25.4	47.3	50.9	83.7	105.4	105.4	112.8	112.8	109.1	105.4
90°	17.2	30.9	44.7	48.1	75.5	112.1	130.5	116.0	87.0	65.2	65.2
92.5°	68.6	185.4	302.2	331.4	465.9	645.2	734.9	644.0	462.4	326.2	313.3
95°	164.8	378.5	592.2	645.6	1146.5	1814.3	2148.1	1916.9	1454.5	1107.6	1068.3
97.5°	285.0	473.5	662.0	709.2	1544.3	2657.7	3214.4	3068.3	2776.0	2556.8	2482.0
100°	377.7	548.7	719.7	762.4	1689.1	2924.6	3542.4	3553.0	3574.4	3590.5	3501.4
102.5°	456.7	616.2	775.7	815.6	1755.5	3008.6	3635.2	3821.4	4193.8	4473.1	4396.8
105°	590.7	725.8	860.9	894.7	1804.7	3018.1	3624.8	4042.3	4877.2	5503.3	5462.3
107.5°	728.1	854.0	979.9	1011.4	1813.8	2883.8	3418.8	4001.1	5165.6	6039.1	6049.0
110°	820.8	934.5	1048.2	1076.6	1800.2	2764.7	3247.1	3898.1	5200.0	6176.5	6219.2



TEST NUMBER: P938456

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	911.8	1020.2	1128.6	1155.7	1800.7	2660.8	3090.8	3757.0	5089.5	6088.9	6154.5
115°	1049.2	1149.1	1249.2	1274.1	1817.3	2541.6	2903.7	3545.5	4829.1	5791.8	5882.9
117.5°	1184.8	1275.6	1366.4	1389.1	1851.0	2466.9	2774.8	3354.1	4512.6	5381.5	5482.4
120°	1263.8	1349.3	1434.7	1456.1	1878.5	2441.7	2723.4	3252.6	4311.1	5105.0	5203.1
122.5°	1341.0	1427.3	1513.6	1535.1	1918.1	2428.6	2683.9	3160.4	4113.7	4828.5	4925.3
125°	1459.6	1538.1	1616.8	1636.4	1971.3	2417.8	2640.9	3045.8	3855.5	4462.8	4551.9
127.5°	1555.7	1635.1	1714.4	1734.3	2024.4	2411.4	2604.9	2952.5	3647.7	4169.2	4244.3
130°	1607.3	1692.7	1778.1	1799.5	2063.3	2415.2	2591.1	2900.6	3519.5	3983.7	4053.2
132.5°	1660.5	1745.9	1831.4	1852.7	2094.8	2417.7	2579.1	2856.1	3410.2	3825.8	3888.0
135°	1739.4	1817.2	1895.1	1914.6	2129.2	2415.5	2558.5	2790.5	3254.5	3602.5	3656.1
137.5°	1820.2	1897.2	1974.3	1993.6	2180.7	2430.2	2555.0	2751.2	3143.5	3437.7	3481.6
140°	1887.1	1958.1	2029.1	2046.8	2212.2	2432.7	2543.0	2712.4	3051.3	3305.4	3346.5
142.5°	1938.6	2004.2	2069.9	2086.3	2238.5	2441.5	2543.0	2691.9	2989.5	3212.8	3248.1
145°	2017.6	2074.9	2132.1	2146.4	2272.9	2441.5	2525.9	2647.6	2891.0	3073.6	3100.3
147.5°	2096.6	2152.3	2208.0	2221.9	2323.2	2458.3	2525.9	2621.7	2813.2	2956.9	2979.0
150°	2148.1	2198.5	2248.9	2261.5	2349.6	2467.1	2525.9	2606.8	2768.6	2889.9	2907.8
152.5°	2201.4	2239.5	2277.6	2287.2	2366.7	2472.8	2525.9	2595.0	2733.1	2836.7	2850.3
155°	2280.4	2308.6	2336.8	2343.9	2404.5	2485.4	2525.9	2580.8	2690.8	2773.2	2782.2
157.5°	2338.7	2366.2	2393.6	2400.5	2442.3	2498.0	2525.9	2568.6	2654.1	2718.2	2724.5
160°	2378.2	2399.6	2421.0	2426.3	2459.5	2503.7	2525.9	2562.5	2635.7	2690.7	2694.4
162.5°	2417.7	2433.7	2449.7	2453.7	2477.8	2509.8	2525.9	2556.8	2618.6	2665.0	2668.4
165°	2460.6	2475.1	2489.6	2493.3	2504.1	2518.6	2525.9	2548.0	2592.2	2625.4	2629.1
167.5°	2500.2	2507.1	2513.8	2515.6	2524.8	2537.0	2543.0	2557.5	2586.5	2608.3	2609.8
170°	2525.9	2532.7	2539.6	2541.4	2541.9	2542.7	2543.0	2557.5	2586.5	2608.3	2608.3
172.5°	2539.6	2541.1	2542.7	2543.0	2543.0	2543.0	2543.0	2554.5	2577.4	2594.6	2593.2
175°	2558.5	2558.5	2558.5	2558.5	2553.4	2546.5	2543.0	2550.3	2564.8	2575.7	2575.7
177.5°	2558.5	2558.5	2558.5	2558.5	2554.5	2549.2	2546.5	2552.2	2563.7	2572.2	2570.6
180°	2558.5	2558.5	2558.5	2558.5	2558.5	2558.5	2558.5	2558.5	2558.5	2558.5	2558.5



TEST NUMBER: P938456

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	1131.2	1131.2
2.5°	1207.6	1200.3
5°	1553.2	1560.4
7.5°	2091.5	2087.8
10°	2600.7	2633.4
12.5°	2971.8	2979.0
15°	3197.2	3211.8
17.5°	3284.5	3288.2
20°	3288.2	3280.9
22.5°	3248.2	3240.9
25°	3200.9	3197.2
27.5°	3157.2	3160.9
30°	3139.1	3150.0
32.5°	3139.1	3157.2
35°	3146.3	3164.5
37.5°	3142.6	3164.5
40°	3128.1	3153.6
42.5°	3088.1	3106.3
45°	3026.3	3048.1
47.5°	2946.3	2960.9
50°	2844.4	2859.0
52.5°	2717.1	2720.8
55°	2564.3	2578.9
57.5°	2400.7	2404.3
60°	2218.8	2229.7
62.5°	2026.0	2026.0
65°	1822.4	1829.6
67.5°	1611.4	1629.6
70°	1396.7	1400.4
72.5°	1185.8	1185.8
75°	967.5	971.2
77.5°	760.2	760.2
80°	563.8	567.4
82.5°	389.2	396.4
85°	243.7	243.7
87.5°	112.8	101.9
90°	65.2	65.2
92.5°	261.4	209.5
95°	911.0	753.8
97.5°	2182.8	1883.7
100°	3145.0	2788.6
102.5°	4091.5	3786.2
105°	5298.3	5134.2
107.5°	6088.7	6128.4
110°	6390.2	6561.2





TEST NUMBER: P938456

CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	6417.1	6679.6
115°	6246.8	6610.9
117.5°	5886.1	6289.8
120°	5595.3	5987.6
122.5°	5312.3	5699.2
125°	4908.3	5264.7
127.5°	4545.1	4845.7
130°	4331.0	4608.8
132.5°	4136.7	4385.5
135°	3870.6	4085.0
137.5°	3657.1	3832.6
140°	3510.6	3674.6
142.5°	3389.2	3530.4
145°	3207.3	3314.1
147.5°	3067.6	3156.0
150°	2979.6	3051.3
152.5°	2904.4	2958.6
155°	2818.0	2853.8
157.5°	2749.7	2774.8
160°	2708.9	2723.4
162.5°	2682.1	2695.9
165°	2643.6	2658.1
167.5°	2615.9	2622.0
170°	2608.3	2608.3
172.5°	2587.9	2582.6
175°	2575.7	2575.7
177.5°	2564.6	2558.5
180°	2558.5	2558.5



TEST NUMBER: P938456  
 CATALOG NUMBER: SQ4-FB-150U-100D-93050-1D-UNV-STD-W-12-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.75	4.52	4.83	5.59	7.07	16.95	17.71	18.02	18.79	20.26
	3H	4.45	5.14	5.53	6.22	7.71	18.78	19.47	19.86	20.55	22.04
	4H	4.74	5.39	5.84	6.48	7.98	19.43	20.08	20.52	21.16	22.66
	6H	4.99	5.59	6.09	6.68	8.19	19.86	20.45	20.96	21.55	23.06
	8H	5.05	5.62	6.16	6.73	8.24	19.98	20.55	21.08	21.65	23.16
	12H	5.07	5.61	6.18	6.71	8.24	20.04	20.58	21.15	21.69	23.21
4H	2H	10.96	11.61	12.06	12.70	14.20	17.21	17.86	18.31	18.94	20.44
	3H	12.52	13.07	13.63	14.18	15.69	19.25	19.79	20.36	20.91	22.42
	4H	12.61	13.11	13.72	14.22	15.75	20.01	20.51	21.13	21.62	23.15
	6H	12.62	13.05	13.74	14.17	15.70	20.55	20.98	21.67	22.11	23.63
	8H	12.59	12.99	13.71	14.11	15.65	20.71	21.11	21.83	22.23	23.77
	12H	12.54	12.91	13.68	14.04	15.58	20.81	21.17	21.94	22.30	23.85
8H	4H	14.05	14.45	15.17	15.57	17.11	20.07	20.47	21.18	21.59	23.13
	6H	14.29	14.62	15.43	15.78	17.32	20.69	21.03	21.84	22.19	23.72
	8H	14.31	14.60	15.45	15.74	17.29	20.92	21.21	22.06	22.35	23.90
	12H	14.27	14.52	15.42	15.66	17.25	21.06	21.31	22.21	22.45	24.04
12H	4H	14.19	14.55	15.33	15.69	17.23	20.01	20.38	21.15	21.51	23.05
	6H	14.55	14.84	15.70	15.98	17.54	20.68	20.97	21.82	22.11	23.67
	8H	14.61	14.87	15.76	16.01	17.60	20.90	21.16	22.06	22.30	23.89