

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938555

Luminaire Tested: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938555
REPORT IS A COMBINATION OF REPORTS P933624 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 27424.6 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938555
CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P938555

CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39	33
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32	27
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23	19
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19	16
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17	14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15	12
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4421	4421	4421
5°	4320	5110	5942
10°	3920	7451	9850
15°	3333	9737	11894
20°	2714	11286	12122
25°	2265	11814	11876
30°	1911	11891	11853
35°	1690	11697	12160
40°	1474	11443	12477
45°	1335	11259	12525
50°	1226	11094	12318
55°	1176	10850	11772
60°	1205	10378	10910
65°	1255	9659	9725
70°	1340	8429	8216
75°	1491	6879	6411
80°	1641	4776	4320
85°	1491	2539	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12525 cd/sqm



TEST NUMBER: P938555

CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	0.7
10°-20°	819.3	3.0
20°-30°	1433.1	5.2
30°-40°	1844.8	6.7
40°-50°	2060.6	7.5
50°-60°	1973.6	7.2
60°-70°	1564.1	5.7
70°-80°	919.7	3.4
80°-90°	265.1	1.0
90°-100°	1230.1	4.5
100°-110°	3234.0	11.8
110°-120°	3353.3	12.2
120°-130°	2689.8	9.8
130°-140°	2110.5	7.7
140°-150°	1619.9	5.9
150°-160°	1166.6	4.3
160°-170°	713.8	2.6
170°-180°	241.2	0.9
0°-30°	2437.3	8.9
0°-40°	4282.1	15.6
0°-60°	8316.3	30.3
0°-90°	11065.3	40.3
90°-120°	7817.5	28.5
90°-150°	14237.7	51.9
90°-180°	16359.0	59.7
0°-180°	27424.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1392	1493	1682	1902	1971	129
15°	1043	1925	3244	3934	4058	290
25°	666	2183	3865	4035	4039	307
35°	450	2086	3639	3846	3998	281
45°	308	1664	3217	3685	3851	238
55°	221	1057	2730	3171	3258	201
65°	175	561	2026	2279	2311	173
75°	129	345	1112	1222	1227	135
85°	46	106	276	303	308	49
90°	17	47	129	64	64	17
95°	163	637	2119	1092	744	181
105°	583	882	3575	5428	5064	618
115°	1035	1257	2864	5713	6521	1022
125°	1440	1614	2605	4402	5193	1278
135°	1716	1888	2524	3553	4029	1327
145°	1990	2117	2491	3032	3269	1247
155°	2249	2312	2491	2735	2815	1033
165°	2427	2459	2491	2590	2622	685
175°	2524	2524	2508	2540	2540	240
180°	2524	2524	2524	2524	2524	



TEST NUMBER: P938555
 CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2	1429.2
2.5°	1429.2	1429.2	1438.3	1442.9	1452.1	1456.7	1465.9	1475.1	1502.7	1507.3	1516.4
5°	1392.3	1410.7	1470.4	1493.4	1557.8	1645.1	1681.9	1741.6	1865.6	1902.5	1925.4
7.5°	1337.2	1378.6	1525.6	1562.4	1723.2	1953.0	2049.5	2178.2	2375.8	2472.3	2550.4
10°	1249.9	1337.2	1599.1	1686.4	1948.4	2297.6	2476.8	2656.0	2954.7	3088.0	3138.6
12.5°	1153.4	1295.8	1677.3	1796.7	2173.6	2683.6	2899.6	3097.2	3437.3	3616.5	3644.0
15°	1043.1	1236.1	1750.8	1925.4	2412.5	3005.3	3244.2	3487.8	3804.8	3933.6	3965.7
17.5°	946.6	1190.2	1819.7	2003.5	2596.3	3294.8	3538.4	3740.5	3997.8	4085.2	4108.2
20°	827.1	1116.6	1865.6	2104.6	2789.3	3506.1	3740.5	3896.7	4071.4	4126.5	4135.7
22.5°	739.8	1038.5	1893.2	2141.3	2918.0	3634.9	3832.5	3956.5	4075.9	4094.3	4098.9
25°	666.3	951.2	1888.6	2182.7	3028.2	3713.0	3864.6	3956.5	4025.4	4034.6	4034.6
27.5°	597.4	854.7	1870.2	2191.9	3110.9	3731.3	3850.8	3915.1	3947.3	3965.7	3965.7
30°	537.7	762.8	1824.3	2173.6	3147.7	3713.0	3809.5	3841.6	3873.8	3901.3	3915.1
32.5°	491.7	675.5	1755.4	2136.8	3152.3	3667.0	3736.0	3754.3	3800.2	3864.6	3887.6
35°	450.3	588.2	1677.3	2086.2	3124.8	3593.5	3639.4	3657.8	3749.7	3846.2	3878.3
37.5°	409.0	523.8	1576.2	1999.0	3083.4	3506.1	3538.4	3570.5	3713.0	3827.8	3864.6
40°	367.6	468.7	1456.7	1902.5	3019.1	3400.5	3428.0	3478.6	3667.0	3800.2	3837.0
42.5°	335.5	422.8	1328.1	1801.4	2936.3	3281.0	3322.4	3395.9	3611.9	3754.3	3795.7
45°	307.8	376.8	1190.2	1663.5	2830.6	3156.9	3216.7	3317.8	3547.5	3685.4	3722.1
47.5°	280.3	344.7	1047.7	1521.0	2715.8	3032.8	3110.9	3225.8	3460.2	3593.5	3625.6
50°	257.3	312.5	905.3	1369.4	2591.7	2899.6	2991.5	3110.9	3349.9	3474.0	3515.4
52.5°	239.0	284.9	772.0	1217.7	2449.3	2761.7	2867.5	2991.5	3216.7	3336.2	3363.7
55°	220.6	262.0	657.1	1056.9	2302.2	2614.6	2729.6	2849.1	3069.6	3170.7	3189.1
57.5°	211.4	243.6	560.7	905.3	2146.0	2449.3	2577.9	2688.2	2895.0	2973.1	2991.5
60°	197.6	229.7	487.1	776.6	1976.0	2293.0	2403.3	2513.6	2688.2	2752.5	2766.4
62.5°	183.8	220.6	431.9	652.5	1801.4	2109.2	2219.5	2320.6	2467.6	2513.6	2532.0
65°	174.6	211.4	390.6	560.7	1622.1	1916.2	2026.5	2113.8	2233.3	2279.2	2288.4
67.5°	165.5	202.2	358.4	482.5	1442.9	1723.2	1805.9	1888.6	1980.6	2026.5	2031.1
70°	151.6	193.0	330.8	427.3	1259.1	1502.7	1571.5	1658.9	1732.4	1755.4	1769.1
72.5°	142.5	179.2	312.5	386.0	1070.7	1291.3	1355.6	1406.2	1470.4	1493.4	1493.4
75°	128.6	160.8	294.1	344.7	877.6	1056.9	1112.1	1162.6	1213.1	1222.3	1208.6
77.5°	114.9	142.5	252.7	289.5	684.7	836.4	882.3	909.9	951.2	960.4	965.0
80°	96.5	124.1	197.6	225.2	496.3	615.8	647.9	670.9	707.7	707.7	716.9
82.5°	73.5	96.5	142.5	160.8	335.5	422.8	450.3	464.1	487.1	487.1	487.1
85°	46.0	59.7	91.9	105.7	202.2	257.3	275.7	280.3	298.7	303.3	303.3
87.5°	23.0	32.1	59.7	64.4	105.7	133.2	133.2	142.5	142.5	137.9	133.2
90°	16.9	30.5	44.1	47.4	74.5	110.6	128.7	114.4	85.8	64.4	64.4
92.5°	67.7	182.8	298.1	326.9	459.6	636.4	724.9	635.2	456.1	321.8	309.0
95°	162.6	373.3	584.1	636.8	1130.8	1789.5	2118.8	1890.7	1434.6	1092.4	1053.7
97.5°	281.1	467.1	653.0	699.5	1523.2	2621.4	3170.5	3026.4	2738.1	2521.9	2448.1
100°	372.6	541.2	709.8	752.0	1666.0	2884.7	3494.0	3504.5	3525.6	3541.4	3453.6
102.5°	450.5	607.8	765.1	804.5	1731.5	2967.5	3585.5	3769.2	4136.5	4412.0	4336.7
105°	582.7	715.9	849.1	882.4	1780.1	2976.9	3575.3	3987.1	4810.6	5428.2	5387.7
107.5°	718.2	842.3	966.5	997.6	1789.1	2844.4	3372.1	3946.4	5095.1	5956.6	5966.4
110°	809.6	921.7	1033.9	1061.9	1775.6	2727.0	3202.7	3844.9	5129.0	6092.1	6134.3



TEST NUMBER: P938555

CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	899.4	1006.3	1113.2	1139.9	1776.1	2624.4	3048.6	3705.7	5020.0	6005.7	6070.5
115°	1034.9	1133.4	1232.1	1256.7	1792.5	2506.8	2864.0	3497.1	4763.1	5712.7	5802.5
117.5°	1168.7	1258.2	1347.8	1370.1	1825.7	2433.2	2736.9	3308.3	4450.9	5308.0	5407.5
120°	1246.5	1330.9	1415.1	1436.2	1852.9	2408.4	2686.2	3208.2	4252.2	5035.2	5132.0
122.5°	1322.7	1407.8	1492.9	1514.2	1891.9	2395.4	2647.2	3117.3	4057.5	4762.6	4858.0
125°	1439.7	1517.1	1594.7	1614.1	1944.4	2384.7	2604.9	3004.2	3802.9	4401.8	4489.7
127.5°	1534.4	1612.7	1691.0	1710.6	1996.8	2378.5	2569.3	2912.2	3597.9	4112.2	4186.4
130°	1585.3	1669.6	1753.8	1774.9	2035.2	2382.2	2555.7	2860.9	3471.5	3929.3	3997.8
132.5°	1637.8	1722.1	1806.3	1827.4	2066.2	2384.6	2543.9	2817.1	3363.7	3773.5	3834.9
135°	1715.6	1792.4	1869.2	1888.4	2100.2	2382.5	2523.6	2752.4	3210.1	3553.3	3606.2
137.5°	1795.3	1871.3	1947.4	1966.4	2150.9	2397.0	2520.1	2713.6	3100.5	3390.7	3434.0
140°	1861.4	1931.3	2001.4	2018.9	2182.0	2399.5	2508.3	2675.4	3009.7	3260.3	3300.8
142.5°	1912.2	1976.9	2041.6	2057.8	2208.0	2408.2	2508.3	2655.1	2948.7	3168.9	3203.7
145°	1990.1	2046.6	2103.0	2117.1	2241.8	2408.2	2491.4	2611.4	2851.5	3031.7	3058.0
147.5°	2067.9	2122.9	2177.8	2191.6	2291.5	2424.7	2491.4	2585.9	2774.8	2916.5	2938.3
150°	2118.8	2168.5	2218.2	2230.6	2317.5	2433.4	2491.4	2571.2	2730.8	2850.4	2868.1
152.5°	2171.3	2209.0	2246.5	2255.9	2334.4	2439.0	2491.4	2559.5	2695.8	2797.9	2811.3
155°	2249.2	2277.1	2304.9	2311.9	2371.7	2451.4	2491.4	2545.6	2654.0	2735.3	2744.2
157.5°	2306.8	2333.9	2360.9	2367.7	2408.9	2463.8	2491.4	2533.5	2617.8	2681.1	2687.3
160°	2345.7	2366.8	2387.9	2393.2	2425.9	2469.6	2491.4	2527.5	2599.7	2653.9	2657.6
162.5°	2384.6	2400.5	2416.2	2420.2	2443.9	2475.5	2491.4	2521.9	2582.9	2628.6	2631.9
165°	2427.0	2441.3	2455.6	2459.2	2469.9	2484.2	2491.4	2513.2	2556.8	2589.6	2593.2
167.5°	2466.0	2472.8	2479.5	2481.2	2490.3	2502.3	2508.3	2522.6	2551.2	2572.6	2574.2
170°	2491.4	2498.2	2504.9	2506.7	2507.2	2507.9	2508.3	2522.6	2551.2	2572.6	2572.6
172.5°	2504.9	2506.4	2507.9	2508.3	2508.3	2508.3	2508.3	2519.6	2542.2	2559.2	2557.8
175°	2523.6	2523.6	2523.6	2523.6	2518.5	2511.7	2508.3	2515.4	2529.7	2540.5	2540.5
177.5°	2523.6	2523.6	2523.6	2523.6	2519.6	2514.4	2511.7	2517.3	2528.7	2537.1	2535.5
180°	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6	2523.6



TEST NUMBER: P938555

CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1429.2	1429.2
2.5°	1525.6	1516.4
5°	1962.2	1971.4
7.5°	2642.3	2637.6
10°	3285.6	3326.9
12.5°	3754.3	3763.5
15°	4039.2	4057.6
17.5°	4149.5	4154.1
20°	4154.1	4144.9
22.5°	4103.5	4094.3
25°	4043.8	4039.2
27.5°	3988.7	3993.3
30°	3965.7	3979.4
32.5°	3965.7	3988.7
35°	3974.8	3997.8
37.5°	3970.3	3997.8
40°	3951.9	3984.1
42.5°	3901.3	3924.3
45°	3823.2	3850.8
47.5°	3722.1	3740.5
50°	3593.5	3611.9
52.5°	3432.6	3437.3
55°	3239.7	3258.0
57.5°	3032.8	3037.4
60°	2803.1	2816.9
62.5°	2559.5	2559.5
65°	2302.2	2311.4
67.5°	2035.7	2058.7
70°	1764.6	1769.1
72.5°	1498.0	1498.0
75°	1222.3	1226.9
77.5°	960.4	960.4
80°	712.3	716.9
82.5°	491.7	500.9
85°	307.8	307.8
87.5°	142.5	128.6
90°	64.4	64.4
92.5°	257.8	206.6
95°	898.6	743.5
97.5°	2153.0	1857.9
100°	3102.1	2750.5
102.5°	4035.7	3734.5
105°	5225.9	5064.1
107.5°	6005.6	6044.7
110°	6302.9	6471.5



TEST NUMBER: P938555

CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6329.4	6588.4
115°	6161.5	6520.6
117.5°	5805.7	6203.9
120°	5518.9	5905.8
122.5°	5239.7	5621.3
125°	4841.3	5192.8
127.5°	4483.0	4779.5
130°	4271.8	4545.8
132.5°	4080.2	4325.6
135°	3817.7	4029.2
137.5°	3607.2	3780.2
140°	3462.6	3624.4
142.5°	3342.9	3482.2
145°	3163.4	3268.8
147.5°	3025.7	3112.9
150°	2938.9	3009.7
152.5°	2864.7	2918.1
155°	2779.5	2814.9
157.5°	2712.1	2736.9
160°	2671.9	2686.2
162.5°	2645.5	2659.1
165°	2607.5	2621.8
167.5°	2580.2	2586.2
170°	2572.6	2572.6
172.5°	2552.6	2547.3
175°	2540.5	2540.5
177.5°	2529.6	2523.6
180°	2523.6	2523.6



TEST NUMBER: P938555
 CATALOG NUMBER: SQ4-FB-150U-125D-93050-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.22	6.03	6.25	7.07	8.47	18.41	19.22	19.44	20.26	21.66
	3H	5.92	6.65	6.96	7.70	9.12	20.25	20.98	21.29	22.03	23.45
	4H	6.22	6.91	7.27	7.96	9.39	20.90	21.59	21.95	22.64	24.07
	6H	6.47	7.10	7.53	8.16	9.60	21.33	21.97	22.39	23.03	24.46
	8H	6.53	7.14	7.60	8.21	9.65	21.45	22.06	22.52	23.13	24.57
	12H	6.55	7.13	7.62	8.19	9.65	21.52	22.10	22.59	23.17	24.62
4H	2H	12.44	13.13	13.50	14.18	15.61	18.68	19.37	19.74	20.42	21.85
	3H	14.00	14.58	15.07	15.66	17.10	20.73	21.30	21.79	22.38	23.82
	4H	14.09	14.62	15.17	15.69	17.15	21.50	22.03	22.57	23.10	24.56
	6H	14.10	14.56	15.18	15.65	17.11	22.04	22.49	23.12	23.59	25.04
	8H	14.08	14.50	15.16	15.59	17.06	22.20	22.63	23.28	23.71	25.18
	12H	14.03	14.42	15.13	15.52	16.99	22.29	22.68	23.39	23.78	25.26
8H	4H	15.54	15.96	16.62	17.05	18.52	21.55	21.98	22.63	23.06	24.53
	6H	15.78	16.13	16.88	17.26	18.73	22.18	22.54	23.29	23.66	25.13
	8H	15.79	16.10	16.91	17.21	18.70	22.40	22.71	23.52	23.82	25.31
	12H	15.76	16.03	16.88	17.14	18.66	22.55	22.82	23.67	23.93	25.45
12H	4H	15.68	16.07	16.78	17.16	18.64	21.50	21.89	22.60	22.99	24.46
	6H	16.04	16.35	17.15	17.46	18.94	22.16	22.48	23.28	23.58	25.07
	8H	16.10	16.38	17.22	17.48	19.01	22.40	22.67	23.51	23.77	25.30