

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521751

Luminaire Tested: **SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521751
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5905.3 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521751

CATALOG NUMBER: SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521751

CATALOG NUMBER: SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	69				
1	104	100	96	93	98	95	92	89	85	83	81	76	74	73	68	67	66	62				
2	96	89	84	79	91	85	80	76	76	73	70	69	66	64	62	60	58	54				
3	89	80	73	68	84	76	70	65	69	64	61	62	59	56	56	54	51	48				
4	82	72	65	59	78	69	62	57	63	57	53	57	53	49	52	48	46	43				
5	76	65	58	52	72	62	56	51	57	52	47	52	48	44	47	44	41	38				
6	71	59	52	46	67	57	50	45	52	47	42	48	43	40	44	40	37	35				
7	66	54	47	42	63	52	45	41	48	42	38	44	39	36	40	37	34	32				
8	62	50	43	38	59	48	41	37	44	39	35	41	36	33	38	34	31	29				
9	58	46	39	34	55	44	38	33	41	36	32	38	33	30	35	31	28	26				
10	54	43	36	31	52	41	35	31	38	33	29	36	31	28	33	29	26	24				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25986	25986	25986
5°	25662	25570	25718
10°	24244	24464	25032
15°	22381	22900	23927
20°	20324	21089	22484
25°	18229	19224	20947
30°	16300	17366	19354
35°	14253	15284	17469
40°	11997	12950	15122
45°	9901	10755	12626
50°	8266	9011	10520
55°	7018	7732	8688
60°	5997	6704	6933
65°	4774	5639	4478
70°	4235	4400	2733
75°	3921	3568	1675
80°	3613	3284	1445
85°	3271	3006	1175



TEST NUMBER: P521751

CATALOG NUMBER: SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.3	4.4
10°-20°	671.9	11.4
20°-30°	870.4	14.7
30°-40°	852.3	14.4
40°-50°	652.4	11.0
50°-60°	434.7	7.4
60°-70°	237.2	4.0
70°-80°	98.9	1.7
80°-90°	28.0	0.5
90°-100°	143.4	2.4
100°-110°	346.6	5.9
110°-120°	369.6	6.3
120°-130°	299.4	5.1
130°-140°	231.8	3.9
140°-150°	176.8	3.0
150°-160°	128.0	2.2
160°-170°	78.8	1.3
170°-180°	26.7	0.5
0°-30°	1800.7	30.5
0°-40°	2653.0	44.9
0°-60°	3740.1	63.3
0°-90°	4104.1	69.5
90°-120°	859.6	14.6
90°-150°	1567.6	26.5
90°-180°	1801.0	30.5
0°-180°	5905.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2816	2816	2816	2816	2816	
5°	2771	2743	2761	2767	2777	258
15°	2343	2335	2398	2463	2505	654
25°	1791	1796	1888	1971	2058	824
35°	1266	1272	1357	1448	1551	787
45°	759	773	824	887	968	592
55°	436	454	481	499	540	396
65°	219	237	258	226	205	227
75°	110	110	100	69	47	117
85°	31	31	28	18	11	34
90°	0	0	0	0	0	2
95°	14	72	246	160	112	16
105°	55	96	416	539	532	58
115°	101	130	335	634	708	100
125°	144	166	290	505	593	129
135°	177	198	279	398	458	137
145°	210	225	273	338	365	131
155°	240	251	277	300	310	111
165°	266	270	280	285	289	75
175°	281	280	281	279	278	27
180°	278	278	278	278	278	

TEST NUMBER: P521751

CATALOG NUMBER: SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2816.5	2816.5	2816.5	2816.5	2816.5
2.5°	2823.4	2798.3	2804.6	2804.4	2796.7
5°	2770.8	2743.0	2760.9	2767.3	2776.9
7.5°	2667.9	2646.9	2679.5	2703.7	2723.3
10°	2587.8	2569.7	2611.3	2646.5	2671.9
12.5°	2494.9	2479.7	2531.2	2578.5	2611.6
15°	2343.2	2334.7	2397.5	2462.8	2505.0
17.5°	2180.8	2176.7	2248.7	2324.9	2379.0
20°	2070.0	2068.8	2147.9	2227.2	2290.0
22.5°	1958.3	1961.0	2044.1	2126.5	2198.1
25°	1790.7	1795.6	1888.4	1970.7	2057.7
27.5°	1635.8	1637.9	1733.9	1820.8	1913.6
30°	1530.0	1536.0	1630.1	1720.0	1816.7
32.5°	1424.2	1431.2	1523.3	1616.2	1714.9
35°	1265.5	1271.5	1357.0	1448.3	1551.0
37.5°	1101.9	1110.1	1185.9	1272.2	1373.3
40°	996.1	1008.2	1075.2	1156.5	1255.6
42.5°	894.3	909.2	971.4	1048.5	1138.0
45°	758.8	773.3	824.3	886.7	967.7
47.5°	642.1	658.8	698.0	751.7	820.8
50°	575.9	591.6	627.8	667.6	732.9
52.5°	517.6	533.3	565.5	596.2	651.8
55°	436.3	454.4	480.7	499.0	540.1
57.5°	369.5	386.9	407.8	416.1	440.9
60°	325.0	344.4	363.3	362.4	375.7
62.5°	284.5	300.9	319.8	306.8	307.5
65°	218.7	236.9	258.3	225.7	205.1
67.5°	176.7	180.6	202.7	157.4	133.0
70°	157.0	157.0	163.1	121.9	101.3
72.5°	138.2	138.2	132.5	99.1	77.6
75°	110.0	110.0	100.1	68.7	47.0
77.5°	84.8	83.8	76.6	51.3	34.1
80°	68.0	68.0	61.8	40.5	27.2
82.5°	53.1	53.1	48.0	31.6	20.3
85°	30.9	30.9	28.4	18.4	11.1
87.5°	10.9	10.9	9.9	5.9	4.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	38.8	91.4	44.5	30.2
95°	14.1	71.7	245.7	159.8	111.9
97.5°	25.1	79.5	323.6	311.7	267.6
100°	33.6	84.3	366.5	386.8	350.6
102.5°	41.6	88.6	394.7	449.4	427.9
105°	55.4	95.7	416.5	538.9	532.0
107.5°	68.9	104.1	403.7	610.7	627.0
110°	78.4	111.2	383.0	641.7	672.2

TEST NUMBER: P521751

CATALOG NUMBER: SQ4-WB-025U-125D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	87.8	118.3	364.6	649.3	701.5
115°	101.3	129.6	334.6	634.4	707.6
117.5°	114.8	141.4	317.1	600.3	686.0
120°	123.7	148.5	305.8	573.5	663.4
122.5°	133.2	156.1	298.7	546.2	634.7
125°	144.3	166.2	290.5	504.6	592.7
127.5°	155.4	176.0	284.7	469.3	546.7
130°	162.0	182.2	282.8	444.8	520.8
132.5°	168.1	189.2	280.0	427.1	491.6
135°	177.3	198.1	278.7	397.9	457.8
137.5°	186.1	206.9	274.6	378.1	423.3
140°	192.7	211.7	274.6	363.9	405.3
142.5°	199.3	218.3	272.2	351.5	386.5
145°	209.7	225.3	273.4	338.2	364.7
147.5°	219.5	234.6	272.7	322.9	344.8
150°	225.7	238.9	274.6	316.2	333.5
152.5°	232.3	245.0	274.1	309.1	324.5
155°	240.4	250.8	276.9	299.5	310.5
157.5°	250.2	259.0	276.3	295.9	302.4
160°	253.9	261.4	278.7	291.2	295.8
162.5°	260.1	266.6	277.7	289.7	292.5
165°	265.7	269.7	280.4	284.7	288.7
167.5°	272.7	275.3	279.7	284.3	284.5
170°	274.6	276.3	281.6	281.1	284.0
172.5°	277.9	279.1	280.2	281.5	279.7
175°	281.0	279.9	281.0	278.7	278.1
177.5°	280.4	280.4	279.5	278.5	276.2
180°	278.1	278.1	278.1	278.1	278.1

(END OF REPORT)