

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P522065

Luminaire Tested: **SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/5/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P522065  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,  
Test Lab: INNOVATION CENTER  
Issue Date: 5/5/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10428.9 lumens  
Efficiency: N/A  
Efficacy: 97.8 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 106.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P522065  
CATALOG NUMBER: SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P522065

CATALOG NUMBER: SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				
1	97	93	89	86	88	85	82	79	70	68	66	56	55	53	43	43	42	36				
2	89	82	76	72	81	75	70	66	62	59	56	50	48	46	39	38	37	32				
3	82	73	66	61	74	67	61	57	56	52	48	45	43	40	36	34	32	28				
4	75	65	58	52	68	60	54	49	50	46	42	41	38	35	33	31	29	25				
5	69	59	51	46	63	54	48	43	45	41	37	37	34	31	30	28	26	22				
6	64	53	45	40	59	49	42	38	41	36	33	34	31	28	28	25	23	20				
7	60	48	41	35	54	45	38	33	38	33	29	31	28	25	25	23	21	18				
8	55	44	37	32	51	41	34	30	35	30	26	29	25	23	24	21	19	17				
9	52	40	33	29	47	37	31	27	32	27	24	27	23	21	22	19	18	15				
10	48	37	30	26	44	35	28	24	30	25	22	25	21	19	21	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	26765	26765	26765
5°	26431	26337	26490
10°	24972	25199	25782
15°	23052	23587	24645
20°	20934	21721	23158
25°	18776	19800	21575
30°	16789	17887	19935
35°	14681	15742	17993
40°	12357	13337	15576
45°	10198	11078	13005
50°	8514	9281	10834
55°	7227	7965	8948
60°	6178	6905	7141
65°	4919	5807	4613
70°	4362	4532	2816
75°	4039	3675	1725
80°	3719	3379	1488
85°	3366	3102	1217



TEST NUMBER: P522065

CATALOG NUMBER: SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	266.1	2.6
10°-20°	692.1	6.6
20°-30°	896.5	8.6
30°-40°	877.9	8.4
40°-50°	672.0	6.4
50°-60°	447.8	4.3
60°-70°	244.3	2.3
70°-80°	101.8	1.0
80°-90°	28.8	0.3
90°-100°	493.7	4.7
100°-110°	1193.3	11.4
110°-120°	1272.7	12.2
120°-130°	1030.8	9.9
130°-140°	798.1	7.7
140°-150°	608.8	5.8
150°-160°	440.7	4.2
160°-170°	271.4	2.6
170°-180°	91.9	0.9
0°-30°	1854.7	17.8
0°-40°	2732.5	26.2
0°-60°	3852.3	36.9
0°-90°	4227.2	40.5
90°-120°	2959.8	28.4
90°-150°	5397.5	51.8
90°-180°	6202.0	59.5
0°-180°	10428.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2901	2901	2901	2901	2901	
5°	2854	2825	2844	2850	2860	265
15°	2413	2405	2469	2537	2580	674
25°	1844	1849	1945	2030	2119	848
35°	1304	1310	1398	1492	1598	810
45°	782	796	849	913	997	610
55°	449	468	495	514	556	407
65°	225	244	266	232	211	234
75°	113	113	103	71	48	121
85°	32	32	29	19	12	35
90°	0	0	0	0	0	4
95°	49	247	846	550	385	55
105°	191	330	1434	1856	1832	201
115°	349	446	1152	2184	2436	345
125°	497	572	1000	1737	2041	443
135°	611	682	960	1370	1576	471
145°	722	776	941	1164	1256	451
155°	828	863	954	1031	1069	382
165°	915	929	966	980	994	258
175°	968	964	968	960	958	91
180°	958	958	958	958	958	

TEST NUMBER: P522065

CATALOG NUMBER: SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2901.0	2901.0	2901.0	2901.0	2901.0
2.5°	2908.1	2882.2	2888.7	2888.6	2880.6
5°	2853.9	2825.2	2843.7	2850.3	2860.2
7.5°	2748.0	2726.3	2759.9	2784.8	2805.0
10°	2665.5	2646.8	2689.7	2725.9	2752.0
12.5°	2569.7	2554.1	2607.2	2655.8	2689.9
15°	2413.4	2404.7	2469.4	2536.6	2580.2
17.5°	2246.2	2241.9	2316.2	2394.6	2450.3
20°	2132.1	2130.9	2212.3	2294.0	2358.7
22.5°	2017.0	2019.8	2105.4	2190.3	2264.0
25°	1844.4	1849.4	1945.0	2029.8	2119.4
27.5°	1684.8	1687.1	1785.9	1875.4	1971.0
30°	1575.9	1582.1	1679.0	1771.6	1871.2
32.5°	1466.9	1474.1	1569.0	1664.7	1766.3
35°	1303.5	1309.7	1397.7	1491.7	1597.5
37.5°	1134.9	1143.4	1221.5	1310.4	1414.5
40°	1026.0	1038.4	1107.4	1191.2	1293.3
42.5°	921.1	936.5	1000.5	1080.0	1172.1
45°	781.6	796.5	849.0	913.3	996.7
47.5°	661.4	678.6	718.9	774.3	845.5
50°	593.2	609.4	646.6	687.6	754.8
52.5°	533.1	549.3	582.5	614.1	671.3
55°	449.3	468.0	495.2	513.9	556.3
57.5°	380.6	398.5	420.1	428.5	454.2
60°	334.8	354.7	374.2	373.3	387.0
62.5°	293.0	310.0	329.4	316.0	316.7
65°	225.3	244.0	266.0	232.5	211.3
67.5°	182.0	186.0	208.8	162.1	137.0
70°	161.7	161.7	168.0	125.5	104.4
72.5°	142.3	142.3	136.5	102.1	79.9
75°	113.3	113.3	103.1	70.8	48.4
77.5°	87.3	86.3	78.9	52.8	35.1
80°	70.0	70.0	63.6	41.7	28.0
82.5°	54.7	54.7	49.4	32.6	20.9
85°	31.8	31.8	29.3	18.9	11.5
87.5°	11.2	11.2	10.2	6.1	5.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.2	133.7	314.8	153.1	103.9
95°	48.7	247.0	845.9	550.1	385.4
97.5°	86.4	273.7	1114.1	1073.3	921.4
100°	115.6	290.2	1261.8	1332.0	1207.0
102.5°	143.2	305.1	1359.2	1547.4	1473.2
105°	190.7	329.5	1434.2	1855.7	1831.9
107.5°	237.3	358.3	1390.0	2102.9	2158.9
110°	269.8	382.9	1318.6	2209.5	2314.7

TEST NUMBER: P522065

CATALOG NUMBER: SQ4-WB-150U-125D-93050-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	302.3	407.4	1255.3	2235.6	2415.3
115°	348.9	446.1	1152.3	2184.5	2436.4
117.5°	395.2	486.8	1091.8	2067.0	2362.1
120°	426.0	511.3	1052.9	1974.8	2284.2
122.5°	458.5	537.4	1028.5	1880.6	2185.2
125°	497.0	572.4	1000.1	1737.3	2040.8
127.5°	535.2	606.2	980.2	1616.0	1882.6
130°	557.9	627.3	973.7	1531.5	1793.3
132.5°	579.0	651.6	964.0	1470.5	1692.7
135°	610.6	682.0	959.5	1370.0	1576.2
137.5°	640.6	712.4	945.3	1301.9	1457.4
140°	663.4	728.8	945.3	1252.9	1395.7
142.5°	686.1	751.5	937.2	1210.2	1330.8
145°	722.2	775.7	941.3	1164.5	1255.7
147.5°	755.9	807.8	938.9	1111.8	1187.2
150°	777.0	822.6	945.3	1088.7	1148.2
152.5°	799.7	843.7	943.7	1064.2	1117.4
155°	827.7	863.4	953.5	1031.4	1069.1
157.5°	861.4	891.9	951.4	1018.9	1041.1
160°	874.3	900.1	959.5	1002.5	1018.4
162.5°	895.4	918.1	956.3	997.5	1007.0
165°	914.9	928.8	965.6	980.1	994.0
167.5°	938.9	948.0	963.2	979.0	979.4
170°	945.3	951.3	969.7	967.9	977.8
172.5°	956.7	961.1	964.8	969.1	963.2
175°	967.7	963.7	967.7	959.5	957.5
177.5°	965.6	965.6	962.4	959.0	951.0
180°	957.5	957.5	957.5	957.5	957.5

(END OF REPORT)