

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521829

Luminaire Tested: **SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521829
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5469.3 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 55.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521829

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521829

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	46	46	40				
2	90	83	78	73	82	77	72	68	65	61	58	53	51	49	43	41	40	35				
3	83	74	67	62	76	68	63	58	58	54	50	48	45	43	39	37	35	31				
4	76	66	59	54	70	61	55	50	52	48	44	44	40	38	36	33	31	28				
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25				
6	65	54	46	41	60	50	44	39	43	38	34	36	33	30	30	27	25	23				
7	61	49	42	36	56	46	39	35	39	34	31	33	30	27	28	25	23	20				
8	56	45	38	33	52	42	35	31	36	31	28	31	27	24	26	23	21	19				
9	53	41	34	29	49	39	32	28	33	28	25	29	25	22	24	21	19	17				
10	49	38	31	27	46	36	29	25	31	26	23	27	23	20	23	20	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15637	15637	15637
5°	15442	15387	15477
10°	14590	14722	15064
15°	13468	13781	14399
20°	12231	12690	13531
25°	10970	11569	12605
30°	9809	10450	11646
35°	8577	9197	10512
40°	7219	7792	9100
45°	5958	6472	7598
50°	4975	5423	6330
55°	4222	4654	5228
60°	3609	4034	4172
65°	2873	3393	2696
70°	2546	2649	1646
75°	2360	2146	1009
80°	2173	1976	871
85°	1969	1810	709



TEST NUMBER: P521829

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.8
10°-20°	404.4	7.4
20°-30°	523.8	9.6
30°-40°	512.9	9.4
40°-50°	392.6	7.2
50°-60°	261.6	4.8
60°-70°	142.7	2.6
70°-80°	59.5	1.1
80°-90°	16.8	0.3
90°-100°	238.8	4.4
100°-110°	577.2	10.6
110°-120°	615.6	11.3
120°-130°	498.6	9.1
130°-140°	386.0	7.1
140°-150°	294.5	5.4
150°-160°	213.2	3.9
160°-170°	131.3	2.4
170°-180°	44.5	0.8
0°-30°	1083.6	19.8
0°-40°	1596.5	29.2
0°-60°	2250.6	41.2
0°-90°	2469.7	45.2
90°-120°	1431.6	26.2
90°-150°	2610.7	47.7
90°-180°	3000.0	54.9
0°-180°	5469.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1667	1651	1661	1665	1671	155
15°	1410	1405	1443	1482	1508	394
25°	1078	1080	1136	1186	1238	496
35°	762	765	817	872	933	473
45°	457	465	496	534	582	356
55°	262	273	289	300	325	238
65°	132	142	155	136	124	137
75°	66	66	60	41	28	71
85°	19	19	17	11	7	20
90°	0	0	0	0	0	2
95°	24	120	409	266	186	26
105°	92	159	694	898	886	97
115°	169	216	557	1057	1178	167
125°	240	277	484	840	987	215
135°	295	330	464	663	762	228
145°	349	375	455	563	607	218
155°	400	418	461	499	517	185
165°	442	449	467	474	481	125
175°	468	466	468	464	463	44
180°	463	463	463	463	463	

TEST NUMBER: P521829

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1694.9	1694.9	1694.9	1694.9	1694.9
2.5°	1699.0	1683.9	1687.7	1687.6	1683.0
5°	1667.3	1650.6	1661.4	1665.3	1671.1
7.5°	1605.5	1592.8	1612.5	1627.0	1638.8
10°	1557.3	1546.4	1571.4	1592.6	1607.9
12.5°	1501.4	1492.2	1523.2	1551.6	1571.6
15°	1410.0	1404.9	1442.8	1482.0	1507.5
17.5°	1312.3	1309.8	1353.2	1399.0	1431.6
20°	1245.7	1245.0	1292.5	1340.2	1378.1
22.5°	1178.4	1180.0	1230.1	1279.7	1322.7
25°	1077.6	1080.5	1136.4	1185.9	1238.2
27.5°	984.3	985.7	1043.4	1095.7	1151.5
30°	920.7	924.3	980.9	1035.0	1093.2
32.5°	857.0	861.2	916.7	972.6	1031.9
35°	761.5	765.2	816.6	871.5	933.3
37.5°	663.1	668.0	713.6	765.6	826.4
40°	599.4	606.7	647.0	696.0	755.6
42.5°	538.1	547.1	584.5	631.0	684.8
45°	456.6	465.4	496.0	533.6	582.3
47.5°	386.4	396.5	420.0	452.4	494.0
50°	346.6	356.0	377.8	401.7	441.0
52.5°	311.5	320.9	340.3	358.8	392.2
55°	262.5	273.4	289.3	300.3	325.0
57.5°	222.4	232.8	245.4	250.4	265.3
60°	195.6	207.2	218.6	218.1	226.1
62.5°	171.2	181.1	192.5	184.6	185.0
65°	131.6	142.5	155.4	135.8	123.5
67.5°	106.3	108.7	122.0	94.7	80.0
70°	94.4	94.4	98.2	73.3	61.0
72.5°	83.1	83.1	79.7	59.6	46.7
75°	66.2	66.2	60.2	41.3	28.3
77.5°	51.0	50.4	46.1	30.9	20.5
80°	40.9	40.9	37.2	24.4	16.4
82.5°	32.0	32.0	28.9	19.0	12.2
85°	18.6	18.6	17.1	11.1	6.7
87.5°	6.5	6.5	5.9	3.6	3.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	64.6	152.3	74.0	50.2
95°	23.5	119.5	409.2	266.1	186.4
97.5°	41.8	132.4	538.9	519.2	445.7
100°	55.9	140.4	610.3	644.3	583.8
102.5°	69.3	147.6	657.4	748.4	712.6
105°	92.2	159.4	693.7	897.5	886.0
107.5°	114.8	173.3	672.3	1017.2	1044.2
110°	130.5	185.2	637.8	1068.7	1119.6

TEST NUMBER: P521829

CATALOG NUMBER: SQ4-WB-075U-075D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.2	197.0	607.2	1081.3	1168.2
115°	168.8	215.8	557.3	1056.6	1178.4
117.5°	191.1	235.5	528.1	999.8	1142.5
120°	206.1	247.3	509.2	955.2	1104.8
122.5°	221.8	259.9	497.5	909.6	1057.0
125°	240.4	276.9	483.7	840.3	987.1
127.5°	258.8	293.2	474.1	781.6	910.6
130°	269.8	303.4	471.0	740.8	867.4
132.5°	280.0	315.2	466.3	711.3	818.7
135°	295.3	329.9	464.1	662.6	762.4
137.5°	309.9	344.6	457.2	629.7	704.9
140°	320.9	352.5	457.2	606.0	675.1
142.5°	331.8	363.5	453.3	585.3	643.7
145°	349.3	375.2	455.3	563.2	607.4
147.5°	365.6	390.7	454.1	537.7	574.2
150°	375.8	397.9	457.2	526.6	555.4
152.5°	386.8	408.1	456.5	514.7	540.5
155°	400.3	417.6	461.2	498.9	517.1
157.5°	416.6	431.4	460.2	492.8	503.6
160°	422.9	435.4	464.1	484.9	492.6
162.5°	433.1	444.0	462.5	482.5	487.1
165°	442.5	449.2	467.1	474.1	480.8
167.5°	454.1	458.5	465.9	473.5	473.7
170°	457.2	460.1	469.0	468.1	472.9
172.5°	462.7	464.9	466.7	468.8	465.9
175°	468.0	466.1	468.0	464.1	463.1
177.5°	467.1	467.1	465.5	463.8	460.0
180°	463.1	463.1	463.1	463.1	463.1

(END OF REPORT)