

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P521881

Luminaire Tested: **SQ4-WB-0U-075D-93050-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P521881
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-075D-93050-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2469.7 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P521881

CATALOG NUMBER: SQ4-WB-0U-075D-93050-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P521881

CATALOG NUMBER: SQ4-WB-OU-075D-93050-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62				62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55				55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50				50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45				45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41				41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38				38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35				35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15637	15637	15637
5°	15442	15387	15477
10°	14590	14722	15064
15°	13468	13781	14399
20°	12231	12690	13531
25°	10970	11569	12605
30°	9809	10450	11646
35°	8577	9197	10512
40°	7219	7792	9100
45°	5958	6472	7598
50°	4975	5423	6330
55°	4222	4654	5228
60°	3609	4034	4172
65°	2873	3393	2696
70°	2546	2649	1646
75°	2360	2146	1009
80°	2173	1976	871
85°	1969	1810	709



TEST NUMBER: P521881

CATALOG NUMBER: SQ4-WB-OU-075D-93050-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	6.3
10°-20°	404.4	16.4
20°-30°	523.8	21.2
30°-40°	512.9	20.8
40°-50°	392.6	15.9
50°-60°	261.6	10.6
60°-70°	142.7	5.8
70°-80°	59.5	2.4
80°-90°	16.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1083.6	43.9
0°-40°	1596.5	64.6
0°-60°	2250.6	91.1
0°-90°	2469.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2469.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1667	1651	1661	1665	1671	155
15°	1410	1405	1443	1482	1508	394
25°	1078	1080	1136	1186	1238	496
35°	762	765	817	872	933	473
45°	457	465	496	534	582	356
55°	262	273	289	300	325	238
65°	132	142	155	136	124	137
75°	66	66	60	41	28	71
85°	19	19	17	11	7	21
90°	0	0	0	0	0	



TEST NUMBER: P521881

CATALOG NUMBER: SQ4-WB-OU-075D-93050-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1694.9	1694.9	1694.9	1694.9	1694.9
2.5°	1699.0	1683.9	1687.7	1687.6	1683.0
5°	1667.3	1650.6	1661.4	1665.3	1671.1
7.5°	1605.5	1592.8	1612.5	1627.0	1638.8
10°	1557.3	1546.4	1571.4	1592.6	1607.9
12.5°	1501.4	1492.2	1523.2	1551.6	1571.6
15°	1410.0	1404.9	1442.8	1482.0	1507.5
17.5°	1312.3	1309.8	1353.2	1399.0	1431.6
20°	1245.7	1245.0	1292.5	1340.2	1378.1
22.5°	1178.4	1180.0	1230.1	1279.7	1322.7
25°	1077.6	1080.5	1136.4	1185.9	1238.2
27.5°	984.3	985.7	1043.4	1095.7	1151.5
30°	920.7	924.3	980.9	1035.0	1093.2
32.5°	857.0	861.2	916.7	972.6	1031.9
35°	761.5	765.2	816.6	871.5	933.3
37.5°	663.1	668.0	713.6	765.6	826.4
40°	599.4	606.7	647.0	696.0	755.6
42.5°	538.1	547.1	584.5	631.0	684.8
45°	456.6	465.4	496.0	533.6	582.3
47.5°	386.4	396.5	420.0	452.4	494.0
50°	346.6	356.0	377.8	401.7	441.0
52.5°	311.5	320.9	340.3	358.8	392.2
55°	262.5	273.4	289.3	300.3	325.0
57.5°	222.4	232.8	245.4	250.4	265.3
60°	195.6	207.2	218.6	218.1	226.1
62.5°	171.2	181.1	192.5	184.6	185.0
65°	131.6	142.5	155.4	135.8	123.5
67.5°	106.3	108.7	122.0	94.7	80.0
70°	94.4	94.4	98.2	73.3	61.0
72.5°	83.1	83.1	79.7	59.6	46.7
75°	66.2	66.2	60.2	41.3	28.3
77.5°	51.0	50.4	46.1	30.9	20.5
80°	40.9	40.9	37.2	24.4	16.4
82.5°	32.0	32.0	28.9	19.0	12.2
85°	18.6	18.6	17.1	11.1	6.7
87.5°	6.5	6.5	5.9	3.6	3.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)