

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P522012

Luminaire Tested: **SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/5/2021

Test Information

Test Method: LM-79-08
Report Number: P522012
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-50,
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K/5000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9283.3 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 96.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P522012

CATALOG NUMBER: SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P522012

CATALOG NUMBER: SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	46	46	40
2	90	83	78	73	82	77	72	68	64	61	58	53	51	49	43	41	40	35
3	83	74	67	62	76	68	63	58	58	54	50	48	45	43	39	37	35	31
4	76	66	59	54	70	61	55	50	52	47	44	44	40	38	36	33	31	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	46	41	60	50	44	39	43	38	34	36	33	30	30	27	25	22
7	61	49	42	36	56	46	39	34	39	34	31	33	30	27	28	25	23	20
8	56	45	38	33	52	42	35	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	33	28	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	29	25	31	26	23	27	23	20	22	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26483	26483	26483
5°	26152	26059	26211
10°	24709	24932	25511
15°	22809	23339	24385
20°	20714	21492	22915
25°	18578	19591	21348
30°	16612	17699	19725
35°	14526	15576	17804
40°	12227	13198	15413
45°	10090	10961	12868
50°	8424	9183	10721
55°	7152	7880	8853
60°	6111	6833	7065
65°	4866	5746	4565
70°	4316	4486	2787
75°	3996	3636	1708
80°	3682	3347	1472
85°	3335	3070	1196



TEST NUMBER: P522012

CATALOG NUMBER: SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.3	2.8
10°-20°	684.8	7.4
20°-30°	887.0	9.6
30°-40°	868.6	9.4
40°-50°	664.9	7.2
50°-60°	443.0	4.8
60°-70°	241.8	2.6
70°-80°	100.7	1.1
80°-90°	28.5	0.3
90°-100°	406.1	4.4
100°-110°	981.4	10.6
110°-120°	1046.8	11.3
120°-130°	847.8	9.1
130°-140°	656.4	7.1
140°-150°	500.7	5.4
150°-160°	362.5	3.9
160°-170°	223.3	2.4
170°-180°	75.6	0.8
0°-30°	1835.1	19.8
0°-40°	2703.7	29.1
0°-60°	3811.7	41.1
0°-90°	4182.7	45.1
90°-120°	2434.3	26.2
90°-150°	4439.2	47.8
90°-180°	5101.0	54.9
0°-180°	9283.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2870	2870	2870	2870	2870	
5°	2824	2796	2814	2820	2830	263
15°	2388	2379	2443	2510	2553	667
25°	1825	1830	1924	2008	2097	839
35°	1290	1296	1383	1476	1581	802
45°	773	788	840	904	986	603
55°	445	463	490	508	550	403
65°	223	241	263	230	209	232
75°	112	112	102	70	48	120
85°	32	32	29	19	11	34
90°	0	0	0	0	0	3
95°	40	203	696	452	317	45
105°	157	271	1180	1526	1507	166
115°	287	367	948	1797	2004	284
125°	409	471	822	1429	1678	365
135°	502	561	789	1127	1296	388
145°	594	638	774	958	1033	371
155°	681	710	784	848	879	314
165°	752	764	794	806	818	212
175°	796	793	796	789	788	75
180°	788	788	788	788	788	

TEST NUMBER: P522012

CATALOG NUMBER: SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2870.4	2870.4	2870.4	2870.4	2870.4
2.5°	2877.5	2851.8	2858.3	2858.1	2850.3
5°	2823.8	2795.5	2813.7	2820.3	2830.1
7.5°	2719.0	2697.6	2730.9	2755.5	2775.4
10°	2637.4	2618.9	2661.3	2697.2	2723.0
12.5°	2542.7	2527.2	2579.7	2627.8	2661.6
15°	2388.0	2379.4	2443.4	2509.9	2553.0
17.5°	2222.5	2218.3	2291.8	2369.4	2424.5
20°	2109.7	2108.4	2189.0	2269.8	2333.9
22.5°	1995.8	1998.5	2083.2	2167.2	2240.2
25°	1825.0	1829.9	1924.5	2008.4	2097.1
27.5°	1667.1	1669.3	1767.1	1855.6	1950.2
30°	1559.3	1565.4	1661.3	1752.9	1851.5
32.5°	1451.5	1458.6	1552.5	1647.2	1747.7
35°	1289.7	1295.9	1382.9	1476.0	1580.7
37.5°	1123.0	1131.3	1208.6	1296.6	1399.6
40°	1015.2	1027.5	1095.8	1178.7	1279.7
42.5°	911.4	926.6	990.0	1068.6	1159.8
45°	773.3	788.1	840.1	903.7	986.2
47.5°	654.4	671.4	711.4	766.1	836.6
50°	586.9	602.9	639.8	680.4	746.9
52.5°	527.5	543.5	576.3	607.6	664.3
55°	444.6	463.1	489.9	508.5	550.4
57.5°	376.6	394.3	415.6	424.0	449.4
60°	331.2	351.0	370.3	369.3	382.9
62.5°	289.9	306.7	326.0	312.6	313.4
65°	222.9	241.4	263.2	230.0	209.1
67.5°	180.1	184.0	206.6	160.4	135.5
70°	160.0	160.0	166.3	124.2	103.3
72.5°	140.8	140.8	135.0	101.0	79.1
75°	112.1	112.1	102.0	70.0	47.9
77.5°	86.4	85.4	78.1	52.2	34.8
80°	69.3	69.3	63.0	41.3	27.7
82.5°	54.2	54.2	48.9	32.2	20.7
85°	31.5	31.5	29.0	18.7	11.3
87.5°	11.1	11.1	10.1	6.0	5.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.3	109.9	258.9	125.9	85.4
95°	40.0	203.2	695.7	452.4	317.0
97.5°	71.1	225.1	916.3	882.8	757.8
100°	95.1	238.7	1037.8	1095.5	992.7
102.5°	117.8	250.9	1117.9	1272.6	1211.6
105°	156.8	271.0	1179.6	1526.2	1506.6
107.5°	195.2	294.7	1143.2	1729.6	1775.6
110°	221.9	314.9	1084.5	1817.2	1903.7

TEST NUMBER: P522012

CATALOG NUMBER: SQ4-WB-125U-125D-93050-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	248.6	335.1	1032.4	1838.7	1986.5
115°	287.0	366.9	947.7	1796.6	2003.8
117.5°	325.0	400.4	898.0	1700.0	1942.7
120°	350.4	420.5	865.9	1624.2	1878.7
122.5°	377.1	442.0	845.9	1546.7	1797.3
125°	408.8	470.8	822.5	1428.9	1678.5
127.5°	440.1	498.5	806.2	1329.1	1548.3
130°	458.8	515.9	800.9	1259.6	1474.9
132.5°	476.2	535.9	792.8	1209.4	1392.2
135°	502.2	560.9	789.2	1126.7	1296.4
137.5°	526.9	586.0	777.5	1070.7	1198.6
140°	545.6	599.4	777.5	1030.4	1147.9
142.5°	564.3	618.1	770.8	995.3	1094.5
145°	594.0	638.0	774.2	957.7	1032.8
147.5°	621.7	664.4	772.2	914.4	976.4
150°	639.0	676.5	777.5	895.4	944.3
152.5°	657.7	693.9	776.2	875.3	919.0
155°	680.7	710.1	784.2	848.3	879.3
157.5°	708.4	733.5	782.5	838.0	856.2
160°	719.1	740.3	789.2	824.5	837.6
162.5°	736.5	755.0	786.5	820.4	828.2
165°	752.5	763.9	794.2	806.1	817.5
167.5°	772.2	779.7	792.2	805.2	805.5
170°	777.5	782.4	797.5	796.0	804.2
172.5°	786.8	790.4	793.5	797.1	792.2
175°	795.8	792.6	795.8	789.1	787.5
177.5°	794.2	794.2	791.5	788.7	782.2
180°	787.5	787.5	787.5	787.5	787.5

(END OF REPORT)