

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938049

Luminaire Tested: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938049
REPORT IS A COMBINATION OF REPORTS P933591 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19712.1 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3062	3062	3062
5°	2992	3540	4115
10°	2715	5161	6823
15°	2308	6744	8238
20°	1880	7817	8396
25°	1569	8182	8225
30°	1324	8236	8210
35°	1171	8102	8422
40°	1021	7926	8641
45°	925	7798	8676
50°	850	7684	8532
55°	814	7515	8154
60°	834	7188	7556
65°	869	6690	6736
70°	928	5838	5691
75°	1033	4764	4441
80°	1136	3309	2992
85°	1030	1759	1532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 8676 cd/sqm

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	0.6
10°-20°	567.5	2.9
20°-30°	992.6	5.0
30°-40°	1277.8	6.5
40°-50°	1427.2	7.2
50°-60°	1367.0	6.9
60°-70°	1083.3	5.5
70°-80°	637.0	3.2
80°-90°	184.1	0.9
90°-100°	905.9	4.6
100°-110°	2381.7	12.1
110°-120°	2469.5	12.5
120°-130°	1980.9	10.0
130°-140°	1554.3	7.9
140°-150°	1193.0	6.1
150°-160°	859.1	4.4
160°-170°	525.7	2.7
170°-180°	177.6	0.9
0°-30°	1688.1	8.6
0°-40°	2965.9	15.0
0°-60°	5760.1	29.2
0°-90°	7664.5	38.9
90°-120°	5757.1	29.2
90°-150°	10485.2	53.2
90°-180°	12048.0	61.1
0°-180°	19712.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	990	990	990	990	990	
5°	964	1034	1165	1318	1365	89
15°	722	1334	2247	2724	2810	201
25°	462	1512	2677	2794	2798	213
35°	312	1445	2521	2664	2769	195
45°	213	1152	2228	2553	2667	165
55°	153	732	1891	2196	2257	139
65°	121	388	1404	1579	1601	120
75°	89	239	770	847	850	93
85°	32	73	191	210	213	34
90°	12	35	95	47	47	12
95°	120	469	1560	804	548	133
105°	429	650	2633	3998	3729	455
115°	762	926	2109	4207	4802	753
125°	1060	1189	1918	3242	3824	941
135°	1264	1391	1858	2617	2967	978
145°	1466	1559	1835	2233	2407	918
155°	1656	1702	1835	2014	2073	761
165°	1787	1811	1835	1907	1931	504
175°	1858	1858	1847	1871	1871	176
180°	1858	1858	1858	1858	1858	

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	989.9	989.9	989.9	989.9	989.9	989.9	989.9	989.9	989.9	989.9	989.9
2.5°	989.9	989.9	996.2	999.4	1005.8	1009.0	1015.3	1021.7	1040.8	1044.0	1050.3
5°	964.4	977.1	1018.5	1034.4	1079.0	1139.5	1164.9	1206.3	1292.2	1317.6	1333.5
7.5°	926.2	954.8	1056.7	1082.1	1193.5	1352.7	1419.5	1508.6	1645.5	1712.3	1766.4
10°	865.7	926.2	1107.6	1168.0	1349.5	1591.4	1715.5	1839.7	2046.5	2138.8	2173.8
12.5°	798.9	897.5	1161.7	1244.5	1505.5	1858.7	2008.3	2145.2	2380.7	2504.9	2523.9
15°	722.5	856.2	1212.6	1333.5	1671.0	2081.5	2247.0	2415.7	2635.4	2724.4	2746.7
17.5°	655.6	824.4	1260.4	1387.7	1798.2	2282.0	2450.8	2590.8	2769.0	2829.5	2845.4
20°	572.9	773.4	1292.2	1457.7	1931.9	2428.4	2590.8	2699.0	2819.9	2858.1	2864.5
22.5°	512.4	719.3	1311.3	1483.1	2021.1	2517.6	2654.4	2740.4	2823.1	2835.9	2839.0
25°	461.5	658.9	1308.1	1511.8	2097.4	2571.7	2676.7	2740.4	2788.1	2794.4	2794.4
27.5°	413.8	592.0	1295.4	1518.2	2154.8	2584.4	2667.2	2711.7	2734.0	2746.7	2746.7
30°	372.4	528.4	1263.5	1505.5	2180.2	2571.7	2638.5	2660.8	2683.1	2702.2	2711.7
32.5°	340.6	467.8	1215.8	1480.0	2183.4	2539.9	2587.6	2600.4	2632.2	2676.7	2692.6
35°	311.9	407.4	1161.7	1445.0	2164.2	2488.9	2520.8	2533.5	2597.1	2664.0	2686.3
37.5°	283.3	362.9	1091.7	1384.5	2135.7	2428.4	2450.8	2473.0	2571.7	2651.3	2676.7
40°	254.6	324.7	1009.0	1317.6	2091.1	2355.3	2374.3	2409.3	2539.9	2632.2	2657.6
42.5°	232.3	292.9	919.8	1247.6	2033.8	2272.5	2301.2	2352.1	2501.7	2600.4	2628.9
45°	213.3	261.0	824.4	1152.1	1960.6	2186.6	2227.9	2297.9	2457.1	2552.6	2578.0
47.5°	194.2	238.7	725.7	1053.5	1881.0	2100.6	2154.8	2234.3	2396.6	2488.9	2511.2
50°	178.3	216.4	627.0	948.5	1795.1	2008.3	2072.0	2154.8	2320.3	2406.2	2434.9
52.5°	165.5	197.3	534.7	843.5	1696.4	1912.8	1986.1	2072.0	2227.9	2310.7	2329.8
55°	152.8	181.4	455.1	732.0	1594.6	1811.0	1890.6	1973.3	2126.1	2196.1	2208.8
57.5°	146.4	168.7	388.3	627.0	1486.4	1696.4	1785.6	1861.9	2005.2	2059.2	2072.0
60°	136.8	159.2	337.3	537.8	1368.6	1588.2	1664.6	1741.0	1861.9	1906.5	1916.0
62.5°	127.3	152.8	299.2	451.9	1247.6	1460.9	1537.3	1607.3	1709.2	1741.0	1753.7
65°	120.9	146.4	270.5	388.3	1123.6	1327.2	1403.6	1464.1	1546.8	1578.6	1585.0
67.5°	114.6	140.0	248.3	334.2	999.4	1193.5	1250.8	1308.1	1371.8	1403.6	1406.8
70°	105.0	133.7	229.2	296.0	872.1	1040.8	1088.5	1149.0	1199.9	1215.8	1225.4
72.5°	98.7	124.1	216.4	267.3	741.6	894.4	938.9	974.0	1018.5	1034.4	1034.4
75°	89.1	111.4	203.7	238.7	607.9	732.0	770.2	805.2	840.3	846.6	837.0
77.5°	79.6	98.7	175.1	200.5	474.3	579.3	611.1	630.2	658.9	665.2	668.4
80°	66.8	85.9	136.8	155.9	343.8	426.5	448.8	464.7	490.2	490.2	496.5
82.5°	50.9	66.8	98.7	111.4	232.3	292.9	311.9	321.4	337.3	337.3	337.3
85°	31.8	41.4	63.7	73.2	140.0	178.3	191.0	194.2	206.9	210.1	210.1
87.5°	15.9	22.2	41.4	44.6	73.2	92.3	92.3	98.7	98.7	95.5	92.3
90°	12.4	22.4	32.4	34.9	54.8	81.4	94.8	84.2	63.2	47.4	47.4
92.5°	49.9	134.7	219.5	240.7	338.5	468.7	533.8	467.8	335.9	237.0	227.6
95°	119.7	274.9	430.2	469.0	832.7	1317.8	1560.3	1392.3	1056.4	804.5	775.9
97.5°	207.0	343.9	480.9	515.1	1121.7	1930.5	2334.9	2228.7	2016.4	1857.2	1802.8
100°	274.4	398.6	522.8	553.8	1226.9	2124.4	2573.1	2580.9	2596.4	2608.1	2543.3
102.5°	331.8	447.7	563.5	592.5	1275.2	2185.4	2640.5	2775.7	3046.3	3249.2	3193.8
105°	429.0	527.2	625.3	649.9	1310.9	2192.3	2633.0	2936.2	3542.7	3997.5	3967.7
107.5°	528.9	620.3	711.8	734.7	1317.6	2094.8	2483.4	2906.3	3752.2	4386.6	4393.9
110°	596.2	678.8	761.4	782.0	1307.5	2008.2	2358.6	2831.5	3777.2	4486.4	4517.5

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	662.3	741.0	819.7	839.4	1307.9	1932.7	2245.1	2729.1	3696.9	4422.8	4470.5
115°	762.0	834.6	907.3	925.5	1320.1	1846.1	2109.2	2575.4	3507.7	4207.1	4273.2
117.5°	860.7	926.6	992.6	1009.0	1344.5	1791.9	2015.6	2436.4	3277.8	3908.9	3982.2
120°	918.0	980.1	1042.2	1057.7	1364.5	1773.7	1978.2	2362.7	3131.5	3708.2	3779.4
122.5°	974.1	1036.8	1099.4	1115.0	1393.2	1764.1	1949.5	2295.7	2988.0	3507.3	3577.6
125°	1060.2	1117.3	1174.4	1188.7	1431.9	1756.2	1918.3	2212.3	2800.5	3241.6	3306.4
127.5°	1130.1	1187.7	1245.4	1259.7	1470.5	1751.6	1892.1	2144.6	2649.6	3028.4	3083.0
130°	1167.5	1229.6	1291.6	1307.1	1498.8	1754.4	1882.2	2106.9	2556.5	2893.7	2944.1
132.5°	1206.1	1268.2	1330.3	1345.8	1521.7	1756.2	1873.4	2074.6	2477.1	2778.9	2824.2
135°	1263.5	1320.1	1376.6	1390.7	1546.7	1754.6	1858.5	2027.0	2364.0	2616.8	2655.8
137.5°	1322.1	1378.1	1434.1	1448.0	1584.0	1765.3	1856.0	1998.4	2283.3	2497.0	2528.9
140°	1370.7	1422.3	1473.8	1486.8	1606.9	1767.1	1847.2	1970.2	2216.4	2401.0	2430.8
142.5°	1408.1	1455.8	1503.5	1515.4	1626.0	1773.5	1847.2	1955.3	2171.6	2333.7	2359.3
145°	1465.6	1507.2	1548.7	1559.1	1651.0	1773.5	1834.8	1923.2	2100.0	2232.6	2252.0
147.5°	1522.9	1563.4	1603.8	1613.9	1687.6	1785.7	1834.8	1904.3	2043.5	2147.8	2163.8
150°	1560.3	1596.9	1633.5	1642.7	1706.7	1792.1	1834.8	1893.6	2011.0	2099.1	2112.1
152.5°	1599.0	1626.7	1654.5	1661.4	1719.2	1796.2	1834.8	1885.0	1985.3	2060.5	2070.4
155°	1656.3	1676.9	1697.4	1702.5	1746.6	1805.4	1834.8	1874.7	1954.5	2014.3	2020.8
157.5°	1698.8	1718.7	1738.7	1743.7	1774.1	1814.5	1834.8	1865.8	1927.8	1974.4	1979.0
160°	1727.5	1743.0	1758.6	1762.4	1786.5	1818.7	1834.8	1861.4	1914.6	1954.5	1957.2
162.5°	1756.2	1767.8	1779.4	1782.3	1799.8	1823.1	1834.8	1857.3	1902.1	1935.8	1938.3
165°	1787.3	1797.8	1808.4	1811.0	1819.0	1829.5	1834.8	1850.8	1883.0	1907.0	1909.7
167.5°	1816.1	1821.0	1826.0	1827.2	1833.9	1842.8	1847.2	1857.7	1878.8	1894.6	1895.7
170°	1834.8	1839.8	1844.7	1845.9	1846.3	1846.9	1847.2	1857.7	1878.8	1894.6	1894.6
172.5°	1844.7	1845.9	1847.0	1847.2	1847.2	1847.2	1847.2	1855.6	1872.2	1884.6	1883.7
175°	1858.5	1858.5	1858.5	1858.5	1854.7	1849.7	1847.2	1852.5	1863.0	1870.9	1870.9
177.5°	1858.5	1858.5	1858.5	1858.5	1855.6	1851.6	1849.7	1853.9	1862.2	1868.4	1867.3
180°	1858.5	1858.5	1858.5	1858.5	1858.5	1858.5	1858.5	1858.5	1858.5	1858.5	1858.5

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	989.9	989.9
2.5°	1056.7	1050.3
5°	1359.1	1365.4
7.5°	1830.1	1826.9
10°	2275.7	2304.3
12.5°	2600.4	2606.7
15°	2797.7	2810.4
17.5°	2874.0	2877.2
20°	2877.2	2870.9
22.5°	2842.2	2835.9
25°	2800.9	2797.7
27.5°	2762.6	2765.9
30°	2746.7	2756.3
32.5°	2746.7	2762.6
35°	2753.1	2769.0
37.5°	2749.9	2769.0
40°	2737.2	2759.4
42.5°	2702.2	2718.1
45°	2648.1	2667.2
47.5°	2578.0	2590.8
50°	2488.9	2501.7
52.5°	2377.5	2380.7
55°	2243.8	2256.6
57.5°	2100.6	2103.8
60°	1941.5	1951.0
62.5°	1772.8	1772.8
65°	1594.6	1600.9
67.5°	1410.0	1425.9
70°	1222.2	1225.4
72.5°	1037.6	1037.6
75°	846.6	849.8
77.5°	665.2	665.2
80°	493.4	496.5
82.5°	340.6	346.9
85°	213.3	213.3
87.5°	98.7	89.1
90°	47.4	47.4
92.5°	189.8	152.2
95°	661.8	547.6
97.5°	1585.5	1368.2
100°	2284.5	2025.6
102.5°	2972.0	2750.3
105°	3848.5	3729.4
107.5°	4422.7	4451.5
110°	4641.7	4765.8

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4661.2	4851.9
115°	4537.6	4802.0
117.5°	4275.5	4568.7
120°	4064.3	4349.2
122.5°	3858.7	4139.7
125°	3565.2	3824.1
127.5°	3301.4	3519.8
130°	3145.9	3347.7
132.5°	3004.8	3185.5
135°	2811.5	2967.2
137.5°	2656.4	2783.9
140°	2550.0	2669.2
142.5°	2461.8	2564.4
145°	2329.6	2407.2
147.5°	2228.2	2292.5
150°	2164.3	2216.4
152.5°	2109.7	2149.1
155°	2046.9	2072.9
157.5°	1997.3	2015.6
160°	1967.7	1978.2
162.5°	1948.2	1958.2
165°	1920.2	1930.8
167.5°	1900.1	1904.6
170°	1894.6	1894.6
172.5°	1879.7	1875.9
175°	1870.9	1870.9
177.5°	1862.9	1858.5
180°	1858.5	1858.5

TEST NUMBER: P938049

CATALOG NUMBER: SQ4-FB-125U-100D-930-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.79	4.58	4.83	5.63	7.05	16.98	17.78	18.02	18.83	20.25
	3H	4.49	5.20	5.54	6.26	7.70	18.82	19.53	19.87	20.59	22.03
	4H	4.78	5.46	5.84	6.52	7.97	19.46	20.14	20.53	21.21	22.65
	6H	5.03	5.66	6.10	6.72	8.18	19.90	20.52	20.97	21.59	23.04
	8H	5.10	5.69	6.17	6.77	8.22	20.02	20.61	21.09	21.70	23.15
	12H	5.11	5.68	6.19	6.75	8.23	20.09	20.65	21.17	21.73	23.20
4H	2H	11.00	11.68	12.07	12.74	14.19	17.24	17.92	18.31	18.99	20.43
	3H	12.56	13.13	13.64	14.22	15.68	19.29	19.86	20.37	20.95	22.40
	4H	12.66	13.18	13.74	14.26	15.74	20.06	20.58	21.14	21.66	23.14
	6H	12.66	13.11	13.75	14.21	15.69	20.60	21.05	21.69	22.15	23.62
	8H	12.64	13.06	13.73	14.15	15.64	20.76	21.18	21.85	22.27	23.76
	12H	12.59	12.97	13.70	14.08	15.57	20.85	21.23	21.96	22.34	23.84
8H	4H	14.10	14.52	15.19	15.61	17.10	20.11	20.53	21.20	21.63	23.11
	6H	14.34	14.68	15.45	15.82	17.31	20.74	21.09	21.86	22.23	23.71
	8H	14.35	14.66	15.47	15.78	17.28	20.96	21.27	22.08	22.39	23.89
	12H	14.32	14.59	15.44	15.70	17.24	21.11	21.38	22.23	22.49	24.03
12H	4H	14.24	14.62	15.35	15.73	17.22	20.06	20.44	21.17	21.55	23.04
	6H	14.60	14.90	15.72	16.02	17.52	20.72	21.03	21.85	22.15	23.65
	8H	14.66	14.93	15.79	16.05	17.59	20.95	21.22	22.08	22.34	23.88

END OF REPORT