

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937056

Luminaire Tested: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937056
REPORT IS A COMBINATION OF REPORTS P933493 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12690.8 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1776	1776	1776
5°	1736	2053	2388
10°	1575	2994	3958
15°	1339	3913	4780
20°	1091	4535	4871
25°	910	4747	4772
30°	768	4778	4763
35°	679	4700	4886
40°	592	4599	5013
45°	537	4524	5033
50°	493	4458	4950
55°	472	4360	4730
60°	484	4171	4384
65°	505	3882	3908
70°	538	3388	3301
75°	599	2764	2576
80°	660	1920	1736
85°	596	1020	888

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5033 cd/sqm

TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.3	0.6
10°-20°	329.2	2.6
20°-30°	575.9	4.5
30°-40°	741.3	5.8
40°-50°	828.0	6.5
50°-60°	793.1	6.2
60°-70°	628.5	5.0
70°-80°	369.6	2.9
80°-90°	107.5	0.8
90°-100°	619.8	4.9
100°-110°	1629.6	12.8
110°-120°	1689.7	13.3
120°-130°	1355.4	10.7
130°-140°	1063.5	8.4
140°-150°	816.3	6.4
150°-160°	587.8	4.6
160°-170°	359.7	2.8
170°-180°	121.5	1.0
0°-30°	979.4	7.7
0°-40°	1720.7	13.6
0°-60°	3341.8	26.3
0°-90°	4447.4	35.0
90°-120°	3939.2	31.0
90°-150°	7174.3	56.5
90°-180°	8243.0	65.0
0°-180°	12690.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	560	600	676	764	792	52
15°	419	774	1304	1581	1630	117
25°	268	877	1553	1621	1623	123
35°	181	838	1462	1546	1606	113
45°	124	668	1293	1481	1547	96
55°	89	425	1097	1274	1309	81
65°	70	225	814	916	929	70
75°	52	138	447	491	493	54
85°	18	42	111	122	124	20
90°	8	24	65	32	32	8
95°	82	321	1068	550	375	91
105°	294	445	1802	2735	2552	311
115°	521	633	1443	2879	3286	515
125°	725	813	1313	2218	2617	644
135°	865	952	1272	1790	2030	669
145°	1003	1067	1255	1528	1647	628
155°	1133	1165	1255	1378	1418	521
165°	1223	1239	1255	1305	1321	345
175°	1272	1272	1264	1280	1280	121
180°	1272	1272	1272	1272	1272	

TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3	574.3
2.5°	574.3	574.3	578.0	579.8	583.5	585.3	589.1	592.7	603.8	605.7	609.3
5°	559.5	566.9	590.9	600.1	626.0	661.0	675.8	699.8	749.7	764.4	773.7
7.5°	537.3	553.9	613.0	627.8	692.5	784.8	823.5	875.3	954.7	993.4	1024.8
10°	502.3	537.3	642.6	677.7	782.9	923.3	995.2	1067.3	1187.3	1240.9	1261.2
12.5°	463.4	520.7	674.0	722.0	873.4	1078.4	1165.2	1244.6	1381.2	1453.3	1464.3
15°	419.2	496.7	703.5	773.7	969.5	1207.6	1303.7	1401.5	1529.0	1580.6	1593.6
17.5°	380.4	478.2	731.2	805.1	1043.3	1324.0	1421.8	1503.1	1606.5	1641.6	1650.8
20°	332.4	448.8	749.7	845.7	1120.9	1408.9	1503.1	1565.9	1636.1	1658.2	1661.9
22.5°	297.3	417.3	760.8	860.5	1172.5	1460.6	1540.0	1589.9	1637.9	1645.2	1647.1
25°	267.8	382.2	758.9	877.1	1216.9	1492.0	1552.9	1589.9	1617.5	1621.3	1621.3
27.5°	240.1	343.5	751.5	880.8	1250.1	1499.4	1547.4	1573.2	1586.1	1593.6	1593.6
30°	216.0	306.5	733.1	873.4	1264.9	1492.0	1530.8	1543.7	1556.6	1567.7	1573.2
32.5°	197.6	271.5	705.3	858.6	1266.7	1473.5	1501.3	1508.6	1527.0	1552.9	1562.2
35°	181.0	236.4	674.0	838.3	1255.7	1444.0	1462.4	1469.9	1506.8	1545.6	1558.4
37.5°	164.4	210.5	633.4	803.3	1239.0	1408.9	1421.8	1434.7	1492.0	1538.1	1552.9
40°	147.7	188.3	585.3	764.4	1213.2	1366.4	1377.6	1397.8	1473.5	1527.0	1541.8
42.5°	134.8	169.9	533.6	723.9	1180.0	1318.5	1335.1	1364.6	1451.3	1508.6	1525.2
45°	123.7	151.4	478.2	668.4	1137.5	1268.5	1292.6	1333.2	1425.5	1480.9	1495.7
47.5°	112.6	138.5	421.0	611.2	1091.3	1218.7	1250.1	1296.2	1390.4	1444.0	1456.9
50°	103.4	125.5	363.8	550.2	1041.4	1165.2	1202.1	1250.1	1346.2	1396.0	1412.6
52.5°	96.0	114.5	310.2	489.3	984.2	1109.8	1152.3	1202.1	1292.6	1340.6	1351.7
55°	88.6	105.3	264.0	424.7	925.1	1050.7	1096.8	1144.8	1233.5	1274.1	1281.5
57.5°	85.0	97.8	225.3	363.8	862.4	984.2	1035.9	1080.2	1163.3	1194.7	1202.1
60°	79.4	92.3	195.7	312.1	794.0	921.5	965.8	1010.0	1080.2	1106.1	1111.6
62.5°	73.9	88.6	173.5	262.2	723.9	847.6	891.9	932.5	991.6	1010.0	1017.4
65°	70.2	85.0	156.9	225.3	651.8	770.0	814.4	849.4	897.4	915.9	919.5
67.5°	66.4	81.2	144.0	193.9	579.8	692.5	725.7	758.9	795.8	814.4	816.2
70°	60.9	77.5	133.0	171.7	505.9	603.8	631.6	666.6	696.2	705.3	710.9
72.5°	57.3	72.0	125.5	155.1	430.2	518.9	544.7	565.0	590.9	600.1	600.1
75°	51.7	64.6	118.2	138.5	352.7	424.7	446.8	467.2	487.5	491.2	485.6
77.5°	46.2	57.3	101.6	116.4	275.1	336.1	354.5	365.6	382.2	385.9	387.7
80°	38.8	49.8	79.4	90.5	199.4	247.4	260.4	269.6	284.4	284.4	288.1
82.5°	29.5	38.8	57.3	64.6	134.8	169.9	181.0	186.5	195.7	195.7	195.7
85°	18.4	24.0	36.9	42.5	81.2	103.4	110.8	112.6	120.0	121.9	121.9
87.5°	9.3	12.9	24.0	25.9	42.5	53.6	53.6	57.3	57.3	55.4	53.6
90°	8.5	15.3	22.1	23.9	37.5	55.8	64.9	57.6	43.2	32.4	32.4
92.5°	34.1	92.1	150.2	164.7	231.5	320.6	365.2	320.1	229.9	162.2	155.7
95°	82.0	188.1	294.4	320.9	569.8	901.7	1067.6	952.8	722.9	550.4	530.9
97.5°	141.7	235.4	329.1	352.5	767.6	1320.9	1597.6	1524.9	1379.7	1270.7	1233.6
100°	187.8	272.7	357.7	378.9	839.5	1453.5	1760.6	1765.9	1776.6	1784.5	1740.2
102.5°	227.0	306.3	385.5	405.3	872.5	1495.3	1806.8	1899.3	2084.4	2223.2	2185.3
105°	293.6	360.7	427.8	444.6	897.0	1500.1	1801.6	2009.1	2424.1	2735.3	2714.9
107.5°	361.8	424.4	487.0	502.7	901.5	1433.3	1699.2	1988.6	2567.4	3001.5	3006.5
110°	407.9	464.4	521.0	535.1	894.7	1374.2	1613.9	1937.4	2584.5	3069.8	3091.0

TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	453.2	507.0	560.9	574.4	895.0	1322.5	1536.2	1867.3	2529.6	3026.3	3058.9
115°	521.4	571.1	620.8	633.2	903.2	1263.2	1443.2	1762.2	2400.1	2878.6	2923.9
117.5°	588.9	634.0	679.1	690.4	920.0	1226.0	1379.1	1667.0	2242.8	2674.6	2724.8
120°	628.2	670.7	713.0	723.7	933.7	1213.6	1353.5	1616.5	2142.6	2537.2	2586.0
122.5°	666.5	709.4	752.2	763.0	953.3	1207.0	1333.9	1570.7	2044.5	2399.9	2448.0
125°	725.4	764.5	803.6	813.4	979.7	1201.6	1312.6	1513.8	1916.2	2218.1	2262.4
127.5°	773.2	812.7	852.2	862.0	1006.3	1198.5	1294.7	1467.5	1813.0	2072.2	2109.5
130°	798.9	841.3	883.7	894.4	1025.5	1200.3	1287.8	1441.6	1749.2	1979.9	2014.4
132.5°	825.3	867.8	910.2	920.8	1041.1	1201.6	1281.8	1419.5	1694.9	1901.5	1932.4
135°	864.6	903.2	941.9	951.6	1058.3	1200.5	1271.6	1386.9	1617.5	1790.5	1817.1
137.5°	904.7	942.9	981.3	990.8	1083.9	1207.9	1269.9	1367.4	1562.4	1708.6	1730.4
140°	937.9	973.1	1008.5	1017.3	1099.5	1209.2	1263.9	1348.2	1516.6	1642.9	1663.2
142.5°	963.5	996.2	1028.7	1036.9	1112.6	1213.5	1263.9	1337.9	1485.8	1596.8	1614.3
145°	1002.8	1031.2	1059.7	1066.8	1129.7	1213.5	1255.4	1315.9	1436.9	1527.7	1541.0
147.5°	1042.0	1069.8	1097.5	1104.4	1154.7	1221.8	1255.4	1303.0	1398.2	1469.6	1480.6
150°	1067.6	1092.7	1117.8	1124.0	1167.8	1226.2	1255.4	1295.6	1376.0	1436.3	1445.2
152.5°	1094.1	1113.1	1132.0	1136.7	1176.3	1229.1	1255.4	1289.7	1358.4	1409.9	1416.6
155°	1133.4	1147.4	1161.4	1164.9	1195.1	1235.3	1255.4	1282.8	1337.4	1378.3	1382.8
157.5°	1162.4	1176.0	1189.7	1193.1	1213.8	1241.5	1255.4	1276.6	1319.1	1350.9	1354.1
160°	1182.0	1192.6	1203.3	1205.9	1222.5	1244.4	1255.4	1273.6	1310.0	1337.4	1339.2
162.5°	1201.6	1209.6	1217.5	1219.5	1231.5	1247.4	1255.4	1270.7	1301.5	1324.5	1326.3
165°	1223.0	1230.2	1237.3	1239.2	1244.6	1251.8	1255.4	1266.4	1288.4	1304.9	1306.7
167.5°	1242.6	1246.0	1249.4	1250.3	1254.9	1260.9	1263.9	1271.1	1285.5	1296.3	1297.1
170°	1255.4	1258.8	1262.3	1263.1	1263.4	1263.8	1263.9	1271.1	1285.5	1296.3	1296.3
172.5°	1262.2	1262.9	1263.8	1263.9	1263.9	1263.9	1263.9	1269.6	1281.0	1289.5	1288.9
175°	1271.6	1271.6	1271.6	1271.6	1269.1	1265.7	1263.9	1267.5	1274.8	1280.2	1280.2
177.5°	1271.6	1271.6	1271.6	1271.6	1269.6	1267.0	1265.7	1268.5	1274.2	1278.4	1277.7
180°	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6

TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	574.3	574.3
2.5°	613.0	609.3
5°	788.5	792.2
7.5°	1061.8	1059.9
10°	1320.3	1336.9
12.5°	1508.6	1512.3
15°	1623.1	1630.5
17.5°	1667.5	1669.3
20°	1669.3	1665.6
22.5°	1648.9	1645.2
25°	1625.0	1623.1
27.5°	1602.8	1604.7
30°	1593.6	1599.1
32.5°	1593.6	1602.8
35°	1597.2	1606.5
37.5°	1595.4	1606.5
40°	1588.0	1600.9
42.5°	1567.7	1577.0
45°	1536.3	1547.4
47.5°	1495.7	1503.1
50°	1444.0	1451.3
52.5°	1379.4	1381.2
55°	1301.8	1309.2
57.5°	1218.7	1220.5
60°	1126.4	1131.9
62.5°	1028.6	1028.6
65°	925.1	928.8
67.5°	818.0	827.2
70°	709.1	710.9
72.5°	602.0	602.0
75°	491.2	493.0
77.5°	385.9	385.9
80°	286.2	288.1
82.5°	197.6	201.3
85°	123.7	123.7
87.5°	57.3	51.7
90°	32.4	32.4
92.5°	129.9	104.2
95°	452.8	374.7
97.5°	1084.9	936.2
100°	1563.1	1386.0
102.5°	2033.5	1881.8
105°	2633.3	2551.7
107.5°	3026.2	3045.9
110°	3176.0	3260.9



TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3189.4	3319.9
115°	3104.7	3285.7
117.5°	2925.4	3126.1
120°	2781.0	2975.9
122.5°	2640.2	2832.6
125°	2439.5	2616.6
127.5°	2259.0	2408.4
130°	2152.5	2290.7
132.5°	2056.0	2179.7
135°	1923.8	2030.3
137.5°	1817.6	1904.9
140°	1744.8	1826.3
142.5°	1684.5	1754.6
145°	1594.0	1647.1
147.5°	1524.6	1568.6
150°	1480.9	1516.6
152.5°	1443.5	1470.4
155°	1400.6	1418.4
157.5°	1366.6	1379.1
160°	1346.4	1353.5
162.5°	1333.0	1339.9
165°	1313.9	1321.1
167.5°	1300.2	1303.2
170°	1296.3	1296.3
172.5°	1286.2	1283.6
175°	1280.2	1280.2
177.5°	1274.7	1271.6
180°	1271.6	1271.6

TEST NUMBER: P937056

CATALOG NUMBER: SQ4-FB-075U-050D-93050-1D-UNV-STD-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.46	2.22	2.53	3.30	4.76	14.65	15.41	15.72	16.49	17.96
	3H	2.15	2.84	3.23	3.92	5.41	16.49	17.17	17.56	18.26	19.74
	4H	2.45	3.10	3.54	4.18	5.68	17.13	17.78	18.22	18.87	20.36
	6H	2.69	3.29	3.79	4.38	5.89	17.56	18.16	18.66	19.25	20.75
	8H	2.76	3.33	3.86	4.43	5.93	17.68	18.25	18.78	19.36	20.85
	12H	2.77	3.31	3.88	4.41	5.94	17.75	18.29	18.85	19.39	20.91
4H	2H	8.67	9.32	9.76	10.41	11.90	14.91	15.56	16.01	16.65	18.14
	3H	10.23	10.77	11.33	11.88	13.39	16.95	17.50	18.06	18.61	20.11
	4H	10.32	10.82	11.42	11.92	13.44	17.72	18.22	18.83	19.32	20.85
	6H	10.32	10.75	11.44	11.88	13.39	18.26	18.69	19.37	19.81	21.33
	8H	10.29	10.70	11.41	11.81	13.35	18.42	18.82	19.53	19.94	21.47
	12H	10.25	10.61	11.38	11.74	13.28	18.51	18.87	19.64	20.00	21.54
8H	4H	11.76	12.16	12.87	13.28	14.81	17.77	18.17	18.89	19.29	20.82
	6H	11.99	12.33	13.13	13.49	15.02	18.40	18.73	19.54	19.89	21.42
	8H	12.01	12.30	13.15	13.44	14.99	18.62	18.91	19.76	20.05	21.60
	12H	11.97	12.23	13.12	13.37	14.95	18.76	19.02	19.91	20.16	21.74
12H	4H	11.90	12.26	13.03	13.39	14.93	17.72	18.08	18.85	19.21	20.75
	6H	12.25	12.54	13.40	13.68	15.23	18.38	18.67	19.52	19.81	21.36
	8H	12.32	12.57	13.47	13.71	15.30	18.61	18.87	19.76	20.00	21.59