

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936577

Luminaire Tested: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936577  
REPORT IS A COMBINATION OF REPORTS P933432 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15057.5 lumens  
Efficiency: N/A  
Efficacy: 101.2 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 148.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936577  
CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P936577

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4864	4864	4864
5°	4753	5623	6538
10°	4314	8199	10839
15°	3667	10714	13088
20°	2987	12419	13339
25°	2493	12999	13067
30°	2103	13085	13043
35°	1860	12871	13380
40°	1622	12592	13729
45°	1469	12389	13783
50°	1349	12207	13554
55°	1293	11939	12953
60°	1326	11420	12005
65°	1381	10628	10701
70°	1475	9275	9040
75°	1640	7570	7055
80°	1806	5255	4754
85°	1640	2794	2433

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13783 cd/sqm



TEST NUMBER: P936577

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.4	1.4
10°-20°	901.5	6.0
20°-30°	1576.9	10.5
30°-40°	2030.0	13.5
40°-50°	2267.4	15.1
50°-60°	2171.7	14.4
60°-70°	1721.0	11.4
70°-80°	1012.0	6.7
80°-90°	282.8	1.9
90°-100°	217.4	1.4
100°-110°	571.4	3.8
110°-120°	592.5	3.9
120°-130°	475.3	3.2
130°-140°	372.9	2.5
140°-150°	286.2	1.9
150°-160°	206.1	1.4
160°-170°	126.1	0.8
170°-180°	42.6	0.3
0°-30°	2681.9	17.8
0°-40°	4711.9	31.3
0°-60°	9150.9	60.8
0°-90°	12166.8	80.8
90°-120°	1381.3	9.2
90°-150°	2515.8	16.7
90°-180°	2891.0	19.2
0°-180°	15057.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1573	1573	1573	1573	1573	
5°	1532	1643	1851	2093	2169	141
15°	1148	2119	3570	4328	4465	319
25°	733	2402	4252	4440	4445	338
35°	496	2296	4005	4232	4399	309
45°	339	1830	3540	4055	4237	262
55°	243	1163	3004	3489	3585	221
65°	192	617	2230	2508	2543	190
75°	142	379	1224	1345	1350	148
85°	51	116	303	334	339	54
90°	3	8	23	11	11	6
95°	29	112	374	193	131	32
105°	103	156	632	959	895	109
115°	183	222	506	1009	1152	181
125°	254	285	460	778	918	226
135°	303	334	446	628	712	235
145°	352	374	440	536	578	220
155°	397	408	440	483	497	183
165°	429	435	440	458	463	121
175°	446	446	443	449	449	42
180°	446	446	446	446	446	



TEST NUMBER: P936577  
 CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1572.6	1572.6	1572.6	1572.6	1572.6	1572.6	1572.6	1572.6	1572.6	1572.6	1572.6
2.5°	1572.6	1572.6	1582.6	1587.7	1597.8	1602.9	1613.0	1623.1	1653.5	1658.5	1668.6
5°	1532.0	1552.3	1618.0	1643.3	1714.1	1810.2	1850.7	1916.4	2052.9	2093.4	2118.6
7.5°	1471.4	1516.9	1678.8	1719.2	1896.2	2149.0	2255.1	2396.8	2614.2	2720.4	2806.3
10°	1375.4	1471.4	1759.6	1855.6	2143.9	2528.1	2725.4	2922.6	3251.2	3397.9	3453.5
12.5°	1269.2	1425.9	1845.6	1977.1	2391.7	2952.9	3190.6	3408.0	3782.2	3979.4	4009.7
15°	1147.8	1360.1	1926.5	2118.6	2654.6	3306.9	3569.8	3837.8	4186.7	4328.3	4363.7
17.5°	1041.6	1309.6	2002.4	2204.5	2856.8	3625.4	3893.5	4115.9	4399.0	4495.1	4520.4
20°	910.1	1228.7	2052.9	2315.8	3069.3	3858.0	4115.9	4287.8	4480.0	4540.7	4550.7
22.5°	814.0	1142.7	2083.2	2356.2	3210.8	3999.6	4217.1	4353.5	4485.0	4505.2	4510.3
25°	733.2	1046.7	2078.2	2401.8	3332.1	4085.6	4252.4	4353.5	4429.4	4439.5	4439.5
27.5°	657.4	940.5	2057.9	2411.9	3423.2	4105.8	4237.3	4308.0	4343.5	4363.7	4363.7
30°	591.6	839.3	2007.3	2391.7	3463.6	4085.6	4191.8	4227.1	4262.6	4292.9	4308.0
32.5°	541.0	743.3	1931.5	2351.3	3468.7	4035.0	4110.9	4131.1	4181.6	4252.4	4277.7
35°	495.5	647.2	1845.6	2295.6	3438.4	3954.1	4004.6	4024.9	4126.0	4232.2	4267.6
37.5°	450.0	576.4	1734.3	2199.6	3392.9	3858.0	3893.5	3928.8	4085.6	4212.0	4252.4
40°	404.5	515.7	1602.9	2093.4	3322.1	3741.8	3772.1	3827.7	4035.0	4181.6	4222.0
42.5°	369.1	465.2	1461.3	1982.1	3231.0	3610.3	3655.8	3736.7	3974.3	4131.1	4176.6
45°	338.7	414.6	1309.6	1830.4	3114.7	3473.7	3539.5	3650.7	3903.5	4055.2	4095.7
47.5°	308.5	379.3	1152.9	1673.7	2988.3	3337.2	3423.2	3549.5	3807.5	3954.1	3989.5
50°	283.2	343.8	996.1	1506.8	2851.8	3190.6	3291.7	3423.2	3686.1	3822.6	3868.2
52.5°	262.9	313.5	849.5	1339.9	2695.1	3038.9	3155.2	3291.7	3539.5	3671.0	3701.2
55°	242.7	288.2	723.1	1162.9	2533.2	2877.0	3003.5	3135.0	3377.6	3488.9	3509.1
57.5°	232.6	268.0	616.9	996.1	2361.3	2695.1	2836.6	2958.0	3185.5	3271.5	3291.7
60°	217.4	252.8	535.9	854.6	2174.3	2523.2	2644.5	2765.9	2958.0	3028.7	3044.0
62.5°	202.3	242.7	475.3	718.0	1982.1	2320.9	2442.2	2553.4	2715.3	2765.9	2786.1
65°	192.1	232.6	429.8	616.9	1784.9	2108.5	2229.8	2326.0	2457.4	2507.9	2518.1
67.5°	182.1	222.5	394.4	531.0	1587.7	1896.2	1987.1	2078.2	2179.3	2229.8	2234.9
70°	166.8	212.3	364.0	470.2	1385.4	1653.5	1729.3	1825.4	1906.2	1931.5	1946.7
72.5°	156.8	197.2	343.8	424.7	1178.2	1420.9	1491.6	1547.3	1618.0	1643.3	1643.3
75°	141.5	177.0	323.6	379.3	965.7	1162.9	1223.7	1279.3	1334.8	1345.0	1329.9
77.5°	126.4	156.8	278.1	318.5	753.4	920.3	970.8	1001.2	1046.7	1056.8	1061.8
80°	106.2	136.6	217.4	247.8	546.1	677.6	712.9	738.2	778.7	778.7	788.8
82.5°	80.9	106.2	156.8	177.0	369.1	465.2	495.5	510.6	535.9	535.9	535.9
85°	50.6	65.7	101.1	116.3	222.5	283.2	303.4	308.5	328.7	333.8	333.8
87.5°	25.3	35.4	65.7	70.8	116.3	146.6	146.6	156.8	156.8	151.7	146.6
90°	3.0	5.4	7.8	8.4	13.1	19.5	22.7	20.2	15.1	11.4	11.4
92.5°	12.0	32.3	52.7	57.8	81.2	112.4	128.1	112.2	80.6	56.9	54.6
95°	28.7	65.9	103.2	112.5	199.8	316.2	374.4	334.1	253.5	193.0	186.2
97.5°	49.7	82.6	115.4	123.6	269.1	463.2	560.2	534.8	483.9	445.6	432.6
100°	65.8	95.6	125.4	132.9	294.4	509.8	617.4	619.3	623.0	625.8	610.2
102.5°	79.6	107.4	135.2	142.1	306.0	524.4	633.6	666.0	730.9	779.6	766.2
105°	103.0	126.5	150.0	155.9	314.5	526.0	631.8	704.5	850.0	959.1	952.0
107.5°	126.9	148.8	170.8	176.3	316.1	502.6	595.8	697.3	900.3	1052.6	1054.3
110°	143.0	162.8	182.7	187.6	313.7	481.9	565.9	679.4	906.3	1076.5	1083.9



TEST NUMBER: P936577

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	159.0	177.8	196.7	201.4	313.8	463.7	538.7	654.9	887.0	1061.2	1072.7
115°	182.9	200.3	217.7	222.1	316.7	442.9	506.1	617.9	841.6	1009.4	1025.3
117.5°	206.5	222.3	238.1	242.1	322.6	430.0	483.7	584.7	786.5	937.9	955.6
120°	220.2	235.2	250.1	253.8	327.4	425.5	474.6	566.8	751.4	889.7	906.9
122.5°	233.8	248.8	263.7	267.5	334.3	423.2	467.7	550.8	716.9	841.5	858.4
125°	254.4	268.1	281.9	285.3	343.6	421.4	460.3	530.8	671.9	777.8	793.3
127.5°	271.1	285.0	298.8	302.3	352.9	420.3	454.0	514.5	635.7	726.6	739.7
130°	280.1	295.0	310.0	313.6	359.7	420.9	451.6	505.6	613.4	694.3	706.5
132.5°	289.4	304.3	319.2	322.9	365.1	421.4	449.5	497.8	594.4	666.8	677.7
135°	303.2	316.7	330.3	333.7	371.1	421.0	445.9	486.3	567.2	627.9	637.2
137.5°	317.2	330.7	344.0	347.4	380.1	423.6	445.3	479.5	547.8	599.1	606.8
140°	328.9	341.2	353.7	356.8	385.6	424.0	443.2	472.7	531.8	576.1	583.3
142.5°	337.8	349.3	360.8	363.6	390.1	425.5	443.2	469.1	521.0	560.0	566.1
145°	351.7	361.6	371.6	374.1	396.1	425.5	440.2	461.4	503.9	535.6	540.3
147.5°	365.4	375.1	384.9	387.2	404.9	428.5	440.2	457.0	490.3	515.3	519.2
150°	374.4	383.2	391.9	394.1	409.5	430.0	440.2	454.4	482.6	503.7	506.8
152.5°	383.7	390.3	396.9	398.6	412.4	431.0	440.2	452.3	476.4	494.4	496.8
155°	397.4	402.3	407.3	408.5	419.0	433.2	440.2	449.8	469.0	483.4	485.0
157.5°	407.6	412.3	417.2	418.4	425.7	435.4	440.2	447.7	462.5	473.7	474.8
160°	414.5	418.2	422.0	422.9	428.7	436.3	440.2	446.6	459.4	468.9	469.5
162.5°	421.4	424.2	427.0	427.7	431.9	437.4	440.2	445.6	456.4	464.4	465.0
165°	428.9	431.4	434.0	434.6	436.4	438.9	440.2	444.1	451.8	457.6	458.2
167.5°	435.8	436.9	438.1	438.4	440.0	442.1	443.2	445.7	450.8	454.6	454.9
170°	440.2	441.4	442.6	442.9	443.0	443.1	443.2	445.7	450.8	454.6	454.6
172.5°	442.6	442.9	443.1	443.2	443.2	443.2	443.2	445.2	449.2	452.2	452.0
175°	445.9	445.9	445.9	445.9	445.0	443.8	443.2	444.5	447.0	448.9	448.9
177.5°	445.9	445.9	445.9	445.9	445.2	444.3	443.8	444.8	446.8	448.3	448.0
180°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9



TEST NUMBER: P936577

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	1572.6	1572.6
2.5°	1678.8	1668.6
5°	2159.1	2169.2
7.5°	2907.4	2902.3
10°	3615.3	3660.8
12.5°	4131.1	4141.2
15°	4444.6	4464.8
17.5°	4566.0	4570.9
20°	4570.9	4560.9
22.5°	4515.4	4505.2
25°	4449.6	4444.6
27.5°	4389.0	4394.1
30°	4363.7	4378.8
32.5°	4363.7	4389.0
35°	4373.7	4399.0
37.5°	4368.8	4399.0
40°	4348.5	4383.9
42.5°	4292.9	4318.2
45°	4206.9	4237.3
47.5°	4095.7	4115.9
50°	3954.1	3974.3
52.5°	3777.1	3782.2
55°	3564.8	3585.0
57.5°	3337.2	3342.3
60°	3084.4	3099.6
62.5°	2816.4	2816.4
65°	2533.2	2543.4
67.5°	2240.0	2265.3
70°	1941.7	1946.7
72.5°	1648.4	1648.4
75°	1345.0	1350.1
77.5°	1056.8	1056.8
80°	783.8	788.8
82.5°	541.0	551.2
85°	338.7	338.7
87.5°	156.8	141.5
90°	11.4	11.4
92.5°	45.6	36.6
95°	158.8	131.4
97.5°	380.5	328.3
100°	548.2	486.0
102.5°	713.0	659.8
105°	923.4	894.8
107.5°	1061.2	1068.1
110°	1113.7	1143.5





TEST NUMBER: P936577

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1118.4	1164.1
115°	1088.7	1152.2
117.5°	1025.9	1096.2
120°	975.2	1043.5
122.5°	925.9	993.3
125°	855.4	917.5
127.5°	792.1	844.5
130°	754.9	803.3
132.5°	721.0	764.3
135°	674.6	711.9
137.5°	637.3	668.0
140°	611.8	640.4
142.5°	590.7	615.3
145°	559.0	577.6
147.5°	534.7	550.1
150°	519.3	531.8
152.5°	506.2	515.6
155°	491.1	497.4
157.5°	479.3	483.7
160°	472.1	474.6
162.5°	467.4	469.8
165°	460.7	463.2
167.5°	455.9	457.0
170°	454.6	454.6
172.5°	451.0	450.1
175°	448.9	448.9
177.5°	447.0	445.9
180°	445.9	445.9



TEST NUMBER: P936577  
 CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-12-2700K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.93	10.23	9.56	10.88	11.63	22.12	23.42	22.75	24.08	24.82
	3H	9.67	10.84	10.31	11.50	12.29	24.00	25.18	24.64	25.84	26.62
	4H	9.98	11.10	10.65	11.77	12.56	24.67	25.78	25.33	26.45	27.25
	6H	10.26	11.29	10.94	11.97	12.78	25.12	26.16	25.80	26.84	27.65
	8H	10.34	11.32	11.03	12.03	12.84	25.26	26.24	25.95	26.95	27.76
	12H	10.37	11.31	11.07	12.01	12.85	25.35	26.29	26.04	26.98	27.83
4H	2H	16.20	17.32	16.87	17.99	18.78	22.45	23.56	23.11	24.23	25.03
	3H	17.81	18.75	18.49	19.46	20.27	24.54	25.47	25.22	26.18	27.00
	4H	17.92	18.78	18.62	19.49	20.33	25.33	26.18	26.02	26.89	27.73
	6H	17.96	18.70	18.68	19.44	20.29	25.90	26.64	26.61	27.38	28.23
	8H	17.95	18.64	18.67	19.38	20.25	26.07	26.77	26.79	27.50	28.37
	12H	17.93	18.55	18.67	19.31	20.19	26.19	26.82	26.93	27.58	28.45
8H	4H	19.41	20.10	20.13	20.84	21.71	25.42	26.12	26.15	26.85	27.72
	6H	19.67	20.25	20.43	21.03	21.90	26.08	26.66	26.83	27.43	28.30
	8H	19.70	20.21	20.46	20.99	21.88	26.31	26.82	27.07	27.60	28.49
	12H	19.69	20.14	20.45	20.91	21.86	26.48	26.93	27.24	27.70	28.64
12H	4H	19.58	20.20	20.32	20.96	21.84	25.40	26.03	26.14	26.79	27.66
	6H	19.94	20.46	20.70	21.23	22.12	26.07	26.58	26.83	27.36	28.25
	8H	20.03	20.49	20.80	21.26	22.20	26.32	26.78	27.09	27.55	28.49