

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936592

Luminaire Tested: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936592  
REPORT IS A COMBINATION OF REPORTS P933456 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10038.7 lumens  
Efficiency: N/A  
Efficacy: 101.2 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936592  
CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4864	4864	4864
5°	4752	5622	6538
10°	4310	8195	10840
15°	3663	10706	13088
20°	2982	12408	13339
25°	2488	12984	13068
30°	2098	13066	13044
35°	1855	12849	13380
40°	1617	12567	13730
45°	1464	12360	13783
50°	1342	12175	13555
55°	1286	11903	12954
60°	1316	11379	12005
65°	1370	10585	10702
70°	1460	9231	9041
75°	1617	7527	7055
80°	1766	5220	4754
85°	1570	2770	2434

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13783 cd/sqm



TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.6	1.4
10°-20°	601.1	6.0
20°-30°	1051.3	10.5
30°-40°	1353.4	13.5
40°-50°	1511.7	15.1
50°-60°	1447.8	14.4
60°-70°	1147.4	11.4
70°-80°	674.7	6.7
80°-90°	188.6	1.9
90°-100°	144.9	1.4
100°-110°	381.0	3.8
110°-120°	395.0	3.9
120°-130°	316.9	3.2
130°-140°	248.6	2.5
140°-150°	190.8	1.9
150°-160°	137.4	1.4
160°-170°	84.1	0.8
170°-180°	28.4	0.3
0°-30°	1788.0	17.8
0°-40°	3141.4	31.3
0°-60°	6100.9	60.8
0°-90°	8111.6	80.8
90°-120°	920.9	9.2
90°-150°	1677.2	16.7
90°-180°	1927.0	19.2
0°-180°	10038.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1021	1096	1234	1396	1446	94
15°	765	1412	2380	2886	2977	213
25°	489	1601	2835	2960	2963	225
35°	330	1530	2670	2822	2933	206
45°	226	1220	2360	2704	2825	175
55°	162	775	2002	2326	2390	147
65°	128	411	1487	1672	1696	127
75°	94	253	816	897	900	99
85°	34	78	202	222	226	36
90°	2	6	15	8	8	4
95°	19	75	250	129	88	21
105°	69	104	421	639	596	73
115°	122	148	337	673	768	120
125°	170	190	307	518	612	151
135°	202	222	297	419	475	156
145°	234	249	294	357	385	147
155°	265	272	294	322	332	122
165°	286	290	294	305	309	81
175°	297	297	296	299	299	28
180°	297	297	297	297	297	



TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1048.4	1048.4	1055.2	1058.5	1065.2	1068.6	1075.4	1082.2	1102.4	1105.8	1112.4
5°	1021.4	1034.9	1078.8	1095.6	1142.8	1206.9	1233.8	1277.7	1368.6	1395.6	1412.4
7.5°	981.0	1011.3	1119.2	1146.2	1264.1	1432.7	1503.5	1597.9	1742.8	1813.6	1871.0
10°	916.9	981.0	1173.1	1237.1	1429.4	1685.5	1817.0	1948.5	2167.6	2265.4	2302.5
12.5°	846.1	950.7	1230.5	1318.1	1594.5	1968.7	2127.2	2272.1	2521.6	2653.0	2673.3
15°	765.2	906.9	1284.3	1412.4	1769.8	2204.6	2379.9	2558.6	2791.3	2885.6	2909.2
17.5°	694.4	873.1	1334.9	1469.8	1904.7	2417.1	2595.7	2744.1	2932.8	2996.9	3013.7
20°	606.8	819.2	1368.6	1543.9	2046.3	2572.2	2744.1	2858.6	2986.8	3027.2	3033.9
22.5°	542.7	761.8	1388.9	1570.9	2140.6	2666.5	2811.5	2902.4	2990.1	3003.6	3007.0
25°	488.8	697.8	1385.5	1601.3	2221.6	2723.9	2835.1	2902.4	2953.0	2959.8	2959.8
27.5°	438.2	627.0	1372.0	1608.0	2282.2	2737.3	2825.0	2872.2	2895.8	2909.2	2909.2
30°	394.4	559.6	1338.3	1594.5	2309.2	2723.9	2794.6	2818.2	2841.8	2862.0	2872.2
32.5°	360.8	495.5	1287.7	1567.5	2312.5	2690.1	2740.7	2754.1	2787.9	2835.1	2851.9
35°	330.4	431.5	1230.5	1530.5	2292.3	2636.2	2669.9	2683.3	2750.8	2821.6	2845.2
37.5°	300.0	384.3	1156.3	1466.4	2262.0	2572.2	2595.7	2619.3	2723.9	2808.1	2835.1
40°	269.7	343.8	1068.6	1395.6	2214.8	2494.6	2514.8	2551.9	2690.1	2787.9	2814.8
42.5°	246.1	310.2	974.3	1321.5	2154.1	2406.9	2437.3	2491.2	2649.7	2754.1	2784.5
45°	225.9	276.4	873.1	1220.3	2076.6	2315.9	2359.7	2433.9	2602.4	2703.6	2730.5
47.5°	205.7	252.8	768.6	1115.8	1992.3	2224.9	2282.2	2366.5	2538.4	2636.2	2659.8
50°	188.7	229.3	664.1	1004.6	1901.3	2127.2	2194.6	2282.2	2457.5	2548.6	2578.8
52.5°	175.3	209.0	566.3	893.3	1796.8	2026.0	2103.6	2194.6	2359.7	2447.4	2467.6
55°	161.8	192.1	482.1	775.4	1688.9	1918.1	2002.5	2090.1	2251.9	2326.1	2339.5
57.5°	155.1	178.7	411.2	664.1	1574.3	1796.8	1891.2	1972.1	2123.8	2181.0	2194.6
60°	144.9	168.5	357.4	569.7	1449.6	1682.1	1763.0	1844.0	1972.1	2019.3	2029.4
62.5°	134.9	161.8	316.9	478.7	1321.5	1547.3	1628.3	1702.4	1810.2	1844.0	1857.4
65°	128.1	155.1	286.5	411.2	1190.0	1405.8	1486.6	1550.7	1638.3	1672.1	1678.8
67.5°	121.3	148.3	262.9	354.0	1058.5	1264.1	1324.8	1385.5	1453.0	1486.6	1490.0
70°	111.3	141.6	242.7	313.5	923.7	1102.4	1152.9	1216.9	1270.9	1287.7	1297.9
72.5°	104.5	131.5	229.3	283.2	785.4	947.3	994.5	1031.6	1078.8	1095.6	1095.6
75°	94.4	118.0	215.7	252.8	643.9	775.4	815.8	852.9	889.9	896.7	886.6
77.5°	84.3	104.5	185.5	212.3	502.3	613.5	647.2	667.5	697.8	704.6	708.0
80°	70.8	91.0	144.9	165.1	364.0	451.7	475.3	492.2	519.1	519.1	525.9
82.5°	54.0	70.8	104.5	118.0	246.1	310.2	330.4	340.4	357.4	357.4	357.4
85°	33.7	43.8	67.4	77.5	148.3	188.7	202.3	205.7	219.1	222.5	222.5
87.5°	16.8	23.6	43.8	47.2	77.5	97.8	97.8	104.5	104.5	101.1	97.8
90°	2.0	3.6	5.2	5.6	8.8	13.0	15.1	13.4	10.1	7.6	7.6
92.5°	8.0	21.5	35.2	38.5	54.2	75.0	85.4	74.8	53.8	37.9	36.5
95°	19.1	43.9	68.8	75.0	133.2	210.8	249.6	222.7	169.0	128.7	124.1
97.5°	33.2	55.1	76.9	82.4	179.4	308.8	373.5	356.6	322.6	297.1	288.4
100°	43.9	63.7	83.6	88.5	196.2	339.7	411.5	412.8	415.3	417.2	406.9
102.5°	53.1	71.6	90.1	94.7	204.0	349.6	422.4	444.0	487.2	519.7	510.8
105°	68.6	84.4	100.1	104.0	209.8	350.7	421.2	469.7	566.7	639.4	634.7
107.5°	84.6	99.2	113.8	117.5	210.8	335.1	397.2	464.8	600.2	701.7	702.9
110°	95.4	108.6	121.8	125.1	209.2	321.2	377.3	452.9	604.2	717.6	722.6



TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	106.0	118.5	131.1	134.3	209.3	309.2	359.2	436.5	591.3	707.5	715.1
115°	121.9	133.5	145.1	148.0	211.2	295.3	337.3	411.9	561.1	673.0	683.6
117.5°	137.6	148.2	158.8	161.5	215.1	286.6	322.4	389.7	524.3	625.3	637.0
120°	146.8	156.8	166.7	169.2	218.3	283.8	316.4	377.9	500.9	593.1	604.5
122.5°	155.8	165.8	175.9	178.4	222.9	282.2	311.8	367.2	478.0	561.0	572.3
125°	169.6	178.8	187.8	190.1	229.1	281.0	306.9	353.9	448.0	518.5	528.9
127.5°	180.8	189.9	199.2	201.5	235.3	280.2	302.7	343.1	423.9	484.5	493.2
130°	186.8	196.7	206.6	209.1	239.7	280.7	301.1	337.0	409.0	462.8	470.9
132.5°	192.9	202.9	212.7	215.2	243.4	281.0	299.7	331.9	396.2	444.5	451.8
135°	202.1	211.2	220.2	222.5	247.4	280.7	297.3	324.3	378.2	418.6	424.8
137.5°	211.5	220.4	229.4	231.7	253.4	282.4	296.9	319.7	365.2	399.4	404.5
140°	219.2	227.5	235.8	237.8	257.1	282.7	295.5	315.2	354.6	384.1	388.8
142.5°	225.3	232.9	240.5	242.4	260.2	283.8	295.5	312.8	347.4	373.3	377.4
145°	234.5	241.1	247.7	249.4	264.1	283.8	293.5	307.7	336.0	357.2	360.3
147.5°	243.6	250.1	256.6	258.2	269.9	285.7	293.5	304.7	326.9	343.5	346.1
150°	249.6	255.5	261.3	262.7	273.0	286.6	293.5	302.9	321.7	335.8	337.8
152.5°	255.8	260.2	264.6	265.7	275.0	287.3	293.5	301.5	317.5	329.6	331.2
155°	264.9	268.2	271.5	272.3	279.4	288.8	293.5	299.9	312.6	322.2	323.2
157.5°	271.7	274.9	278.1	278.9	283.8	290.2	293.5	298.5	308.4	315.8	316.5
160°	276.3	278.8	281.3	281.9	285.8	290.9	293.5	297.8	306.3	312.6	313.0
162.5°	280.9	282.8	284.6	285.1	287.8	291.6	293.5	297.1	304.3	309.7	310.1
165°	286.0	287.6	289.3	289.7	291.0	292.7	293.5	296.1	301.2	305.1	305.5
167.5°	290.5	291.3	292.1	292.3	293.4	294.8	295.5	297.2	300.6	303.1	303.3
170°	293.5	294.3	295.1	295.3	295.4	295.5	295.5	297.2	300.6	303.1	303.1
172.5°	295.1	295.3	295.5	295.5	295.5	295.5	295.5	296.8	299.5	301.5	301.3
175°	297.3	297.3	297.3	297.3	296.7	295.9	295.5	296.3	298.0	299.3	299.3
177.5°	297.3	297.3	297.3	297.3	296.8	296.2	295.9	296.6	297.9	298.9	298.7
180°	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3



TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	1048.4	1048.4
2.5°	1119.2	1112.4
5°	1439.4	1446.2
7.5°	1938.3	1935.0
10°	2410.3	2440.7
12.5°	2754.1	2760.9
15°	2963.2	2976.6
17.5°	3044.1	3047.5
20°	3047.5	3040.7
22.5°	3010.4	3003.6
25°	2966.6	2963.2
27.5°	2926.0	2929.4
30°	2909.2	2919.4
32.5°	2909.2	2926.0
35°	2916.0	2932.8
37.5°	2912.6	2932.8
40°	2899.2	2922.8
42.5°	2862.0	2878.9
45°	2804.7	2825.0
47.5°	2730.5	2744.1
50°	2636.2	2649.7
52.5°	2518.2	2521.6
55°	2376.6	2390.1
57.5°	2224.9	2228.3
60°	2056.3	2066.5
62.5°	1877.7	1877.7
65°	1688.9	1695.7
67.5°	1493.4	1510.2
70°	1294.5	1297.9
72.5°	1099.0	1099.0
75°	896.7	900.1
77.5°	704.6	704.6
80°	522.5	525.9
82.5°	360.8	367.4
85°	225.9	225.9
87.5°	104.5	94.4
90°	7.6	7.6
92.5°	30.4	24.3
95°	105.9	87.5
97.5°	253.6	218.8
100°	365.4	324.0
102.5°	475.4	439.9
105°	615.6	596.5
107.5°	707.5	712.0
110°	742.4	762.3





TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	745.6	776.1
115°	725.9	768.1
117.5°	684.0	730.9
120°	650.1	695.7
122.5°	617.2	662.1
125°	570.3	611.7
127.5°	528.1	563.0
130°	503.2	535.4
132.5°	480.7	509.6
135°	449.7	474.6
137.5°	424.9	445.3
140°	407.9	427.0
142.5°	393.8	410.2
145°	372.7	385.1
147.5°	356.4	366.7
150°	346.2	354.6
152.5°	337.4	343.7
155°	327.4	331.6
157.5°	319.5	322.4
160°	314.7	316.4
162.5°	311.6	313.2
165°	307.2	308.9
167.5°	304.0	304.7
170°	303.1	303.1
172.5°	300.7	300.1
175°	299.3	299.3
177.5°	298.0	297.3
180°	297.3	297.3



TEST NUMBER: P936592

CATALOG NUMBER: SQ4-FB-025U-125D-B2750-1D-UNV-STD-W-8-2700K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.93	10.23	9.56	10.88	11.63	22.10	23.41	22.74	24.06	24.81
	3H	9.66	10.84	10.31	11.50	12.28	23.97	25.15	24.62	25.81	26.59
	4H	9.98	11.09	10.64	11.77	12.56	24.64	25.75	25.30	26.43	27.22
	6H	10.25	11.28	10.93	11.97	12.78	25.09	26.12	25.77	26.81	27.62
	8H	10.33	11.32	11.02	12.02	12.84	25.23	26.21	25.92	26.92	27.73
	12H	10.37	11.31	11.06	12.01	12.85	25.31	26.25	26.01	26.95	27.79
4H	2H	16.19	17.30	16.86	17.98	18.77	22.43	23.54	23.10	24.21	25.01
	3H	17.80	18.73	18.48	19.44	20.26	24.51	25.45	25.19	26.16	26.97
	4H	17.91	18.76	18.61	19.48	20.32	25.30	26.15	26.00	26.87	27.71
	6H	17.95	18.69	18.67	19.43	20.28	25.87	26.61	26.58	27.35	28.20
	8H	17.94	18.63	18.66	19.37	20.23	26.04	26.73	26.76	27.47	28.34
	12H	17.92	18.54	18.66	19.30	20.17	26.16	26.78	26.90	27.54	28.41
8H	4H	19.39	20.09	20.12	20.83	21.69	25.40	26.09	26.12	26.83	27.69
	6H	19.66	20.24	20.41	21.01	21.88	26.05	26.63	26.80	27.40	28.27
	8H	19.68	20.20	20.45	20.98	21.86	26.27	26.79	27.04	27.57	28.45
	12H	19.67	20.13	20.44	20.90	21.84	26.44	26.90	27.21	27.67	28.61
12H	4H	19.56	20.19	20.30	20.95	21.82	25.37	26.00	26.12	26.76	27.63
	6H	19.92	20.44	20.69	21.22	22.10	26.04	26.55	26.80	27.33	28.22
	8H	20.01	20.47	20.78	21.24	22.18	26.29	26.75	27.06	27.51	28.46