

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937287

Luminaire Tested: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P937287  
REPORT IS A COMBINATION OF REPORTS P933511 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9225.0 lumens  
Efficiency: N/A  
Efficacy: 120.1 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 76.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937287  
CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3797	3797	3797
5°	3709	4388	5104
10°	3362	6395	8462
15°	2857	8353	10218
20°	2325	9677	10414
25°	1939	10124	10202
30°	1634	10185	10183
35°	1444	10014	10447
40°	1258	9791	10718
45°	1138	9628	10760
50°	1044	9479	10583
55°	998	9264	10113
60°	1021	8853	9372
65°	1060	8230	8354
70°	1126	7173	7058
75°	1244	5843	5508
80°	1347	4047	3712
85°	1175	2143	1900

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10760 cd/sqm



TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.4	0.9
10°-20°	351.9	3.8
20°-30°	615.6	6.7
30°-40°	792.4	8.6
40°-50°	885.1	9.6
50°-60°	847.8	9.2
60°-70°	671.8	7.3
70°-80°	395.1	4.3
80°-90°	112.4	1.2
90°-100°	336.4	3.6
100°-110°	884.4	9.6
110°-120°	917.0	9.9
120°-130°	735.5	8.0
130°-140°	577.1	6.3
140°-150°	443.0	4.8
150°-160°	319.0	3.5
160°-170°	195.2	2.1
170°-180°	65.9	0.7
0°-30°	1046.9	11.3
0°-40°	1839.4	19.9
0°-60°	3572.3	38.7
0°-90°	4751.6	51.5
90°-120°	2137.7	23.2
90°-150°	3893.3	42.2
90°-180°	4473.0	48.5
0°-180°	9225.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	614	614	614	614	614	
5°	598	642	722	817	847	55
15°	448	827	1394	1690	1743	125
25°	286	938	1660	1733	1735	132
35°	193	896	1563	1652	1717	121
45°	132	714	1382	1583	1654	102
55°	95	454	1172	1362	1400	86
65°	75	241	870	979	993	74
75°	55	148	478	525	527	58
85°	20	45	118	130	132	21
90°	5	13	35	18	18	5
95°	44	174	579	299	203	49
105°	159	241	978	1484	1385	169
115°	283	344	783	1562	1783	279
125°	394	441	712	1204	1420	349
135°	469	516	690	972	1102	363
145°	544	579	681	829	894	341
155°	615	632	681	748	770	283
165°	664	672	681	708	717	187
175°	690	690	686	695	695	66
180°	690	690	690	690	690	



TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	613.8	613.8	613.8	613.8	613.8	613.8	613.8	613.8	613.8	613.8	613.8
2.5°	613.8	613.8	617.8	619.8	623.7	625.7	629.7	633.7	645.4	647.4	651.4
5°	598.1	606.0	631.7	641.5	669.1	706.7	722.4	748.1	801.4	817.2	827.1
7.5°	574.4	592.1	655.4	671.1	740.2	838.9	880.4	935.6	1020.5	1061.9	1095.5
10°	536.8	574.4	686.9	724.4	836.9	986.9	1063.9	1140.9	1269.2	1326.5	1348.2
12.5°	495.4	556.7	720.5	771.8	933.7	1152.8	1245.5	1330.4	1476.5	1553.5	1565.3
15°	448.1	531.0	752.1	827.1	1036.2	1290.9	1393.6	1498.2	1634.3	1689.6	1703.5
17.5°	406.7	511.2	781.7	860.6	1115.2	1415.3	1519.9	1606.7	1717.3	1754.8	1764.6
20°	355.3	479.7	801.4	904.1	1198.2	1506.1	1606.7	1673.9	1748.9	1772.6	1776.5
22.5°	317.8	446.1	813.2	919.8	1253.4	1561.3	1646.2	1699.5	1750.9	1758.7	1760.7
25°	286.3	408.6	811.2	937.6	1300.8	1594.9	1660.0	1699.5	1729.2	1733.0	1733.0
27.5°	256.6	367.1	803.4	941.5	1336.3	1602.8	1654.1	1681.7	1695.6	1703.5	1703.5
30°	231.0	327.7	783.7	933.7	1352.1	1594.9	1636.3	1650.2	1664.0	1675.8	1681.7
32.5°	211.3	290.1	754.0	917.8	1354.1	1575.2	1604.8	1612.6	1632.3	1660.0	1669.9
35°	193.4	252.7	720.5	896.1	1342.2	1543.6	1563.3	1571.2	1610.6	1652.2	1665.9
37.5°	175.7	225.0	677.1	858.7	1324.5	1506.1	1519.9	1533.7	1594.9	1644.2	1660.0
40°	157.9	201.3	625.7	817.2	1296.8	1460.6	1472.5	1494.2	1575.2	1632.3	1648.2
42.5°	144.1	181.6	570.4	773.8	1261.3	1409.3	1427.1	1458.6	1551.5	1612.6	1630.5
45°	132.3	161.8	511.2	714.5	1215.9	1356.1	1381.8	1425.2	1523.8	1583.0	1598.9
47.5°	120.4	148.0	450.1	653.4	1166.5	1302.8	1336.3	1385.6	1486.3	1543.6	1557.3
50°	110.6	134.3	388.8	588.2	1113.2	1245.5	1285.0	1336.3	1438.9	1492.2	1510.0
52.5°	102.7	122.4	331.6	523.1	1052.1	1186.3	1231.7	1285.0	1381.8	1433.0	1444.9
55°	94.7	112.5	282.3	454.0	988.9	1123.1	1172.5	1223.8	1318.5	1361.9	1369.9
57.5°	90.8	104.6	240.8	388.8	921.8	1052.1	1107.4	1154.8	1243.5	1277.1	1285.0
60°	84.9	98.7	209.3	333.6	848.8	984.9	1032.4	1079.7	1154.8	1182.4	1188.2
62.5°	79.0	94.7	185.6	280.3	773.8	906.0	953.4	996.8	1059.9	1079.7	1087.6
65°	75.0	90.8	167.8	240.8	696.8	823.1	870.5	908.0	959.3	979.1	983.0
67.5°	71.0	86.9	154.0	207.3	619.8	740.2	775.7	811.2	850.8	870.5	872.5
70°	65.1	82.9	142.1	183.6	540.8	645.4	675.1	712.5	744.1	754.0	759.9
72.5°	61.2	77.0	134.3	165.8	460.0	554.7	582.3	604.0	631.7	641.5	641.5
75°	55.3	69.1	126.3	148.0	377.0	454.0	477.7	499.4	521.1	525.1	519.1
77.5°	49.3	61.2	108.6	124.4	294.1	359.3	379.0	390.8	408.6	412.5	414.5
80°	41.4	53.3	84.9	96.7	213.1	264.5	278.3	288.1	304.0	304.0	308.0
82.5°	31.6	41.4	61.2	69.1	144.1	181.6	193.4	199.4	209.3	209.3	209.3
85°	19.7	25.7	39.4	45.4	86.9	110.6	118.4	120.4	128.3	130.3	130.3
87.5°	9.9	13.8	25.7	27.6	45.4	57.3	57.3	61.2	61.2	59.3	57.3
90°	4.6	8.3	12.1	12.9	20.3	30.2	35.2	31.3	23.5	17.6	17.6
92.5°	18.5	50.0	81.5	89.3	125.6	174.0	198.2	173.7	124.7	87.9	84.5
95°	44.4	102.1	159.7	174.1	309.2	489.3	579.4	517.0	392.2	298.7	288.1
97.5°	76.9	127.7	178.5	191.2	416.5	716.8	867.0	827.6	748.8	689.6	669.4
100°	101.9	148.0	194.1	205.7	455.6	788.8	955.5	958.4	964.1	968.4	944.4
102.5°	123.2	166.2	209.3	220.0	473.5	811.4	980.5	1030.7	1131.2	1206.5	1185.8
105°	159.4	195.8	232.3	241.3	486.7	814.0	977.7	1090.2	1315.4	1484.3	1473.3
107.5°	196.4	230.4	264.3	272.8	489.2	777.8	922.1	1079.2	1393.3	1628.9	1631.5
110°	221.4	252.1	282.7	290.3	485.5	745.7	875.8	1051.4	1402.6	1665.9	1677.5



TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	245.9	275.1	304.4	311.6	485.6	717.6	833.7	1013.3	1372.7	1642.2	1659.9
115°	283.0	310.0	336.8	343.6	490.1	685.4	783.2	956.3	1302.5	1562.1	1586.6
117.5°	319.5	344.0	368.5	374.7	499.3	665.3	748.4	904.7	1217.1	1451.5	1478.7
120°	340.8	363.9	386.9	392.7	506.7	658.6	734.6	877.3	1162.7	1376.9	1403.4
122.5°	361.7	385.0	408.3	414.0	517.3	655.1	723.9	852.4	1109.4	1302.3	1328.4
125°	393.6	414.8	436.0	441.3	531.7	652.1	712.3	821.5	1039.9	1203.7	1227.7
127.5°	419.6	441.0	462.3	467.7	546.0	650.4	702.6	796.3	983.8	1124.5	1144.8
130°	433.5	456.6	479.6	485.4	556.6	651.5	698.9	782.4	949.3	1074.5	1093.2
132.5°	447.8	470.9	493.9	499.7	565.0	652.1	695.6	770.3	919.8	1031.9	1048.6
135°	469.1	490.1	511.1	516.4	574.3	651.5	690.0	752.6	877.8	971.6	986.0
137.5°	490.9	511.6	532.5	537.6	588.1	655.5	689.1	742.0	847.8	927.2	939.0
140°	509.0	528.1	547.3	552.1	596.7	656.2	685.8	731.6	823.0	891.5	902.6
142.5°	522.9	540.6	558.4	562.7	603.8	658.5	685.8	726.0	806.3	866.5	876.1
145°	544.2	559.7	575.0	578.9	613.0	658.6	681.3	714.1	779.8	829.0	836.1
147.5°	565.4	580.5	595.5	599.3	626.6	663.0	681.3	707.1	758.8	797.5	803.5
150°	579.4	592.9	606.6	610.0	633.8	665.4	681.3	703.1	746.7	779.5	784.4
152.5°	593.7	604.1	614.3	616.9	638.3	666.9	681.3	699.9	737.1	765.1	768.8
155°	615.0	622.6	630.3	632.2	648.5	670.3	681.3	696.1	725.8	748.0	750.4
157.5°	630.8	638.2	645.6	647.5	658.8	673.8	681.3	692.8	715.8	733.2	734.8
160°	641.4	647.2	653.0	654.4	663.3	675.3	681.3	691.1	710.8	725.7	726.7
162.5°	652.1	656.5	660.7	661.8	668.3	677.0	681.3	689.6	706.3	718.8	719.7
165°	663.6	667.6	671.5	672.5	675.4	679.3	681.3	687.2	699.2	708.2	709.2
167.5°	674.3	676.2	678.0	678.5	681.0	684.3	685.8	689.7	697.6	703.5	703.9
170°	681.3	683.2	684.9	685.4	685.5	685.7	685.8	689.7	697.6	703.5	703.5
172.5°	684.9	685.3	685.7	685.8	685.8	685.8	685.8	688.9	695.1	699.8	699.4
175°	690.0	690.0	690.0	690.0	688.6	686.7	685.8	687.8	691.7	694.7	694.7
177.5°	690.0	690.0	690.0	690.0	688.9	687.5	686.8	688.4	691.5	693.8	693.4
180°	690.0	690.0	690.0	690.0	690.0	690.0	690.0	690.0	690.0	690.0	690.0



TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	613.8	613.8
2.5°	655.4	651.4
5°	842.8	846.8
7.5°	1134.9	1133.0
10°	1411.3	1429.1
12.5°	1612.6	1616.6
15°	1735.0	1742.9
17.5°	1782.4	1784.3
20°	1784.3	1780.4
22.5°	1762.6	1758.7
25°	1737.0	1735.0
27.5°	1713.3	1715.3
30°	1703.5	1709.3
32.5°	1703.5	1713.3
35°	1707.4	1717.3
37.5°	1705.5	1717.3
40°	1697.5	1711.3
42.5°	1675.8	1685.7
45°	1642.3	1654.1
47.5°	1598.9	1606.7
50°	1543.6	1551.5
52.5°	1474.5	1476.5
55°	1391.6	1399.5
57.5°	1302.8	1304.8
60°	1204.1	1209.9
62.5°	1099.5	1099.5
65°	988.9	992.8
67.5°	874.4	884.2
70°	758.0	759.9
72.5°	643.5	643.5
75°	525.1	527.0
77.5°	412.5	412.5
80°	306.0	308.0
82.5°	211.3	215.1
85°	132.3	132.3
87.5°	61.2	55.3
90°	17.6	17.6
92.5°	70.4	56.5
95°	245.7	203.3
97.5°	588.7	508.1
100°	848.2	752.1
102.5°	1103.6	1021.2
105°	1429.0	1384.7
107.5°	1642.2	1652.9
110°	1723.5	1769.6





TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1730.7	1801.6
115°	1684.8	1783.0
117.5°	1587.5	1696.4
120°	1509.1	1614.9
122.5°	1432.7	1537.1
125°	1323.9	1420.0
127.5°	1225.9	1307.0
130°	1168.1	1243.0
132.5°	1115.7	1182.8
135°	1043.9	1101.8
137.5°	986.3	1033.7
140°	946.9	991.1
142.5°	914.1	952.2
145°	865.0	893.8
147.5°	827.3	851.2
150°	803.7	823.0
152.5°	783.4	798.0
155°	760.0	769.7
157.5°	741.6	748.4
160°	730.6	734.6
162.5°	723.4	727.1
165°	713.0	716.9
167.5°	705.6	707.2
170°	703.5	703.5
172.5°	698.0	696.5
175°	694.7	694.7
177.5°	691.7	690.0
180°	690.0	690.0



TEST NUMBER: P937287

CATALOG NUMBER: SQ4-FB-075U-100D-B2750-1D-UNV-STD-W-6-2700K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.77	6.69	6.71	7.65	8.89	18.94	19.85	19.87	20.81	22.06
	3H	6.48	7.31	7.43	8.27	9.54	20.78	21.60	21.72	22.57	23.84
	4H	6.78	7.56	7.75	8.54	9.81	21.42	22.20	22.38	23.17	24.45
	6H	7.04	7.76	8.01	8.73	10.03	21.85	22.57	22.82	23.55	24.84
	8H	7.11	7.79	8.09	8.79	10.08	21.97	22.66	22.95	23.65	24.94
	12H	7.13	7.78	8.11	8.77	10.08	22.04	22.69	23.02	23.68	24.99
4H	2H	12.99	13.77	13.95	14.74	16.02	19.22	20.00	20.19	20.97	22.25
	3H	14.56	15.21	15.54	16.22	17.51	21.27	21.92	22.24	22.92	24.21
	4H	14.66	15.26	15.64	16.25	17.57	22.03	22.63	23.02	23.62	24.94
	6H	14.67	15.19	15.67	16.21	17.52	22.57	23.09	23.57	24.10	25.42
	8H	14.65	15.13	15.65	16.14	17.47	22.73	23.21	23.73	24.23	25.55
	12H	14.61	15.05	15.63	16.07	17.41	22.82	23.26	23.84	24.29	25.62
8H	4H	16.10	16.59	17.10	17.60	18.93	22.10	22.58	23.10	23.59	24.92
	6H	16.35	16.75	17.37	17.80	19.13	22.72	23.12	23.75	24.18	25.50
	8H	16.37	16.72	17.40	17.76	19.11	22.94	23.30	23.98	24.34	25.68
	12H	16.34	16.65	17.38	17.68	19.07	23.09	23.40	24.13	24.43	25.82
12H	4H	16.25	16.69	17.27	17.71	19.05	22.05	22.49	23.07	23.52	24.85
	6H	16.61	16.96	17.64	18.00	19.34	22.71	23.06	23.74	24.10	25.45
	8H	16.68	16.99	17.72	18.02	19.41	22.94	23.25	23.98	24.28	25.67