

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938592

Luminaire Tested: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938592  
REPORT IS A COMBINATION OF REPORTS P933648 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20118.2 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 166.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938592  
CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39	33
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32	27
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23	19
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19	16
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17	14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15	12
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4864	4864	4864
5°	4752	5622	6538
10°	4310	8195	10840
15°	3663	10706	13088
20°	2982	12408	13339
25°	2488	12984	13068
30°	2098	13066	13044
35°	1855	12849	13380
40°	1617	12567	13730
45°	1464	12360	13783
50°	1342	12175	13555
55°	1286	11903	12954
60°	1316	11379	12005
65°	1370	10585	10702
70°	1460	9231	9041
75°	1617	7527	7055
80°	1766	5220	4754
85°	1570	2770	2434

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13783 cd/sqm



TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.6	0.7
10°-20°	601.1	3.0
20°-30°	1051.3	5.2
30°-40°	1353.4	6.7
40°-50°	1511.7	7.5
50°-60°	1447.8	7.2
60°-70°	1147.4	5.7
70°-80°	674.7	3.4
80°-90°	194.5	1.0
90°-100°	902.4	4.5
100°-110°	2372.4	11.8
110°-120°	2459.9	12.2
120°-130°	1973.1	9.8
130°-140°	1548.2	7.7
140°-150°	1188.3	5.9
150°-160°	855.8	4.3
160°-170°	523.6	2.6
170°-180°	176.9	0.9
0°-30°	1788.0	8.9
0°-40°	3141.4	15.6
0°-60°	6100.9	30.3
0°-90°	8117.5	40.3
90°-120°	5734.7	28.5
90°-150°	10444.4	51.9
90°-180°	12001.0	59.7
0°-180°	20118.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1021	1096	1234	1396	1446	94
15°	765	1412	2380	2886	2977	213
25°	489	1601	2835	2960	2963	225
35°	330	1530	2670	2822	2933	206
45°	226	1220	2360	2704	2825	175
55°	162	775	2002	2326	2390	147
65°	128	411	1487	1672	1696	127
75°	94	253	816	897	900	99
85°	34	78	202	222	226	36
90°	12	35	94	47	47	13
95°	119	467	1554	801	545	132
105°	427	647	2623	3982	3715	453
115°	759	922	2101	4191	4783	750
125°	1056	1184	1911	3229	3809	938
135°	1258	1385	1851	2607	2956	974
145°	1460	1553	1828	2224	2398	915
155°	1650	1696	1828	2006	2065	758
165°	1780	1804	1828	1900	1923	502
175°	1851	1851	1840	1864	1864	176
180°	1851	1851	1851	1851	1851	



TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1048.4	1048.4	1055.2	1058.5	1065.2	1068.6	1075.4	1082.2	1102.4	1105.8	1112.4
5°	1021.4	1034.9	1078.8	1095.6	1142.8	1206.9	1233.8	1277.7	1368.6	1395.6	1412.4
7.5°	981.0	1011.3	1119.2	1146.2	1264.1	1432.7	1503.5	1597.9	1742.8	1813.6	1871.0
10°	916.9	981.0	1173.1	1237.1	1429.4	1685.5	1817.0	1948.5	2167.6	2265.4	2302.5
12.5°	846.1	950.7	1230.5	1318.1	1594.5	1968.7	2127.2	2272.1	2521.6	2653.0	2673.3
15°	765.2	906.9	1284.3	1412.4	1769.8	2204.6	2379.9	2558.6	2791.3	2885.6	2909.2
17.5°	694.4	873.1	1334.9	1469.8	1904.7	2417.1	2595.7	2744.1	2932.8	2996.9	3013.7
20°	606.8	819.2	1368.6	1543.9	2046.3	2572.2	2744.1	2858.6	2986.8	3027.2	3033.9
22.5°	542.7	761.8	1388.9	1570.9	2140.6	2666.5	2811.5	2902.4	2990.1	3003.6	3007.0
25°	488.8	697.8	1385.5	1601.3	2221.6	2723.9	2835.1	2902.4	2953.0	2959.8	2959.8
27.5°	438.2	627.0	1372.0	1608.0	2282.2	2737.3	2825.0	2872.2	2895.8	2909.2	2909.2
30°	394.4	559.6	1338.3	1594.5	2309.2	2723.9	2794.6	2818.2	2841.8	2862.0	2872.2
32.5°	360.8	495.5	1287.7	1567.5	2312.5	2690.1	2740.7	2754.1	2787.9	2835.1	2851.9
35°	330.4	431.5	1230.5	1530.5	2292.3	2636.2	2669.9	2683.3	2750.8	2821.6	2845.2
37.5°	300.0	384.3	1156.3	1466.4	2262.0	2572.2	2595.7	2619.3	2723.9	2808.1	2835.1
40°	269.7	343.8	1068.6	1395.6	2214.8	2494.6	2514.8	2551.9	2690.1	2787.9	2814.8
42.5°	246.1	310.2	974.3	1321.5	2154.1	2406.9	2437.3	2491.2	2649.7	2754.1	2784.5
45°	225.9	276.4	873.1	1220.3	2076.6	2315.9	2359.7	2433.9	2602.4	2703.6	2730.5
47.5°	205.7	252.8	768.6	1115.8	1992.3	2224.9	2282.2	2366.5	2538.4	2636.2	2659.8
50°	188.7	229.3	664.1	1004.6	1901.3	2127.2	2194.6	2282.2	2457.5	2548.6	2578.8
52.5°	175.3	209.0	566.3	893.3	1796.8	2026.0	2103.6	2194.6	2359.7	2447.4	2467.6
55°	161.8	192.1	482.1	775.4	1688.9	1918.1	2002.5	2090.1	2251.9	2326.1	2339.5
57.5°	155.1	178.7	411.2	664.1	1574.3	1796.8	1891.2	1972.1	2123.8	2181.0	2194.6
60°	144.9	168.5	357.4	569.7	1449.6	1682.1	1763.0	1844.0	1972.1	2019.3	2029.4
62.5°	134.9	161.8	316.9	478.7	1321.5	1547.3	1628.3	1702.4	1810.2	1844.0	1857.4
65°	128.1	155.1	286.5	411.2	1190.0	1405.8	1486.6	1550.7	1638.3	1672.1	1678.8
67.5°	121.3	148.3	262.9	354.0	1058.5	1264.1	1324.8	1385.5	1453.0	1486.6	1490.0
70°	111.3	141.6	242.7	313.5	923.7	1102.4	1152.9	1216.9	1270.9	1287.7	1297.9
72.5°	104.5	131.5	229.3	283.2	785.4	947.3	994.5	1031.6	1078.8	1095.6	1095.6
75°	94.4	118.0	215.7	252.8	643.9	775.4	815.8	852.9	889.9	896.7	886.6
77.5°	84.3	104.5	185.5	212.3	502.3	613.5	647.2	667.5	697.8	704.6	708.0
80°	70.8	91.0	144.9	165.1	364.0	451.7	475.3	492.2	519.1	519.1	525.9
82.5°	54.0	70.8	104.5	118.0	246.1	310.2	330.4	340.4	357.4	357.4	357.4
85°	33.7	43.8	67.4	77.5	148.3	188.7	202.3	205.7	219.1	222.5	222.5
87.5°	16.8	23.6	43.8	47.2	77.5	97.8	97.8	104.5	104.5	101.1	97.8
90°	12.4	22.4	32.3	34.8	54.7	81.2	94.4	84.0	62.9	47.2	47.2
92.5°	49.7	134.2	218.7	239.8	337.1	466.9	531.8	466.0	334.7	236.1	226.7
95°	119.3	273.9	428.5	467.1	829.5	1312.6	1554.3	1386.9	1052.4	801.4	772.9
97.5°	206.3	342.6	479.1	513.1	1117.4	1923.1	2325.9	2220.1	2008.6	1850.0	1795.9
100°	273.3	397.0	520.7	551.7	1222.2	2116.1	2563.1	2570.9	2586.3	2597.9	2533.4
102.5°	330.5	445.9	561.2	590.1	1270.2	2176.9	2630.2	2765.0	3034.4	3236.5	3181.3
105°	427.4	525.1	622.9	647.3	1305.8	2183.7	2622.8	2924.9	3528.9	3982.0	3952.3
107.5°	526.8	617.9	709.0	731.8	1312.4	2086.6	2473.7	2895.0	3737.7	4369.7	4376.8
110°	593.9	676.2	758.5	779.0	1302.5	2000.5	2349.5	2820.5	3762.5	4469.1	4499.9



TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	659.8	738.1	816.5	836.1	1302.9	1925.2	2236.3	2718.4	3682.5	4405.6	4453.1
115°	759.2	831.5	903.8	921.9	1314.9	1838.9	2101.0	2565.3	3494.1	4190.7	4256.5
117.5°	857.3	923.0	988.7	1005.2	1339.3	1784.9	2007.7	2426.9	3265.1	3893.8	3966.8
120°	914.4	976.3	1038.1	1053.6	1359.2	1766.7	1970.5	2353.4	3119.4	3693.8	3764.7
122.5°	970.3	1032.8	1095.1	1110.7	1387.8	1757.2	1941.9	2286.7	2976.4	3493.7	3563.7
125°	1056.1	1112.9	1169.8	1184.0	1426.3	1749.3	1910.8	2203.7	2789.6	3229.0	3293.5
127.5°	1125.7	1183.0	1240.5	1254.9	1464.8	1744.8	1884.7	2136.2	2639.3	3016.6	3071.0
130°	1162.9	1224.8	1286.6	1302.1	1493.0	1747.5	1874.8	2098.7	2546.6	2882.4	2932.7
132.5°	1201.5	1263.3	1325.2	1340.6	1515.8	1749.4	1866.1	2066.5	2467.4	2768.1	2813.1
135°	1258.5	1314.9	1371.3	1385.3	1540.6	1747.7	1851.2	2019.1	2354.8	2606.6	2645.4
137.5°	1317.0	1372.8	1428.5	1442.4	1577.9	1758.4	1848.8	1990.7	2274.5	2487.3	2519.1
140°	1365.4	1416.8	1468.1	1481.0	1600.7	1760.2	1840.0	1962.6	2207.8	2391.7	2421.4
142.5°	1402.7	1450.2	1497.7	1509.5	1619.7	1766.6	1840.0	1947.7	2163.0	2324.6	2350.1
145°	1459.8	1501.3	1542.7	1553.1	1644.6	1766.6	1827.6	1915.6	2091.8	2224.0	2243.3
147.5°	1517.0	1557.3	1597.7	1607.7	1681.0	1778.8	1827.6	1896.9	2035.4	2139.4	2155.4
150°	1554.3	1590.7	1627.2	1636.2	1700.0	1785.0	1827.6	1886.1	2003.2	2091.0	2104.0
152.5°	1592.8	1620.4	1648.1	1655.0	1712.5	1789.2	1827.6	1877.6	1977.5	2052.5	2062.2
155°	1650.0	1670.4	1690.8	1695.9	1739.8	1798.3	1827.6	1867.3	1946.9	2006.5	2013.0
157.5°	1692.2	1712.1	1731.9	1736.9	1767.1	1807.4	1827.6	1858.5	1920.4	1966.8	1971.4
160°	1720.8	1736.2	1751.7	1755.5	1779.6	1811.5	1827.6	1854.1	1907.1	1946.9	1949.5
162.5°	1749.4	1760.9	1772.6	1775.5	1792.8	1816.0	1827.6	1850.0	1894.7	1928.3	1930.7
165°	1780.4	1790.8	1801.4	1804.0	1811.8	1822.3	1827.6	1843.6	1875.7	1899.7	1902.3
167.5°	1808.9	1813.9	1818.9	1820.2	1826.8	1835.6	1840.0	1850.5	1871.5	1887.2	1888.3
170°	1827.6	1832.5	1837.5	1838.8	1839.2	1839.7	1840.0	1850.5	1871.5	1887.2	1887.2
172.5°	1837.5	1838.6	1839.7	1840.0	1840.0	1840.0	1840.0	1848.3	1864.8	1877.3	1876.3
175°	1851.2	1851.2	1851.2	1851.2	1847.5	1842.5	1840.0	1845.3	1855.7	1863.6	1863.6
177.5°	1851.2	1851.2	1851.2	1851.2	1848.3	1844.4	1842.5	1846.7	1855.0	1861.1	1860.0
180°	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2



TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	1048.4	1048.4
2.5°	1119.2	1112.4
5°	1439.4	1446.2
7.5°	1938.3	1935.0
10°	2410.3	2440.7
12.5°	2754.1	2760.9
15°	2963.2	2976.6
17.5°	3044.1	3047.5
20°	3047.5	3040.7
22.5°	3010.4	3003.6
25°	2966.6	2963.2
27.5°	2926.0	2929.4
30°	2909.2	2919.4
32.5°	2909.2	2926.0
35°	2916.0	2932.8
37.5°	2912.6	2932.8
40°	2899.2	2922.8
42.5°	2862.0	2878.9
45°	2804.7	2825.0
47.5°	2730.5	2744.1
50°	2636.2	2649.7
52.5°	2518.2	2521.6
55°	2376.6	2390.1
57.5°	2224.9	2228.3
60°	2056.3	2066.5
62.5°	1877.7	1877.7
65°	1688.9	1695.7
67.5°	1493.4	1510.2
70°	1294.5	1297.9
72.5°	1099.0	1099.0
75°	896.7	900.1
77.5°	704.6	704.6
80°	522.5	525.9
82.5°	360.8	367.4
85°	225.9	225.9
87.5°	104.5	94.4
90°	47.2	47.2
92.5°	189.1	151.6
95°	659.2	545.4
97.5°	1579.4	1362.9
100°	2275.6	2017.7
102.5°	2960.4	2739.6
105°	3833.6	3714.9
107.5°	4405.5	4434.2
110°	4623.6	4747.3





TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	4643.1	4833.0
115°	4519.9	4783.3
117.5°	4258.9	4551.0
120°	4048.5	4332.3
122.5°	3843.7	4123.6
125°	3551.4	3809.3
127.5°	3288.6	3506.1
130°	3133.7	3334.7
132.5°	2993.1	3173.2
135°	2800.6	2955.7
137.5°	2646.1	2773.1
140°	2540.1	2658.8
142.5°	2452.3	2554.4
145°	2320.6	2397.9
147.5°	2219.5	2283.5
150°	2155.9	2207.8
152.5°	2101.5	2140.7
155°	2039.0	2064.9
157.5°	1989.5	2007.7
160°	1960.0	1970.5
162.5°	1940.6	1950.6
165°	1912.8	1923.3
167.5°	1892.8	1897.2
170°	1887.2	1887.2
172.5°	1872.5	1868.6
175°	1863.6	1863.6
177.5°	1855.5	1851.2
180°	1851.2	1851.2



TEST NUMBER: P938592  
 CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-STD-W-8-2700K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.55	6.36	6.58	7.40	8.80	18.73	19.54	19.76	20.58	21.98
	3H	6.25	6.98	7.29	8.03	9.45	20.56	21.29	21.60	22.34	23.76
	4H	6.55	7.24	7.60	8.29	9.71	21.21	21.90	22.26	22.95	24.37
	6H	6.79	7.43	7.85	8.49	9.92	21.63	22.27	22.70	23.33	24.77
	8H	6.86	7.47	7.93	8.54	9.97	21.75	22.36	22.82	23.43	24.87
	12H	6.88	7.45	7.95	8.52	9.98	21.82	22.40	22.89	23.46	24.92
4H	2H	12.76	13.45	13.82	14.50	15.93	19.00	19.69	20.05	20.74	22.16
	3H	14.32	14.90	15.39	15.98	17.42	21.04	21.61	22.10	22.69	24.13
	4H	14.41	14.94	15.49	16.01	17.47	21.80	22.33	22.87	23.40	24.86
	6H	14.42	14.88	15.50	15.97	17.43	22.34	22.79	23.42	23.89	25.34
	8H	14.40	14.82	15.48	15.91	17.38	22.50	22.93	23.58	24.01	25.48
	12H	14.35	14.74	15.45	15.84	17.31	22.59	22.98	23.69	24.08	25.55
8H	4H	15.85	16.28	16.94	17.37	18.84	21.86	22.28	22.94	23.37	24.84
	6H	16.09	16.45	17.20	17.57	19.04	22.48	22.84	23.59	23.97	25.43
	8H	16.11	16.42	17.22	17.53	19.02	22.70	23.01	23.81	24.12	25.61
	12H	16.08	16.35	17.19	17.46	18.98	22.85	23.12	23.96	24.22	25.75
12H	4H	15.99	16.38	17.09	17.48	18.96	21.81	22.19	22.91	23.29	24.77
	6H	16.35	16.66	17.46	17.77	19.26	22.47	22.78	23.58	23.89	25.37
	8H	16.42	16.69	17.53	17.80	19.32	22.69	22.97	23.81	24.07	25.60