

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936482

Luminaire Tested: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936482
REPORT IS A COMBINATION OF REPORTS P933439 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4130.4 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 38.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936482
CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63				63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51				51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42				42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35				35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30				30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26				26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22				22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20				20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20	17				17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16				16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3798	3798	3798
5°	3707	4387	5105
10°	3358	6390	8463
15°	2850	8342	10219
20°	2317	9659	10414
25°	1931	10100	10204
30°	1627	10156	10184
35°	1436	9980	10448
40°	1249	9753	10720
45°	1128	9583	10762
50°	1033	9430	10583
55°	986	9209	10115
60°	1007	8792	9374
65°	1042	8165	8355
70°	1102	7106	7059
75°	1210	5779	5509
80°	1292	3994	3712
85°	1085	2109	1898

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10762 cd/sqm



TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	1.3
10°-20°	234.6	5.7
20°-30°	410.4	9.9
30°-40°	528.3	12.8
40°-50°	590.2	14.3
50°-60°	565.2	13.7
60°-70°	448.0	10.8
70°-80°	263.4	6.4
80°-90°	73.7	1.8
90°-100°	72.5	1.8
100°-110°	190.5	4.6
110°-120°	197.5	4.8
120°-130°	158.4	3.8
130°-140°	124.3	3.0
140°-150°	95.4	2.3
150°-160°	68.7	1.7
160°-170°	42.0	1.0
170°-180°	14.2	0.3
0°-30°	698.0	16.9
0°-40°	1226.4	29.7
0°-60°	2381.8	57.7
0°-90°	3166.9	76.7
90°-120°	460.5	11.1
90°-150°	838.6	20.3
90°-180°	964.0	23.3
0°-180°	4130.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	399	428	482	545	565	37
15°	299	551	929	1127	1162	83
25°	191	625	1107	1156	1157	88
35°	129	598	1042	1102	1145	81
45°	88	476	921	1056	1103	68
55°	63	303	782	908	933	58
65°	50	161	580	653	662	50
75°	37	99	318	350	351	39
85°	13	30	79	87	88	14
90°	1	3	8	4	4	2
95°	10	38	125	64	44	11
105°	34	52	211	320	298	36
115°	61	74	169	336	384	60
125°	85	95	153	259	306	75
135°	101	111	149	209	237	78
145°	117	125	147	179	192	73
155°	132	136	147	161	166	61
165°	143	145	147	152	154	40
175°	149	149	148	150	150	14
180°	149	149	149	149	149	



TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	409.3	409.3	411.9	413.2	415.8	417.2	419.8	422.4	430.4	431.7	434.3
5°	398.8	404.1	421.1	427.7	446.1	471.1	481.7	498.8	534.4	544.8	551.4
7.5°	383.0	394.8	436.9	447.5	493.5	559.4	586.9	623.8	680.4	708.1	730.4
10°	358.0	383.0	458.0	483.0	558.0	658.1	709.4	760.6	846.2	884.3	898.9
12.5°	330.4	371.1	480.4	514.5	622.5	768.6	830.5	887.0	984.4	1035.7	1043.6
15°	298.7	354.0	501.4	551.4	690.9	860.7	929.2	998.9	1089.7	1126.6	1135.7
17.5°	271.1	340.8	521.1	573.8	743.6	943.6	1013.3	1071.3	1145.0	1170.0	1176.6
20°	236.8	319.8	534.4	602.8	798.9	1004.2	1071.3	1116.0	1166.0	1181.9	1184.4
22.5°	211.8	297.4	542.2	613.2	835.6	1041.0	1097.6	1133.1	1167.3	1172.6	1173.9
25°	190.8	272.4	540.9	625.1	867.3	1063.3	1106.8	1133.1	1152.9	1155.5	1155.5
27.5°	171.1	244.8	535.6	627.8	890.9	1068.6	1102.9	1121.3	1130.5	1135.7	1135.7
30°	154.0	218.4	522.5	622.5	901.5	1063.3	1091.0	1100.2	1109.4	1117.3	1121.3
32.5°	140.8	193.4	502.8	611.9	902.8	1050.2	1069.9	1075.2	1088.3	1106.8	1113.4
35°	129.0	168.4	480.4	597.5	894.9	1029.2	1042.3	1047.6	1073.9	1101.6	1110.7
37.5°	117.1	150.0	451.4	572.5	883.1	1004.2	1013.3	1022.6	1063.3	1096.3	1106.8
40°	105.3	134.3	417.2	544.8	864.6	973.9	981.8	996.3	1050.2	1088.3	1098.9
42.5°	96.1	121.1	380.4	515.9	840.9	939.6	951.5	972.6	1034.4	1075.2	1087.0
45°	88.1	107.9	340.8	476.4	810.6	904.2	921.2	950.2	1016.0	1055.5	1066.0
47.5°	80.3	98.7	300.1	435.7	777.8	868.6	890.9	923.9	991.0	1029.2	1038.3
50°	73.7	89.5	259.3	392.2	742.2	830.5	856.8	890.9	959.4	994.9	1006.8
52.5°	68.4	81.6	221.1	348.8	701.5	790.9	821.2	856.8	921.2	955.5	963.3
55°	63.1	75.0	188.2	302.7	659.4	748.8	781.8	815.9	879.2	908.1	913.3
57.5°	60.6	69.7	160.6	259.3	614.6	701.5	738.3	769.9	829.1	851.5	856.8
60°	56.6	65.8	139.5	222.4	565.9	656.7	688.3	719.9	769.9	788.3	792.2
62.5°	52.7	63.1	123.7	186.8	515.9	604.1	635.6	664.6	706.8	719.9	725.2
65°	50.0	60.6	111.9	160.6	464.5	548.8	580.4	605.4	639.6	652.8	655.4
67.5°	47.4	57.9	102.7	138.1	413.2	493.5	517.2	540.9	567.2	580.4	581.7
70°	43.4	55.3	94.7	122.4	360.6	430.4	450.1	475.1	496.1	502.8	506.7
72.5°	40.8	51.3	89.5	110.6	306.7	369.8	388.2	402.7	421.1	427.7	427.7
75°	36.9	46.0	84.3	98.7	251.4	302.7	318.5	333.0	347.4	350.1	346.1
77.5°	32.9	40.8	72.4	82.9	196.1	239.5	252.7	260.6	272.4	275.1	276.4
80°	27.6	35.6	56.6	64.4	142.1	176.4	185.6	192.1	202.7	202.7	205.3
82.5°	21.0	27.6	40.8	46.0	96.1	121.1	129.0	133.0	139.5	139.5	139.5
85°	13.1	17.1	26.3	30.3	57.9	73.7	79.0	80.3	85.6	86.9	86.9
87.5°	6.6	9.2	17.1	18.4	30.3	38.1	38.1	40.8	40.8	39.4	38.1
90°	1.0	1.8	2.6	2.8	4.4	6.5	7.6	6.8	5.1	3.8	3.8
92.5°	4.0	10.8	17.5	19.2	27.1	37.5	42.7	37.4	26.9	18.9	18.1
95°	9.6	22.0	34.5	37.5	66.6	105.4	124.8	111.4	84.5	64.3	62.1
97.5°	16.5	27.5	38.4	41.2	89.7	154.4	186.8	178.3	161.3	148.5	144.1
100°	21.9	31.9	41.8	44.3	98.1	169.9	205.8	206.4	207.7	208.6	203.4
102.5°	26.5	35.8	45.1	47.4	102.0	174.8	211.2	222.0	243.6	259.9	255.4
105°	34.4	42.2	50.0	52.0	104.9	175.3	210.6	234.9	283.4	319.7	317.3
107.5°	42.3	49.6	57.0	58.8	105.4	167.5	198.6	232.5	300.1	350.9	351.5
110°	47.7	54.3	60.9	62.5	104.6	160.7	188.6	226.5	302.1	358.9	361.3



TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	53.0	59.3	65.5	67.1	104.6	154.6	179.6	218.3	295.7	353.8	357.6
115°	61.0	66.7	72.5	74.0	105.6	147.7	168.7	206.0	280.6	336.4	341.7
117.5°	68.8	74.1	79.4	80.7	107.6	143.3	161.3	194.9	262.1	312.6	318.5
120°	73.4	78.4	83.4	84.6	109.1	141.8	158.2	188.9	250.5	296.6	302.3
122.5°	77.9	82.9	87.8	89.1	111.4	141.0	155.9	183.6	238.9	280.5	286.1
125°	84.8	89.3	93.9	95.1	114.5	140.4	153.4	176.9	224.0	259.3	264.4
127.5°	90.3	95.0	99.6	100.8	117.6	140.0	151.3	171.5	211.9	242.2	246.6
130°	93.3	98.3	103.3	104.6	119.9	140.3	150.5	168.5	204.5	231.5	235.5
132.5°	96.5	101.5	106.5	107.7	121.7	140.4	149.8	165.9	198.1	222.3	225.9
135°	101.1	105.6	110.2	111.3	123.7	140.3	148.6	162.0	189.0	209.3	212.3
137.5°	105.8	110.3	114.7	115.8	126.7	141.1	148.4	159.8	182.6	199.7	202.3
140°	109.7	113.7	117.9	118.9	128.5	141.3	147.7	157.6	177.3	192.0	194.4
142.5°	112.6	116.4	120.2	121.2	130.1	141.8	147.7	156.4	173.7	186.7	188.7
145°	117.2	120.5	123.9	124.7	132.1	141.8	146.7	153.8	167.9	178.6	180.2
147.5°	121.8	125.0	128.3	129.1	135.0	142.8	146.7	152.3	163.4	171.8	173.1
150°	124.8	127.7	130.7	131.4	136.5	143.3	146.7	151.4	160.9	167.9	168.9
152.5°	127.9	130.1	132.3	132.9	137.4	143.6	146.7	150.7	158.8	164.8	165.6
155°	132.5	134.1	135.8	136.2	139.6	144.3	146.7	149.9	156.4	161.2	161.7
157.5°	135.9	137.4	139.0	139.4	141.8	145.1	146.7	149.2	154.2	157.9	158.3
160°	138.1	139.3	140.6	140.9	142.8	145.4	146.7	148.8	153.1	156.3	156.5
162.5°	140.4	141.3	142.3	142.5	143.9	145.8	146.7	148.5	152.1	154.8	155.0
165°	142.9	143.7	144.6	144.8	145.4	146.3	146.7	148.0	150.6	152.5	152.7
167.5°	145.2	145.6	146.0	146.1	146.6	147.3	147.7	148.5	150.2	151.5	151.6
170°	146.7	147.1	147.5	147.6	147.6	147.7	147.7	148.5	150.2	151.5	151.5
172.5°	147.5	147.6	147.7	147.7	147.7	147.7	147.7	148.4	149.7	150.7	150.6
175°	148.6	148.6	148.6	148.6	148.3	147.9	147.7	148.1	149.0	149.6	149.6
177.5°	148.6	148.6	148.6	148.6	148.4	148.1	147.9	148.2	148.9	149.4	149.3
180°	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6



TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	409.3	409.3
2.5°	436.9	434.3
5°	561.9	564.6
7.5°	756.8	755.4
10°	941.0	952.8
12.5°	1075.2	1077.9
15°	1156.9	1162.0
17.5°	1188.4	1189.7
20°	1189.7	1187.0
22.5°	1175.3	1172.6
25°	1158.1	1156.9
27.5°	1142.3	1143.6
30°	1135.7	1139.7
32.5°	1135.7	1142.3
35°	1138.4	1145.0
37.5°	1137.0	1145.0
40°	1131.9	1141.0
42.5°	1117.3	1123.9
45°	1095.0	1102.9
47.5°	1066.0	1071.3
50°	1029.2	1034.4
52.5°	983.1	984.4
55°	927.8	933.1
57.5°	868.6	869.9
60°	802.8	806.8
62.5°	733.1	733.1
65°	659.4	661.9
67.5°	583.1	589.6
70°	505.4	506.7
72.5°	429.1	429.1
75°	350.1	351.4
77.5°	275.1	275.1
80°	204.0	205.3
82.5°	140.8	143.4
85°	88.1	88.1
87.5°	40.8	36.9
90°	3.8	3.8
92.5°	15.1	12.2
95°	53.0	43.8
97.5°	126.8	109.5
100°	182.8	162.0
102.5°	237.6	219.9
105°	307.9	298.3
107.5°	353.8	356.1
110°	371.2	381.2



TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	372.8	388.0
115°	362.9	384.1
117.5°	341.9	365.4
120°	325.1	347.8
122.5°	308.6	331.1
125°	285.2	305.9
127.5°	264.0	281.5
130°	251.6	267.7
132.5°	240.3	254.8
135°	224.9	237.3
137.5°	212.4	222.7
140°	203.9	213.4
142.5°	196.9	205.1
145°	186.4	192.5
147.5°	178.2	183.4
150°	173.1	177.3
152.5°	168.7	171.9
155°	163.7	165.8
157.5°	159.8	161.3
160°	157.4	158.2
162.5°	155.8	156.6
165°	153.6	154.4
167.5°	151.9	152.3
170°	151.5	151.5
172.5°	150.3	150.0
175°	149.6	149.6
177.5°	149.0	148.6
180°	148.6	148.6



TEST NUMBER: P936482

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.76	8.99	8.44	9.70	10.53	20.90	22.13	21.58	22.84	23.66
	3H	8.49	9.61	9.19	10.32	11.18	22.75	23.86	23.44	24.58	25.44
	4H	8.81	9.86	9.52	10.59	11.46	23.40	24.45	24.11	25.18	26.05
	6H	9.08	10.05	9.80	10.79	11.68	23.84	24.81	24.56	25.55	26.44
	8H	9.16	10.09	9.89	10.84	11.73	23.96	24.89	24.70	25.65	26.54
	12H	9.19	10.08	9.93	10.83	11.74	24.04	24.93	24.78	25.68	26.59
4H	2H	14.99	16.05	15.71	16.77	17.64	21.22	22.27	21.93	23.00	23.87
	3H	16.60	17.48	17.33	18.24	19.13	23.28	24.17	24.01	24.93	25.82
	4H	16.71	17.51	17.45	18.28	19.20	24.05	24.86	24.80	25.62	26.54
	6H	16.74	17.44	17.50	18.23	19.16	24.60	25.30	25.37	26.09	27.02
	8H	16.73	17.38	17.50	18.17	19.11	24.77	25.42	25.54	26.21	27.15
	12H	16.70	17.30	17.49	18.10	19.05	24.87	25.46	25.66	26.27	27.22
8H	4H	18.17	18.83	18.94	19.61	20.56	24.15	24.80	24.91	25.59	26.53
	6H	18.43	18.98	19.23	19.81	20.75	24.78	25.33	25.58	26.15	27.10
	8H	18.46	18.94	19.27	19.77	20.73	25.00	25.49	25.81	26.31	27.27
	12H	18.44	18.87	19.26	19.69	20.70	25.15	25.58	25.97	26.40	27.41
12H	4H	18.33	18.93	19.12	19.73	20.68	24.12	24.71	24.91	25.52	26.46
	6H	18.69	19.18	19.50	20.01	20.96	24.77	25.26	25.58	26.08	27.04
	8H	18.78	19.21	19.59	20.03	21.04	25.01	25.44	25.82	26.26	27.27