

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936483

Luminaire Tested: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936483  
REPORT IS A COMBINATION OF REPORTS P933439 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4088.9 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 38.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936483  
CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63				63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51				51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42				42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35				35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30				30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26				26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22				22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20				20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20	17				17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16				16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3759	3759	3759
5°	3669	4342	5054
10°	3325	6325	8378
15°	2822	8258	10117
20°	2295	9562	10310
25°	1912	9998	10101
30°	1610	10055	10082
35°	1422	9879	10343
40°	1236	9654	10612
45°	1118	9487	10654
50°	1023	9335	10478
55°	976	9116	10013
60°	996	8704	9280
65°	1032	8082	8271
70°	1092	7035	6988
75°	1197	5721	5454
80°	1278	3953	3674
85°	1076	2087	1881

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10654 cd/sqm



TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.4	1.3
10°-20°	232.3	5.7
20°-30°	406.3	9.9
30°-40°	523.0	12.8
40°-50°	584.2	14.3
50°-60°	559.6	13.7
60°-70°	443.5	10.8
70°-80°	260.8	6.4
80°-90°	73.0	1.8
90°-100°	71.7	1.8
100°-110°	188.6	4.6
110°-120°	195.5	4.8
120°-130°	156.8	3.8
130°-140°	123.1	3.0
140°-150°	94.5	2.3
150°-160°	68.0	1.7
160°-170°	41.6	1.0
170°-180°	14.1	0.3
0°-30°	691.0	16.9
0°-40°	1214.1	29.7
0°-60°	2357.8	57.7
0°-90°	3135.1	76.7
90°-120°	455.8	11.1
90°-150°	830.2	20.3
90°-180°	954.0	23.3
0°-180°	4088.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	405	405	405	405	405	
5°	395	423	477	539	559	36
15°	296	546	920	1115	1150	82
25°	189	619	1096	1144	1145	87
35°	128	592	1032	1090	1134	80
45°	87	472	912	1045	1092	68
55°	62	300	774	899	924	57
65°	50	159	574	646	655	49
75°	36	98	315	347	348	38
85°	13	30	78	86	87	14
90°	1	3	8	4	4	2
95°	10	37	124	64	43	11
105°	34	52	208	316	295	36
115°	60	73	167	333	380	60
125°	84	94	152	257	303	74
135°	100	110	147	207	235	77
145°	116	123	145	177	191	73
155°	131	135	145	160	164	60
165°	142	143	145	151	153	40
175°	147	147	146	148	148	14
180°	147	147	147	147	147	



TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	405.1	405.1	405.1	405.1	405.1	405.1	405.1	405.1	405.1	405.1	405.1
2.5°	405.1	405.1	407.8	409.1	411.7	413.0	415.6	418.2	426.1	427.3	429.9
5°	394.8	400.0	416.9	423.4	441.6	466.4	476.8	493.8	529.0	539.3	545.8
7.5°	379.1	390.9	432.6	443.0	488.6	553.7	581.0	617.5	673.5	700.9	723.0
10°	354.4	379.1	453.4	478.1	552.4	651.5	702.2	753.0	837.7	875.5	889.9
12.5°	327.1	367.4	475.5	509.4	616.2	760.9	822.1	878.1	974.6	1025.3	1033.1
15°	295.7	350.4	496.4	545.8	684.0	852.1	919.8	988.9	1078.8	1115.3	1124.3
17.5°	268.4	337.4	515.9	568.0	736.1	934.1	1003.2	1060.5	1133.5	1158.3	1164.8
20°	234.5	316.6	529.0	596.7	790.9	994.1	1060.5	1104.8	1154.3	1170.0	1172.6
22.5°	209.7	294.4	536.8	607.1	827.3	1030.6	1086.6	1121.8	1155.6	1160.8	1162.1
25°	188.9	269.7	535.5	618.8	858.6	1052.7	1095.6	1121.8	1141.3	1143.9	1143.9
27.5°	169.4	242.4	530.3	621.5	882.0	1057.9	1091.8	1110.0	1119.1	1124.3	1124.3
30°	152.4	216.2	517.3	616.2	892.4	1052.7	1080.1	1089.1	1098.3	1106.1	1110.0
32.5°	139.4	191.5	497.7	605.8	893.7	1039.6	1059.2	1064.4	1077.4	1095.6	1102.2
35°	127.7	166.7	475.5	591.5	885.9	1018.8	1031.8	1037.1	1063.1	1090.5	1099.6
37.5°	116.0	148.5	446.9	566.8	874.2	994.1	1003.2	1012.3	1052.7	1085.3	1095.6
40°	104.2	132.9	413.0	539.3	855.9	964.1	971.9	986.3	1039.6	1077.4	1087.9
42.5°	95.1	119.9	376.6	510.7	832.5	930.2	941.9	962.8	1024.1	1064.4	1076.1
45°	87.3	106.8	337.4	471.6	802.5	895.1	912.0	940.6	1005.8	1044.9	1055.3
47.5°	79.5	97.7	297.1	431.3	770.0	859.9	882.0	914.6	981.1	1018.8	1027.9
50°	73.0	88.6	256.7	388.3	734.8	822.1	848.2	882.0	949.8	984.9	996.6
52.5°	67.7	80.8	218.9	345.3	694.4	783.0	813.0	848.2	912.0	945.9	953.7
55°	62.5	74.2	186.4	299.6	652.7	741.3	773.9	807.7	870.3	898.9	904.2
57.5°	59.9	69.0	158.9	256.7	608.5	694.4	730.9	762.2	820.7	842.9	848.2
60°	56.0	65.2	138.1	220.2	560.2	650.1	681.4	712.7	762.2	780.4	784.3
62.5°	52.2	62.5	122.5	185.0	510.7	598.0	629.3	658.0	699.7	712.7	717.9
65°	49.5	59.9	110.7	158.9	459.9	543.3	574.5	599.3	633.2	646.2	648.8
67.5°	46.9	57.3	101.7	136.8	409.1	488.6	512.0	535.5	561.5	574.5	575.8
70°	43.0	54.7	93.8	121.2	356.9	426.1	445.6	470.3	491.1	497.7	501.6
72.5°	40.4	50.8	88.6	109.4	303.6	366.1	384.3	398.6	416.9	423.4	423.4
75°	36.5	45.6	83.4	97.7	248.9	299.6	315.3	329.6	343.9	346.6	342.6
77.5°	32.5	40.4	71.7	82.0	194.1	237.1	250.1	257.9	269.7	272.3	273.6
80°	27.3	35.2	56.0	63.8	140.7	174.6	183.7	190.2	200.7	200.7	203.2
82.5°	20.8	27.3	40.4	45.6	95.1	119.9	127.7	131.6	138.1	138.1	138.1
85°	13.0	17.0	26.0	30.0	57.3	73.0	78.2	79.5	84.7	86.0	86.0
87.5°	6.5	9.1	17.0	18.2	30.0	37.8	37.8	40.4	40.4	39.0	37.8
90°	1.0	1.8	2.6	2.8	4.3	6.4	7.5	6.7	5.0	3.7	3.7
92.5°	3.9	10.6	17.4	19.0	26.8	37.2	42.3	37.1	26.6	18.7	17.9
95°	9.5	21.8	34.1	37.2	66.0	104.3	123.5	110.2	83.6	63.7	61.4
97.5°	16.4	27.2	38.1	40.8	88.8	152.8	184.9	176.5	159.6	147.0	142.7
100°	21.7	31.6	41.4	43.9	97.1	168.2	203.7	204.3	205.6	206.5	201.3
102.5°	26.2	35.4	44.7	46.9	101.0	173.0	209.0	219.8	241.2	257.2	252.8
105°	34.0	41.8	49.5	51.5	103.8	173.5	208.4	232.5	280.5	316.5	314.1
107.5°	41.9	49.1	56.4	58.2	104.3	165.8	196.6	230.1	297.1	347.4	348.0
110°	47.2	53.7	60.2	61.9	103.5	159.0	186.7	224.2	299.1	355.3	357.7



TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	52.5	58.7	64.9	66.5	103.5	153.0	177.8	216.1	292.7	350.2	354.0
115°	60.3	66.1	71.8	73.3	104.5	146.2	167.0	203.9	277.8	333.1	338.3
117.5°	68.1	73.4	78.6	79.9	106.5	141.9	159.6	193.0	259.5	309.5	315.3
120°	72.7	77.6	82.5	83.7	108.0	140.4	156.6	187.0	248.0	293.6	299.3
122.5°	77.1	82.0	87.0	88.2	110.2	139.6	154.3	181.7	236.5	277.7	283.2
125°	83.9	88.4	93.0	94.2	113.4	139.0	151.8	175.1	221.8	256.7	261.8
127.5°	89.4	94.1	98.6	99.8	116.4	138.6	149.8	169.8	209.8	239.8	244.1
130°	92.4	97.3	102.2	103.5	118.7	138.9	149.0	166.8	202.4	229.1	233.1
132.5°	95.5	100.5	105.4	106.6	120.5	139.0	148.3	164.3	196.1	220.1	223.6
135°	100.1	104.5	109.1	110.1	122.5	138.9	147.1	160.4	187.1	207.2	210.2
137.5°	104.7	109.2	113.6	114.7	125.4	139.7	146.9	158.2	180.7	197.7	200.3
140°	108.6	112.6	116.7	117.7	127.2	139.9	146.2	156.0	175.5	190.1	192.5
142.5°	111.5	115.3	119.0	120.0	128.8	140.4	146.2	154.8	172.0	184.8	186.8
145°	116.1	119.3	122.7	123.4	130.7	140.4	145.2	152.2	166.2	176.8	178.4
147.5°	120.6	123.7	127.0	127.8	133.6	141.4	145.2	150.8	161.8	170.1	171.4
150°	123.5	126.4	129.4	130.1	135.1	141.9	145.2	149.9	159.2	166.2	167.2
152.5°	126.6	128.8	130.9	131.5	136.1	142.2	145.2	149.2	157.2	163.2	164.0
155°	131.1	132.7	134.4	134.8	138.2	142.9	145.2	148.4	154.8	159.5	160.0
157.5°	134.5	136.1	137.6	138.0	140.4	143.7	145.2	147.7	152.6	156.3	156.7
160°	136.8	137.9	139.2	139.5	141.4	144.0	145.2	147.3	151.5	154.7	154.9
162.5°	139.0	139.9	140.9	141.1	142.5	144.4	145.2	147.0	150.6	153.2	153.4
165°	141.5	142.3	143.2	143.4	144.0	144.8	145.2	146.5	149.1	151.0	151.2
167.5°	143.8	144.2	144.5	144.6	145.1	145.8	146.2	147.0	148.7	150.0	150.1
170°	145.2	145.6	146.0	146.1	146.1	146.2	146.2	147.0	148.7	150.0	150.0
172.5°	146.0	146.1	146.2	146.2	146.2	146.2	146.2	146.9	148.2	149.2	149.1
175°	147.1	147.1	147.1	147.1	146.8	146.4	146.2	146.6	147.5	148.1	148.1
177.5°	147.1	147.1	147.1	147.1	146.9	146.6	146.4	146.7	147.4	147.9	147.8
180°	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1



TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	405.1	405.1
2.5°	432.6	429.9
5°	556.3	559.0
7.5°	749.2	747.8
10°	931.6	943.2
12.5°	1064.4	1067.0
15°	1145.2	1150.4
17.5°	1176.5	1177.8
20°	1177.8	1175.1
22.5°	1163.5	1160.8
25°	1146.5	1145.2
27.5°	1130.8	1132.1
30°	1124.3	1128.3
32.5°	1124.3	1130.8
35°	1127.0	1133.5
37.5°	1125.6	1133.5
40°	1120.5	1129.6
42.5°	1106.1	1112.6
45°	1084.0	1091.8
47.5°	1055.3	1060.5
50°	1018.8	1024.1
52.5°	973.2	974.6
55°	918.5	923.7
57.5°	859.9	861.2
60°	794.7	798.7
62.5°	725.7	725.7
65°	652.7	655.3
67.5°	577.2	583.7
70°	500.3	501.6
72.5°	424.8	424.8
75°	346.6	347.9
77.5°	272.3	272.3
80°	201.9	203.2
82.5°	139.4	142.0
85°	87.3	87.3
87.5°	40.4	36.5
90°	3.7	3.7
92.5°	15.0	12.0
95°	52.5	43.4
97.5°	125.5	108.4
100°	180.9	160.4
102.5°	235.3	217.7
105°	304.8	295.3
107.5°	350.2	352.5
110°	367.5	377.3





TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	369.1	384.1
115°	359.3	380.2
117.5°	338.5	361.8
120°	321.8	344.3
122.5°	305.5	327.7
125°	282.3	302.8
127.5°	261.4	278.6
130°	249.1	265.0
132.5°	237.9	252.2
135°	222.6	235.0
137.5°	210.3	220.5
140°	201.8	211.3
142.5°	194.9	203.0
145°	184.5	190.6
147.5°	176.4	181.5
150°	171.4	175.5
152.5°	167.0	170.2
155°	162.1	164.2
157.5°	158.2	159.6
160°	155.8	156.6
162.5°	154.2	155.0
165°	152.0	152.8
167.5°	150.4	150.8
170°	150.0	150.0
172.5°	148.8	148.5
175°	148.1	148.1
177.5°	147.5	147.1
180°	147.1	147.1



TEST NUMBER: P936483

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-STD-W-4-3000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.72	8.96	8.40	9.66	10.49	20.86	22.10	21.54	22.80	23.63
	3H	8.45	9.57	9.15	10.28	11.14	22.71	23.83	23.41	24.54	25.40
	4H	8.77	9.82	9.48	10.55	11.42	23.36	24.42	24.08	25.14	26.02
	6H	9.04	10.02	9.77	10.75	11.64	23.80	24.78	24.53	25.51	26.40
	8H	9.12	10.05	9.85	10.81	11.70	23.93	24.86	24.66	25.61	26.50
	12H	9.15	10.04	9.89	10.79	11.71	24.00	24.89	24.74	25.64	26.56
4H	2H	14.96	16.01	15.67	16.74	17.61	21.18	22.24	21.90	22.96	23.83
	3H	16.56	17.45	17.29	18.21	19.10	23.25	24.13	23.97	24.89	25.78
	4H	16.67	17.48	17.42	18.24	19.16	24.02	24.82	24.76	25.59	26.51
	6H	16.70	17.41	17.47	18.19	19.12	24.57	25.27	25.33	26.06	26.98
	8H	16.69	17.35	17.46	18.13	19.07	24.73	25.39	25.50	26.17	27.11
	12H	16.67	17.26	17.46	18.07	19.01	24.84	25.43	25.63	26.24	27.18
8H	4H	18.14	18.79	18.91	19.58	20.52	24.11	24.77	24.88	25.55	26.49
	6H	18.40	18.94	19.20	19.77	20.71	24.75	25.29	25.54	26.12	27.06
	8H	18.42	18.91	19.23	19.73	20.69	24.96	25.45	25.77	26.27	27.23
	12H	18.41	18.84	19.22	19.65	20.67	25.12	25.55	25.93	26.36	27.38
12H	4H	18.30	18.89	19.09	19.70	20.64	24.08	24.68	24.87	25.48	26.43
	6H	18.66	19.15	19.47	19.97	20.93	24.73	25.22	25.54	26.05	27.00
	8H	18.75	19.18	19.56	19.99	21.01	24.97	25.40	25.79	26.22	27.24