

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937677

Luminaire Tested: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P937677  
REPORT IS A COMBINATION OF REPORTS P933559 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 21509.6 lumens  
Efficiency: N/A  
Efficacy: 123.6 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 174  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937677  
CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42	36
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34	30
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29	24
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24	20
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3798	3798	3798
5°	3711	4390	5104
10°	3368	6401	8462
15°	2863	8365	10218
20°	2332	9696	10414
25°	1946	10149	10202
30°	1641	10216	10183
35°	1452	10049	10446
40°	1266	9831	10719
45°	1147	9672	10760
50°	1053	9530	10582
55°	1010	9321	10113
60°	1035	8916	9373
65°	1079	8298	8355
70°	1152	7242	7058
75°	1282	5910	5508
80°	1410	4104	3711
85°	1277	2180	1900

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10760 cd/sqm



TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.8	0.7
10°-20°	703.9	3.3
20°-30°	1231.2	5.7
30°-40°	1584.9	7.4
40°-50°	1770.3	8.2
50°-60°	1695.5	7.9
60°-70°	1343.7	6.2
70°-80°	790.1	3.7
80°-90°	226.6	1.1
90°-100°	902.7	4.2
100°-110°	2373.2	11.0
110°-120°	2460.7	11.4
120°-130°	1973.8	9.2
130°-140°	1548.7	7.2
140°-150°	1188.7	5.5
150°-160°	856.1	4.0
160°-170°	523.8	2.4
170°-180°	177.0	0.8
0°-30°	2093.9	9.7
0°-40°	3678.8	17.1
0°-60°	7144.5	33.2
0°-90°	9504.9	44.2
90°-120°	5736.6	26.7
90°-150°	10447.9	48.6
90°-180°	12005.0	55.8
0°-180°	21509.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1228	1228	1228	1228	1228	
5°	1196	1283	1445	1634	1694	110
15°	896	1654	2787	3379	3486	249
25°	572	1875	3320	3466	3470	264
35°	387	1792	3127	3304	3434	242
45°	264	1429	2763	3166	3308	205
55°	190	908	2345	2724	2799	173
65°	150	482	1741	1958	1986	149
75°	111	296	955	1050	1054	116
85°	39	91	237	261	264	42
90°	12	35	94	47	47	13
95°	119	467	1555	802	546	132
105°	428	648	2624	3983	3716	453
115°	759	922	2102	4192	4785	750
125°	1056	1184	1912	3230	3810	938
135°	1259	1386	1852	2607	2957	974
145°	1460	1554	1828	2225	2399	915
155°	1650	1696	1828	2007	2066	758
165°	1781	1805	1828	1900	1924	503
175°	1852	1852	1841	1864	1864	176
180°	1852	1852	1852	1852	1852	



TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8
2.5°	1227.8	1227.8	1235.6	1239.6	1247.5	1251.5	1259.3	1267.2	1290.9	1294.9	1302.8
5°	1196.2	1211.9	1263.3	1283.0	1338.3	1413.3	1444.9	1496.2	1602.8	1634.3	1654.1
7.5°	1148.8	1184.3	1310.6	1342.2	1480.4	1677.8	1760.7	1871.2	2041.0	2123.9	2191.0
10°	1073.8	1148.8	1373.8	1448.8	1673.9	1973.9	2127.9	2281.8	2538.4	2652.8	2696.3
12.5°	990.9	1113.2	1440.9	1543.6	1867.3	2305.4	2491.0	2660.8	2952.9	3106.9	3130.5
15°	896.1	1061.9	1504.1	1654.1	2072.6	2581.8	2787.1	2996.4	3268.8	3379.2	3406.9
17.5°	813.2	1022.5	1563.3	1721.2	2230.4	2830.5	3039.8	3213.5	3434.5	3509.5	3529.3
20°	710.5	959.3	1602.8	1808.0	2396.3	3012.1	3213.5	3347.7	3497.7	3545.1	3552.9
22.5°	635.5	892.2	1626.5	1839.6	2506.8	3122.7	3292.4	3399.0	3501.6	3517.5	3521.4
25°	572.4	817.2	1622.5	1875.2	2601.6	3189.8	3320.1	3399.0	3458.2	3466.1	3466.1
27.5°	513.2	734.3	1606.7	1883.0	2672.7	3205.5	3308.2	3363.5	3391.1	3406.9	3406.9
30°	461.8	655.4	1567.2	1867.3	2704.2	3189.8	3272.7	3300.3	3327.9	3351.6	3363.5
32.5°	422.4	580.3	1508.0	1835.7	2708.1	3150.3	3209.5	3225.3	3264.8	3320.1	3339.8
35°	386.8	505.3	1440.9	1792.3	2684.4	3087.1	3126.6	3142.4	3221.4	3304.2	3331.9
37.5°	351.4	450.1	1354.1	1717.3	2649.0	3012.1	3039.8	3067.4	3189.8	3288.5	3320.1
40°	315.8	402.7	1251.5	1634.3	2593.7	2921.4	2945.0	2988.4	3150.3	3264.8	3296.4
42.5°	288.1	363.2	1140.9	1547.5	2522.6	2818.7	2854.2	2917.4	3102.9	3225.3	3260.8
45°	264.5	323.7	1022.5	1429.1	2431.8	2712.1	2763.4	2850.3	3047.7	3166.1	3197.7
47.5°	240.8	296.1	900.1	1306.8	2333.1	2605.5	2672.7	2771.3	2972.7	3087.1	3114.8
50°	221.1	268.4	777.7	1176.5	2226.6	2491.0	2570.0	2672.7	2877.9	2984.5	3020.1
52.5°	205.3	244.7	663.2	1046.2	2104.1	2372.6	2463.4	2570.0	2763.4	2866.1	2889.8
55°	189.5	225.0	564.5	908.0	1977.9	2246.3	2345.0	2447.6	2637.1	2724.0	2739.7
57.5°	181.6	209.3	481.7	777.7	1843.6	2104.1	2214.7	2309.4	2487.1	2554.1	2570.0
60°	169.7	197.4	418.4	667.1	1697.5	1969.9	2064.7	2159.4	2309.4	2364.7	2376.6
62.5°	157.9	189.5	371.1	560.5	1547.5	1812.0	1906.7	1993.6	2120.0	2159.4	2175.2
65°	150.0	181.6	335.6	481.7	1393.6	1646.2	1740.9	1816.0	1918.6	1958.0	1966.0
67.5°	142.1	173.7	308.0	414.5	1239.6	1480.4	1551.5	1622.5	1701.5	1740.9	1744.9
70°	130.3	165.8	284.3	367.1	1081.7	1290.9	1350.2	1425.2	1488.3	1508.0	1519.9
72.5°	122.4	154.0	268.4	331.6	919.8	1109.3	1164.6	1208.0	1263.3	1283.0	1283.0
75°	110.6	138.1	252.7	296.1	754.0	908.0	955.4	998.8	1042.2	1050.1	1038.2
77.5°	98.7	122.4	217.1	248.7	588.2	718.5	758.0	781.7	817.2	825.1	829.1
80°	82.9	106.6	169.7	193.4	426.4	529.0	556.7	576.4	608.0	608.0	615.8
82.5°	63.1	82.9	122.4	138.1	288.1	363.2	386.8	398.7	418.4	418.4	418.4
85°	39.4	51.3	79.0	90.8	173.7	221.1	236.8	240.8	256.6	260.6	260.6
87.5°	19.7	27.6	51.3	55.3	90.8	114.4	114.4	122.4	122.4	118.4	114.4
90°	12.4	22.4	32.3	34.8	54.7	81.2	94.4	84.0	62.9	47.2	47.2
92.5°	49.7	134.2	218.7	239.8	337.2	467.0	532.0	466.2	334.8	236.2	226.8
95°	119.3	274.0	428.7	467.3	829.8	1313.1	1554.8	1387.4	1052.7	801.6	773.1
97.5°	206.3	342.7	479.2	513.3	1117.7	1923.6	2326.6	2220.8	2009.2	1850.6	1796.5
100°	273.4	397.1	520.8	551.8	1222.5	2116.8	2564.0	2571.8	2587.2	2598.8	2534.3
102.5°	330.6	446.0	561.4	590.3	1270.6	2177.7	2631.1	2765.9	3035.4	3237.6	3182.3
105°	427.6	525.3	623.1	647.5	1306.3	2184.5	2623.7	2925.8	3530.1	3983.3	3953.6
107.5°	527.0	618.1	709.3	732.1	1312.8	2087.2	2474.5	2896.0	3738.9	4371.0	4378.2
110°	594.1	676.4	758.7	779.3	1302.9	2001.1	2350.2	2821.4	3763.7	4470.4	4501.4



TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	659.9	738.4	816.8	836.4	1303.4	1925.9	2237.1	2719.4	3683.8	4407.1	4454.6
115°	759.4	831.8	904.1	922.2	1315.3	1839.5	2101.7	2566.2	3495.3	4192.1	4257.9
117.5°	857.6	923.3	989.0	1005.5	1339.8	1785.5	2008.4	2427.7	3266.2	3895.1	3968.1
120°	914.7	976.6	1038.5	1054.0	1359.7	1767.4	1971.2	2354.2	3120.4	3695.0	3766.0
122.5°	970.7	1033.2	1095.5	1111.1	1388.3	1757.8	1942.6	2287.5	2977.4	3494.9	3564.9
125°	1056.5	1113.3	1170.2	1184.4	1426.8	1750.0	1911.5	2204.5	2790.6	3230.1	3294.6
127.5°	1126.0	1183.4	1240.9	1255.3	1465.3	1745.4	1885.4	2137.0	2640.2	3017.6	3072.0
130°	1163.3	1225.2	1287.0	1302.5	1493.5	1748.2	1875.5	2099.5	2547.5	2883.4	2933.7
132.5°	1201.9	1263.7	1325.6	1341.0	1516.2	1749.9	1866.7	2067.2	2468.3	2769.1	2814.1
135°	1259.0	1315.3	1371.7	1385.7	1541.1	1748.3	1851.9	2019.8	2355.5	2607.4	2646.3
137.5°	1317.4	1373.2	1429.0	1442.9	1578.4	1759.0	1849.4	1991.3	2275.3	2488.2	2520.0
140°	1365.9	1417.3	1468.6	1481.5	1601.2	1760.8	1840.6	1963.2	2208.5	2392.5	2422.2
142.5°	1403.2	1450.7	1498.2	1510.0	1620.2	1767.1	1840.6	1948.4	2163.8	2325.4	2350.9
145°	1460.3	1501.8	1543.2	1553.6	1645.1	1767.2	1828.3	1916.3	2092.5	2224.7	2244.0
147.5°	1517.5	1557.8	1598.2	1608.2	1681.5	1779.4	1828.3	1897.6	2036.2	2140.2	2156.2
150°	1554.8	1591.2	1627.7	1636.8	1700.7	1785.7	1828.3	1886.8	2003.9	2091.7	2104.6
152.5°	1593.3	1620.9	1648.6	1655.5	1713.0	1789.8	1828.3	1878.3	1978.2	2053.2	2062.9
155°	1650.5	1670.9	1691.4	1696.5	1740.4	1799.0	1828.3	1868.0	1947.5	2007.1	2013.6
157.5°	1692.7	1712.6	1732.5	1737.5	1767.8	1808.1	1828.3	1859.1	1921.0	1967.4	1972.0
160°	1721.3	1736.8	1752.3	1756.1	1780.2	1812.2	1828.3	1854.8	1907.7	1947.5	1950.1
162.5°	1749.9	1761.4	1773.1	1776.0	1793.4	1816.6	1828.3	1850.6	1895.3	1928.9	1931.3
165°	1780.9	1791.4	1802.0	1804.6	1812.4	1823.0	1828.3	1844.3	1876.3	1900.3	1902.9
167.5°	1809.5	1814.5	1819.5	1820.8	1827.4	1836.2	1840.6	1851.2	1872.2	1887.9	1889.0
170°	1828.3	1833.2	1838.2	1839.4	1839.8	1840.3	1840.6	1851.2	1872.2	1887.9	1887.9
172.5°	1838.1	1839.2	1840.3	1840.6	1840.6	1840.6	1840.6	1848.9	1865.5	1878.0	1877.0
175°	1851.9	1851.9	1851.9	1851.9	1848.1	1843.1	1840.6	1845.9	1856.3	1864.2	1864.2
177.5°	1851.9	1851.9	1851.9	1851.9	1849.0	1845.1	1843.1	1847.3	1855.5	1861.7	1860.6
180°	1851.9	1851.9	1851.9	1851.9	1851.9	1851.9	1851.9	1851.9	1851.9	1851.9	1851.9



TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	1227.8	1227.8
2.5°	1310.6	1302.8
5°	1685.7	1693.6
7.5°	2270.0	2266.0
10°	2822.7	2858.1
12.5°	3225.3	3233.2
15°	3470.1	3485.9
17.5°	3564.8	3568.8
20°	3568.8	3560.9
22.5°	3525.3	3517.5
25°	3474.0	3470.1
27.5°	3426.6	3430.6
30°	3406.9	3418.8
32.5°	3406.9	3426.6
35°	3414.8	3434.5
37.5°	3410.8	3434.5
40°	3395.1	3422.7
42.5°	3351.6	3371.4
45°	3284.5	3308.2
47.5°	3197.7	3213.5
50°	3087.1	3102.9
52.5°	2949.0	2952.9
55°	2783.1	2799.0
57.5°	2605.5	2609.4
60°	2408.1	2420.0
62.5°	2198.9	2198.9
65°	1977.9	1985.7
67.5°	1748.9	1768.6
70°	1515.9	1519.9
72.5°	1286.9	1286.9
75°	1050.1	1054.1
77.5°	825.1	825.1
80°	611.9	615.8
82.5°	422.4	430.3
85°	264.5	264.5
87.5°	122.4	110.6
90°	47.2	47.2
92.5°	189.1	151.6
95°	659.4	545.6
97.5°	1580.0	1363.4
100°	2276.4	2018.4
102.5°	2961.4	2740.5
105°	3834.8	3716.1
107.5°	4407.0	4435.7
110°	4625.1	4748.9





TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	4644.6	4834.7
115°	4521.4	4784.9
117.5°	4260.3	4552.5
120°	4049.8	4333.8
122.5°	3844.9	4124.9
125°	3552.5	3810.5
127.5°	3289.7	3507.3
130°	3134.7	3335.8
132.5°	2994.2	3174.3
135°	2801.4	2956.7
137.5°	2647.0	2774.1
140°	2541.0	2659.7
142.5°	2453.0	2555.2
145°	2321.4	2398.7
147.5°	2220.3	2284.3
150°	2156.6	2208.5
152.5°	2102.2	2141.4
155°	2039.6	2065.6
157.5°	1990.2	2008.4
160°	1960.6	1971.2
162.5°	1941.3	1951.3
165°	1913.4	1923.9
167.5°	1893.4	1897.8
170°	1887.9	1887.9
172.5°	1873.1	1869.2
175°	1864.2	1864.2
177.5°	1856.2	1851.9
180°	1851.9	1851.9



TEST NUMBER: P937677

CATALOG NUMBER: SQ4-FB-100U-100D-B2750-1D-UNV-STD-W-12-2700K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.09	5.94	6.09	6.95	8.30	18.28	19.13	19.28	20.14	21.49
	3H	5.80	6.55	6.80	7.58	8.95	20.13	20.88	21.13	21.91	23.28
	4H	6.09	6.81	7.11	7.84	9.21	20.77	21.49	21.80	22.52	23.90
	6H	6.34	7.01	7.37	8.04	9.43	21.21	21.87	22.24	22.90	24.29
	8H	6.41	7.04	7.45	8.09	9.47	21.33	21.96	22.37	23.01	24.40
	12H	6.43	7.03	7.47	8.07	9.48	21.40	22.00	22.44	23.04	24.45
4H	2H	12.31	13.03	13.34	14.06	15.43	18.55	19.27	19.58	20.30	21.68
	3H	13.88	14.48	14.91	15.53	16.92	20.60	21.21	21.64	22.26	23.65
	4H	13.97	14.52	15.02	15.57	16.98	21.37	21.93	22.42	22.97	24.38
	6H	13.98	14.46	15.03	15.53	16.93	21.92	22.39	22.97	23.46	24.87
	8H	13.96	14.40	15.01	15.46	16.89	22.08	22.53	23.14	23.59	25.01
	12H	13.91	14.32	14.99	15.39	16.82	22.18	22.58	23.25	23.65	25.08
8H	4H	15.42	15.86	16.47	16.93	18.35	21.43	21.88	22.49	22.94	24.36
	6H	15.66	16.03	16.74	17.13	18.55	22.07	22.43	23.14	23.54	24.96
	8H	15.68	16.00	16.76	17.09	18.53	22.29	22.61	23.37	23.70	25.14
	12H	15.64	15.93	16.74	17.01	18.49	22.43	22.72	23.52	23.80	25.28
12H	4H	15.56	15.96	16.64	17.04	18.47	21.38	21.79	22.46	22.86	24.29
	6H	15.92	16.24	17.01	17.33	18.77	22.05	22.37	23.13	23.46	24.90
	8H	15.99	16.27	17.08	17.36	18.84	22.28	22.57	23.37	23.65	25.13